

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008737

Luminaire Tested: S122DIP-B1005D925UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008737
REPORT IS A COMBINATION OF REPORTS P983789 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7341.0 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008737

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008737

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	48	52	47	42	45	40	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25286	25286	25286
5°	25327	24101	23931
10°	25120	23004	22546
15°	24753	21896	21092
20°	24255	20693	19713
25°	23759	19436	18336
30°	23137	18254	16892
35°	22549	17008	15473
40°	21822	15778	14131
45°	21100	14558	12816
50°	20312	13317	11451
55°	19481	11990	10160
60°	18550	10553	8816
65°	17526	9093	7403
70°	16232	7493	5978
75°	14433	5777	4615
80°	12263	3926	2971
85°	8899	1826	1265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21100 cd/sqm

TEST NUMBER: P1008737

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.3	2.0
10°-20°	423.0	5.8
20°-30°	621.6	8.5
30°-40°	722.0	9.8
40°-50°	721.1	9.8
50°-60°	628.8	8.6
60°-70°	464.8	6.3
70°-80°	263.0	3.6
80°-90°	72.7	1.0
90°-100°	72.4	1.0
100°-110°	230.3	3.1
110°-120°	394.0	5.4
120°-130°	518.2	7.1
130°-140°	581.7	7.9
140°-150°	570.4	7.8
150°-160°	478.5	6.5
160°-170°	317.3	4.3
170°-180°	110.9	1.5
0°-30°	1195.0	16.3
0°-40°	1917.0	26.1
0°-60°	3266.8	44.5
0°-90°	4067.4	55.4
90°-120°	696.7	9.5
90°-150°	2367.0	32.2
90°-180°	3274.0	44.6
0°-180°	7341.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1597	1597	1597	1597	1597	
5°	1597	1591	1574	1587	1584	152
15°	1521	1511	1491	1498	1490	428
25°	1376	1364	1338	1341	1338	633
35°	1187	1172	1147	1138	1130	741
45°	966	955	932	915	909	746
55°	731	722	704	685	677	654
65°	493	484	468	455	447	487
75°	258	255	247	238	241	275
85°	63	61	60	55	54	70
90°	1	13	35	33	34	7
95°	51	61	63	63	61	57
105°	212	215	217	219	219	224
115°	395	401	399	398	395	391
125°	575	584	581	578	577	514
135°	744	755	757	756	753	575
145°	903	910	916	917	913	564
155°	1033	1036	1038	1044	1040	475
165°	1124	1122	1122	1129	1124	317
175°	1169	1166	1164	1171	1165	111
180°	1171	1171	1171	1171	1171	

TEST NUMBER: P1008737

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1597.4	1597.4	1597.4	1597.4	1597.4
2.5°	1606.6	1598.9	1582.0	1597.4	1594.3
5°	1597.4	1591.2	1574.3	1586.6	1583.6
7.5°	1586.6	1577.4	1560.5	1572.8	1569.7
10°	1569.7	1559.0	1540.6	1552.8	1548.2
12.5°	1546.7	1537.5	1519.1	1526.7	1523.7
15°	1520.6	1511.4	1491.4	1497.5	1489.9
17.5°	1488.3	1479.1	1459.1	1466.8	1459.1
20°	1453.0	1443.8	1422.3	1426.9	1420.8
22.5°	1417.7	1403.9	1383.9	1383.9	1380.8
25°	1376.2	1363.9	1337.8	1340.9	1337.8
27.5°	1330.1	1319.4	1299.4	1294.8	1287.1
30°	1284.1	1271.8	1248.7	1244.1	1238.0
32.5°	1234.9	1225.7	1201.1	1191.9	1185.8
35°	1187.3	1171.9	1147.4	1138.1	1130.5
37.5°	1133.5	1119.7	1095.1	1084.4	1076.7
40°	1078.2	1065.9	1041.4	1027.5	1021.4
42.5°	1024.5	1012.2	987.6	972.3	963.0
45°	966.1	955.4	932.3	915.4	909.3
47.5°	909.3	898.5	874.0	857.1	847.8
50°	849.4	841.7	820.2	798.7	791.0
52.5°	791.0	780.3	760.3	743.4	732.6
55°	731.1	721.9	703.5	685.0	677.4
57.5°	671.2	663.5	643.6	625.1	619.0
60°	611.3	605.2	583.7	566.8	562.2
62.5°	552.9	542.2	526.8	511.5	505.3
65°	493.0	483.8	468.5	454.6	447.0
67.5°	431.6	423.9	410.1	399.3	393.2
70°	374.8	368.6	354.8	344.1	337.9
72.5°	316.4	310.3	302.6	291.8	287.2
75°	258.0	255.0	247.3	238.1	241.1
77.5°	205.8	199.7	196.6	192.0	187.4
80°	153.6	152.1	149.0	144.4	141.3
82.5°	104.4	104.4	102.9	96.8	96.8
85°	63.0	61.4	59.9	55.3	53.8
87.5°	27.6	24.6	21.5	16.9	15.4
90°	1.0	12.8	34.6	32.6	33.6
92.5°	21.7	29.6	30.6	31.6	31.6
95°	51.4	61.3	63.2	63.2	61.3
97.5°	86.0	94.9	98.8	98.8	98.8
100°	125.5	133.4	136.4	136.4	135.4
102.5°	167.0	172.9	176.9	177.9	176.9
105°	212.4	215.4	217.4	219.4	219.4
107.5°	257.9	261.9	261.9	262.8	257.9
110°	301.4	307.3	307.3	307.3	304.3

TEST NUMBER: P1008737

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	348.8	354.7	353.7	350.8	348.8
115°	395.2	401.2	399.2	398.2	395.2
117.5°	441.7	449.6	444.7	441.7	438.7
120°	488.1	496.0	488.1	488.1	485.2
122.5°	530.6	540.5	535.6	532.6	530.6
125°	575.1	584.0	581.0	578.0	577.1
127.5°	618.6	629.4	625.5	621.5	618.6
130°	659.1	671.9	669.9	668.0	664.0
132.5°	704.5	714.4	715.4	710.5	707.5
135°	744.1	754.9	756.9	755.9	752.9
137.5°	787.5	796.4	798.4	797.4	793.5
140°	826.1	835.0	839.9	839.9	835.9
142.5°	865.6	874.5	877.4	878.4	874.5
145°	903.1	910.1	916.0	917.0	913.0
147.5°	936.7	945.6	949.6	951.6	947.6
150°	971.3	977.2	981.2	984.2	981.2
152.5°	1002.0	1007.9	1012.8	1016.8	1012.8
155°	1032.6	1035.5	1038.5	1043.5	1040.5
157.5°	1059.3	1061.2	1063.2	1070.1	1065.2
160°	1083.0	1085.0	1085.9	1091.9	1087.9
162.5°	1104.7	1104.7	1105.7	1112.6	1107.7
165°	1123.5	1122.5	1122.5	1129.4	1124.5
167.5°	1140.3	1137.3	1137.3	1144.2	1139.3
170°	1153.1	1150.2	1149.2	1156.1	1150.2
172.5°	1162.0	1159.1	1158.1	1165.0	1159.1
175°	1168.9	1166.0	1164.0	1170.9	1165.0
177.5°	1172.9	1169.9	1168.0	1173.9	1168.0
180°	1170.9	1170.9	1170.9	1170.9	1170.9

(END OF REPORT)