

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009242

Luminaire Tested: S122DIP-B675D1080UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009242
REPORT IS A COMBINATION OF REPORTS P984468 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D1080UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6888.8 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009242

CATALOG NUMBER: S122DIP-B675D1080UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009242

CATALOG NUMBER: S122DIP-B675D1080UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39
2	87	80	74	68	79	73	67	63	59	56	52	47	45	42	36	34	33
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28
4	72	62	54	48	66	56	50	45	46	41	38	37	34	31	28	26	24
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	18
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16800	16800	16800
5°	16827	16012	15899
10°	16689	15283	14979
15°	16445	14547	14012
20°	16114	13747	13096
25°	15785	12913	12182
30°	15371	12127	11222
35°	14981	11300	10279
40°	14497	10483	9388
45°	14019	9672	8515
50°	13494	8847	7608
55°	12942	7966	6749
60°	12323	7011	5857
65°	11646	6040	4917
70°	10783	4978	3972
75°	9588	3838	3066
80°	8143	2609	1974
85°	5905	1214	839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14019 cd/sqm

TEST NUMBER: P1009242

CATALOG NUMBER: S122DIP-B675D1080UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	1.4
10°-20°	281.0	4.1
20°-30°	413.0	6.0
30°-40°	479.7	7.0
40°-50°	479.1	7.0
50°-60°	417.7	6.1
60°-70°	308.8	4.5
70°-80°	174.7	2.5
80°-90°	49.9	0.7
90°-100°	243.3	3.5
100°-110°	822.6	11.9
110°-120°	864.7	12.6
120°-130°	711.0	10.3
130°-140°	571.4	8.3
140°-150°	431.6	6.3
150°-160°	303.4	4.4
160°-170°	178.7	2.6
170°-180°	58.1	0.8
0°-30°	793.9	11.5
0°-40°	1273.6	18.5
0°-60°	2170.4	31.5
0°-90°	2703.8	39.2
90°-120°	1930.6	28.0
90°-150°	3644.7	52.9
90°-180°	4185.0	60.8
0°-180°	6888.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1061	1061	1061	1061	1061	
5°	1061	1057	1046	1054	1052	101
15°	1010	1004	991	995	990	285
25°	914	906	889	891	889	421
35°	789	779	762	756	751	493
45°	642	635	619	608	604	495
55°	486	480	467	455	450	434
65°	328	321	311	302	297	324
75°	171	169	164	158	160	183
85°	42	41	40	37	36	47
90°	1	16	39	38	38	5
95°	40	99	452	171	132	42
105°	141	212	855	1529	1301	150
115°	248	313	716	1477	1712	246
125°	346	410	688	1196	1389	308
135°	406	485	680	1005	1151	314
145°	464	533	676	840	919	291
155°	528	570	657	743	772	243
165°	575	592	629	667	678	162
175°	599	600	605	612	611	57
180°	600	600	600	600	600	

TEST NUMBER: P1009242

CATALOG NUMBER: S122DIP-B675D1080UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.4	1062.3	1051.0	1061.3	1059.2
5°	1061.3	1057.2	1045.9	1054.1	1052.1
7.5°	1054.1	1048.0	1036.8	1044.9	1042.9
10°	1042.9	1035.7	1023.5	1031.7	1028.6
12.5°	1027.6	1021.5	1009.2	1014.3	1012.3
15°	1010.2	1004.1	990.8	994.9	989.8
17.5°	988.8	982.7	969.4	974.5	969.4
20°	965.3	959.2	944.9	948.0	943.9
22.5°	941.9	932.7	919.4	919.4	917.4
25°	914.3	906.1	888.8	890.8	888.8
27.5°	883.7	876.6	863.3	860.2	855.1
30°	853.1	844.9	829.6	826.6	822.5
32.5°	820.4	814.3	798.0	791.9	787.8
35°	788.8	778.6	762.3	756.1	751.0
37.5°	753.1	743.9	727.6	720.4	715.3
40°	716.3	708.2	691.9	682.7	678.6
42.5°	680.6	672.5	656.1	645.9	639.8
45°	641.9	634.7	619.4	608.2	604.1
47.5°	604.1	597.0	580.6	569.4	563.3
50°	564.3	559.2	544.9	530.6	525.5
52.5°	525.5	518.4	505.1	493.9	486.7
55°	485.7	479.6	467.4	455.1	450.0
57.5°	445.9	440.8	427.6	415.3	411.2
60°	406.1	402.1	387.8	376.5	373.5
62.5°	367.4	360.2	350.0	339.8	335.7
65°	327.6	321.4	311.2	302.0	296.9
67.5°	286.7	281.6	272.5	265.3	261.2
70°	249.0	244.9	235.7	228.6	224.5
72.5°	210.2	206.1	201.0	193.9	190.8
75°	171.4	169.4	164.3	158.2	160.2
77.5°	136.7	132.7	130.6	127.6	124.5
80°	102.0	101.0	99.0	95.9	93.9
82.5°	69.4	69.4	68.4	64.3	64.3
85°	41.8	40.8	39.8	36.7	35.7
87.5°	18.4	16.3	14.3	11.2	10.2
90°	1.2	15.6	39.2	37.5	38.1
92.5°	17.3	54.8	177.8	81.9	70.4
95°	40.4	99.2	452.5	170.8	131.6
97.5°	60.0	131.0	737.6	342.8	220.5
100°	88.9	160.4	911.9	682.8	413.2
102.5°	115.4	187.0	917.7	1154.4	805.7
105°	140.8	212.4	855.4	1528.9	1300.9
107.5°	168.5	237.8	797.6	1664.5	1634.5
110°	196.2	263.8	758.4	1642.6	1770.7

TEST NUMBER: P1009242

CATALOG NUMBER: S122DIP-B675D1080UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.6	288.6	733.0	1568.2	1768.4
115°	248.2	313.4	715.7	1477.0	1711.9
117.5°	275.9	338.2	706.4	1389.8	1626.4
120°	301.3	362.5	698.4	1311.9	1544.5
122.5°	325.5	387.2	693.7	1251.3	1459.1
125°	346.3	409.8	688.0	1196.4	1388.7
127.5°	363.6	431.2	684.5	1149.7	1322.9
130°	378.6	450.2	682.2	1102.4	1268.6
132.5°	392.5	468.6	681.1	1053.3	1212.0
135°	406.3	484.8	679.9	1005.4	1150.9
137.5°	419.0	498.7	679.9	957.0	1092.0
140°	434.0	511.4	678.7	914.2	1030.8
142.5°	449.0	521.8	678.7	873.2	969.6
145°	464.0	533.3	676.4	839.8	918.8
147.5°	480.2	542.6	673.0	810.3	873.8
150°	496.4	551.8	669.5	785.0	834.6
152.5°	512.5	561.0	663.7	763.6	801.1
155°	527.5	569.6	656.8	742.8	772.2
157.5°	540.2	576.6	649.9	723.2	746.8
160°	552.9	583.6	643.0	703.6	722.6
162.5°	565.6	588.7	637.2	685.1	699.5
165°	574.9	592.2	629.1	667.2	677.6
167.5°	582.9	595.6	622.2	651.0	656.8
170°	591.0	597.4	616.4	636.0	638.3
172.5°	595.6	599.0	609.5	622.8	623.3
175°	599.1	599.7	604.9	612.3	610.6
177.5°	601.4	600.2	600.2	604.9	601.4
180°	600.2	600.2	600.2	600.2	600.2

(END OF REPORT)