

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009251

Luminaire Tested: S122DIP-B675D1080UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009251
REPORT IS A COMBINATION OF REPORTS P984477 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D1080UB50-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6661.6 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009251

CATALOG NUMBER: S122DIP-B675D1080UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009251

CATALOG NUMBER: S122DIP-B675D1080UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39		
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33		
2	87	80	74	68	79	73	67	63	59	56	52	47	45	42	36	34	33	28		
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	23		
4	72	62	54	48	66	56	50	45	46	41	38	37	34	31	28	26	24	20		
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	17		
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	18	15		
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14		
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15	12		
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11		
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16246	16246	16246
5°	16272	15485	15375
10°	16139	14779	14486
15°	15903	14068	13550
20°	15583	13295	12665
25°	15265	12487	11780
30°	14865	11728	10853
35°	14487	10926	9941
40°	14020	10138	9078
45°	13556	9353	8234
50°	13050	8556	7357
55°	12516	7703	6527
60°	11916	6780	5664
65°	11262	5842	4757
70°	10428	4815	3841
75°	9275	3712	2965
80°	7880	2522	1909
85°	5721	1174	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13556 cd/sqm

TEST NUMBER: P1009251

CATALOG NUMBER: S122DIP-B675D1080UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.4
10°-20°	271.8	4.1
20°-30°	399.4	6.0
30°-40°	463.9	7.0
40°-50°	463.3	7.0
50°-60°	404.0	6.1
60°-70°	298.6	4.5
70°-80°	169.0	2.5
80°-90°	48.3	0.7
90°-100°	235.3	3.5
100°-110°	795.5	11.9
110°-120°	836.1	12.6
120°-130°	687.6	10.3
130°-140°	552.5	8.3
140°-150°	417.4	6.3
150°-160°	293.4	4.4
160°-170°	172.8	2.6
170°-180°	56.2	0.8
0°-30°	767.7	11.5
0°-40°	1231.6	18.5
0°-60°	2098.9	31.5
0°-90°	2614.7	39.3
90°-120°	1866.9	28.0
90°-150°	3524.5	52.9
90°-180°	4047.0	60.8
0°-180°	6661.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1026	1022	1012	1019	1017	97
15°	977	971	958	962	957	275
25°	884	876	860	862	860	407
35°	763	753	737	731	726	476
45°	621	614	599	588	584	479
55°	470	464	452	440	435	420
65°	317	311	301	292	287	313
75°	166	164	159	153	155	177
85°	40	40	38	36	34	45
90°	1	15	38	36	37	5
95°	39	96	438	165	127	40
105°	136	205	827	1478	1258	145
115°	240	303	692	1428	1655	238
125°	335	396	665	1157	1343	298
135°	393	469	658	972	1113	304
145°	449	516	654	812	888	282
155°	510	551	635	718	747	235
165°	556	573	608	645	655	157
175°	579	580	585	592	590	55
180°	580	580	580	580	580	

TEST NUMBER: P1009251

CATALOG NUMBER: S122DIP-B675D1080UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1032.2	1027.3	1016.4	1026.3	1024.3
5°	1026.3	1022.3	1011.5	1019.4	1017.4
7.5°	1019.4	1013.4	1002.6	1010.5	1008.5
10°	1008.5	1001.6	989.8	997.7	994.7
12.5°	993.7	987.8	975.9	980.9	978.9
15°	976.9	971.0	958.2	962.1	957.2
17.5°	956.2	950.3	937.5	942.4	937.5
20°	933.5	927.6	913.8	916.7	912.8
22.5°	910.8	901.9	889.1	889.1	887.1
25°	884.2	876.3	859.5	861.5	859.5
27.5°	854.6	847.7	834.8	831.9	826.9
30°	825.0	817.1	802.3	799.3	795.4
32.5°	793.4	787.5	771.7	765.8	761.8
35°	762.8	752.9	737.1	731.2	726.3
37.5°	728.3	719.4	703.6	696.7	691.7
40°	692.7	684.8	669.1	660.2	656.2
42.5°	658.2	650.3	634.5	624.6	618.7
45°	620.7	613.8	599.0	588.1	584.2
47.5°	584.2	577.3	561.5	550.6	544.7
50°	545.7	540.8	527.0	513.1	508.2
52.5°	508.2	501.3	488.5	477.6	470.7
55°	469.7	463.8	452.0	440.1	435.2
57.5°	431.2	426.3	413.5	401.6	397.7
60°	392.7	388.8	375.0	364.1	361.2
62.5°	355.2	348.3	338.5	328.6	324.7
65°	316.8	310.8	301.0	292.1	287.2
67.5°	277.3	272.4	263.5	256.6	252.6
70°	240.8	236.8	228.0	221.0	217.1
72.5°	203.3	199.3	194.4	187.5	184.5
75°	165.8	163.8	158.9	153.0	154.9
77.5°	132.2	128.3	126.3	123.3	120.4
80°	98.7	97.7	95.7	92.8	90.8
82.5°	67.1	67.1	66.1	62.2	62.2
85°	40.5	39.5	38.5	35.5	34.5
87.5°	17.8	15.8	13.8	10.9	9.9
90°	1.1	15.0	38.0	36.2	36.8
92.5°	16.7	53.0	171.9	79.2	68.1
95°	39.1	96.0	437.6	165.2	127.3
97.5°	58.0	126.7	713.3	331.5	213.2
100°	86.0	155.2	881.8	660.2	399.6
102.5°	111.6	180.8	887.4	1116.2	779.1
105°	136.2	205.4	827.1	1478.5	1258.0
107.5°	163.0	230.0	771.3	1609.6	1580.6
110°	189.8	255.0	733.4	1588.4	1712.3

TEST NUMBER: P1009251

CATALOG NUMBER: S122DIP-B675D1080UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.3	279.0	708.8	1516.4	1710.1
115°	240.0	303.0	692.1	1428.2	1655.4
117.5°	266.8	327.0	683.1	1344.0	1572.8
120°	291.3	350.5	675.3	1268.6	1493.5
122.5°	314.8	374.5	670.9	1210.1	1410.9
125°	334.9	396.2	665.3	1157.0	1342.8
127.5°	351.6	416.9	661.9	1111.8	1279.2
130°	366.1	435.4	659.7	1066.1	1226.8
132.5°	379.5	453.2	658.6	1018.6	1172.1
135°	392.9	468.8	657.5	972.2	1112.9
137.5°	405.2	482.2	657.5	925.4	1056.0
140°	419.7	494.5	656.4	884.0	996.8
142.5°	434.2	504.6	656.4	844.4	937.7
145°	448.7	515.7	654.1	812.1	888.5
147.5°	464.4	524.6	650.8	783.6	845.0
150°	480.0	533.6	647.4	759.0	807.0
152.5°	495.6	542.5	641.8	738.4	774.7
155°	510.1	550.8	635.1	718.3	746.8
157.5°	522.4	557.6	628.4	699.3	722.2
160°	534.7	564.2	621.8	680.3	698.8
162.5°	547.0	569.3	616.2	662.5	676.4
165°	555.9	572.6	608.4	645.2	655.2
167.5°	563.7	576.0	601.7	629.6	635.1
170°	571.5	577.6	596.1	615.0	617.3
172.5°	576.0	579.4	589.4	602.2	602.8
175°	579.3	579.9	584.9	592.2	590.5
177.5°	581.6	580.5	580.5	584.9	581.6
180°	580.5	580.5	580.5	580.5	580.5

(END OF REPORT)