

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009268

Luminaire Tested: S122DIP-B675D330UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009268
REPORT IS A COMBINATION OF REPORTS P984509 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D330UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3894.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009268

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009268

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	71	73	68	64	65	62	58	58	55	53
3	85	75	68	61	80	71	65	59	64	59	54	57	53	50	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	43	46	42	39
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	54	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16891	16891	16891
5°	16919	16102	15987
10°	16782	15368	15062
15°	16536	14627	14090
20°	16204	13824	13168
25°	15873	12984	12249
30°	15456	12195	11284
35°	15064	11362	10336
40°	14578	10541	9441
45°	14096	9725	8563
50°	13569	8896	7650
55°	13014	8010	6787
60°	12393	7049	5890
65°	11710	6075	4946
70°	10844	5005	3993
75°	9644	3859	3084
80°	8191	2622	1985
85°	5947	1220	844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14096 cd/sqm

TEST NUMBER: P1009268

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	2.6
10°-20°	282.6	7.3
20°-30°	415.3	10.7
30°-40°	482.3	12.4
40°-50°	481.7	12.4
50°-60°	420.0	10.8
60°-70°	310.5	8.0
70°-80°	175.7	4.5
80°-90°	47.6	1.2
90°-100°	26.1	0.7
100°-110°	82.8	2.1
110°-120°	141.8	3.6
120°-130°	186.4	4.8
130°-140°	209.3	5.4
140°-150°	205.2	5.3
150°-160°	172.1	4.4
160°-170°	114.2	2.9
170°-180°	39.9	1.0
0°-30°	798.3	20.5
0°-40°	1280.6	32.9
0°-60°	2182.4	56.0
0°-90°	2716.2	69.8
90°-120°	250.7	6.4
90°-150°	851.6	21.9
90°-180°	1178.0	30.3
0°-180°	3894.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1067	1067	1067	1067	1067	
5°	1067	1063	1052	1060	1058	101
15°	1016	1010	996	1000	995	286
25°	919	911	894	896	894	423
35°	793	783	766	760	755	495
45°	645	638	623	612	608	498
55°	488	482	470	458	452	437
65°	329	323	313	304	299	326
75°	172	170	165	159	161	184
85°	42	41	40	37	36	47
90°	0	5	12	12	12	4
95°	18	22	23	23	22	21
105°	76	78	78	79	79	81
115°	142	144	144	143	142	141
125°	207	210	209	208	208	185
135°	268	272	272	272	271	207
145°	325	327	330	330	328	203
155°	372	373	374	375	374	171
165°	404	404	404	406	405	114
175°	421	420	419	421	419	40
180°	421	421	421	421	421	

TEST NUMBER: P1009268

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.1	1067.1	1067.1	1067.1	1067.1
2.5°	1073.3	1068.2	1056.9	1067.1	1065.1
5°	1067.1	1063.0	1051.8	1060.0	1057.9
7.5°	1060.0	1053.8	1042.5	1050.7	1048.7
10°	1048.7	1041.5	1029.2	1037.4	1034.3
12.5°	1033.3	1027.1	1014.8	1019.9	1017.9
15°	1015.8	1009.7	996.3	1000.5	995.3
17.5°	994.3	988.1	974.8	979.9	974.8
20°	970.7	964.5	950.2	953.3	949.1
22.5°	947.1	937.9	924.5	924.5	922.5
25°	919.4	911.2	893.7	895.8	893.7
27.5°	888.6	881.4	868.1	865.0	859.9
30°	857.8	849.6	834.2	831.1	827.0
32.5°	825.0	818.8	802.4	796.3	792.2
35°	793.2	782.9	766.5	760.3	755.2
37.5°	757.3	748.0	731.6	724.4	719.3
40°	720.3	712.1	695.7	686.5	682.4
42.5°	684.4	676.2	659.8	649.5	643.4
45°	645.4	638.2	622.8	611.6	607.5
47.5°	607.5	600.3	583.9	572.6	566.4
50°	567.4	562.3	547.9	533.6	528.4
52.5°	528.4	521.3	507.9	496.6	489.5
55°	488.4	482.3	470.0	457.6	452.5
57.5°	448.4	443.3	429.9	417.6	413.5
60°	408.4	404.3	389.9	378.6	375.6
62.5°	369.4	362.2	352.0	341.7	337.6
65°	329.4	323.2	313.0	303.7	298.6
67.5°	288.3	283.2	274.0	266.8	262.7
70°	250.4	246.3	237.0	229.8	225.7
72.5°	211.4	207.3	202.1	195.0	191.9
75°	172.4	170.3	165.2	159.0	161.1
77.5°	137.5	133.4	131.3	128.3	125.2
80°	102.6	101.6	99.5	96.5	94.4
82.5°	69.8	69.8	68.7	64.6	64.6
85°	42.1	41.0	40.0	36.9	35.9
87.5°	18.5	16.4	14.4	11.3	10.3
90°	0.4	4.6	12.4	11.7	12.1
92.5°	7.8	10.7	11.0	11.4	11.4
95°	18.5	22.0	22.8	22.8	22.0
97.5°	30.9	34.1	35.6	35.6	35.6
100°	45.1	48.0	49.1	49.1	48.7
102.5°	60.1	62.2	63.6	64.0	63.6
105°	76.4	77.5	78.2	78.9	78.9
107.5°	92.8	94.2	94.2	94.6	92.8
110°	108.4	110.6	110.6	110.6	109.5



TEST NUMBER: P1009268

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	125.5	127.6	127.3	126.2	125.5
115°	142.2	144.3	143.6	143.3	142.2
117.5°	158.9	161.8	160.0	158.9	157.8
120°	175.6	178.5	175.6	175.6	174.6
122.5°	190.9	194.5	192.7	191.6	190.9
125°	206.9	210.1	209.0	208.0	207.6
127.5°	222.5	226.5	225.0	223.6	222.5
130°	237.1	241.7	241.0	240.3	238.9
132.5°	253.5	257.0	257.4	255.6	254.5
135°	267.7	271.6	272.3	272.0	270.9
137.5°	283.3	286.5	287.2	286.9	285.5
140°	297.2	300.4	302.2	302.2	300.8
142.5°	311.4	314.6	315.7	316.0	314.6
145°	324.9	327.4	329.6	329.9	328.5
147.5°	337.0	340.2	341.6	342.4	340.9
150°	349.5	351.6	353.0	354.1	353.0
152.5°	360.5	362.6	364.4	365.8	364.4
155°	371.5	372.6	373.6	375.4	374.3
157.5°	381.1	381.8	382.5	385.0	383.2
160°	389.6	390.3	390.7	392.8	391.4
162.5°	397.5	397.5	397.8	400.3	398.5
165°	404.2	403.9	403.9	406.3	404.6
167.5°	410.3	409.2	409.2	411.7	409.9
170°	414.9	413.8	413.5	415.9	413.8
172.5°	418.1	417.0	416.7	419.1	417.0
175°	420.6	419.5	418.8	421.3	419.1
177.5°	422.0	420.9	420.2	422.3	420.2
180°	421.3	421.3	421.3	421.3	421.3

(END OF REPORT)