

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009269

Luminaire Tested: S122DIP-B675D330UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009269
REPORT IS A COMBINATION OF REPORTS P984510 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D330UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4004.5 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009269

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009269

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	61
2	93	85	79	73	87	80	75	70	72	67	64	64	60	57	56	54	52
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	47	44
4	77	66	58	52	73	63	56	50	56	50	46	50	46	42	45	41	38
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	25	32	26	23	28	24	21
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16891	16891	16891
5°	16919	16102	15987
10°	16782	15368	15062
15°	16536	14627	14090
20°	16204	13824	13168
25°	15873	12984	12249
30°	15456	12195	11284
35°	15064	11362	10336
40°	14578	10541	9441
45°	14096	9725	8563
50°	13569	8896	7650
55°	13014	8010	6787
60°	12393	7049	5890
65°	11710	6075	4946
70°	10844	5005	3993
75°	9644	3859	3084
80°	8191	2622	1985
85°	5947	1220	844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14096 cd/sqm

TEST NUMBER: P1009269

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	2.5
10°-20°	282.6	7.1
20°-30°	415.3	10.4
30°-40°	482.3	12.0
40°-50°	481.7	12.0
50°-60°	420.0	10.5
60°-70°	310.5	7.8
70°-80°	175.7	4.4
80°-90°	47.5	1.2
90°-100°	74.9	1.9
100°-110°	253.2	6.3
110°-120°	266.2	6.6
120°-130°	218.9	5.5
130°-140°	175.9	4.4
140°-150°	132.9	3.3
150°-160°	93.4	2.3
160°-170°	55.0	1.4
170°-180°	17.9	0.4
0°-30°	798.3	19.9
0°-40°	1280.6	32.0
0°-60°	2182.4	54.5
0°-90°	2716.2	67.8
90°-120°	594.3	14.8
90°-150°	1122.0	28.0
90°-180°	1288.0	32.2
0°-180°	4004.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1067	1067	1067	1067	1067	
5°	1067	1063	1052	1060	1058	101
15°	1016	1010	996	1000	995	286
25°	919	911	894	896	894	423
35°	793	783	766	760	755	495
45°	645	638	623	612	608	498
55°	488	482	470	458	452	437
65°	329	323	313	304	299	326
75°	172	170	165	159	161	184
85°	42	41	40	37	36	47
90°	0	5	12	12	12	3
95°	12	31	139	53	40	13
105°	43	65	263	471	400	46
115°	76	96	220	455	527	76
125°	107	126	212	368	428	95
135°	125	149	209	310	354	97
145°	143	164	208	259	283	90
155°	162	175	202	229	238	75
165°	177	182	194	205	209	50
175°	184	185	186	188	188	18
180°	185	185	185	185	185	

TEST NUMBER: P1009269

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.1	1067.1	1067.1	1067.1	1067.1
2.5°	1073.3	1068.2	1056.9	1067.1	1065.1
5°	1067.1	1063.0	1051.8	1060.0	1057.9
7.5°	1060.0	1053.8	1042.5	1050.7	1048.7
10°	1048.7	1041.5	1029.2	1037.4	1034.3
12.5°	1033.3	1027.1	1014.8	1019.9	1017.9
15°	1015.8	1009.7	996.3	1000.5	995.3
17.5°	994.3	988.1	974.8	979.9	974.8
20°	970.7	964.5	950.2	953.3	949.1
22.5°	947.1	937.9	924.5	924.5	922.5
25°	919.4	911.2	893.7	895.8	893.7
27.5°	888.6	881.4	868.1	865.0	859.9
30°	857.8	849.6	834.2	831.1	827.0
32.5°	825.0	818.8	802.4	796.3	792.2
35°	793.2	782.9	766.5	760.3	755.2
37.5°	757.3	748.0	731.6	724.4	719.3
40°	720.3	712.1	695.7	686.5	682.4
42.5°	684.4	676.2	659.8	649.5	643.4
45°	645.4	638.2	622.8	611.6	607.5
47.5°	607.5	600.3	583.9	572.6	566.4
50°	567.4	562.3	547.9	533.6	528.4
52.5°	528.4	521.3	507.9	496.6	489.5
55°	488.4	482.3	470.0	457.6	452.5
57.5°	448.4	443.3	429.9	417.6	413.5
60°	408.4	404.3	389.9	378.6	375.6
62.5°	369.4	362.2	352.0	341.7	337.6
65°	329.4	323.2	313.0	303.7	298.6
67.5°	288.3	283.2	274.0	266.8	262.7
70°	250.4	246.3	237.0	229.8	225.7
72.5°	211.4	207.3	202.1	195.0	191.9
75°	172.4	170.3	165.2	159.0	161.1
77.5°	137.5	133.4	131.3	128.3	125.2
80°	102.6	101.6	99.5	96.5	94.4
82.5°	69.8	69.8	68.7	64.6	64.6
85°	42.1	41.0	40.0	36.9	35.9
87.5°	18.5	16.4	14.4	11.3	10.3
90°	0.4	4.8	12.1	11.6	11.7
92.5°	5.3	16.8	54.7	25.2	21.7
95°	12.4	30.6	139.3	52.6	40.5
97.5°	18.5	40.3	227.1	105.6	67.9
100°	27.4	49.4	280.7	210.2	127.2
102.5°	35.5	57.6	282.5	355.3	248.0
105°	43.4	65.4	263.3	470.6	400.5
107.5°	51.9	73.2	245.5	512.4	503.2
110°	60.4	81.2	233.5	505.6	545.1



TEST NUMBER: P1009269

CATALOG NUMBER: S122DIP-B675D330UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.2	88.8	225.6	482.8	544.4
115°	76.4	96.5	220.3	454.7	527.0
117.5°	84.9	104.1	217.5	427.8	500.7
120°	92.7	111.6	215.0	403.8	475.5
122.5°	100.2	119.2	213.6	385.2	449.2
125°	106.6	126.2	211.8	368.3	427.5
127.5°	111.9	132.8	210.7	354.0	407.2
130°	116.6	138.6	210.0	339.4	390.5
132.5°	120.8	144.2	209.7	324.2	373.1
135°	125.1	149.2	209.3	309.6	354.3
137.5°	129.0	153.5	209.3	294.6	336.2
140°	133.6	157.4	208.9	281.5	317.3
142.5°	138.2	160.6	208.9	268.8	298.5
145°	142.8	164.2	208.2	258.6	282.9
147.5°	147.8	167.0	207.2	249.4	269.0
150°	152.8	169.9	206.1	241.6	256.9
152.5°	157.8	172.7	204.3	235.0	246.6
155°	162.4	175.4	202.2	228.6	237.7
157.5°	166.3	177.5	200.1	222.6	229.9
160°	170.2	179.6	197.9	216.6	222.4
162.5°	174.1	181.2	196.2	210.9	215.3
165°	177.0	182.3	193.7	205.4	208.6
167.5°	179.4	183.4	191.5	200.4	202.2
170°	181.9	183.9	189.8	195.8	196.5
172.5°	183.4	184.4	187.6	191.7	191.9
175°	184.4	184.6	186.2	188.5	188.0
177.5°	185.1	184.8	184.8	186.2	185.1
180°	184.8	184.8	184.8	184.8	184.8

(END OF REPORT)