

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008773

Luminaire Tested: S122DIP-B290D1080UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008773
REPORT IS A COMBINATION OF REPORTS P983825 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D1080UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4977.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008773

CATALOG NUMBER: S122DIP-B290D1080UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008773

CATALOG NUMBER: S122DIP-B290D1080UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27
2	84	76	71	66	74	68	63	59	52	49	46	38	36	34	25	23	22
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	20	19
4	70	59	52	46	62	53	47	42	41	36	33	30	27	25	19	18	16
5	64	53	45	39	56	47	40	35	36	32	28	27	24	21	17	16	14
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	16	14	12
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	29	22	18	22	18	15	17	14	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7217	7217	7217
5°	7228	6880	6831
10°	7171	6566	6435
15°	7065	6250	6021
20°	6923	5907	5626
25°	6781	5548	5234
30°	6604	5210	4822
35°	6436	4855	4417
40°	6230	4503	4033
45°	6023	4155	3658
50°	5797	3801	3269
55°	5561	3422	2899
60°	5295	3012	2517
65°	5002	2595	2113
70°	4634	2139	1707
75°	4123	1649	1317
80°	3497	1120	847
85°	2543	521	360

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6023 cd/sqm

TEST NUMBER: P1008773

CATALOG NUMBER: S122DIP-B290D1080UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.9	0.9
10°-20°	120.7	2.4
20°-30°	177.4	3.6
30°-40°	206.1	4.1
40°-50°	205.8	4.1
50°-60°	179.5	3.6
60°-70°	132.7	2.7
70°-80°	75.1	1.5
80°-90°	23.7	0.5
90°-100°	84.4	1.7
100°-110°	268.2	5.4
110°-120°	458.9	9.2
120°-130°	603.6	12.1
130°-140°	677.5	13.6
140°-150°	664.4	13.3
150°-160°	557.3	11.2
160°-170°	369.6	7.4
170°-180°	129.2	2.6
0°-30°	341.1	6.9
0°-40°	547.2	11.0
0°-60°	932.5	18.7
0°-90°	1163.9	23.4
90°-120°	811.5	16.3
90°-150°	2757.0	55.4
90°-180°	3813.0	76.6
0°-180°	4977.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	456	456	456	456	456	
5°	456	454	449	453	452	43
15°	434	431	426	427	425	122
25°	393	389	382	383	382	181
35°	339	334	328	325	323	212
45°	276	273	266	261	260	213
55°	209	206	201	196	193	187
65°	141	138	134	130	128	139
75°	74	73	71	68	69	79
85°	18	18	17	16	15	20
90°	1	15	40	38	39	5
95°	60	71	74	74	71	67
105°	248	251	253	256	256	261
115°	460	467	465	464	460	455
125°	670	680	677	673	672	599
135°	867	879	882	880	877	670
145°	1052	1060	1067	1068	1064	657
155°	1203	1206	1210	1215	1212	554
165°	1309	1308	1308	1316	1310	369
175°	1362	1358	1356	1364	1357	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P1008773

CATALOG NUMBER: S122DIP-B290D1080UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	455.9	455.9	455.9	455.9	455.9
2.5°	458.6	456.4	451.6	455.9	455.1
5°	455.9	454.2	449.4	452.9	452.0
7.5°	452.9	450.2	445.4	448.9	448.1
10°	448.1	445.0	439.7	443.2	441.9
12.5°	441.5	438.8	433.6	435.8	434.9
15°	434.0	431.4	425.7	427.4	425.3
17.5°	424.8	422.2	416.5	418.7	416.5
20°	414.7	412.1	406.0	407.3	405.5
22.5°	404.7	400.7	395.0	395.0	394.1
25°	392.8	389.3	381.9	382.7	381.9
27.5°	379.7	376.6	370.9	369.6	367.4
30°	366.5	363.0	356.4	355.1	353.4
32.5°	352.5	349.9	342.8	340.2	338.5
35°	338.9	334.5	327.5	324.9	322.7
37.5°	323.5	319.6	312.6	309.5	307.3
40°	307.8	304.3	297.2	293.3	291.5
42.5°	292.4	288.9	281.9	277.5	274.9
45°	275.8	272.7	266.1	261.3	259.5
47.5°	259.5	256.5	249.5	244.6	242.0
50°	242.4	240.2	234.1	228.0	225.8
52.5°	225.8	222.7	217.0	212.2	209.1
55°	208.7	206.1	200.8	195.5	193.3
57.5°	191.6	189.4	183.7	178.4	176.7
60°	174.5	172.7	166.6	161.8	160.5
62.5°	157.8	154.8	150.4	146.0	144.2
65°	140.7	138.1	133.7	129.8	127.6
67.5°	123.2	121.0	117.1	114.0	112.2
70°	107.0	105.2	101.3	98.2	96.5
72.5°	90.3	88.6	86.4	83.3	82.0
75°	73.7	72.8	70.6	68.0	68.8
77.5°	58.7	57.0	56.1	54.8	53.5
80°	43.8	43.4	42.5	41.2	40.3
82.5°	29.8	29.8	29.4	27.6	27.6
85°	18.0	17.5	17.1	15.8	15.3
87.5°	7.9	7.0	6.1	4.8	4.4
90°	1.2	15.0	40.3	38.0	39.1
92.5°	25.3	34.5	35.7	36.8	36.8
95°	59.8	71.4	73.7	73.7	71.4
97.5°	100.1	110.5	115.1	115.1	115.1
100°	146.2	155.4	158.8	158.8	157.7
102.5°	194.5	201.4	206.0	207.2	206.0
105°	247.5	250.9	253.2	255.5	255.5
107.5°	300.4	305.0	305.0	306.2	300.4
110°	351.0	357.9	357.9	357.9	354.5

TEST NUMBER: P1008773

CATALOG NUMBER: S122DIP-B290D1080UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	406.3	413.2	412.0	408.6	406.3
115°	460.4	467.3	465.0	463.8	460.4
117.5°	514.5	523.7	517.9	514.5	511.0
120°	568.6	577.8	568.6	568.6	565.1
122.5°	618.1	629.6	623.8	620.4	618.1
125°	669.8	680.2	676.8	673.3	672.2
127.5°	720.5	733.2	728.5	723.9	720.5
130°	767.7	782.6	780.3	778.0	773.4
132.5°	820.6	832.1	833.3	827.5	824.1
135°	866.7	879.3	881.6	880.5	877.0
137.5°	917.3	927.7	930.0	928.8	924.2
140°	962.2	972.5	978.3	978.3	973.7
142.5°	1008.2	1018.6	1022.0	1023.2	1018.6
145°	1052.0	1060.0	1066.9	1068.1	1063.5
147.5°	1091.1	1101.5	1106.1	1108.4	1103.8
150°	1131.4	1138.3	1142.9	1146.3	1142.9
152.5°	1167.1	1174.0	1179.7	1184.3	1179.7
155°	1202.7	1206.2	1209.6	1215.4	1211.9
157.5°	1233.8	1236.1	1238.4	1246.5	1240.7
160°	1261.4	1263.7	1264.9	1271.8	1267.2
162.5°	1286.8	1286.8	1287.9	1296.0	1290.2
165°	1308.6	1307.5	1307.5	1315.5	1309.8
167.5°	1328.2	1324.7	1324.7	1332.8	1327.0
170°	1343.2	1339.7	1338.5	1346.6	1339.7
172.5°	1353.5	1350.1	1348.9	1357.0	1350.1
175°	1361.6	1358.1	1355.8	1363.9	1357.0
177.5°	1366.2	1362.7	1360.4	1367.3	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9

(END OF REPORT)