

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009286

Luminaire Tested: S122DIP-B675D330UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009286
REPORT IS A COMBINATION OF REPORTS P984527 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D330UB40-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3872.0 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009286

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009286

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53
3	85	75	68	61	80	71	65	59	64	59	54	57	53	50	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	43	46	42	39
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	54	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16800	16800	16800
5°	16827	16012	15899
10°	16689	15283	14979
15°	16445	14547	14012
20°	16114	13747	13096
25°	15785	12913	12182
30°	15371	12127	11222
35°	14981	11300	10279
40°	14497	10483	9388
45°	14019	9672	8515
50°	13494	8847	7608
55°	12942	7966	6749
60°	12323	7011	5857
65°	11646	6040	4917
70°	10783	4978	3972
75°	9588	3838	3066
80°	8143	2609	1974
85°	5905	1214	839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14019 cd/sqm

TEST NUMBER: P1009286

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	2.6
10°-20°	281.0	7.3
20°-30°	413.0	10.7
30°-40°	479.7	12.4
40°-50°	479.1	12.4
50°-60°	417.7	10.8
60°-70°	308.8	8.0
70°-80°	174.7	4.5
80°-90°	47.3	1.2
90°-100°	25.9	0.7
100°-110°	82.3	2.1
110°-120°	140.9	3.6
120°-130°	185.3	4.8
130°-140°	208.0	5.4
140°-150°	204.0	5.3
150°-160°	171.1	4.4
160°-170°	113.5	2.9
170°-180°	39.7	1.0
0°-30°	793.9	20.5
0°-40°	1273.6	32.9
0°-60°	2170.4	56.1
0°-90°	2701.2	69.8
90°-120°	249.2	6.4
90°-150°	846.5	21.9
90°-180°	1171.0	30.2
0°-180°	3872.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1061	1061	1061	1061	1061	
5°	1061	1057	1046	1054	1052	101
15°	1010	1004	991	995	990	285
25°	914	906	889	891	889	421
35°	789	779	762	756	751	493
45°	642	635	619	608	604	495
55°	486	480	467	455	450	434
65°	328	321	311	302	297	324
75°	171	169	164	158	160	183
85°	42	41	40	37	36	47
90°	0	5	12	12	12	4
95°	18	22	23	23	22	21
105°	76	77	78	78	78	80
115°	141	144	143	142	141	140
125°	206	209	208	207	206	184
135°	266	270	271	270	269	206
145°	323	326	328	328	326	202
155°	369	370	371	373	372	170
165°	402	402	402	404	402	113
175°	418	417	416	419	417	40
180°	419	419	419	419	419	

TEST NUMBER: P1009286

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.4	1062.3	1051.0	1061.3	1059.2
5°	1061.3	1057.2	1045.9	1054.1	1052.1
7.5°	1054.1	1048.0	1036.8	1044.9	1042.9
10°	1042.9	1035.7	1023.5	1031.7	1028.6
12.5°	1027.6	1021.5	1009.2	1014.3	1012.3
15°	1010.2	1004.1	990.8	994.9	989.8
17.5°	988.8	982.7	969.4	974.5	969.4
20°	965.3	959.2	944.9	948.0	943.9
22.5°	941.9	932.7	919.4	919.4	917.4
25°	914.3	906.1	888.8	890.8	888.8
27.5°	883.7	876.6	863.3	860.2	855.1
30°	853.1	844.9	829.6	826.6	822.5
32.5°	820.4	814.3	798.0	791.9	787.8
35°	788.8	778.6	762.3	756.1	751.0
37.5°	753.1	743.9	727.6	720.4	715.3
40°	716.3	708.2	691.9	682.7	678.6
42.5°	680.6	672.5	656.1	645.9	639.8
45°	641.9	634.7	619.4	608.2	604.1
47.5°	604.1	597.0	580.6	569.4	563.3
50°	564.3	559.2	544.9	530.6	525.5
52.5°	525.5	518.4	505.1	493.9	486.7
55°	485.7	479.6	467.4	455.1	450.0
57.5°	445.9	440.8	427.6	415.3	411.2
60°	406.1	402.1	387.8	376.5	373.5
62.5°	367.4	360.2	350.0	339.8	335.7
65°	327.6	321.4	311.2	302.0	296.9
67.5°	286.7	281.6	272.5	265.3	261.2
70°	249.0	244.9	235.7	228.6	224.5
72.5°	210.2	206.1	201.0	193.9	190.8
75°	171.4	169.4	164.3	158.2	160.2
77.5°	136.7	132.7	130.6	127.6	124.5
80°	102.0	101.0	99.0	95.9	93.9
82.5°	69.4	69.4	68.4	64.3	64.3
85°	41.8	40.8	39.8	36.7	35.7
87.5°	18.4	16.3	14.3	11.2	10.2
90°	0.4	4.6	12.4	11.7	12.0
92.5°	7.8	10.6	11.0	11.3	11.3
95°	18.4	21.9	22.6	22.6	21.9
97.5°	30.7	33.9	35.3	35.3	35.3
100°	44.9	47.7	48.8	48.8	48.4
102.5°	59.7	61.8	63.3	63.6	63.3
105°	76.0	77.0	77.7	78.5	78.5
107.5°	92.2	93.6	93.6	94.0	92.2
110°	107.8	109.9	109.9	109.9	108.8

TEST NUMBER: P1009286

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	124.7	126.9	126.5	125.5	124.7
115°	141.4	143.5	142.8	142.4	141.4
117.5°	158.0	160.8	159.0	158.0	156.9
120°	174.6	177.4	174.6	174.6	173.5
122.5°	189.8	193.3	191.5	190.5	189.8
125°	205.7	208.9	207.8	206.7	206.4
127.5°	221.2	225.1	223.7	222.3	221.2
130°	235.7	240.3	239.6	238.9	237.5
132.5°	252.0	255.5	255.9	254.1	253.0
135°	266.1	270.0	270.7	270.3	269.3
137.5°	281.7	284.8	285.5	285.2	283.8
140°	295.4	298.6	300.4	300.4	299.0
142.5°	309.6	312.8	313.8	314.2	312.8
145°	323.0	325.5	327.6	328.0	326.5
147.5°	335.0	338.2	339.6	340.3	338.9
150°	347.4	349.5	350.9	352.0	350.9
152.5°	358.3	360.5	362.2	363.6	362.2
155°	369.3	370.4	371.4	373.2	372.1
157.5°	378.8	379.5	380.3	382.7	381.0
160°	387.3	388.0	388.4	390.5	389.1
162.5°	395.1	395.1	395.4	397.9	396.2
165°	401.8	401.5	401.5	403.9	402.2
167.5°	407.8	406.8	406.8	409.2	407.5
170°	412.4	411.4	411.0	413.5	411.4
172.5°	415.6	414.5	414.2	416.7	414.5
175°	418.1	417.0	416.3	418.8	416.7
177.5°	419.5	418.4	417.7	419.8	417.7
180°	418.8	418.8	418.8	418.8	418.8

(END OF REPORT)