

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009290

Luminaire Tested: S122DIP-B675D330UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009290
REPORT IS A COMBINATION OF REPORTS P984531 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D330UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4071.0 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64
2	94	87	81	76	89	83	77	73	74	70	66	67	63	61	59	57	55
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27
9	55	43	35	30	52	41	34	29	38	32	27	34	29	26	31	27	24
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20367	21665	20445	17235
10°	20130	23650	20257	14211
15°	19642	24945	19915	11969
20°	19336	23422	19336	10403
25°	18720	20122	18804	9304
30°	17706	15818	18043	8427
35°	16808	10938	17089	7711
40°	15774	8258	15954	7139
45°	14502	6787	14738	6522
50°	13401	5956	13425	5970
55°	12145	5075	12225	5371
60°	10809	4239	10957	4687
65°	9609	3448	9787	4003
70°	8419	2705	8631	3229
75°	7065	1964	7339	2341
80°	5517	1245	5908	1390
85°	3630	626	3899	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21003 cd/sqm

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	3.0
10°-20°	355.8	8.7
20°-30°	516.4	12.7
30°-40°	544.4	13.4
40°-50°	481.8	11.8
50°-60°	384.7	9.4
60°-70°	261.3	6.4
70°-80°	133.7	3.3
80°-90°	32.7	0.8
90°-100°	69.3	1.7
100°-110°	244.0	6.0
110°-120°	256.3	6.3
120°-130°	210.8	5.2
130°-140°	169.4	4.2
140°-150°	127.9	3.1
150°-160°	89.9	2.2
160°-170°	52.9	1.3
170°-180°	17.2	0.4
0°-30°	994.6	24.4
0°-40°	1539.0	37.8
0°-60°	2405.4	59.1
0°-90°	2833.1	69.6
90°-120°	569.6	14.0
90°-150°	1077.7	26.5
90°-180°	1238.0	30.4
0°-180°	4071.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	30
90°	0	11	0	11	0	2
95°	12	39	12	39	12	12
105°	42	385	42	385	42	44
115°	74	507	74	507	74	73
125°	102	411	102	411	102	91
135°	120	341	120	341	120	93
145°	137	272	137	272	137	86
155°	156	229	156	229	156	72
165°	170	201	170	201	170	48
175°	177	181	177	181	177	17
180°	178	178	178	178	178	

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	0.3	1.4	2.7	3.4	4.1	4.6	5.1	6.8	9.2	11.3	11.6
92.5°	5.1	7.2	9.9	11.6	14.4	16.2	18.1	27.3	40.3	52.0	52.6
95°	12.0	13.3	16.7	19.8	25.3	29.4	33.5	49.2	79.0	118.6	134.0
97.5°	17.8	19.8	23.6	28.0	34.2	38.8	43.4	63.6	104.9	168.9	218.4
100°	26.3	27.3	30.4	35.9	42.7	47.5	52.3	70.4	112.1	186.0	270.0
102.5°	34.2	34.9	37.9	43.4	50.6	55.4	60.2	76.6	112.5	179.5	271.8
105°	41.7	43.1	45.5	50.6	58.1	62.9	67.7	83.7	114.2	170.6	253.3
107.5°	49.9	50.9	53.3	58.1	65.6	70.4	75.2	90.9	117.9	165.8	236.2
110°	58.1	59.5	61.5	66.0	73.2	78.2	83.1	98.1	122.7	164.4	224.6

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.6	67.0	69.4	73.5	80.3	85.4	90.6	104.9	127.8	164.8	217.1
115°	73.5	75.2	77.3	81.4	88.2	92.8	97.4	112.1	133.0	166.1	211.9
117.5°	81.7	83.1	85.1	88.9	95.4	100.2	104.9	118.6	138.4	168.2	209.2
120°	89.2	90.6	92.6	95.7	102.5	107.3	112.1	125.5	143.9	170.2	206.8
122.5°	96.4	97.4	99.5	102.9	109.7	114.6	119.6	131.9	148.7	172.6	205.4
125°	102.5	103.6	105.6	109.7	116.6	121.4	126.1	138.4	153.8	175.0	203.7
127.5°	107.7	109.0	111.8	116.2	122.7	127.6	132.6	144.6	158.6	177.4	202.7
130°	112.1	113.5	116.9	121.7	128.5	133.3	138.1	150.1	163.1	180.1	202.0
132.5°	116.2	117.9	121.7	126.8	134.0	138.8	143.6	154.8	167.5	182.9	201.7
135°	120.3	121.7	125.8	130.9	138.8	143.6	148.4	159.3	171.3	184.9	201.3
137.5°	124.1	125.8	129.9	135.4	143.2	147.6	152.1	163.1	174.3	187.0	201.3
140°	128.5	129.9	134.0	139.5	147.0	151.4	155.9	166.1	176.7	188.3	201.0
142.5°	133.0	134.0	137.8	143.2	150.4	154.5	158.6	168.5	178.8	189.4	201.0
145°	137.4	138.8	142.2	147.3	154.2	158.0	161.7	170.9	180.5	190.1	200.3
147.5°	142.2	143.2	146.6	151.4	157.2	160.6	164.1	173.0	181.5	190.4	199.3
150°	147.0	148.0	150.7	155.2	160.3	163.4	166.5	174.3	182.2	190.1	198.3
152.5°	151.8	152.1	154.8	158.6	163.4	166.2	168.9	175.7	182.5	189.4	196.6
155°	156.2	156.6	158.6	162.4	166.1	168.7	171.3	177.1	182.9	188.7	194.5
157.5°	160.0	160.3	162.0	165.4	168.5	170.8	173.0	178.1	182.9	187.3	192.4
160°	163.7	164.1	165.4	168.2	170.9	172.8	174.7	178.8	182.9	186.3	190.4
162.5°	167.5	167.2	168.5	170.6	173.0	174.4	175.7	179.1	182.5	185.3	188.7
165°	170.2	169.9	170.6	172.6	174.3	175.4	176.4	179.5	181.9	183.9	186.3
167.5°	172.6	172.3	173.0	174.3	175.7	176.4	177.1	179.5	181.5	182.5	184.2
170°	175.0	174.3	174.7	175.7	176.4	176.9	177.4	179.1	180.8	181.5	182.5
172.5°	176.4	176.0	175.7	176.7	177.1	177.4	177.8	178.8	179.8	180.1	180.5
175°	177.4	177.1	176.7	177.4	177.4	177.6	177.8	178.4	179.1	178.8	179.1
177.5°	178.1	177.4	177.1	177.8	177.8	177.8	177.8	178.1	178.8	178.1	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	11.3	10.9	10.3	10.9	11.1	11.3	11.3	11.3	11.3	11.3	11.3
92.5°	44.1	34.5	29.4	25.6	24.2	22.9	22.6	21.2	21.5	20.9	21.5
95°	117.2	89.6	68.7	54.4	50.6	46.8	42.4	39.7	38.6	39.0	38.6
97.5°	220.1	183.2	146.3	111.8	101.6	91.3	77.9	71.1	67.3	65.3	67.3
100°	319.3	312.1	269.7	222.9	202.2	181.5	153.1	138.4	128.5	122.4	128.5
102.5°	356.2	396.5	395.2	364.0	341.8	319.6	288.2	260.5	247.5	238.6	247.5
105°	344.2	415.3	453.9	458.4	452.8	447.1	425.9	404.7	390.0	385.2	390.0
107.5°	318.9	395.2	452.6	486.1	493.0	499.8	499.4	496.3	491.9	484.0	491.9
110°	295.3	367.5	428.7	472.4	486.4	500.4	515.1	521.6	524.7	524.4	524.7

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	278.9	342.2	400.3	447.8	464.4	481.0	502.8	514.8	521.3	523.7	521.3
115°	265.9	322.3	375.0	419.8	437.4	455.0	479.2	495.0	503.9	506.9	503.9
117.5°	257.1	305.9	353.1	394.8	411.6	428.3	453.3	470.0	479.2	481.6	479.2
120°	250.2	294.3	336.7	372.9	388.4	404.0	428.0	444.0	453.9	457.4	453.9
122.5°	244.4	285.1	323.0	356.9	370.5	384.2	405.1	420.8	429.3	432.1	429.3
125°	238.9	276.2	311.4	341.5	354.3	367.1	386.9	399.9	408.5	411.2	408.5
127.5°	233.8	267.3	299.8	328.5	340.4	352.4	369.9	382.2	389.7	391.7	389.7
130°	228.7	258.8	288.2	315.2	326.4	337.7	354.5	366.1	372.9	375.7	372.9
132.5°	224.6	250.6	277.2	301.5	311.9	322.3	338.8	350.4	356.5	358.9	356.5
135°	220.8	243.0	265.6	288.2	297.8	307.3	322.0	333.3	339.4	340.8	339.4
137.5°	218.1	236.9	256.4	274.8	283.4	291.9	305.9	315.8	321.3	323.4	321.3
140°	215.7	231.1	247.5	263.2	270.7	278.2	289.2	298.1	303.2	305.3	303.2
142.5°	213.3	226.3	239.6	252.6	258.6	264.6	274.8	282.7	287.1	287.1	287.1
145°	211.2	221.8	233.1	243.7	248.6	253.6	261.8	267.7	271.1	272.1	271.1
147.5°	209.2	218.4	227.7	236.2	240.0	243.7	250.9	255.7	258.1	258.8	258.1
150°	206.5	214.7	222.2	229.4	232.4	235.5	240.6	244.7	246.8	247.1	246.8
152.5°	204.1	210.9	217.7	223.6	226.2	228.7	232.4	235.9	237.2	237.2	237.2
155°	201.0	207.5	213.0	218.1	220.0	221.8	225.6	228.0	229.4	228.7	229.4
157.5°	198.3	203.4	208.2	212.6	214.2	215.7	218.4	220.5	221.2	221.2	221.2
160°	195.2	199.6	203.4	207.1	208.3	209.5	211.9	213.6	214.0	214.0	214.0
162.5°	192.4	195.9	198.9	202.0	202.8	203.7	206.1	207.1	207.5	207.1	207.5
165°	189.4	192.1	194.5	196.9	197.6	198.3	199.6	201.0	201.0	200.7	201.0
167.5°	186.3	188.3	190.4	192.1	192.8	193.5	194.2	194.8	194.8	194.5	194.8
170°	183.9	185.6	186.6	188.0	188.4	188.7	189.0	190.1	189.7	189.0	189.7
172.5°	181.5	182.5	183.2	184.2	184.4	184.6	184.9	185.3	184.9	184.6	184.9
175°	179.5	180.5	180.8	181.2	181.4	181.5	181.5	181.9	181.5	180.8	181.5
177.5°	178.1	178.8	178.8	179.1	179.1	179.1	179.1	179.1	178.8	178.1	178.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	11.3	11.3	11.3	11.1	10.9	10.3	10.9	11.3	11.6	11.3	9.2
92.5°	21.2	22.6	22.9	24.2	25.6	29.4	34.5	44.1	52.6	52.0	40.3
95°	39.7	42.4	46.8	50.6	54.4	68.7	89.6	117.2	134.0	118.6	79.0
97.5°	71.1	77.9	91.3	101.6	111.8	146.3	183.2	220.1	218.4	168.9	104.9
100°	138.4	153.1	181.5	202.2	222.9	269.7	312.1	319.3	270.0	186.0	112.1
102.5°	260.5	288.2	319.6	341.8	364.0	395.2	396.5	356.2	271.8	179.5	112.5
105°	404.7	425.9	447.1	452.8	458.4	453.9	415.3	344.2	253.3	170.6	114.2
107.5°	496.3	499.4	499.8	493.0	486.1	452.6	395.2	318.9	236.2	165.8	117.9
110°	521.6	515.1	500.4	486.4	472.4	428.7	367.5	295.3	224.6	164.4	122.7

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	514.8	502.8	481.0	464.4	447.8	400.3	342.2	278.9	217.1	164.8	127.8
115°	495.0	479.2	455.0	437.4	419.8	375.0	322.3	265.9	211.9	166.1	133.0
117.5°	470.0	453.3	428.3	411.6	394.8	353.1	305.9	257.1	209.2	168.2	138.4
120°	444.0	428.0	404.0	388.4	372.9	336.7	294.3	250.2	206.8	170.2	143.9
122.5°	420.8	405.1	384.2	370.5	356.9	323.0	285.1	244.4	205.4	172.6	148.7
125°	399.9	386.9	367.1	354.3	341.5	311.4	276.2	238.9	203.7	175.0	153.8
127.5°	382.2	369.9	352.4	340.4	328.5	299.8	267.3	233.8	202.7	177.4	158.6
130°	366.1	354.5	337.7	326.4	315.2	288.2	258.8	228.7	202.0	180.1	163.1
132.5°	350.4	338.8	322.3	311.9	301.5	277.2	250.6	224.6	201.7	182.9	167.5
135°	333.3	322.0	307.3	297.8	288.2	265.6	243.0	220.8	201.3	184.9	171.3
137.5°	315.8	305.9	291.9	283.4	274.8	256.4	236.9	218.1	201.3	187.0	174.3
140°	298.1	289.2	278.2	270.7	263.2	247.5	231.1	215.7	201.0	188.3	176.7
142.5°	282.7	274.8	264.6	258.6	252.6	239.6	226.3	213.3	201.0	189.4	178.8
145°	267.7	261.8	253.6	248.6	243.7	233.1	221.8	211.2	200.3	190.1	180.5
147.5°	255.7	250.9	243.7	240.0	236.2	227.7	218.4	209.2	199.3	190.4	181.5
150°	244.7	240.6	235.5	232.4	229.4	222.2	214.7	206.5	198.3	190.1	182.2
152.5°	235.9	232.4	228.7	226.2	223.6	217.7	210.9	204.1	196.6	189.4	182.5
155°	228.0	225.6	221.8	220.0	218.1	213.0	207.5	201.0	194.5	188.7	182.9
157.5°	220.5	218.4	215.7	214.2	212.6	208.2	203.4	198.3	192.4	187.3	182.9
160°	213.6	211.9	209.5	208.3	207.1	203.4	199.6	195.2	190.4	186.3	182.9
162.5°	207.1	206.1	203.7	202.8	202.0	198.9	195.9	192.4	188.7	185.3	182.5
165°	201.0	199.6	198.3	197.6	196.9	194.5	192.1	189.4	186.3	183.9	181.9
167.5°	194.8	194.2	193.5	192.8	192.1	190.4	188.3	186.3	184.2	182.5	181.5
170°	190.1	189.0	188.7	188.4	188.0	186.6	185.6	183.9	182.5	181.5	180.8
172.5°	185.3	184.9	184.6	184.4	184.2	183.2	182.5	181.5	180.5	180.1	179.8
175°	181.9	181.5	181.5	181.4	181.2	180.8	180.5	179.5	179.1	178.8	179.1
177.5°	179.1	179.1	179.1	179.1	179.1	178.8	178.8	178.1	177.8	178.1	178.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	6.8	5.1	4.6	4.1	3.4	2.7	1.4	0.3	1.4	2.7	3.4
92.5°	27.3	18.1	16.2	14.4	11.6	9.9	7.2	5.1	7.2	9.9	11.6
95°	49.2	33.5	29.4	25.3	19.8	16.7	13.3	12.0	13.3	16.7	19.8
97.5°	63.6	43.4	38.8	34.2	28.0	23.6	19.8	17.8	19.8	23.6	28.0
100°	70.4	52.3	47.5	42.7	35.9	30.4	27.3	26.3	27.3	30.4	35.9
102.5°	76.6	60.2	55.4	50.6	43.4	37.9	34.9	34.2	34.9	37.9	43.4
105°	83.7	67.7	62.9	58.1	50.6	45.5	43.1	41.7	43.1	45.5	50.6
107.5°	90.9	75.2	70.4	65.6	58.1	53.3	50.9	49.9	50.9	53.3	58.1
110°	98.1	83.1	78.2	73.2	66.0	61.5	59.5	58.1	59.5	61.5	66.0

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	104.9	90.6	85.4	80.3	73.5	69.4	67.0	65.6	67.0	69.4	73.5
115°	112.1	97.4	92.8	88.2	81.4	77.3	75.2	73.5	75.2	77.3	81.4
117.5°	118.6	104.9	100.2	95.4	88.9	85.1	83.1	81.7	83.1	85.1	88.9
120°	125.5	112.1	107.3	102.5	95.7	92.6	90.6	89.2	90.6	92.6	95.7
122.5°	131.9	119.6	114.6	109.7	102.9	99.5	97.4	96.4	97.4	99.5	102.9
125°	138.4	126.1	121.4	116.6	109.7	105.6	103.6	102.5	103.6	105.6	109.7
127.5°	144.6	132.6	127.6	122.7	116.2	111.8	109.0	107.7	109.0	111.8	116.2
130°	150.1	138.1	133.3	128.5	121.7	116.9	113.5	112.1	113.5	116.9	121.7
132.5°	154.8	143.6	138.8	134.0	126.8	121.7	117.9	116.2	117.9	121.7	126.8
135°	159.3	148.4	143.6	138.8	130.9	125.8	121.7	120.3	121.7	125.8	130.9
137.5°	163.1	152.1	147.6	143.2	135.4	129.9	125.8	124.1	125.8	129.9	135.4
140°	166.1	155.9	151.4	147.0	139.5	134.0	129.9	128.5	129.9	134.0	139.5
142.5°	168.5	158.6	154.5	150.4	143.2	137.8	134.0	133.0	134.0	137.8	143.2
145°	170.9	161.7	158.0	154.2	147.3	142.2	138.8	137.4	138.8	142.2	147.3
147.5°	173.0	164.1	160.6	157.2	151.4	146.6	143.2	142.2	143.2	146.6	151.4
150°	174.3	166.5	163.4	160.3	155.2	150.7	148.0	147.0	148.0	150.7	155.2
152.5°	175.7	168.9	166.2	163.4	158.6	154.8	152.1	151.8	152.1	154.8	158.6
155°	177.1	171.3	168.7	166.1	162.4	158.6	156.6	156.2	156.6	158.6	162.4
157.5°	178.1	173.0	170.8	168.5	165.4	162.0	160.3	160.0	160.3	162.0	165.4
160°	178.8	174.7	172.8	170.9	168.2	165.4	164.1	163.7	164.1	165.4	168.2
162.5°	179.1	175.7	174.4	173.0	170.6	168.5	167.2	167.5	167.2	168.5	170.6
165°	179.5	176.4	175.4	174.3	172.6	170.6	169.9	170.2	169.9	170.6	172.6
167.5°	179.5	177.1	176.4	175.7	174.3	173.0	172.3	172.6	172.3	173.0	174.3
170°	179.1	177.4	176.9	176.4	175.7	174.7	174.3	175.0	174.3	174.7	175.7
172.5°	178.8	177.8	177.4	177.1	176.7	175.7	176.0	176.4	176.0	175.7	176.7
175°	178.4	177.8	177.6	177.4	177.4	176.7	177.1	177.4	177.1	176.7	177.4
177.5°	178.1	177.8	177.8	177.8	177.8	177.1	177.4	178.1	177.4	177.1	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	4.1	4.6	5.1	6.8	9.2	11.3	11.6	11.3	10.9	10.3	10.9
92.5°	14.4	16.2	18.1	27.3	40.3	52.0	52.6	44.1	34.5	29.4	25.6
95°	25.3	29.4	33.5	49.2	79.0	118.6	134.0	117.2	89.6	68.7	54.4
97.5°	34.2	38.8	43.4	63.6	104.9	168.9	218.4	220.1	183.2	146.3	111.8
100°	42.7	47.5	52.3	70.4	112.1	186.0	270.0	319.3	312.1	269.7	222.9
102.5°	50.6	55.4	60.2	76.6	112.5	179.5	271.8	356.2	396.5	395.2	364.0
105°	58.1	62.9	67.7	83.7	114.2	170.6	253.3	344.2	415.3	453.9	458.4
107.5°	65.6	70.4	75.2	90.9	117.9	165.8	236.2	318.9	395.2	452.6	486.1
110°	73.2	78.2	83.1	98.1	122.7	164.4	224.6	295.3	367.5	428.7	472.4

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	80.3	85.4	90.6	104.9	127.8	164.8	217.1	278.9	342.2	400.3	447.8
115°	88.2	92.8	97.4	112.1	133.0	166.1	211.9	265.9	322.3	375.0	419.8
117.5°	95.4	100.2	104.9	118.6	138.4	168.2	209.2	257.1	305.9	353.1	394.8
120°	102.5	107.3	112.1	125.5	143.9	170.2	206.8	250.2	294.3	336.7	372.9
122.5°	109.7	114.6	119.6	131.9	148.7	172.6	205.4	244.4	285.1	323.0	356.9
125°	116.6	121.4	126.1	138.4	153.8	175.0	203.7	238.9	276.2	311.4	341.5
127.5°	122.7	127.6	132.6	144.6	158.6	177.4	202.7	233.8	267.3	299.8	328.5
130°	128.5	133.3	138.1	150.1	163.1	180.1	202.0	228.7	258.8	288.2	315.2
132.5°	134.0	138.8	143.6	154.8	167.5	182.9	201.7	224.6	250.6	277.2	301.5
135°	138.8	143.6	148.4	159.3	171.3	184.9	201.3	220.8	243.0	265.6	288.2
137.5°	143.2	147.6	152.1	163.1	174.3	187.0	201.3	218.1	236.9	256.4	274.8
140°	147.0	151.4	155.9	166.1	176.7	188.3	201.0	215.7	231.1	247.5	263.2
142.5°	150.4	154.5	158.6	168.5	178.8	189.4	201.0	213.3	226.3	239.6	252.6
145°	154.2	158.0	161.7	170.9	180.5	190.1	200.3	211.2	221.8	233.1	243.7
147.5°	157.2	160.6	164.1	173.0	181.5	190.4	199.3	209.2	218.4	227.7	236.2
150°	160.3	163.4	166.5	174.3	182.2	190.1	198.3	206.5	214.7	222.2	229.4
152.5°	163.4	166.2	168.9	175.7	182.5	189.4	196.6	204.1	210.9	217.7	223.6
155°	166.1	168.7	171.3	177.1	182.9	188.7	194.5	201.0	207.5	213.0	218.1
157.5°	168.5	170.8	173.0	178.1	182.9	187.3	192.4	198.3	203.4	208.2	212.6
160°	170.9	172.8	174.7	178.8	182.9	186.3	190.4	195.2	199.6	203.4	207.1
162.5°	173.0	174.4	175.7	179.1	182.5	185.3	188.7	192.4	195.9	198.9	202.0
165°	174.3	175.4	176.4	179.5	181.9	183.9	186.3	189.4	192.1	194.5	196.9
167.5°	175.7	176.4	177.1	179.5	181.5	182.5	184.2	186.3	188.3	190.4	192.1
170°	176.4	176.9	177.4	179.1	180.8	181.5	182.5	183.9	185.6	186.6	188.0
172.5°	177.1	177.4	177.8	178.8	179.8	180.1	180.5	181.5	182.5	183.2	184.2
175°	177.4	177.6	177.8	178.4	179.1	178.8	179.1	179.5	180.5	180.8	181.2
177.5°	177.8	177.8	177.8	178.1	178.8	178.1	177.8	178.1	178.8	178.8	179.1
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	11.1	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.1
92.5°	24.2	22.9	22.6	21.2	21.5	20.9	21.5	21.2	22.6	22.9	24.2
95°	50.6	46.8	42.4	39.7	38.6	39.0	38.6	39.7	42.4	46.8	50.6
97.5°	101.6	91.3	77.9	71.1	67.3	65.3	67.3	71.1	77.9	91.3	101.6
100°	202.2	181.5	153.1	138.4	128.5	122.4	128.5	138.4	153.1	181.5	202.2
102.5°	341.8	319.6	288.2	260.5	247.5	238.6	247.5	260.5	288.2	319.6	341.8
105°	452.8	447.1	425.9	404.7	390.0	385.2	390.0	404.7	425.9	447.1	452.8
107.5°	493.0	499.8	499.4	496.3	491.9	484.0	491.9	496.3	499.4	499.8	493.0
110°	486.4	500.4	515.1	521.6	524.7	524.4	524.7	521.6	515.1	500.4	486.4

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	464.4	481.0	502.8	514.8	521.3	523.7	521.3	514.8	502.8	481.0	464.4
115°	437.4	455.0	479.2	495.0	503.9	506.9	503.9	495.0	479.2	455.0	437.4
117.5°	411.6	428.3	453.3	470.0	479.2	481.6	479.2	470.0	453.3	428.3	411.6
120°	388.4	404.0	428.0	444.0	453.9	457.4	453.9	444.0	428.0	404.0	388.4
122.5°	370.5	384.2	405.1	420.8	429.3	432.1	429.3	420.8	405.1	384.2	370.5
125°	354.3	367.1	386.9	399.9	408.5	411.2	408.5	399.9	386.9	367.1	354.3
127.5°	340.4	352.4	369.9	382.2	389.7	391.7	389.7	382.2	369.9	352.4	340.4
130°	326.4	337.7	354.5	366.1	372.9	375.7	372.9	366.1	354.5	337.7	326.4
132.5°	311.9	322.3	338.8	350.4	356.5	358.9	356.5	350.4	338.8	322.3	311.9
135°	297.8	307.3	322.0	333.3	339.4	340.8	339.4	333.3	322.0	307.3	297.8
137.5°	283.4	291.9	305.9	315.8	321.3	323.4	321.3	315.8	305.9	291.9	283.4
140°	270.7	278.2	289.2	298.1	303.2	305.3	303.2	298.1	289.2	278.2	270.7
142.5°	258.6	264.6	274.8	282.7	287.1	287.1	287.1	282.7	274.8	264.6	258.6
145°	248.6	253.6	261.8	267.7	271.1	272.1	271.1	267.7	261.8	253.6	248.6
147.5°	240.0	243.7	250.9	255.7	258.1	258.8	258.1	255.7	250.9	243.7	240.0
150°	232.4	235.5	240.6	244.7	246.8	247.1	246.8	244.7	240.6	235.5	232.4
152.5°	226.2	228.7	232.4	235.9	237.2	237.2	237.2	235.9	232.4	228.7	226.2
155°	220.0	221.8	225.6	228.0	229.4	228.7	229.4	228.0	225.6	221.8	220.0
157.5°	214.2	215.7	218.4	220.5	221.2	221.2	221.2	220.5	218.4	215.7	214.2
160°	208.3	209.5	211.9	213.6	214.0	214.0	214.0	213.6	211.9	209.5	208.3
162.5°	202.8	203.7	206.1	207.1	207.5	207.1	207.5	207.1	206.1	203.7	202.8
165°	197.6	198.3	199.6	201.0	201.0	200.7	201.0	201.0	199.6	198.3	197.6
167.5°	192.8	193.5	194.2	194.8	194.8	194.5	194.8	194.8	194.2	193.5	192.8
170°	188.4	188.7	189.0	190.1	189.7	189.0	189.7	190.1	189.0	188.7	188.4
172.5°	184.4	184.6	184.9	185.3	184.9	184.6	184.9	185.3	184.9	184.6	184.4
175°	181.4	181.5	181.5	181.9	181.5	180.8	181.5	181.9	181.5	181.5	181.4
177.5°	179.1	179.1	179.1	179.1	178.8	178.1	178.8	179.1	179.1	179.1	179.1
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	10.9	10.3	10.9	11.3	11.6	11.3	9.2	6.8	5.1	4.6	4.1
92.5°	25.6	29.4	34.5	44.1	52.6	52.0	40.3	27.3	18.1	16.2	14.4
95°	54.4	68.7	89.6	117.2	134.0	118.6	79.0	49.2	33.5	29.4	25.3
97.5°	111.8	146.3	183.2	220.1	218.4	168.9	104.9	63.6	43.4	38.8	34.2
100°	222.9	269.7	312.1	319.3	270.0	186.0	112.1	70.4	52.3	47.5	42.7
102.5°	364.0	395.2	396.5	356.2	271.8	179.5	112.5	76.6	60.2	55.4	50.6
105°	458.4	453.9	415.3	344.2	253.3	170.6	114.2	83.7	67.7	62.9	58.1
107.5°	486.1	452.6	395.2	318.9	236.2	165.8	117.9	90.9	75.2	70.4	65.6
110°	472.4	428.7	367.5	295.3	224.6	164.4	122.7	98.1	83.1	78.2	73.2

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	447.8	400.3	342.2	278.9	217.1	164.8	127.8	104.9	90.6	85.4	80.3
115°	419.8	375.0	322.3	265.9	211.9	166.1	133.0	112.1	97.4	92.8	88.2
117.5°	394.8	353.1	305.9	257.1	209.2	168.2	138.4	118.6	104.9	100.2	95.4
120°	372.9	336.7	294.3	250.2	206.8	170.2	143.9	125.5	112.1	107.3	102.5
122.5°	356.9	323.0	285.1	244.4	205.4	172.6	148.7	131.9	119.6	114.6	109.7
125°	341.5	311.4	276.2	238.9	203.7	175.0	153.8	138.4	126.1	121.4	116.6
127.5°	328.5	299.8	267.3	233.8	202.7	177.4	158.6	144.6	132.6	127.6	122.7
130°	315.2	288.2	258.8	228.7	202.0	180.1	163.1	150.1	138.1	133.3	128.5
132.5°	301.5	277.2	250.6	224.6	201.7	182.9	167.5	154.8	143.6	138.8	134.0
135°	288.2	265.6	243.0	220.8	201.3	184.9	171.3	159.3	148.4	143.6	138.8
137.5°	274.8	256.4	236.9	218.1	201.3	187.0	174.3	163.1	152.1	147.6	143.2
140°	263.2	247.5	231.1	215.7	201.0	188.3	176.7	166.1	155.9	151.4	147.0
142.5°	252.6	239.6	226.3	213.3	201.0	189.4	178.8	168.5	158.6	154.5	150.4
145°	243.7	233.1	221.8	211.2	200.3	190.1	180.5	170.9	161.7	158.0	154.2
147.5°	236.2	227.7	218.4	209.2	199.3	190.4	181.5	173.0	164.1	160.6	157.2
150°	229.4	222.2	214.7	206.5	198.3	190.1	182.2	174.3	166.5	163.4	160.3
152.5°	223.6	217.7	210.9	204.1	196.6	189.4	182.5	175.7	168.9	166.2	163.4
155°	218.1	213.0	207.5	201.0	194.5	188.7	182.9	177.1	171.3	168.7	166.1
157.5°	212.6	208.2	203.4	198.3	192.4	187.3	182.9	178.1	173.0	170.8	168.5
160°	207.1	203.4	199.6	195.2	190.4	186.3	182.9	178.8	174.7	172.8	170.9
162.5°	202.0	198.9	195.9	192.4	188.7	185.3	182.5	179.1	175.7	174.4	173.0
165°	196.9	194.5	192.1	189.4	186.3	183.9	181.9	179.5	176.4	175.4	174.3
167.5°	192.1	190.4	188.3	186.3	184.2	182.5	181.5	179.5	177.1	176.4	175.7
170°	188.0	186.6	185.6	183.9	182.5	181.5	180.8	179.1	177.4	176.9	176.4
172.5°	184.2	183.2	182.5	181.5	180.5	180.1	179.8	178.8	177.8	177.4	177.1
175°	181.2	180.8	180.5	179.5	179.1	178.8	179.1	178.4	177.8	177.6	177.4
177.5°	179.1	178.8	178.8	178.1	177.8	178.1	178.8	178.1	177.8	177.8	177.8
180°	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8	177.8

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	3.4	2.7	1.4	0.3
92.5°	11.6	9.9	7.2	5.1
95°	19.8	16.7	13.3	12.0
97.5°	28.0	23.6	19.8	17.8
100°	35.9	30.4	27.3	26.3
102.5°	43.4	37.9	34.9	34.2
105°	50.6	45.5	43.1	41.7
107.5°	58.1	53.3	50.9	49.9
110°	66.0	61.5	59.5	58.1

TEST NUMBER: P1009290

CATALOG NUMBER: S122DIP-B675D330UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	73.5	69.4	67.0	65.6
115°	81.4	77.3	75.2	73.5
117.5°	88.9	85.1	83.1	81.7
120°	95.7	92.6	90.6	89.2
122.5°	102.9	99.5	97.4	96.4
125°	109.7	105.6	103.6	102.5
127.5°	116.2	111.8	109.0	107.7
130°	121.7	116.9	113.5	112.1
132.5°	126.8	121.7	117.9	116.2
135°	130.9	125.8	121.7	120.3
137.5°	135.4	129.9	125.8	124.1
140°	139.5	134.0	129.9	128.5
142.5°	143.2	137.8	134.0	133.0
145°	147.3	142.2	138.8	137.4
147.5°	151.4	146.6	143.2	142.2
150°	155.2	150.7	148.0	147.0
152.5°	158.6	154.8	152.1	151.8
155°	162.4	158.6	156.6	156.2
157.5°	165.4	162.0	160.3	160.0
160°	168.2	165.4	164.1	163.7
162.5°	170.6	168.5	167.2	167.5
165°	172.6	170.6	169.9	170.2
167.5°	174.3	173.0	172.3	172.6
170°	175.7	174.7	174.3	175.0
172.5°	176.7	175.7	176.0	176.4
175°	177.4	176.7	177.1	177.4
177.5°	177.8	177.1	177.4	178.1
180°	177.8	177.8	177.8	177.8

(END OF REPORT)