

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009299

Luminaire Tested: S122DIP-B675D530UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009299
REPORT IS A COMBINATION OF REPORTS P984540 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB27-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4973.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	58	56	55
2	92	85	79	74	85	79	74	70	69	65	62	60	57	55	51	49	47
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	38	36
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	34	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20950	20950	20950	20950
5°	21000	22337	21081	17772
10°	20756	24384	20887	14652
15°	20252	25721	20534	12342
20°	19937	24150	19937	10726
25°	19302	20747	19390	9593
30°	18256	16309	18604	8689
35°	17330	11278	17620	7951
40°	16266	8515	16450	7360
45°	14952	6997	15196	6725
50°	13817	6141	13841	6156
55°	12524	5233	12604	5539
60°	11143	4370	11297	4833
65°	9908	3554	10089	4127
70°	8679	2790	8900	3329
75°	7283	2025	7569	2414
80°	5684	1282	6092	1434
85°	3729	647	4026	477

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21656 cd/sqm

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	2.5
10°-20°	366.9	7.4
20°-30°	532.5	10.7
30°-40°	561.3	11.3
40°-50°	496.7	10.0
50°-60°	396.6	8.0
60°-70°	269.4	5.4
70°-80°	137.8	2.8
80°-90°	34.5	0.7
90°-100°	114.8	2.3
100°-110°	404.3	8.1
110°-120°	424.7	8.5
120°-130°	349.4	7.0
130°-140°	280.7	5.6
140°-150°	212.0	4.3
150°-160°	149.0	3.0
160°-170°	87.7	1.8
170°-180°	28.5	0.6
0°-30°	1025.5	20.6
0°-40°	1586.8	31.9
0°-60°	2480.2	49.9
0°-90°	2921.9	58.8
90°-120°	943.8	19.0
90°-150°	1785.8	35.9
90°-180°	2051.0	41.2
0°-180°	4973.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1324	1324	1324	1324	1324	
5°	1324	1478	1330	1176	1324	126
15°	1244	1817	1261	872	1244	351
25°	1118	1514	1123	700	1118	511
35°	912	824	928	581	912	571
45°	685	496	696	477	685	531
55°	470	349	473	369	470	419
65°	279	215	284	249	279	277
75°	130	106	135	126	130	140
85°	26	28	28	20	26	31
90°	1	19	1	19	1	3
95°	20	65	20	65	20	20
105°	69	638	69	638	69	73
115°	122	840	122	840	122	121
125°	170	681	170	681	170	151
135°	199	565	199	565	199	154
145°	228	451	228	451	228	143
155°	259	379	259	379	259	119
165°	282	332	282	332	282	80
175°	294	300	294	300	294	28
180°	294	294	294	294	294	

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1330.6	1333.7	1338.7	1339.8	1349.9	1358.1	1367.2	1367.2	1370.3	1369.3	1361.1
5°	1324.5	1333.7	1346.9	1358.1	1376.4	1384.5	1396.7	1405.9	1414.0	1420.1	1419.1
7.5°	1314.3	1330.6	1349.9	1371.3	1395.7	1409.9	1427.2	1443.5	1454.7	1464.9	1472.0
10°	1297.0	1324.5	1350.9	1379.4	1411.0	1430.3	1450.6	1472.0	1489.3	1508.6	1526.9
12.5°	1273.6	1313.3	1345.9	1383.5	1422.2	1443.5	1476.1	1492.3	1525.9	1574.7	1588.0
15°	1244.1	1298.0	1328.6	1376.4	1427.2	1444.5	1489.3	1515.7	1584.9	1615.4	1652.1
17.5°	1216.7	1276.7	1317.4	1372.3	1422.2	1455.7	1499.5	1553.4	1611.4	1655.1	1695.8
20°	1194.3	1252.3	1301.1	1362.1	1425.2	1467.9	1513.7	1578.8	1641.9	1686.6	1718.2
22.5°	1143.4	1217.7	1274.7	1342.8	1419.1	1478.1	1521.8	1593.1	1661.2	1688.7	1716.1
25°	1118.0	1182.1	1248.2	1325.5	1415.0	1485.2	1522.9	1602.2	1662.2	1672.4	1678.5
27.5°	1071.2	1143.4	1220.7	1309.2	1414.0	1473.0	1520.8	1593.1	1640.9	1633.8	1615.4
30°	1013.2	1101.7	1187.2	1282.8	1399.8	1463.9	1508.6	1574.7	1599.2	1562.5	1530.0
32.5°	970.5	1053.9	1148.5	1259.4	1383.5	1444.5	1488.3	1540.2	1545.2	1479.1	1424.2
35°	912.5	1005.1	1111.9	1228.9	1356.0	1411.0	1451.7	1483.2	1458.8	1366.2	1301.1
37.5°	860.6	952.2	1066.1	1185.1	1318.4	1372.3	1404.9	1409.9	1349.9	1268.5	1172.9
40°	803.7	898.3	1017.3	1142.4	1276.7	1323.5	1343.8	1328.6	1242.1	1147.5	1036.6
42.5°	746.7	840.3	968.4	1096.6	1223.8	1263.5	1271.6	1229.9	1124.1	1013.2	885.0
45°	684.6	782.3	910.5	1039.7	1162.7	1185.1	1186.1	1126.1	1001.0	885.0	766.0
47.5°	633.8	724.3	851.5	980.7	1084.4	1099.7	1093.6	1024.4	888.1	757.9	654.1
50°	577.8	664.3	790.4	917.6	1006.1	1010.2	994.9	896.2	763.0	643.9	561.5
52.5°	517.8	605.3	721.3	843.3	922.7	916.6	887.1	781.3	656.1	557.5	494.4
55°	470.0	547.3	656.1	775.2	831.1	813.8	781.3	673.4	574.8	491.3	436.4
57.5°	417.1	485.2	592.1	695.8	728.4	712.1	679.5	578.8	487.3	424.2	387.6
60°	367.2	429.3	522.9	609.4	634.8	617.5	579.8	489.3	423.2	370.3	342.8
62.5°	321.5	375.4	453.7	533.1	543.2	525.9	493.4	420.1	363.2	321.5	301.1
65°	278.7	329.6	392.7	452.7	461.8	443.5	410.0	357.1	309.3	282.8	263.5
67.5°	237.0	277.7	333.7	377.4	382.5	365.2	337.7	295.0	265.5	237.0	222.8
70°	200.4	230.9	274.7	310.3	312.3	296.0	281.8	243.1	220.7	200.4	189.2
72.5°	164.8	186.2	219.7	246.2	247.2	237.0	223.8	199.4	180.1	165.8	154.6
75°	130.2	148.5	168.9	192.3	191.2	183.1	172.9	157.7	141.4	132.2	127.2
77.5°	99.7	110.9	127.2	142.4	142.4	138.3	132.2	121.1	110.9	101.7	96.6
80°	71.2	78.3	91.6	96.6	98.7	97.7	92.6	84.4	80.4	73.2	71.2
82.5°	45.8	50.9	57.0	62.1	65.1	63.1	62.1	58.0	51.9	49.8	47.8
85°	26.4	28.5	31.5	34.6	35.6	34.6	36.6	33.6	30.5	30.5	29.5
87.5°	11.2	12.2	14.2	14.2	15.3	15.3	14.2	15.3	15.3	14.2	13.2
90°	0.6	2.3	4.5	5.7	6.8	7.6	8.5	11.3	15.3	18.7	19.3
92.5°	8.5	11.9	16.4	19.3	23.8	26.9	30.0	45.3	66.8	86.1	87.2
95°	19.8	22.1	27.8	32.9	41.9	48.7	55.5	81.6	130.8	196.5	222.0
97.5°	29.5	32.9	39.1	46.4	56.6	64.2	71.9	105.4	173.9	279.8	361.9
100°	43.6	45.3	50.4	59.5	70.8	78.8	86.7	116.7	185.8	308.1	447.5
102.5°	56.6	57.8	62.9	71.9	83.8	91.8	99.7	126.9	186.3	297.4	450.3
105°	69.1	71.4	75.3	83.8	96.3	104.2	112.1	138.8	189.2	282.6	419.7
107.5°	82.7	84.4	88.4	96.3	108.7	116.6	124.6	150.7	195.4	274.7	391.4
110°	96.3	98.6	102.0	109.3	121.2	129.4	137.6	162.6	203.3	272.4	372.1

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	108.7	111.0	115.0	121.8	133.1	141.6	150.1	173.9	211.8	273.0	359.7
115°	121.8	124.6	128.0	134.8	146.1	153.8	161.4	185.8	220.3	275.3	351.2
117.5°	135.4	137.6	141.0	147.3	158.0	166.0	173.9	196.5	229.4	278.7	346.6
120°	147.8	150.1	153.5	158.6	169.9	177.9	185.8	207.9	238.5	282.1	342.7
122.5°	159.7	161.4	164.8	170.5	181.8	190.0	198.2	218.6	246.4	286.0	340.4
125°	169.9	171.6	175.0	181.8	193.1	201.0	209.0	229.4	254.9	290.0	337.6
127.5°	178.4	180.7	185.2	192.6	203.3	211.6	219.8	239.6	262.8	294.0	335.9
130°	185.8	188.0	193.7	201.6	213.0	220.9	228.8	248.7	270.2	298.5	334.7
132.5°	192.6	195.4	201.6	210.1	222.0	230.0	237.9	256.6	277.5	303.0	334.2
135°	199.4	201.6	208.4	216.9	230.0	237.9	245.8	263.9	283.8	306.4	333.6
137.5°	205.6	208.4	215.2	224.3	237.3	244.6	252.0	270.2	288.9	309.8	333.6
140°	213.0	215.2	222.0	231.1	243.6	251.0	258.3	275.3	292.8	312.1	333.0
142.5°	220.3	222.0	228.3	237.3	249.2	256.0	262.8	279.2	296.2	313.8	333.0
145°	227.7	230.0	235.6	244.1	255.4	261.6	267.9	283.2	299.1	314.9	331.9
147.5°	235.6	237.3	243.0	250.9	260.5	266.2	271.9	286.6	300.8	315.5	330.2
150°	243.6	245.3	249.8	257.1	265.6	270.7	275.8	288.9	301.9	314.9	328.5
152.5°	251.5	252.0	256.6	262.8	270.7	275.2	279.8	291.1	302.5	313.8	325.7
155°	258.8	259.4	262.8	269.0	275.3	279.6	283.8	293.4	303.0	312.7	322.3
157.5°	265.1	265.6	268.5	274.1	279.2	282.9	286.6	295.1	303.0	310.4	318.9
160°	271.3	271.9	274.1	278.7	283.2	286.3	289.4	296.2	303.0	308.7	315.5
162.5°	277.5	277.0	279.2	282.6	286.6	288.8	291.1	296.8	302.5	307.0	312.7
165°	282.1	281.5	282.6	286.0	288.9	290.6	292.3	297.4	301.3	304.7	308.7
167.5°	286.0	285.5	286.6	288.9	291.1	292.2	293.4	297.4	300.8	302.5	305.3
170°	290.0	288.9	289.4	291.1	292.3	293.2	294.0	296.8	299.6	300.8	302.5
172.5°	292.3	291.7	291.1	292.8	293.4	294.0	294.5	296.2	297.9	298.5	299.1
175°	294.0	293.4	292.8	294.0	294.0	294.2	294.5	295.7	296.8	296.2	296.8
177.5°	295.1	294.0	293.4	294.5	294.5	294.5	294.5	295.1	296.2	295.1	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1375.4	1376.4	1378.4	1388.6	1393.7	1394.7	1390.6	1399.8	1402.8	1399.8	1397.7
5°	1440.5	1446.6	1458.8	1472.0	1471.0	1472.0	1478.1	1484.2	1486.2	1478.1	1481.2
7.5°	1497.4	1509.6	1522.9	1543.2	1543.2	1553.4	1557.5	1562.5	1574.7	1568.6	1566.6
10°	1562.5	1578.8	1603.2	1635.8	1636.8	1647.0	1657.1	1673.4	1678.5	1674.4	1676.5
12.5°	1643.9	1675.5	1677.5	1713.1	1729.4	1731.4	1747.7	1744.6	1754.8	1754.8	1772.1
15°	1679.5	1728.4	1755.8	1790.4	1800.6	1788.4	1801.6	1815.8	1816.9	1816.9	1815.8
17.5°	1743.6	1762.9	1790.4	1808.7	1812.8	1812.8	1813.8	1819.9	1815.8	1807.7	1813.8
20°	1756.8	1765.0	1775.2	1773.1	1775.2	1765.0	1754.8	1744.6	1745.7	1740.6	1755.8
22.5°	1732.4	1730.4	1707.0	1691.7	1691.7	1671.4	1652.1	1642.9	1633.8	1636.8	1641.9
25°	1671.4	1639.9	1611.4	1589.0	1583.9	1551.4	1524.9	1516.8	1501.5	1513.7	1515.7
27.5°	1573.7	1538.1	1492.3	1473.0	1446.6	1433.3	1415.0	1390.6	1359.1	1377.4	1374.3
30°	1469.0	1416.1	1378.4	1331.6	1289.9	1286.9	1252.3	1211.6	1195.3	1195.3	1204.5
32.5°	1352.0	1281.8	1226.8	1160.7	1120.0	1102.7	1061.0	1020.3	1029.5	999.0	1010.2
35°	1215.6	1123.1	1053.9	989.8	959.3	938.9	885.0	862.7	838.2	824.0	850.4
37.5°	1085.4	978.6	890.1	819.9	808.7	772.1	735.5	721.3	707.0	713.1	712.1
40°	926.7	832.1	752.8	697.9	678.5	661.2	636.8	619.5	610.4	615.5	616.5
42.5°	783.3	704.0	645.0	606.3	590.0	577.8	565.6	551.4	548.3	548.3	552.4
45°	672.4	607.3	567.6	536.1	527.0	517.8	508.6	502.5	500.5	496.4	499.5
47.5°	583.9	532.0	507.6	484.2	474.1	472.0	463.9	460.8	456.8	455.7	456.8
50°	509.7	477.1	454.7	441.5	434.4	431.3	427.3	421.2	419.1	424.2	422.2
52.5°	457.8	427.3	415.0	401.8	397.8	393.7	387.6	388.6	387.6	385.5	385.5
55°	405.9	386.6	374.4	364.2	363.2	359.1	354.0	352.0	351.0	348.9	352.0
57.5°	364.2	348.9	337.7	328.6	324.5	324.5	319.4	315.4	315.4	314.3	315.4
60°	322.5	307.2	300.1	290.9	287.9	286.9	283.8	281.8	278.7	278.7	278.7
62.5°	283.8	271.6	263.5	255.3	256.4	251.3	247.2	245.2	245.2	246.2	246.2
65°	247.2	239.1	228.9	221.8	219.7	218.7	216.7	215.7	212.6	214.6	214.6
67.5°	213.6	202.4	196.3	193.3	190.2	189.2	187.2	185.1	184.1	183.1	185.1
70°	180.1	170.9	165.8	163.8	160.7	159.7	158.7	155.6	156.7	157.7	158.7
72.5°	149.5	141.4	140.4	134.3	134.3	134.3	130.2	132.2	131.2	129.2	131.2
75°	118.0	113.9	111.9	108.8	109.9	108.8	107.8	104.8	104.8	105.8	106.8
77.5°	93.6	89.5	88.5	85.5	83.4	85.5	83.4	82.4	82.4	83.4	83.4
80°	69.2	67.1	64.1	64.1	64.1	63.1	63.1	63.1	62.1	61.0	62.1
82.5°	45.8	45.8	44.8	43.7	44.8	42.7	43.7	43.7	43.7	43.7	43.7
85°	29.5	28.5	28.5	27.5	27.5	27.5	28.5	26.4	26.4	27.5	27.5
87.5°	13.2	13.2	13.2	14.2	13.2	13.2	13.2	14.2	13.2	13.2	13.2
90°	18.7	18.1	17.0	18.1	18.4	18.7	18.7	18.7	18.7	18.7	18.7
92.5°	73.1	57.2	48.7	42.5	40.2	37.9	37.4	35.1	35.7	34.6	35.7
95°	194.3	148.4	113.8	90.1	83.8	77.6	70.2	65.7	64.0	64.6	64.0
97.5°	364.8	303.6	242.4	185.2	168.2	151.2	129.1	117.8	111.6	108.2	111.6
100°	529.0	517.1	446.9	369.3	335.0	300.8	253.7	229.4	213.0	202.8	213.0
102.5°	590.2	657.0	654.8	603.2	566.4	529.6	477.5	431.6	410.1	395.3	410.1
105°	570.4	688.2	752.2	759.5	750.2	740.9	705.7	670.6	646.3	638.3	646.3
107.5°	528.5	654.8	749.9	805.4	816.8	828.1	827.5	822.4	815.1	802.0	815.1
110°	489.4	608.9	710.3	782.8	806.0	829.2	853.6	864.3	869.4	868.9	869.4

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	462.2	567.0	663.3	742.0	769.4	796.9	833.2	853.0	863.8	867.7	863.8
115°	440.7	534.1	621.3	695.5	724.7	753.9	794.1	820.1	834.9	840.0	834.9
117.5°	425.9	506.9	585.1	654.2	682.0	709.7	751.0	778.8	794.1	798.1	794.1
120°	414.6	487.7	557.9	617.9	643.7	669.5	709.1	735.8	752.2	757.8	752.2
122.5°	405.0	472.4	535.2	591.3	614.0	636.6	671.2	697.2	711.4	715.9	711.4
125°	395.9	457.7	516.0	565.8	587.0	608.3	641.2	662.7	676.9	681.4	676.9
127.5°	387.4	442.9	496.7	544.3	564.2	584.0	612.8	633.2	645.7	649.1	645.7
130°	378.9	428.8	477.5	522.2	540.9	559.6	587.4	606.6	617.9	622.5	617.9
132.5°	372.1	415.2	459.4	499.6	516.8	534.1	561.3	580.6	590.8	594.7	590.8
135°	365.9	402.7	440.1	477.5	493.4	509.2	533.6	552.2	562.4	564.7	562.4
137.5°	361.4	392.5	424.8	455.4	469.6	483.7	506.9	523.4	532.4	535.8	532.4
140°	357.4	382.9	410.1	436.1	448.6	461.1	479.2	493.9	502.4	505.8	502.4
142.5°	353.4	375.0	397.0	418.6	428.5	438.4	455.4	468.4	475.8	475.8	475.8
145°	350.0	367.6	386.3	403.8	412.0	420.3	433.9	443.5	449.2	450.9	449.2
147.5°	346.6	361.9	377.2	391.4	397.6	403.8	415.7	423.7	427.6	428.8	427.6
150°	342.1	355.7	368.2	380.1	385.2	390.3	398.7	405.5	408.9	409.5	408.9
152.5°	338.1	349.5	360.8	370.4	374.6	378.9	385.2	390.8	393.1	393.1	393.1
155°	333.0	343.8	352.9	361.4	364.5	367.6	373.8	377.8	380.1	378.9	380.1
157.5°	328.5	337.0	344.9	352.3	354.8	357.4	361.9	365.3	366.5	366.5	366.5
160°	323.4	330.8	337.0	343.2	345.2	347.2	351.2	354.0	354.6	354.6	354.6
162.5°	318.9	324.5	329.6	334.7	336.2	337.6	341.5	343.2	343.8	343.2	343.8
165°	313.8	318.3	322.3	326.2	327.4	328.5	330.8	333.0	333.0	332.5	333.0
167.5°	308.7	312.1	315.5	318.3	319.5	320.6	321.7	322.8	322.8	322.3	322.8
170°	304.7	307.6	309.3	311.5	312.1	312.7	313.2	314.9	314.4	313.2	314.4
172.5°	300.8	302.5	303.6	305.3	305.6	305.9	306.4	307.0	306.4	305.9	306.4
175°	297.4	299.1	299.6	300.2	300.5	300.8	300.8	301.3	300.8	299.6	300.8
177.5°	295.1	296.2	296.2	296.8	296.8	296.8	296.8	296.8	296.2	295.1	296.2
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1402.8	1395.7	1389.6	1390.6	1395.7	1391.6	1381.5	1368.2	1363.2	1357.1	1363.2
5°	1487.3	1481.2	1469.0	1470.0	1466.9	1462.8	1446.6	1426.2	1426.2	1409.9	1407.9
7.5°	1570.7	1561.5	1553.4	1551.4	1540.2	1532.0	1517.8	1489.3	1478.1	1458.8	1447.6
10°	1664.3	1657.1	1648.0	1636.8	1630.7	1616.5	1593.1	1551.4	1531.0	1504.6	1485.2
12.5°	1758.9	1757.9	1737.5	1715.1	1714.1	1691.7	1675.5	1619.5	1592.0	1556.4	1510.7
15°	1818.9	1813.8	1802.6	1791.4	1794.5	1770.1	1733.4	1667.3	1649.0	1606.3	1557.5
17.5°	1817.9	1817.9	1814.8	1812.8	1809.7	1802.6	1782.3	1738.5	1709.0	1655.1	1609.3
20°	1759.9	1773.1	1776.2	1775.2	1785.3	1790.4	1789.4	1761.9	1738.5	1690.7	1643.9
22.5°	1643.9	1674.4	1687.7	1695.8	1717.2	1728.4	1754.8	1744.6	1738.5	1702.9	1663.3
25°	1536.1	1546.3	1585.9	1588.0	1617.5	1644.9	1671.4	1688.7	1711.1	1697.8	1664.3
27.5°	1396.7	1420.1	1448.6	1470.0	1476.1	1532.0	1575.8	1608.3	1659.2	1663.3	1652.1
30°	1239.0	1250.2	1297.0	1325.5	1358.1	1398.8	1461.8	1517.8	1563.6	1605.3	1619.5
32.5°	1046.8	1092.6	1120.0	1154.6	1183.1	1255.3	1332.6	1404.9	1457.8	1528.0	1558.5
35°	870.8	906.4	953.2	967.4	1019.3	1080.4	1181.1	1273.6	1354.0	1425.2	1487.3
37.5°	725.3	753.8	803.7	826.0	856.5	934.9	1019.3	1134.3	1230.9	1318.4	1395.7
40°	625.6	647.0	684.6	691.7	717.2	788.4	856.5	964.4	1092.6	1210.6	1295.0
42.5°	557.5	567.6	593.1	602.2	618.5	666.3	727.4	829.1	948.1	1070.2	1189.2
45°	508.6	515.8	531.0	539.2	559.5	580.9	630.7	712.1	805.7	928.8	1057.0
47.5°	464.9	474.1	480.2	485.2	496.4	519.8	552.4	612.4	701.9	814.8	938.9
50°	428.3	431.3	442.5	443.5	450.7	465.9	496.4	533.1	604.3	695.8	815.9
52.5°	391.7	394.7	401.8	408.9	412.0	424.2	444.6	475.1	528.0	600.2	707.0
55°	355.0	359.1	366.2	371.3	374.4	384.5	396.7	426.2	467.9	518.8	606.3
57.5°	318.4	327.6	329.6	332.7	337.7	348.9	360.1	377.4	410.0	456.8	520.8
60°	283.8	286.9	294.0	297.0	302.1	308.2	322.5	335.7	359.1	395.7	453.7
62.5°	248.2	255.3	258.4	261.4	265.5	272.6	281.8	296.0	316.4	345.9	391.7
65°	217.7	218.7	224.8	228.9	233.0	238.0	247.2	260.4	272.6	300.1	333.7
67.5°	188.2	190.2	192.3	196.3	201.4	206.5	214.6	221.8	237.0	255.3	281.8
70°	159.7	159.7	164.8	167.9	166.8	172.9	179.0	187.2	198.4	215.7	237.0
72.5°	134.3	133.3	137.3	138.3	140.4	144.5	148.5	156.7	162.8	176.0	192.3
75°	106.8	108.8	110.9	110.9	113.9	117.0	121.1	125.1	132.2	140.4	152.6
77.5°	84.4	84.4	86.5	87.5	90.5	89.5	93.6	97.7	102.7	109.9	119.0
80°	62.1	64.1	64.1	64.1	65.1	66.1	70.2	73.2	76.3	81.4	85.5
82.5°	43.7	43.7	45.8	45.8	45.8	47.8	47.8	48.8	50.9	53.9	57.0
85°	27.5	27.5	27.5	28.5	27.5	28.5	30.5	29.5	30.5	32.6	32.6
87.5°	13.2	13.2	13.2	13.2	13.2	14.2	13.2	14.2	15.3	15.3	15.3
90°	18.7	18.7	18.7	18.4	18.1	17.0	18.1	18.7	19.3	18.7	15.3
92.5°	35.1	37.4	37.9	40.2	42.5	48.7	57.2	73.1	87.2	86.1	66.8
95°	65.7	70.2	77.6	83.8	90.1	113.8	148.4	194.3	222.0	196.5	130.8
97.5°	117.8	129.1	151.2	168.2	185.2	242.4	303.6	364.8	361.9	279.8	173.9
100°	229.4	253.7	300.8	335.0	369.3	446.9	517.1	529.0	447.5	308.1	185.8
102.5°	431.6	477.5	529.6	566.4	603.2	654.8	657.0	590.2	450.3	297.4	186.3
105°	670.6	705.7	740.9	750.2	759.5	752.2	688.2	570.4	419.7	282.6	189.2
107.5°	822.4	827.5	828.1	816.8	805.4	749.9	654.8	528.5	391.4	274.7	195.4
110°	864.3	853.6	829.2	806.0	782.8	710.3	608.9	489.4	372.1	272.4	203.3

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	853.0	833.2	796.9	769.4	742.0	663.3	567.0	462.2	359.7	273.0	211.8
115°	820.1	794.1	753.9	724.7	695.5	621.3	534.1	440.7	351.2	275.3	220.3
117.5°	778.8	751.0	709.7	682.0	654.2	585.1	506.9	425.9	346.6	278.7	229.4
120°	735.8	709.1	669.5	643.7	617.9	557.9	487.7	414.6	342.7	282.1	238.5
122.5°	697.2	671.2	636.6	614.0	591.3	535.2	472.4	405.0	340.4	286.0	246.4
125°	662.7	641.2	608.3	587.0	565.8	516.0	457.7	395.9	337.6	290.0	254.9
127.5°	633.2	612.8	584.0	564.2	544.3	496.7	442.9	387.4	335.9	294.0	262.8
130°	606.6	587.4	559.6	540.9	522.2	477.5	428.8	378.9	334.7	298.5	270.2
132.5°	580.6	561.3	534.1	516.8	499.6	459.4	415.2	372.1	334.2	303.0	277.5
135°	552.2	533.6	509.2	493.4	477.5	440.1	402.7	365.9	333.6	306.4	283.8
137.5°	523.4	506.9	483.7	469.6	455.4	424.8	392.5	361.4	333.6	309.8	288.9
140°	493.9	479.2	461.1	448.6	436.1	410.1	382.9	357.4	333.0	312.1	292.8
142.5°	468.4	455.4	438.4	428.5	418.6	397.0	375.0	353.4	333.0	313.8	296.2
145°	443.5	433.9	420.3	412.0	403.8	386.3	367.6	350.0	331.9	314.9	299.1
147.5°	423.7	415.7	403.8	397.6	391.4	377.2	361.9	346.6	330.2	315.5	300.8
150°	405.5	398.7	390.3	385.2	380.1	368.2	355.7	342.1	328.5	314.9	301.9
152.5°	390.8	385.2	378.9	374.6	370.4	360.8	349.5	338.1	325.7	313.8	302.5
155°	377.8	373.8	367.6	364.5	361.4	352.9	343.8	333.0	322.3	312.7	303.0
157.5°	365.3	361.9	357.4	354.8	352.3	344.9	337.0	328.5	318.9	310.4	303.0
160°	354.0	351.2	347.2	345.2	343.2	337.0	330.8	323.4	315.5	308.7	303.0
162.5°	343.2	341.5	337.6	336.2	334.7	329.6	324.5	318.9	312.7	307.0	302.5
165°	333.0	330.8	328.5	327.4	326.2	322.3	318.3	313.8	308.7	304.7	301.3
167.5°	322.8	321.7	320.6	319.5	318.3	315.5	312.1	308.7	305.3	302.5	300.8
170°	314.9	313.2	312.7	312.1	311.5	309.3	307.6	304.7	302.5	300.8	299.6
172.5°	307.0	306.4	305.9	305.6	305.3	303.6	302.5	300.8	299.1	298.5	297.9
175°	301.3	300.8	300.8	300.5	300.2	299.6	299.1	297.4	296.8	296.2	296.8
177.5°	296.8	296.8	296.8	296.8	296.8	296.2	296.2	295.1	294.5	295.1	296.2
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1358.1	1353.0	1349.9	1352.0	1345.9	1330.6	1330.6	1335.7	1329.6	1323.5	1314.3
5°	1395.7	1385.5	1379.4	1378.4	1364.2	1339.8	1334.7	1329.6	1316.4	1302.1	1286.9
7.5°	1432.3	1414.0	1403.8	1396.7	1376.4	1344.8	1331.6	1320.4	1299.1	1277.7	1258.4
10°	1462.8	1436.4	1424.2	1413.0	1386.6	1346.9	1325.5	1305.2	1277.7	1250.2	1225.8
12.5°	1487.3	1456.7	1441.5	1425.2	1392.7	1340.8	1314.3	1281.8	1254.3	1217.7	1193.3
15°	1528.0	1464.9	1450.6	1435.4	1401.8	1330.6	1298.0	1261.4	1223.8	1175.0	1148.5
17.5°	1560.5	1476.1	1475.1	1442.5	1398.8	1326.5	1276.7	1228.9	1188.2	1139.4	1097.6
20°	1579.8	1493.4	1477.1	1443.5	1388.6	1299.1	1247.2	1194.3	1150.5	1091.5	1049.8
22.5°	1596.1	1517.8	1475.1	1434.4	1367.2	1289.9	1213.6	1163.8	1103.7	1039.7	1000.0
25°	1602.2	1522.9	1478.1	1431.3	1352.0	1263.5	1177.0	1123.1	1055.9	998.0	944.0
27.5°	1603.2	1521.8	1466.9	1418.1	1330.6	1228.9	1140.4	1083.4	1009.1	942.0	888.1
30°	1593.1	1510.7	1460.8	1407.9	1310.3	1197.3	1095.6	1032.5	953.2	886.1	830.1
32.5°	1562.5	1488.3	1447.6	1389.6	1283.8	1153.6	1052.9	982.7	899.3	833.2	779.2
35°	1511.7	1460.8	1416.1	1362.1	1249.2	1112.9	1010.2	927.8	843.3	780.3	729.4
37.5°	1448.6	1421.1	1379.4	1326.5	1209.5	1076.3	962.3	870.8	786.4	725.3	675.5
40°	1363.2	1370.3	1329.6	1281.8	1162.7	1026.4	900.3	812.8	733.5	676.5	627.7
42.5°	1270.6	1300.1	1276.7	1230.9	1110.9	971.5	854.5	757.9	680.6	621.6	580.9
45°	1170.9	1221.8	1207.5	1173.9	1057.0	913.5	789.4	695.8	627.7	570.7	535.1
47.5°	1062.0	1134.3	1134.3	1109.9	996.9	855.5	733.5	637.8	570.7	530.0	495.4
50°	951.2	1032.5	1045.8	1029.5	929.8	789.4	665.3	578.8	520.8	481.2	455.7
52.5°	835.2	929.8	954.2	946.1	858.6	726.3	609.4	524.9	472.0	437.4	415.0
55°	724.3	834.2	860.6	863.7	782.3	657.2	547.3	473.0	422.2	398.8	379.4
57.5°	619.5	725.3	754.8	759.9	705.0	594.1	489.3	424.2	378.4	359.1	343.8
60°	530.0	618.5	657.2	668.4	620.5	520.8	435.4	372.3	337.7	319.4	305.2
62.5°	456.8	528.0	568.7	571.7	550.3	456.8	379.4	326.5	297.0	280.8	273.6
65°	385.5	449.6	474.1	486.3	469.0	395.7	327.6	283.8	260.4	246.2	239.1
67.5°	328.6	369.3	389.6	405.9	388.6	333.7	278.7	243.1	225.8	211.6	207.5
70°	269.6	303.1	318.4	334.7	319.4	277.7	238.0	205.5	190.2	179.0	174.0
72.5°	215.7	242.1	256.4	266.5	257.4	222.8	190.2	167.9	156.7	148.5	145.5
75°	170.9	189.2	197.4	204.5	200.4	174.0	153.6	135.3	125.1	118.0	116.0
77.5°	130.2	143.4	152.6	154.6	149.5	132.2	115.0	103.8	95.6	91.6	89.5
80°	92.6	100.7	105.8	108.8	103.8	96.6	84.4	76.3	69.2	64.1	63.1
82.5°	62.1	66.1	70.2	69.2	67.1	61.0	53.9	49.8	46.8	42.7	42.7
85°	35.6	36.6	38.7	39.7	38.7	34.6	30.5	28.5	26.4	23.4	23.4
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.2	11.2	11.2	10.2	9.2
90°	11.3	8.5	7.6	6.8	5.7	4.5	2.3	0.6	2.3	4.5	5.7
92.5°	45.3	30.0	26.9	23.8	19.3	16.4	11.9	8.5	11.9	16.4	19.3
95°	81.6	55.5	48.7	41.9	32.9	27.8	22.1	19.8	22.1	27.8	32.9
97.5°	105.4	71.9	64.2	56.6	46.4	39.1	32.9	29.5	32.9	39.1	46.4
100°	116.7	86.7	78.8	70.8	59.5	50.4	45.3	43.6	45.3	50.4	59.5
102.5°	126.9	99.7	91.8	83.8	71.9	62.9	57.8	56.6	57.8	62.9	71.9
105°	138.8	112.1	104.2	96.3	83.8	75.3	71.4	69.1	71.4	75.3	83.8
107.5°	150.7	124.6	116.6	108.7	96.3	88.4	84.4	82.7	84.4	88.4	96.3
110°	162.6	137.6	129.4	121.2	109.3	102.0	98.6	96.3	98.6	102.0	109.3

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	173.9	150.1	141.6	133.1	121.8	115.0	111.0	108.7	111.0	115.0	121.8
115°	185.8	161.4	153.8	146.1	134.8	128.0	124.6	121.8	124.6	128.0	134.8
117.5°	196.5	173.9	166.0	158.0	147.3	141.0	137.6	135.4	137.6	141.0	147.3
120°	207.9	185.8	177.9	169.9	158.6	153.5	150.1	147.8	150.1	153.5	158.6
122.5°	218.6	198.2	190.0	181.8	170.5	164.8	161.4	159.7	161.4	164.8	170.5
125°	229.4	209.0	201.0	193.1	181.8	175.0	171.6	169.9	171.6	175.0	181.8
127.5°	239.6	219.8	211.6	203.3	192.6	185.2	180.7	178.4	180.7	185.2	192.6
130°	248.7	228.8	220.9	213.0	201.6	193.7	188.0	185.8	188.0	193.7	201.6
132.5°	256.6	237.9	230.0	222.0	210.1	201.6	195.4	192.6	195.4	201.6	210.1
135°	263.9	245.8	237.9	230.0	216.9	208.4	201.6	199.4	201.6	208.4	216.9
137.5°	270.2	252.0	244.6	237.3	224.3	215.2	208.4	205.6	208.4	215.2	224.3
140°	275.3	258.3	251.0	243.6	231.1	222.0	215.2	213.0	215.2	222.0	231.1
142.5°	279.2	262.8	256.0	249.2	237.3	228.3	222.0	220.3	222.0	228.3	237.3
145°	283.2	267.9	261.6	255.4	244.1	235.6	230.0	227.7	230.0	235.6	244.1
147.5°	286.6	271.9	266.2	260.5	250.9	243.0	237.3	235.6	237.3	243.0	250.9
150°	288.9	275.8	270.7	265.6	257.1	249.8	245.3	243.6	245.3	249.8	257.1
152.5°	291.1	279.8	275.2	270.7	262.8	256.6	252.0	251.5	252.0	256.6	262.8
155°	293.4	283.8	279.6	275.3	269.0	262.8	259.4	258.8	259.4	262.8	269.0
157.5°	295.1	286.6	282.9	279.2	274.1	268.5	265.6	265.1	265.6	268.5	274.1
160°	296.2	289.4	286.3	283.2	278.7	274.1	271.9	271.3	271.9	274.1	278.7
162.5°	296.8	291.1	288.8	286.6	282.6	279.2	277.0	277.5	277.0	279.2	282.6
165°	297.4	292.3	290.6	288.9	286.0	282.6	281.5	282.1	281.5	282.6	286.0
167.5°	297.4	293.4	292.2	291.1	288.9	286.6	285.5	286.0	285.5	286.6	288.9
170°	296.8	294.0	293.2	292.3	291.1	289.4	288.9	290.0	288.9	289.4	291.1
172.5°	296.2	294.5	294.0	293.4	292.8	291.1	291.7	292.3	291.7	291.1	292.8
175°	295.7	294.5	294.2	294.0	294.0	292.8	293.4	294.0	293.4	292.8	294.0
177.5°	295.1	294.5	294.5	294.5	294.5	293.4	294.0	295.1	294.0	293.4	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1309.2	1314.3	1313.3	1303.1	1291.9	1282.8	1265.5	1267.5	1261.4	1262.4	1268.5
5°	1276.7	1276.7	1272.6	1258.4	1240.1	1229.9	1210.6	1205.5	1193.3	1192.3	1191.2
7.5°	1242.1	1237.0	1231.9	1211.6	1189.2	1172.9	1146.5	1140.4	1128.2	1120.0	1116.0
10°	1201.4	1194.3	1184.1	1160.7	1133.2	1112.9	1085.4	1077.3	1053.9	1043.7	1037.6
12.5°	1156.6	1152.6	1136.3	1117.0	1072.2	1049.8	1010.2	1018.3	994.9	974.6	971.5
15°	1111.9	1096.6	1087.5	1055.9	1002.0	991.8	960.3	944.0	922.7	906.4	906.4
17.5°	1068.1	1044.7	1024.4	990.8	951.2	922.7	899.3	891.1	864.7	848.4	845.4
20°	1010.2	983.7	978.6	930.8	903.3	871.8	849.4	829.1	809.8	802.6	797.5
22.5°	955.2	924.7	916.6	875.9	848.4	816.9	794.5	780.3	766.0	760.9	751.8
25°	896.2	877.9	865.7	822.0	791.4	761.9	746.7	736.5	723.3	722.3	716.2
27.5°	839.3	822.0	809.8	768.0	745.7	718.2	706.0	694.8	687.7	684.6	681.6
30°	790.4	771.1	756.9	726.3	698.9	676.5	666.3	659.2	655.1	650.0	649.0
32.5°	736.5	725.3	706.0	682.6	661.2	639.9	633.8	628.7	622.6	620.5	619.5
35°	690.7	675.5	663.3	636.8	627.7	609.4	602.2	598.2	590.0	588.0	586.0
37.5°	646.0	631.7	618.5	602.2	584.9	574.8	570.7	564.6	560.5	561.5	559.5
40°	601.2	590.0	579.8	562.6	552.4	547.3	539.2	533.1	531.0	532.0	531.0
42.5°	557.5	547.3	541.2	528.0	517.8	512.7	507.6	501.5	504.6	504.6	507.6
45°	517.8	508.6	504.6	494.4	488.3	480.2	475.1	474.1	478.1	477.1	477.1
47.5°	477.1	474.1	469.0	459.8	451.7	446.6	445.6	445.6	449.6	451.7	450.7
50°	445.6	439.5	433.4	426.2	420.1	418.1	415.0	417.1	421.2	421.2	423.2
52.5°	405.9	401.8	399.8	393.7	389.6	389.6	389.6	390.6	393.7	396.7	395.7
55°	371.3	368.3	366.2	363.2	358.1	359.1	358.1	360.1	363.2	366.2	368.3
57.5°	334.7	333.7	331.6	326.5	326.5	325.5	328.6	329.6	334.7	336.7	339.8
60°	302.1	299.1	299.1	295.0	295.0	295.0	298.1	301.1	305.2	306.2	308.2
62.5°	267.5	267.5	266.5	263.5	263.5	266.5	267.5	271.6	273.6	273.6	276.7
65°	235.0	234.0	233.0	234.0	235.0	235.0	238.0	240.1	242.1	243.1	244.1
67.5°	202.4	201.4	203.5	202.4	204.5	208.5	207.5	210.6	213.6	213.6	214.6
70°	171.9	174.0	172.9	175.0	174.0	176.0	179.0	180.1	180.1	181.1	184.1
72.5°	143.4	143.4	143.4	142.4	143.4	145.5	147.5	148.5	150.6	151.6	154.6
75°	116.0	116.0	113.9	116.0	116.0	118.0	120.0	120.0	120.0	122.1	125.1
77.5°	87.5	88.5	87.5	89.5	89.5	90.5	92.6	91.6	93.6	94.6	95.6
80°	64.1	63.1	63.1	63.1	64.1	64.1	66.1	67.1	67.1	70.2	68.2
82.5°	40.7	41.7	40.7	41.7	41.7	42.7	41.7	42.7	43.7	45.8	44.8
85°	23.4	22.4	22.4	23.4	22.4	22.4	23.4	22.4	23.4	22.4	23.4
87.5°	9.2	8.1	8.1	8.1	8.1	7.1	7.1	6.1	6.1	6.1	5.1
90°	6.8	7.6	8.5	11.3	15.3	18.7	19.3	18.7	18.1	17.0	18.1
92.5°	23.8	26.9	30.0	45.3	66.8	86.1	87.2	73.1	57.2	48.7	42.5
95°	41.9	48.7	55.5	81.6	130.8	196.5	222.0	194.3	148.4	113.8	90.1
97.5°	56.6	64.2	71.9	105.4	173.9	279.8	361.9	364.8	303.6	242.4	185.2
100°	70.8	78.8	86.7	116.7	185.8	308.1	447.5	529.0	517.1	446.9	369.3
102.5°	83.8	91.8	99.7	126.9	186.3	297.4	450.3	590.2	657.0	654.8	603.2
105°	96.3	104.2	112.1	138.8	189.2	282.6	419.7	570.4	688.2	752.2	759.5
107.5°	108.7	116.6	124.6	150.7	195.4	274.7	391.4	528.5	654.8	749.9	805.4
110°	121.2	129.4	137.6	162.6	203.3	272.4	372.1	489.4	608.9	710.3	782.8

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	133.1	141.6	150.1	173.9	211.8	273.0	359.7	462.2	567.0	663.3	742.0
115°	146.1	153.8	161.4	185.8	220.3	275.3	351.2	440.7	534.1	621.3	695.5
117.5°	158.0	166.0	173.9	196.5	229.4	278.7	346.6	425.9	506.9	585.1	654.2
120°	169.9	177.9	185.8	207.9	238.5	282.1	342.7	414.6	487.7	557.9	617.9
122.5°	181.8	190.0	198.2	218.6	246.4	286.0	340.4	405.0	472.4	535.2	591.3
125°	193.1	201.0	209.0	229.4	254.9	290.0	337.6	395.9	457.7	516.0	565.8
127.5°	203.3	211.6	219.8	239.6	262.8	294.0	335.9	387.4	442.9	496.7	544.3
130°	213.0	220.9	228.8	248.7	270.2	298.5	334.7	378.9	428.8	477.5	522.2
132.5°	222.0	230.0	237.9	256.6	277.5	303.0	334.2	372.1	415.2	459.4	499.6
135°	230.0	237.9	245.8	263.9	283.8	306.4	333.6	365.9	402.7	440.1	477.5
137.5°	237.3	244.6	252.0	270.2	288.9	309.8	333.6	361.4	392.5	424.8	455.4
140°	243.6	251.0	258.3	275.3	292.8	312.1	333.0	357.4	382.9	410.1	436.1
142.5°	249.2	256.0	262.8	279.2	296.2	313.8	333.0	353.4	375.0	397.0	418.6
145°	255.4	261.6	267.9	283.2	299.1	314.9	331.9	350.0	367.6	386.3	403.8
147.5°	260.5	266.2	271.9	286.6	300.8	315.5	330.2	346.6	361.9	377.2	391.4
150°	265.6	270.7	275.8	288.9	301.9	314.9	328.5	342.1	355.7	368.2	380.1
152.5°	270.7	275.2	279.8	291.1	302.5	313.8	325.7	338.1	349.5	360.8	370.4
155°	275.3	279.6	283.8	293.4	303.0	312.7	322.3	333.0	343.8	352.9	361.4
157.5°	279.2	282.9	286.6	295.1	303.0	310.4	318.9	328.5	337.0	344.9	352.3
160°	283.2	286.3	289.4	296.2	303.0	308.7	315.5	323.4	330.8	337.0	343.2
162.5°	286.6	288.8	291.1	296.8	302.5	307.0	312.7	318.9	324.5	329.6	334.7
165°	288.9	290.6	292.3	297.4	301.3	304.7	308.7	313.8	318.3	322.3	326.2
167.5°	291.1	292.2	293.4	297.4	300.8	302.5	305.3	308.7	312.1	315.5	318.3
170°	292.3	293.2	294.0	296.8	299.6	300.8	302.5	304.7	307.6	309.3	311.5
172.5°	293.4	294.0	294.5	296.2	297.9	298.5	299.1	300.8	302.5	303.6	305.3
175°	294.0	294.2	294.5	295.7	296.8	296.2	296.8	297.4	299.1	299.6	300.2
177.5°	294.5	294.5	294.5	295.1	296.2	295.1	294.5	295.1	296.2	296.2	296.8
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1261.4	1264.5	1257.4	1255.3	1257.4	1250.2	1252.3	1254.3	1254.3	1257.4	1259.4
5°	1188.2	1184.1	1177.0	1175.0	1172.9	1176.0	1173.9	1177.0	1178.0	1185.1	1186.1
7.5°	1116.0	1109.9	1103.7	1097.6	1095.6	1090.5	1095.6	1095.6	1102.7	1100.7	1105.8
10°	1030.5	1029.5	1021.3	1018.3	1014.2	1006.1	1017.3	1014.2	1019.3	1028.5	1030.5
12.5°	967.4	956.2	961.3	947.1	952.2	944.0	945.1	945.1	953.2	954.2	952.2
15°	907.4	898.3	885.0	878.9	875.9	871.8	885.0	886.1	879.9	894.2	889.1
17.5°	846.4	846.4	834.2	831.1	823.0	827.0	825.0	826.0	824.0	834.2	839.3
20°	793.5	788.4	784.3	785.3	775.2	773.1	771.1	773.1	780.3	787.4	789.4
22.5°	750.8	747.7	737.5	739.6	731.4	734.5	732.4	737.5	738.5	738.5	745.7
25°	710.1	706.0	707.0	702.9	699.9	699.9	696.8	699.9	704.0	706.0	707.0
27.5°	679.5	676.5	671.4	668.4	670.4	665.3	669.4	672.4	672.4	670.4	672.4
30°	642.9	645.0	645.0	634.8	638.9	636.8	639.9	641.9	641.9	642.9	640.9
32.5°	618.5	612.4	611.4	610.4	610.4	606.3	606.3	609.4	610.4	611.4	614.4
35°	586.0	586.0	580.9	583.9	579.8	580.9	579.8	580.9	582.9	579.8	582.9
37.5°	556.5	557.5	555.4	557.5	558.5	556.5	554.4	558.5	556.5	556.5	554.4
40°	531.0	530.0	531.0	531.0	531.0	532.0	530.0	530.0	530.0	528.0	525.9
42.5°	509.7	503.6	505.6	506.6	503.6	503.6	504.6	503.6	506.6	500.5	500.5
45°	479.1	477.1	478.1	478.1	480.2	477.1	479.1	480.2	477.1	476.1	474.1
47.5°	451.7	453.7	451.7	453.7	453.7	455.7	451.7	452.7	453.7	449.6	446.6
50°	424.2	424.2	427.3	426.2	427.3	425.2	425.2	424.2	425.2	423.2	420.1
52.5°	398.8	395.7	400.8	399.8	398.8	397.8	396.7	397.8	395.7	393.7	393.7
55°	367.2	367.2	370.3	371.3	371.3	369.3	367.2	368.3	367.2	366.2	365.2
57.5°	341.8	337.7	339.8	340.8	340.8	337.7	339.8	337.7	337.7	338.8	335.7
60°	309.3	309.3	307.2	310.3	310.3	308.2	308.2	309.3	307.2	306.2	305.2
62.5°	274.7	275.7	278.7	279.8	280.8	278.7	276.7	277.7	277.7	274.7	275.7
65°	245.2	247.2	251.3	250.3	248.2	249.2	247.2	248.2	245.2	246.2	243.1
67.5°	216.7	215.7	216.7	216.7	218.7	217.7	215.7	215.7	214.6	217.7	214.6
70°	186.2	186.2	186.2	186.2	187.2	188.2	186.2	184.1	185.1	183.1	182.1
72.5°	154.6	155.6	154.6	156.7	153.6	155.6	155.6	154.6	153.6	153.6	153.6
75°	125.1	127.2	124.1	125.1	124.1	126.1	125.1	125.1	123.1	122.1	123.1
77.5°	95.6	96.6	94.6	95.6	94.6	95.6	95.6	94.6	94.6	94.6	94.6
80°	68.2	69.2	68.2	67.1	66.1	68.2	66.1	67.1	68.2	67.1	69.2
82.5°	43.7	43.7	42.7	43.7	41.7	41.7	42.7	42.7	41.7	43.7	41.7
85°	21.4	21.4	23.4	21.4	20.3	20.3	20.3	21.4	20.3	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	18.4	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.7	18.4
92.5°	40.2	37.9	37.4	35.1	35.7	34.6	35.7	35.1	37.4	37.9	40.2
95°	83.8	77.6	70.2	65.7	64.0	64.6	64.0	65.7	70.2	77.6	83.8
97.5°	168.2	151.2	129.1	117.8	111.6	108.2	111.6	117.8	129.1	151.2	168.2
100°	335.0	300.8	253.7	229.4	213.0	202.8	213.0	229.4	253.7	300.8	335.0
102.5°	566.4	529.6	477.5	431.6	410.1	395.3	410.1	431.6	477.5	529.6	566.4
105°	750.2	740.9	705.7	670.6	646.3	638.3	646.3	670.6	705.7	740.9	750.2
107.5°	816.8	828.1	827.5	822.4	815.1	802.0	815.1	822.4	827.5	828.1	816.8
110°	806.0	829.2	853.6	864.3	869.4	868.9	869.4	864.3	853.6	829.2	806.0

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	769.4	796.9	833.2	853.0	863.8	867.7	863.8	853.0	833.2	796.9	769.4
115°	724.7	753.9	794.1	820.1	834.9	840.0	834.9	820.1	794.1	753.9	724.7
117.5°	682.0	709.7	751.0	778.8	794.1	798.1	794.1	778.8	751.0	709.7	682.0
120°	643.7	669.5	709.1	735.8	752.2	757.8	752.2	735.8	709.1	669.5	643.7
122.5°	614.0	636.6	671.2	697.2	711.4	715.9	711.4	697.2	671.2	636.6	614.0
125°	587.0	608.3	641.2	662.7	676.9	681.4	676.9	662.7	641.2	608.3	587.0
127.5°	564.2	584.0	612.8	633.2	645.7	649.1	645.7	633.2	612.8	584.0	564.2
130°	540.9	559.6	587.4	606.6	617.9	622.5	617.9	606.6	587.4	559.6	540.9
132.5°	516.8	534.1	561.3	580.6	590.8	594.7	590.8	580.6	561.3	534.1	516.8
135°	493.4	509.2	533.6	552.2	562.4	564.7	562.4	552.2	533.6	509.2	493.4
137.5°	469.6	483.7	506.9	523.4	532.4	535.8	532.4	523.4	506.9	483.7	469.6
140°	448.6	461.1	479.2	493.9	502.4	505.8	502.4	493.9	479.2	461.1	448.6
142.5°	428.5	438.4	455.4	468.4	475.8	475.8	475.8	468.4	455.4	438.4	428.5
145°	412.0	420.3	433.9	443.5	449.2	450.9	449.2	443.5	433.9	420.3	412.0
147.5°	397.6	403.8	415.7	423.7	427.6	428.8	427.6	423.7	415.7	403.8	397.6
150°	385.2	390.3	398.7	405.5	408.9	409.5	408.9	405.5	398.7	390.3	385.2
152.5°	374.6	378.9	385.2	390.8	393.1	393.1	393.1	390.8	385.2	378.9	374.6
155°	364.5	367.6	373.8	377.8	380.1	378.9	380.1	377.8	373.8	367.6	364.5
157.5°	354.8	357.4	361.9	365.3	366.5	366.5	366.5	365.3	361.9	357.4	354.8
160°	345.2	347.2	351.2	354.0	354.6	354.6	354.6	354.0	351.2	347.2	345.2
162.5°	336.2	337.6	341.5	343.2	343.8	343.2	343.8	343.2	341.5	337.6	336.2
165°	327.4	328.5	330.8	333.0	333.0	332.5	333.0	333.0	330.8	328.5	327.4
167.5°	319.5	320.6	321.7	322.8	322.8	322.3	322.8	322.8	321.7	320.6	319.5
170°	312.1	312.7	313.2	314.9	314.4	313.2	314.4	314.9	313.2	312.7	312.1
172.5°	305.6	305.9	306.4	307.0	306.4	305.9	306.4	307.0	306.4	305.9	305.6
175°	300.5	300.8	300.8	301.3	300.8	299.6	300.8	301.3	300.8	300.8	300.5
177.5°	296.8	296.8	296.8	296.8	296.2	295.1	296.2	296.8	296.8	296.8	296.8
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1256.3	1264.5	1261.4	1250.2	1263.5	1263.5	1272.6	1272.6	1283.8	1287.9	1294.0
5°	1185.1	1191.2	1196.3	1191.2	1200.4	1214.6	1222.8	1229.9	1245.1	1251.3	1260.4
7.5°	1108.8	1120.0	1125.1	1125.1	1140.4	1156.6	1172.9	1183.1	1204.5	1212.6	1221.8
10°	1034.6	1047.8	1058.0	1057.0	1082.4	1092.6	1112.9	1136.3	1157.7	1169.9	1183.1
12.5°	956.2	963.4	977.6	998.0	1004.1	1022.4	1045.8	1075.3	1113.9	1125.1	1144.4
15°	891.1	910.5	921.7	930.8	945.1	962.3	987.8	1016.3	1054.9	1079.3	1099.7
17.5°	836.2	861.6	868.8	866.7	885.0	911.5	941.0	962.3	996.9	1026.4	1045.8
20°	791.4	801.6	813.8	818.9	833.2	861.6	890.1	914.5	943.0	966.4	988.8
22.5°	746.7	754.8	765.0	774.1	785.3	801.6	829.1	859.6	887.1	909.4	934.9
25°	710.1	715.1	724.3	731.4	743.6	754.8	774.1	807.7	840.3	853.5	875.9
27.5°	674.5	678.5	684.6	692.8	698.9	710.1	727.4	754.8	788.4	801.6	832.1
30°	642.9	646.0	652.1	656.1	659.2	672.4	685.6	707.0	732.4	750.8	773.1
32.5°	613.4	616.5	622.6	623.6	627.7	634.8	647.0	666.3	688.7	704.0	723.3
35°	580.9	582.9	589.0	591.0	594.1	600.2	609.4	623.6	643.9	655.1	672.4
37.5°	555.4	554.4	558.5	561.5	565.6	568.7	571.7	586.0	601.2	611.4	624.6
40°	528.0	525.9	527.0	531.0	533.1	537.1	537.1	551.4	561.5	569.7	579.8
42.5°	500.5	499.5	497.4	499.5	501.5	502.5	503.6	513.7	523.9	531.0	542.2
45°	473.0	472.0	470.0	471.0	471.0	473.0	476.1	480.2	487.3	493.4	499.5
47.5°	447.6	445.6	442.5	441.5	443.5	443.5	443.5	447.6	454.7	456.8	462.9
50°	421.2	418.1	414.0	412.0	412.0	411.0	413.0	414.0	420.1	422.2	427.3
52.5°	392.7	390.6	386.6	382.5	383.5	381.5	382.5	383.5	385.5	388.6	391.7
55°	364.2	360.1	357.1	356.0	353.0	353.0	349.9	354.0	353.0	354.0	358.1
57.5°	336.7	332.7	327.6	325.5	322.5	321.5	319.4	318.4	319.4	322.5	325.5
60°	304.2	302.1	299.1	296.0	294.0	290.9	288.9	288.9	287.9	287.9	288.9
62.5°	272.6	271.6	267.5	266.5	264.5	262.5	259.4	257.4	257.4	259.4	260.4
65°	242.1	241.1	238.0	237.0	231.9	229.9	228.9	227.9	225.8	225.8	225.8
67.5°	213.6	210.6	210.6	205.5	201.4	199.4	197.4	196.3	196.3	196.3	197.4
70°	182.1	182.1	179.0	176.0	171.9	172.9	169.9	166.8	166.8	164.8	165.8
72.5°	151.6	150.6	147.5	146.5	143.4	140.4	138.3	140.4	137.3	136.3	137.3
75°	122.1	121.1	119.0	117.0	118.0	115.0	111.9	110.9	110.9	108.8	108.8
77.5°	93.6	95.6	91.6	90.5	88.5	86.5	85.5	84.4	84.4	84.4	86.5
80°	65.1	66.1	66.1	64.1	65.1	62.1	62.1	62.1	59.0	60.0	61.0
82.5°	41.7	41.7	40.7	41.7	40.7	40.7	39.7	39.7	38.7	38.7	39.7
85°	23.4	22.4	21.4	23.4	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.1	8.1	8.1
90°	18.1	17.0	18.1	18.7	19.3	18.7	15.3	11.3	8.5	7.6	6.8
92.5°	42.5	48.7	57.2	73.1	87.2	86.1	66.8	45.3	30.0	26.9	23.8
95°	90.1	113.8	148.4	194.3	222.0	196.5	130.8	81.6	55.5	48.7	41.9
97.5°	185.2	242.4	303.6	364.8	361.9	279.8	173.9	105.4	71.9	64.2	56.6
100°	369.3	446.9	517.1	529.0	447.5	308.1	185.8	116.7	86.7	78.8	70.8
102.5°	603.2	654.8	657.0	590.2	450.3	297.4	186.3	126.9	99.7	91.8	83.8
105°	759.5	752.2	688.2	570.4	419.7	282.6	189.2	138.8	112.1	104.2	96.3
107.5°	805.4	749.9	654.8	528.5	391.4	274.7	195.4	150.7	124.6	116.6	108.7
110°	782.8	710.3	608.9	489.4	372.1	272.4	203.3	162.6	137.6	129.4	121.2

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	742.0	663.3	567.0	462.2	359.7	273.0	211.8	173.9	150.1	141.6	133.1
115°	695.5	621.3	534.1	440.7	351.2	275.3	220.3	185.8	161.4	153.8	146.1
117.5°	654.2	585.1	506.9	425.9	346.6	278.7	229.4	196.5	173.9	166.0	158.0
120°	617.9	557.9	487.7	414.6	342.7	282.1	238.5	207.9	185.8	177.9	169.9
122.5°	591.3	535.2	472.4	405.0	340.4	286.0	246.4	218.6	198.2	190.0	181.8
125°	565.8	516.0	457.7	395.9	337.6	290.0	254.9	229.4	209.0	201.0	193.1
127.5°	544.3	496.7	442.9	387.4	335.9	294.0	262.8	239.6	219.8	211.6	203.3
130°	522.2	477.5	428.8	378.9	334.7	298.5	270.2	248.7	228.8	220.9	213.0
132.5°	499.6	459.4	415.2	372.1	334.2	303.0	277.5	256.6	237.9	230.0	222.0
135°	477.5	440.1	402.7	365.9	333.6	306.4	283.8	263.9	245.8	237.9	230.0
137.5°	455.4	424.8	392.5	361.4	333.6	309.8	288.9	270.2	252.0	244.6	237.3
140°	436.1	410.1	382.9	357.4	333.0	312.1	292.8	275.3	258.3	251.0	243.6
142.5°	418.6	397.0	375.0	353.4	333.0	313.8	296.2	279.2	262.8	256.0	249.2
145°	403.8	386.3	367.6	350.0	331.9	314.9	299.1	283.2	267.9	261.6	255.4
147.5°	391.4	377.2	361.9	346.6	330.2	315.5	300.8	286.6	271.9	266.2	260.5
150°	380.1	368.2	355.7	342.1	328.5	314.9	301.9	288.9	275.8	270.7	265.6
152.5°	370.4	360.8	349.5	338.1	325.7	313.8	302.5	291.1	279.8	275.2	270.7
155°	361.4	352.9	343.8	333.0	322.3	312.7	303.0	293.4	283.8	279.6	275.3
157.5°	352.3	344.9	337.0	328.5	318.9	310.4	303.0	295.1	286.6	282.9	279.2
160°	343.2	337.0	330.8	323.4	315.5	308.7	303.0	296.2	289.4	286.3	283.2
162.5°	334.7	329.6	324.5	318.9	312.7	307.0	302.5	296.8	291.1	288.8	286.6
165°	326.2	322.3	318.3	313.8	308.7	304.7	301.3	297.4	292.3	290.6	288.9
167.5°	318.3	315.5	312.1	308.7	305.3	302.5	300.8	297.4	293.4	292.2	291.1
170°	311.5	309.3	307.6	304.7	302.5	300.8	299.6	296.8	294.0	293.2	292.3
172.5°	305.3	303.6	302.5	300.8	299.1	298.5	297.9	296.2	294.5	294.0	293.4
175°	300.2	299.6	299.1	297.4	296.8	296.2	296.8	295.7	294.5	294.2	294.0
177.5°	296.8	296.2	296.2	295.1	294.5	295.1	296.2	295.1	294.5	294.5	294.5
180°	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5	294.5

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1323.5	1323.5	1323.5	1323.5
2.5°	1299.1	1299.1	1314.3	1330.6
5°	1270.6	1277.7	1302.1	1324.5
7.5°	1243.1	1255.3	1285.8	1314.3
10°	1209.5	1225.8	1263.5	1297.0
12.5°	1177.0	1192.3	1236.0	1273.6
15°	1131.2	1150.5	1197.3	1244.1
17.5°	1085.4	1104.8	1161.7	1216.7
20°	1031.5	1057.0	1121.0	1194.3
22.5°	981.7	1013.2	1084.4	1143.4
25°	926.7	975.6	1041.7	1118.0
27.5°	877.9	926.7	993.9	1071.2
30°	823.0	872.8	942.0	1013.2
32.5°	770.1	815.9	883.0	970.5
35°	715.1	758.9	824.0	912.5
37.5°	665.3	708.0	779.2	860.6
40°	616.5	661.2	722.3	803.7
42.5°	570.7	610.4	665.3	746.7
45°	529.0	557.5	608.3	684.6
47.5°	485.2	510.7	557.5	633.8
50°	444.6	465.9	506.6	577.8
52.5°	404.9	423.2	460.8	517.8
55°	369.3	386.6	414.0	470.0
57.5°	332.7	345.9	372.3	417.1
60°	297.0	309.3	330.6	367.2
62.5°	261.4	271.6	292.0	321.5
65°	229.9	238.0	253.3	278.7
67.5°	199.4	204.5	216.7	237.0
70°	169.9	174.0	184.1	200.4
72.5°	138.3	142.4	153.6	164.8
75°	111.9	112.9	121.1	130.2
77.5°	87.5	86.5	92.6	99.7
80°	60.0	63.1	68.2	71.2
82.5°	40.7	41.7	43.7	45.8
85°	22.4	23.4	23.4	26.4
87.5°	9.2	10.2	10.2	11.2
90°	5.7	4.5	2.3	0.6
92.5°	19.3	16.4	11.9	8.5
95°	32.9	27.8	22.1	19.8
97.5°	46.4	39.1	32.9	29.5
100°	59.5	50.4	45.3	43.6
102.5°	71.9	62.9	57.8	56.6
105°	83.8	75.3	71.4	69.1
107.5°	96.3	88.4	84.4	82.7
110°	109.3	102.0	98.6	96.3

TEST NUMBER: P1009299

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	121.8	115.0	111.0	108.7
115°	134.8	128.0	124.6	121.8
117.5°	147.3	141.0	137.6	135.4
120°	158.6	153.5	150.1	147.8
122.5°	170.5	164.8	161.4	159.7
125°	181.8	175.0	171.6	169.9
127.5°	192.6	185.2	180.7	178.4
130°	201.6	193.7	188.0	185.8
132.5°	210.1	201.6	195.4	192.6
135°	216.9	208.4	201.6	199.4
137.5°	224.3	215.2	208.4	205.6
140°	231.1	222.0	215.2	213.0
142.5°	237.3	228.3	222.0	220.3
145°	244.1	235.6	230.0	227.7
147.5°	250.9	243.0	237.3	235.6
150°	257.1	249.8	245.3	243.6
152.5°	262.8	256.6	252.0	251.5
155°	269.0	262.8	259.4	258.8
157.5°	274.1	268.5	265.6	265.1
160°	278.7	274.1	271.9	271.3
162.5°	282.6	279.2	277.0	277.5
165°	286.0	282.6	281.5	282.1
167.5°	288.9	286.6	285.5	286.0
170°	291.1	289.4	288.9	290.0
172.5°	292.8	291.1	291.7	292.3
175°	294.0	292.8	293.4	294.0
177.5°	294.5	293.4	294.0	295.1
180°	294.5	294.5	294.5	294.5

(END OF REPORT)