

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008833

Luminaire Tested: S122DIP-B290D330UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008833
REPORT IS A COMBINATION OF REPORTS P983918 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D330UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2359.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008833

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008833

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	63	56	50	68	59	52	46	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7310	7310	7310
5°	7322	6969	6918
10°	7262	6651	6518
15°	7156	6331	6099
20°	7013	5983	5700
25°	6870	5619	5302
30°	6688	5277	4883
35°	6520	4917	4473
40°	6309	4562	4085
45°	6100	4210	3706
50°	5873	3850	3311
55°	5633	3467	2937
60°	5362	3050	2548
65°	5066	2628	2140
70°	4694	2167	1728
75°	4173	1670	1334
80°	3545	1136	860
85°	2571	528	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6100 cd/sqm

TEST NUMBER: P1008833

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	1.8
10°-20°	122.3	5.2
20°-30°	179.7	7.6
30°-40°	208.7	8.8
40°-50°	208.5	8.8
50°-60°	181.8	7.7
60°-70°	134.4	5.7
70°-80°	76.0	3.2
80°-90°	21.3	0.9
90°-100°	26.2	1.1
100°-110°	83.2	3.5
110°-120°	142.4	6.0
120°-130°	187.2	7.9
130°-140°	210.2	8.9
140°-150°	206.1	8.7
150°-160°	172.9	7.3
160°-170°	114.7	4.9
170°-180°	40.1	1.7
0°-30°	345.5	14.6
0°-40°	554.2	23.5
0°-60°	944.5	40.0
0°-90°	1176.2	49.9
90°-120°	251.7	10.7
90°-150°	855.2	36.3
90°-180°	1183.0	50.1
0°-180°	2359.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	462	460	455	459	458	44
15°	440	437	431	433	431	124
25°	398	394	387	388	387	183
35°	343	339	332	329	327	214
45°	279	276	270	265	263	216
55°	211	209	203	198	196	189
65°	142	140	135	131	129	141
75°	75	74	72	69	70	80
85°	18	18	17	16	16	20
90°	0	5	12	12	12	2
95°	19	22	23	23	22	21
105°	77	78	78	79	79	81
115°	143	145	144	144	143	141
125°	208	211	210	209	208	186
135°	269	273	274	273	272	208
145°	326	329	331	331	330	204
155°	373	374	375	377	376	172
165°	406	406	406	408	406	115
175°	422	421	421	423	421	40
180°	423	423	423	423	423	

TEST NUMBER: P1008833

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	461.8	461.8	461.8	461.8	461.8
2.5°	464.5	462.3	457.4	461.8	461.0
5°	461.8	460.1	455.2	458.7	457.8
7.5°	458.7	456.1	451.2	454.7	453.8
10°	453.8	450.7	445.4	449.0	447.6
12.5°	447.2	444.5	439.2	441.4	440.5
15°	439.6	437.0	431.2	433.0	430.8
17.5°	430.3	427.6	421.9	424.1	421.9
20°	420.1	417.4	411.2	412.5	410.8
22.5°	409.9	405.9	400.1	400.1	399.2
25°	397.9	394.3	386.8	387.7	386.8
27.5°	384.6	381.5	375.7	374.4	372.1
30°	371.2	367.7	361.0	359.7	357.9
32.5°	357.0	354.4	347.3	344.6	342.8
35°	343.3	338.8	331.7	329.1	326.8
37.5°	327.7	323.7	316.6	313.5	311.3
40°	311.7	308.2	301.1	297.1	295.3
42.5°	296.2	292.6	285.5	281.1	278.4
45°	279.3	276.2	269.6	264.7	262.9
47.5°	262.9	259.8	252.7	247.8	245.1
50°	245.6	243.4	237.1	230.9	228.7
52.5°	228.7	225.6	219.8	214.9	211.8
55°	211.4	208.7	203.4	198.1	195.8
57.5°	194.1	191.8	186.1	180.7	179.0
60°	176.7	175.0	168.7	163.9	162.5
62.5°	159.9	156.8	152.3	147.9	146.1
65°	142.5	139.9	135.4	131.4	129.2
67.5°	124.8	122.6	118.6	115.5	113.7
70°	108.4	106.6	102.6	99.5	97.7
72.5°	91.5	89.7	87.5	84.4	83.0
75°	74.6	73.7	71.5	68.8	69.7
77.5°	59.5	57.7	56.8	55.5	54.2
80°	44.4	44.0	43.1	41.7	40.9
82.5°	30.2	30.2	29.8	28.0	28.0
85°	18.2	17.8	17.3	16.0	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	0.4	4.6	12.5	11.8	12.1
92.5°	7.9	10.7	11.1	11.4	11.4
95°	18.6	22.1	22.8	22.8	22.1
97.5°	31.1	34.3	35.7	35.7	35.7
100°	45.3	48.2	49.3	49.3	48.9
102.5°	60.3	62.5	63.9	64.3	63.9
105°	76.8	77.8	78.5	79.3	79.3
107.5°	93.2	94.6	94.6	95.0	93.2
110°	108.9	111.0	111.0	111.0	110.0

TEST NUMBER: P1008833

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	126.0	128.2	127.8	126.7	126.0
115°	142.8	144.9	144.2	143.9	142.8
117.5°	159.6	162.4	160.7	159.6	158.5
120°	176.4	179.2	176.4	176.4	175.3
122.5°	191.7	195.3	193.5	192.4	191.7
125°	207.8	211.0	209.9	208.9	208.5
127.5°	223.5	227.4	226.0	224.6	223.5
130°	238.1	242.8	242.1	241.3	239.9
132.5°	254.6	258.1	258.5	256.7	255.6
135°	268.8	272.8	273.5	273.1	272.0
137.5°	284.5	287.8	288.5	288.1	286.7
140°	298.5	301.7	303.5	303.5	302.0
142.5°	312.7	316.0	317.0	317.4	316.0
145°	326.3	328.8	331.0	331.3	329.9
147.5°	338.4	341.7	343.1	343.8	342.4
150°	350.9	353.1	354.5	355.6	354.5
152.5°	362.0	364.2	365.9	367.4	365.9
155°	373.1	374.1	375.2	377.0	375.9
157.5°	382.7	383.4	384.1	386.6	384.9
160°	391.3	392.0	392.4	394.5	393.1
162.5°	399.1	399.1	399.5	402.0	400.2
165°	405.9	405.6	405.6	408.1	406.3
167.5°	412.0	410.9	410.9	413.4	411.6
170°	416.6	415.6	415.2	417.7	415.6
172.5°	419.8	418.8	418.4	420.9	418.8
175°	422.3	421.3	420.6	423.1	420.9
177.5°	423.8	422.7	422.0	424.1	422.0
180°	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)