

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008834

Luminaire Tested: S122DIP-B290D330UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008834
REPORT IS A COMBINATION OF REPORTS P983919 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D330UB35-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2470.5 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008834

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008834

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	82	79	72	69	67	59	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7310	7310	7310
5°	7322	6969	6918
10°	7262	6651	6518
15°	7156	6331	6099
20°	7013	5983	5700
25°	6870	5619	5302
30°	6688	5277	4883
35°	6520	4917	4473
40°	6309	4562	4085
45°	6100	4210	3706
50°	5873	3850	3311
55°	5633	3467	2937
60°	5362	3050	2548
65°	5066	2628	2140
70°	4694	2167	1728
75°	4173	1670	1334
80°	3545	1136	860
85°	2571	528	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6100 cd/sqm

TEST NUMBER: P1008834

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	1.8
10°-20°	122.3	5.0
20°-30°	179.7	7.3
30°-40°	208.7	8.4
40°-50°	208.5	8.4
50°-60°	181.8	7.4
60°-70°	134.4	5.4
70°-80°	76.0	3.1
80°-90°	21.3	0.9
90°-100°	75.3	3.0
100°-110°	254.4	10.3
110°-120°	267.4	10.8
120°-130°	219.9	8.9
130°-140°	176.7	7.2
140°-150°	133.5	5.4
150°-160°	93.9	3.8
160°-170°	55.3	2.2
170°-180°	18.0	0.7
0°-30°	345.5	14.0
0°-40°	554.2	22.4
0°-60°	944.5	38.2
0°-90°	1176.2	47.6
90°-120°	597.1	24.2
90°-150°	1127.2	45.6
90°-180°	1294.0	52.4
0°-180°	2470.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	462	460	455	459	458	44
15°	440	437	431	433	431	124
25°	398	394	387	388	387	183
35°	343	339	332	329	327	214
45°	279	276	270	265	263	216
55°	211	209	203	198	196	189
65°	142	140	135	131	129	141
75°	75	74	72	69	70	80
85°	18	18	17	16	16	20
90°	0	5	12	12	12	2
95°	12	31	140	53	41	13
105°	44	66	264	473	402	46
115°	77	97	221	457	529	76
125°	107	127	213	370	430	95
135°	126	150	210	311	356	97
145°	144	165	209	260	284	90
155°	163	176	203	230	239	75
165°	178	183	195	206	210	50
175°	185	185	187	189	189	18
180°	186	186	186	186	186	

TEST NUMBER: P1008834

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	461.8	461.8	461.8	461.8	461.8
2.5°	464.5	462.3	457.4	461.8	461.0
5°	461.8	460.1	455.2	458.7	457.8
7.5°	458.7	456.1	451.2	454.7	453.8
10°	453.8	450.7	445.4	449.0	447.6
12.5°	447.2	444.5	439.2	441.4	440.5
15°	439.6	437.0	431.2	433.0	430.8
17.5°	430.3	427.6	421.9	424.1	421.9
20°	420.1	417.4	411.2	412.5	410.8
22.5°	409.9	405.9	400.1	400.1	399.2
25°	397.9	394.3	386.8	387.7	386.8
27.5°	384.6	381.5	375.7	374.4	372.1
30°	371.2	367.7	361.0	359.7	357.9
32.5°	357.0	354.4	347.3	344.6	342.8
35°	343.3	338.8	331.7	329.1	326.8
37.5°	327.7	323.7	316.6	313.5	311.3
40°	311.7	308.2	301.1	297.1	295.3
42.5°	296.2	292.6	285.5	281.1	278.4
45°	279.3	276.2	269.6	264.7	262.9
47.5°	262.9	259.8	252.7	247.8	245.1
50°	245.6	243.4	237.1	230.9	228.7
52.5°	228.7	225.6	219.8	214.9	211.8
55°	211.4	208.7	203.4	198.1	195.8
57.5°	194.1	191.8	186.1	180.7	179.0
60°	176.7	175.0	168.7	163.9	162.5
62.5°	159.9	156.8	152.3	147.9	146.1
65°	142.5	139.9	135.4	131.4	129.2
67.5°	124.8	122.6	118.6	115.5	113.7
70°	108.4	106.6	102.6	99.5	97.7
72.5°	91.5	89.7	87.5	84.4	83.0
75°	74.6	73.7	71.5	68.8	69.7
77.5°	59.5	57.7	56.8	55.5	54.2
80°	44.4	44.0	43.1	41.7	40.9
82.5°	30.2	30.2	29.8	28.0	28.0
85°	18.2	17.8	17.3	16.0	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	0.4	4.8	12.1	11.6	11.8
92.5°	5.4	17.0	55.0	25.4	21.8
95°	12.5	30.7	139.9	52.8	40.7
97.5°	18.6	40.5	228.1	106.0	68.2
100°	27.5	49.6	282.0	211.2	127.8
102.5°	35.7	57.8	283.8	357.0	249.2
105°	43.6	65.7	264.5	472.8	402.3
107.5°	52.1	73.5	246.7	514.8	505.5
110°	60.7	81.6	234.5	508.0	547.6

TEST NUMBER: P1008834

CATALOG NUMBER: S122DIP-B290D330UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.5	89.2	226.7	485.0	546.9
115°	76.8	96.9	221.3	456.8	529.4
117.5°	85.3	104.6	218.5	429.8	503.0
120°	93.2	112.1	216.0	405.8	477.7
122.5°	100.7	119.8	214.6	387.0	451.2
125°	107.1	126.7	212.8	370.0	429.5
127.5°	112.5	133.4	211.7	355.6	409.1
130°	117.1	139.2	211.0	341.0	392.3
132.5°	121.4	144.9	210.6	325.8	374.9
135°	125.7	149.9	210.3	311.0	355.9
137.5°	129.6	154.2	210.3	296.0	337.7
140°	134.2	158.2	209.9	282.8	318.8
142.5°	138.9	161.4	209.9	270.0	299.9
145°	143.5	165.0	209.2	259.7	284.2
147.5°	148.5	167.8	208.1	250.6	270.3
150°	153.5	170.6	207.1	242.8	258.1
152.5°	158.5	173.5	205.3	236.2	247.8
155°	163.1	176.2	203.1	229.8	238.8
157.5°	167.1	178.3	201.0	223.7	231.0
160°	171.0	180.4	198.8	217.6	223.5
162.5°	174.9	182.0	197.1	211.9	216.3
165°	177.8	183.1	194.6	206.4	209.6
167.5°	180.3	184.2	192.4	201.4	203.1
170°	182.8	184.8	190.6	196.8	197.4
172.5°	184.2	185.2	188.5	192.6	192.8
175°	185.3	185.4	187.1	189.4	188.9
177.5°	186.0	185.6	185.6	187.1	186.0
180°	185.6	185.6	185.6	185.6	185.6

(END OF REPORT)