

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009349

Luminaire Tested: S122DIP-B675D725UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009349
REPORT IS A COMBINATION OF REPORTS P984605 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5202.0 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009349

CATALOG NUMBER: S122DIP-B675D725UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009349

CATALOG NUMBER: S122DIP-B675D725UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	60	59	51	50	49
2	89	82	76	71	82	76	71	66	65	61	57	54	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	41	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16749	16749	16749
5°	16776	15964	15853
10°	16640	15238	14936
15°	16396	14504	13971
20°	16067	13707	13057
25°	15738	12875	12146
30°	15326	12092	11188
35°	14937	11266	10249
40°	14455	10451	9361
45°	13978	9644	8489
50°	13454	8821	7586
55°	12905	7942	6730
60°	12287	6990	5840
65°	11610	6022	4904
70°	10749	4963	3959
75°	9560	3826	3057
80°	8119	2601	1968
85°	5890	1211	837

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13978 cd/sqm

TEST NUMBER: P1009349

CATALOG NUMBER: S122DIP-B675D725UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.9
10°-20°	280.2	5.4
20°-30°	411.8	7.9
30°-40°	478.3	9.2
40°-50°	477.7	9.2
50°-60°	416.5	8.0
60°-70°	307.9	5.9
70°-80°	174.2	3.3
80°-90°	48.5	0.9
90°-100°	55.5	1.1
100°-110°	176.4	3.4
110°-120°	301.8	5.8
120°-130°	396.9	7.6
130°-140°	445.5	8.6
140°-150°	436.9	8.4
150°-160°	366.5	7.0
160°-170°	243.1	4.7
170°-180°	84.9	1.6
0°-30°	791.6	15.2
0°-40°	1269.8	24.4
0°-60°	2164.0	41.6
0°-90°	2694.5	51.8
90°-120°	533.6	10.3
90°-150°	1813.0	34.9
90°-180°	2507.0	48.2
0°-180°	5202.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1058	1058	1058	1058	1058	
5°	1058	1054	1043	1051	1049	100
15°	1007	1001	988	992	987	284
25°	912	904	886	888	886	419
35°	786	776	760	754	749	491
45°	640	633	618	606	602	494
55°	484	478	466	454	449	433
65°	327	320	310	301	296	323
75°	171	169	164	158	160	182
85°	42	41	40	37	36	46
90°	1	10	26	25	26	5
95°	39	47	48	48	47	44
105°	163	165	166	168	168	172
115°	303	307	306	305	303	300
125°	440	447	445	443	442	394
135°	570	578	580	579	577	440
145°	692	697	702	702	699	432
155°	791	793	795	799	797	364
165°	860	860	860	865	861	243
175°	895	893	892	897	892	85
180°	897	897	897	897	897	

TEST NUMBER: P1009349

CATALOG NUMBER: S122DIP-B675D725UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1058.1	1058.1	1058.1	1058.1	1058.1
2.5°	1064.2	1059.1	1047.9	1058.1	1056.1
5°	1058.1	1054.0	1042.8	1051.0	1049.0
7.5°	1051.0	1044.9	1033.7	1041.8	1039.8
10°	1039.8	1032.7	1020.5	1028.6	1025.6
12.5°	1024.5	1018.4	1006.2	1011.3	1009.3
15°	1007.2	1001.1	987.9	992.0	986.9
17.5°	985.9	979.8	966.5	971.6	966.5
20°	962.5	956.4	942.1	945.2	941.1
22.5°	939.1	929.9	916.7	916.7	914.7
25°	911.6	903.5	886.2	888.2	886.2
27.5°	881.1	874.0	860.7	857.7	852.6
30°	850.6	842.4	827.2	824.1	820.0
32.5°	818.0	811.9	795.6	789.5	785.4
35°	786.5	776.3	760.0	753.9	748.8
37.5°	750.9	741.7	725.4	718.3	713.2
40°	714.2	706.1	689.8	680.6	676.6
42.5°	678.6	670.5	654.2	644.0	637.9
45°	640.0	632.8	617.6	606.4	602.3
47.5°	602.3	595.2	578.9	567.7	561.6
50°	562.6	557.5	543.3	529.1	524.0
52.5°	524.0	516.8	503.6	492.4	485.3
55°	484.3	478.2	466.0	453.8	448.7
57.5°	444.6	439.5	426.3	414.1	410.0
60°	404.9	400.9	386.6	375.4	372.4
62.5°	366.3	359.1	349.0	338.8	334.7
65°	326.6	320.5	310.3	301.2	296.1
67.5°	285.9	280.8	271.6	264.5	260.5
70°	248.2	244.2	235.0	227.9	223.8
72.5°	209.6	205.5	200.4	193.3	190.3
75°	170.9	168.9	163.8	157.7	159.7
77.5°	136.3	132.3	130.2	127.2	124.1
80°	101.7	100.7	98.7	95.6	93.6
82.5°	69.2	69.2	68.2	64.1	64.1
85°	41.7	40.7	39.7	36.6	35.6
87.5°	18.3	16.3	14.2	11.2	10.2
90°	0.8	9.8	26.5	25.0	25.7
92.5°	16.7	22.7	23.5	24.2	24.2
95°	39.4	46.9	48.4	48.4	46.9
97.5°	65.8	72.7	75.7	75.7	75.7
100°	96.1	102.2	104.4	104.4	103.7
102.5°	127.9	132.4	135.5	136.2	135.5
105°	162.7	165.0	166.5	168.0	168.0
107.5°	197.5	200.6	200.6	201.3	197.5
110°	230.8	235.4	235.4	235.4	233.1

TEST NUMBER: P1009349

CATALOG NUMBER: S122DIP-B675D725UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.2	271.7	270.9	268.7	267.2
115°	302.7	307.3	305.8	305.0	302.7
117.5°	338.3	344.4	340.6	338.3	336.0
120°	373.9	379.9	373.9	373.9	371.6
122.5°	406.4	414.0	410.2	407.9	406.4
125°	440.5	447.3	445.0	442.8	442.0
127.5°	473.8	482.1	479.1	476.1	473.8
130°	504.8	514.7	513.1	511.6	508.6
132.5°	539.6	547.2	548.0	544.2	541.9
135°	569.9	578.2	579.7	579.0	576.7
137.5°	603.2	610.0	611.5	610.8	607.7
140°	632.7	639.5	643.3	643.3	640.3
142.5°	663.0	669.8	672.1	672.8	669.8
145°	691.8	697.1	701.6	702.4	699.3
147.5°	717.5	724.3	727.3	728.8	725.8
150°	744.0	748.5	751.5	753.8	751.5
152.5°	767.4	772.0	775.8	778.8	775.8
155°	790.9	793.2	795.4	799.2	797.0
157.5°	811.3	812.8	814.4	819.7	815.9
160°	829.5	831.0	831.8	836.3	833.3
162.5°	846.2	846.2	846.9	852.2	848.4
165°	860.5	859.8	859.8	865.1	861.3
167.5°	873.4	871.1	871.1	876.4	872.6
170°	883.2	881.0	880.2	885.5	881.0
172.5°	890.0	887.8	887.0	892.3	887.8
175°	895.3	893.1	891.6	896.9	892.3
177.5°	898.4	896.1	894.6	899.1	894.6
180°	896.9	896.9	896.9	896.9	896.9

(END OF REPORT)