

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008879

Luminaire Tested: S122DIP-B290D530UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008879
REPORT IS A COMBINATION OF REPORTS P983979 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D530UB35-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3257.4 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008879

CATALOG NUMBER: S122DIP-B290D530UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot





TEST NUMBER: P1008879

CATALOG NUMBER: S122DIP-B290D530UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36			
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30			
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	25			
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	30	28	26	22			
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	23	19			
5	66	55	47	41	59	50	43	38	41	35	31	32	28	26	24	22	20	16			
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	14			
7	56	44	36	31	51	40	33	29	33	28	24	26	22	20	20	17	15	13			
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11			
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10			
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7310	7310	7310
5°	7322	6969	6918
10°	7262	6651	6518
15°	7156	6331	6099
20°	7013	5983	5700
25°	6870	5619	5302
30°	6688	5277	4883
35°	6520	4917	4473
40°	6309	4562	4085
45°	6100	4210	3706
50°	5873	3850	3311
55°	5633	3467	2937
60°	5362	3050	2548
65°	5066	2628	2140
70°	4694	2167	1728
75°	4173	1670	1334
80°	3545	1136	860
85°	2571	528	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6100 cd/sqm

TEST NUMBER: P1008879

CATALOG NUMBER: S122DIP-B290D530UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	1.3
10°-20°	122.3	3.8
20°-30°	179.7	5.5
30°-40°	208.7	6.4
40°-50°	208.5	6.4
50°-60°	181.8	5.6
60°-70°	134.4	4.1
70°-80°	76.0	2.3
80°-90°	22.0	0.7
90°-100°	121.0	3.7
100°-110°	409.0	12.6
110°-120°	429.9	13.2
120°-130°	353.5	10.9
130°-140°	284.1	8.7
140°-150°	214.6	6.6
150°-160°	150.9	4.6
160°-170°	88.8	2.7
170°-180°	28.9	0.9
0°-30°	345.5	10.6
0°-40°	554.2	17.0
0°-60°	944.5	29.0
0°-90°	1176.9	36.1
90°-120°	959.8	29.5
90°-150°	1811.9	55.6
90°-180°	2080.0	63.9
0°-180°	3257.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	462	460	455	459	458	44
15°	440	437	431	433	431	124
25°	398	394	387	388	387	183
35°	343	339	332	329	327	214
45°	279	276	270	265	263	216
55°	211	209	203	198	196	189
65°	142	140	135	131	129	141
75°	75	74	72	69	70	80
85°	18	18	17	16	16	20
90°	1	8	20	19	19	2
95°	20	49	225	85	65	21
105°	70	106	425	760	647	74
115°	123	156	356	734	851	122
125°	172	204	342	595	690	153
135°	202	241	338	500	572	156
145°	231	265	336	418	457	145
155°	262	283	326	369	384	121
165°	286	294	313	332	337	81
175°	298	298	301	304	304	28
180°	298	298	298	298	298	

TEST NUMBER: P1008879

CATALOG NUMBER: S122DIP-B290D530UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	461.8	461.8	461.8	461.8	461.8
2.5°	464.5	462.3	457.4	461.8	461.0
5°	461.8	460.1	455.2	458.7	457.8
7.5°	458.7	456.1	451.2	454.7	453.8
10°	453.8	450.7	445.4	449.0	447.6
12.5°	447.2	444.5	439.2	441.4	440.5
15°	439.6	437.0	431.2	433.0	430.8
17.5°	430.3	427.6	421.9	424.1	421.9
20°	420.1	417.4	411.2	412.5	410.8
22.5°	409.9	405.9	400.1	400.1	399.2
25°	397.9	394.3	386.8	387.7	386.8
27.5°	384.6	381.5	375.7	374.4	372.1
30°	371.2	367.7	361.0	359.7	357.9
32.5°	357.0	354.4	347.3	344.6	342.8
35°	343.3	338.8	331.7	329.1	326.8
37.5°	327.7	323.7	316.6	313.5	311.3
40°	311.7	308.2	301.1	297.1	295.3
42.5°	296.2	292.6	285.5	281.1	278.4
45°	279.3	276.2	269.6	264.7	262.9
47.5°	262.9	259.8	252.7	247.8	245.1
50°	245.6	243.4	237.1	230.9	228.7
52.5°	228.7	225.6	219.8	214.9	211.8
55°	211.4	208.7	203.4	198.1	195.8
57.5°	194.1	191.8	186.1	180.7	179.0
60°	176.7	175.0	168.7	163.9	162.5
62.5°	159.9	156.8	152.3	147.9	146.1
65°	142.5	139.9	135.4	131.4	129.2
67.5°	124.8	122.6	118.6	115.5	113.7
70°	108.4	106.6	102.6	99.5	97.7
72.5°	91.5	89.7	87.5	84.4	83.0
75°	74.6	73.7	71.5	68.8	69.7
77.5°	59.5	57.7	56.8	55.5	54.2
80°	44.4	44.0	43.1	41.7	40.9
82.5°	30.2	30.2	29.8	28.0	28.0
85°	18.2	17.8	17.3	16.0	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	0.6	7.8	19.5	18.6	18.9
92.5°	8.6	27.2	88.4	40.7	35.0
95°	20.1	49.4	224.9	84.9	65.4
97.5°	29.8	65.2	366.7	170.4	109.6
100°	44.2	79.8	453.3	339.4	205.4
102.5°	57.4	93.0	456.2	573.9	400.5
105°	70.0	105.6	425.2	760.0	646.7
107.5°	83.8	118.2	396.5	827.5	812.6
110°	97.6	131.1	377.0	816.6	880.3

TEST NUMBER: P1008879

CATALOG NUMBER: S122DIP-B290D530UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	110.2	143.5	364.4	779.6	879.1
115°	123.4	155.8	355.8	734.2	851.0
117.5°	137.2	168.1	351.2	690.9	808.6
120°	149.8	180.2	347.2	652.2	767.8
122.5°	161.8	192.5	344.9	622.0	725.3
125°	172.2	203.8	342.0	594.8	690.3
127.5°	180.8	214.4	340.3	571.6	657.6
130°	188.2	223.8	339.1	548.0	630.7
132.5°	195.1	233.0	338.6	523.6	602.5
135°	202.0	241.0	338.0	499.8	572.1
137.5°	208.3	247.9	338.0	475.8	542.9
140°	215.8	254.2	337.4	454.5	512.4
142.5°	223.2	259.4	337.4	434.2	482.0
145°	230.7	265.1	336.3	417.5	456.8
147.5°	238.7	269.7	334.6	402.8	434.4
150°	246.8	274.3	332.8	390.2	414.9
152.5°	254.8	278.9	330.0	379.6	398.3
155°	262.2	283.2	326.5	369.2	383.9
157.5°	268.6	286.6	323.1	359.5	371.3
160°	274.9	290.0	319.6	349.8	359.2
162.5°	281.2	292.7	316.8	340.6	347.8
165°	285.8	294.4	312.7	331.6	336.9
167.5°	289.8	296.2	309.3	323.6	326.5
170°	293.8	297.0	306.4	316.2	317.3
172.5°	296.1	297.8	303.0	309.6	309.9
175°	297.8	298.1	300.7	304.4	303.6
177.5°	299.0	298.4	298.4	300.7	299.0
180°	298.4	298.4	298.4	298.4	298.4

(END OF REPORT)