

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009359

Luminaire Tested: S122DIP-B675D725UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009359
REPORT IS A COMBINATION OF REPORTS P984630 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5485.2 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009359

CATALOG NUMBER: S122DIP-B675D725UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009359

CATALOG NUMBER: S122DIP-B675D725UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40
3	81	72	64	58	75	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16891	16891	16891
5°	16919	16102	15987
10°	16782	15368	15062
15°	16536	14627	14090
20°	16204	13824	13168
25°	15873	12984	12249
30°	15456	12195	11284
35°	15064	11362	10336
40°	14578	10541	9441
45°	14096	9725	8563
50°	13569	8896	7650
55°	13014	8010	6787
60°	12393	7049	5890
65°	11710	6075	4946
70°	10844	5005	3993
75°	9644	3859	3084
80°	8191	2622	1985
85°	5947	1220	844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14096 cd/sqm

TEST NUMBER: P1009359

CATALOG NUMBER: S122DIP-B675D725UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	1.8
10°-20°	282.6	5.2
20°-30°	415.3	7.6
30°-40°	482.3	8.8
40°-50°	481.7	8.8
50°-60°	420.0	7.7
60°-70°	310.5	5.7
70°-80°	175.7	3.2
80°-90°	48.9	0.9
90°-100°	160.9	2.9
100°-110°	544.0	9.9
110°-120°	571.8	10.4
120°-130°	470.2	8.6
130°-140°	377.9	6.9
140°-150°	285.5	5.2
150°-160°	200.7	3.7
160°-170°	118.2	2.2
170°-180°	38.4	0.7
0°-30°	798.3	14.6
0°-40°	1280.6	23.3
0°-60°	2182.4	39.8
0°-90°	2717.5	49.5
90°-120°	1276.8	23.3
90°-150°	2410.4	43.9
90°-180°	2768.0	50.5
0°-180°	5485.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1067	1067	1067	1067	1067	
5°	1067	1063	1052	1060	1058	101
15°	1016	1010	996	1000	995	286
25°	919	911	894	896	894	423
35°	793	783	766	760	755	495
45°	645	638	623	612	608	498
55°	488	482	470	458	452	437
65°	329	323	313	304	299	326
75°	172	170	165	159	161	184
85°	42	41	40	37	36	47
90°	1	10	26	25	25	4
95°	27	66	299	113	87	28
105°	93	140	566	1011	860	99
115°	164	207	473	977	1132	163
125°	229	271	455	791	918	204
135°	269	321	450	665	761	208
145°	307	353	447	555	608	193
155°	349	377	434	491	511	161
165°	380	392	416	441	448	107
175°	396	397	400	405	404	38
180°	397	397	397	397	397	

TEST NUMBER: P1009359

CATALOG NUMBER: S122DIP-B675D725UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.1	1067.1	1067.1	1067.1	1067.1
2.5°	1073.3	1068.2	1056.9	1067.1	1065.1
5°	1067.1	1063.0	1051.8	1060.0	1057.9
7.5°	1060.0	1053.8	1042.5	1050.7	1048.7
10°	1048.7	1041.5	1029.2	1037.4	1034.3
12.5°	1033.3	1027.1	1014.8	1019.9	1017.9
15°	1015.8	1009.7	996.3	1000.5	995.3
17.5°	994.3	988.1	974.8	979.9	974.8
20°	970.7	964.5	950.2	953.3	949.1
22.5°	947.1	937.9	924.5	924.5	922.5
25°	919.4	911.2	893.7	895.8	893.7
27.5°	888.6	881.4	868.1	865.0	859.9
30°	857.8	849.6	834.2	831.1	827.0
32.5°	825.0	818.8	802.4	796.3	792.2
35°	793.2	782.9	766.5	760.3	755.2
37.5°	757.3	748.0	731.6	724.4	719.3
40°	720.3	712.1	695.7	686.5	682.4
42.5°	684.4	676.2	659.8	649.5	643.4
45°	645.4	638.2	622.8	611.6	607.5
47.5°	607.5	600.3	583.9	572.6	566.4
50°	567.4	562.3	547.9	533.6	528.4
52.5°	528.4	521.3	507.9	496.6	489.5
55°	488.4	482.3	470.0	457.6	452.5
57.5°	448.4	443.3	429.9	417.6	413.5
60°	408.4	404.3	389.9	378.6	375.6
62.5°	369.4	362.2	352.0	341.7	337.6
65°	329.4	323.2	313.0	303.7	298.6
67.5°	288.3	283.2	274.0	266.8	262.7
70°	250.4	246.3	237.0	229.8	225.7
72.5°	211.4	207.3	202.1	195.0	191.9
75°	172.4	170.3	165.2	159.0	161.1
77.5°	137.5	133.4	131.3	128.3	125.2
80°	102.6	101.6	99.5	96.5	94.4
82.5°	69.8	69.8	68.7	64.6	64.6
85°	42.1	41.0	40.0	36.9	35.9
87.5°	18.5	16.4	14.4	11.3	10.3
90°	0.8	10.4	26.0	24.8	25.2
92.5°	11.5	36.3	117.6	54.2	46.6
95°	26.7	65.6	299.2	113.0	87.0
97.5°	39.7	86.6	487.8	226.7	145.8
100°	58.8	106.1	603.1	451.6	273.3
102.5°	76.3	123.7	606.9	763.4	532.8
105°	93.1	140.5	565.7	1011.1	860.3
107.5°	111.5	157.2	527.5	1100.8	1081.0
110°	129.8	174.4	501.5	1086.3	1171.0

TEST NUMBER: P1009359

CATALOG NUMBER: S122DIP-B675D725UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	146.6	190.9	484.8	1037.0	1169.5
115°	164.1	207.3	473.3	976.8	1132.1
117.5°	182.4	223.7	467.2	919.1	1075.6
120°	199.2	239.7	461.8	867.6	1021.4
122.5°	215.3	256.1	458.8	827.5	964.9
125°	229.0	271.0	455.0	791.2	918.4
127.5°	240.5	285.2	452.7	760.4	874.8
130°	250.4	297.7	451.2	729.0	839.0
132.5°	259.6	309.9	450.4	696.6	801.6
135°	268.7	320.6	449.6	664.9	761.1
137.5°	277.1	329.8	449.6	632.8	722.2
140°	287.0	338.2	448.9	604.6	681.7
142.5°	297.0	345.0	448.9	577.5	641.2
145°	306.9	352.7	447.3	555.3	607.7
147.5°	317.6	358.8	445.1	535.9	577.9
150°	328.3	364.9	442.8	519.1	551.9
152.5°	338.9	371.0	438.9	505.0	529.8
155°	348.9	376.8	434.4	491.2	510.7
157.5°	357.3	381.3	429.8	478.2	493.9
160°	365.7	385.9	425.2	465.3	477.9
162.5°	374.1	389.4	421.4	453.1	462.6
165°	380.2	391.6	416.0	441.2	448.1
167.5°	385.5	393.9	411.5	430.6	434.4
170°	390.9	395.0	407.6	420.6	422.2
172.5°	393.9	396.2	403.1	411.8	412.2
175°	396.2	396.6	400.0	405.0	403.8
177.5°	397.7	397.0	397.0	400.0	397.7
180°	397.0	397.0	397.0	397.0	397.0

(END OF REPORT)