

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008884

Luminaire Tested: S122DIP-B290D530UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1008884  
REPORT IS A COMBINATION OF REPORTS P983984 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/6/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122DIP-B290D530UB40-4F0-XX-W2A-D1  
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3042.0 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 28.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1008884

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-D1

### Luminous Intensity Polar Plot



TEST NUMBER: P1008884

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-D1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    |    | 20 |    |    |    |    | 20 |    |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    |    | 50 |    |    |    |    | 30 |    |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 103 | 103 | 103 | 103 | 93 | 93 | 93 | 93 | 74 | 74 | 74 | 57 | 57 | 57 | 41 | 41 | 41 |    |    | 34 |
| 1   | 93  | 88  | 84  | 81  | 84 | 80 | 76 | 73 | 64 | 61 | 59 | 49 | 47 | 45 | 35 | 34 | 33 |    |    | 26 |
| 2   | 84  | 77  | 70  | 65  | 76 | 69 | 64 | 59 | 55 | 51 | 48 | 42 | 39 | 37 | 30 | 28 | 27 |    |    | 21 |
| 3   | 77  | 67  | 59  | 54  | 69 | 60 | 54 | 49 | 48 | 44 | 40 | 37 | 34 | 31 | 26 | 24 | 22 |    |    | 18 |
| 4   | 70  | 59  | 51  | 45  | 63 | 53 | 46 | 41 | 43 | 37 | 33 | 33 | 29 | 26 | 23 | 21 | 19 |    |    | 15 |
| 5   | 64  | 52  | 44  | 38  | 57 | 47 | 40 | 35 | 38 | 33 | 29 | 29 | 25 | 22 | 21 | 18 | 16 |    |    | 13 |
| 6   | 59  | 47  | 39  | 33  | 53 | 42 | 35 | 30 | 34 | 29 | 25 | 26 | 22 | 19 | 19 | 16 | 14 |    |    | 11 |
| 7   | 54  | 42  | 34  | 28  | 49 | 38 | 31 | 26 | 31 | 25 | 22 | 24 | 20 | 17 | 17 | 15 | 13 |    |    | 10 |
| 8   | 50  | 38  | 30  | 25  | 45 | 34 | 28 | 23 | 28 | 23 | 19 | 22 | 18 | 15 | 16 | 13 | 11 |    |    | 9  |
| 9   | 47  | 34  | 27  | 22  | 42 | 31 | 25 | 20 | 25 | 20 | 17 | 20 | 16 | 13 | 14 | 12 | 10 |    |    | 8  |
| 10  | 43  | 31  | 24  | 20  | 39 | 29 | 22 | 18 | 23 | 18 | 15 | 18 | 15 | 12 | 13 | 11 | 9  |    |    | 7  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 4804 | 4804 | 4804 |
| 5°  | 4826 | 4599 | 4573 |
| 10° | 4793 | 4439 | 4375 |
| 15° | 4726 | 4275 | 4172 |
| 20° | 4641 | 4101 | 3979 |
| 25° | 4556 | 3936 | 3803 |
| 30° | 4438 | 3767 | 3631 |
| 35° | 4319 | 3605 | 3504 |
| 40° | 4194 | 3465 | 3377 |
| 45° | 4073 | 3338 | 3267 |
| 50° | 3943 | 3221 | 3159 |
| 55° | 3808 | 3097 | 3048 |
| 60° | 3644 | 2967 | 2931 |
| 65° | 3470 | 2816 | 2797 |
| 70° | 3278 | 2657 | 2654 |
| 75° | 3026 | 2497 | 2517 |
| 80° | 2635 | 2330 | 2376 |
| 85° | 2232 | 2174 | 2255 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4073 cd/sqm

TEST NUMBER: P1008884

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-D1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 28.8   | 0.9       |
| 10°-20°   | 82.5   | 2.7       |
| 20°-30°   | 125.0  | 4.1       |
| 30°-40°   | 152.2  | 5.0       |
| 40°-50°   | 163.8  | 5.4       |
| 50°-60°   | 159.1  | 5.2       |
| 60°-70°   | 138.9  | 4.6       |
| 70°-80°   | 106.9  | 3.5       |
| 80°-90°   | 73.5   | 2.4       |
| 90°-100°  | 91.1   | 3.0       |
| 100°-110° | 168.5  | 5.5       |
| 110°-120° | 250.3  | 8.2       |
| 120°-130° | 311.2  | 10.2      |
| 130°-140° | 340.0  | 11.2      |
| 140°-150° | 328.9  | 10.8      |
| 150°-160° | 275.1  | 9.0       |
| 160°-170° | 182.4  | 6.0       |
| 170°-180° | 63.8   | 2.1       |
| 0°-30°    | 236.3  | 7.8       |
| 0°-40°    | 388.5  | 12.8      |
| 0°-60°    | 711.5  | 23.4      |
| 0°-90°    | 1030.8 | 33.9      |
| 90°-120°  | 509.9  | 16.8      |
| 90°-150°  | 1489.9 | 49.0      |
| 90°-180°  | 2011.0 | 66.1      |
| 0°-180°   | 3042.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|------|-----|-------|-----|-------|-----|------|
| 0°   | 304 | 304   | 304 | 304   | 304 |      |
| 5°   | 304 | 303   | 300 | 303   | 303 | 29   |
| 15°  | 290 | 291   | 291 | 295   | 295 | 82   |
| 25°  | 264 | 267   | 271 | 276   | 278 | 121  |
| 35°  | 227 | 235   | 243 | 253   | 256 | 142  |
| 45°  | 186 | 198   | 214 | 227   | 232 | 144  |
| 55°  | 143 | 159   | 182 | 198   | 203 | 128  |
| 65°  | 98  | 119   | 145 | 163   | 169 | 97   |
| 75°  | 54  | 79    | 107 | 126   | 132 | 57   |
| 85°  | 16  | 43    | 71  | 90    | 96  | 17   |
| 90°  | 5   | 37    | 78  | 94    | 100 | 5    |
| 95°  | 33  | 59    | 87  | 104   | 108 | 36   |
| 105° | 124 | 139   | 163 | 179   | 184 | 131  |
| 115° | 229 | 237   | 256 | 268   | 272 | 226  |
| 125° | 332 | 337   | 349 | 359   | 363 | 296  |
| 135° | 428 | 434   | 440 | 449   | 450 | 331  |
| 145° | 519 | 523   | 527 | 530   | 530 | 324  |
| 155° | 594 | 595   | 597 | 600   | 598 | 273  |
| 165° | 646 | 645   | 645 | 649   | 646 | 182  |
| 175° | 672 | 670   | 669 | 673   | 670 | 64   |
| 180° | 673 | 673   | 673 | 673   | 673 |      |

TEST NUMBER: P1008884

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-D1

**CANDELA DISTRIBUTION (FULL):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 0°     | 303.5 | 303.5 | 303.5 | 303.5 | 303.5 |
| 2.5°   | 305.7 | 304.4 | 301.3 | 303.5 | 302.6 |
| 5°     | 304.4 | 303.0 | 300.4 | 303.0 | 302.6 |
| 7.5°   | 302.2 | 301.3 | 299.1 | 302.2 | 301.7 |
| 10°    | 299.5 | 298.6 | 297.3 | 300.8 | 300.4 |
| 12.5°  | 295.1 | 295.6 | 294.7 | 298.2 | 297.8 |
| 15°    | 290.3 | 291.2 | 291.2 | 295.1 | 294.7 |
| 17.5°  | 284.1 | 285.9 | 287.2 | 291.2 | 291.2 |
| 20°    | 278.0 | 280.2 | 281.9 | 286.8 | 286.8 |
| 22.5°  | 271.4 | 274.0 | 276.7 | 281.5 | 282.4 |
| 25°    | 263.9 | 267.0 | 270.9 | 276.2 | 277.5 |
| 27.5°  | 255.1 | 259.9 | 264.3 | 270.9 | 271.8 |
| 30°    | 246.3 | 252.0 | 257.7 | 264.8 | 266.1 |
| 32.5°  | 236.6 | 243.2 | 250.3 | 258.6 | 261.3 |
| 35°    | 227.4 | 234.9 | 243.2 | 252.9 | 256.0 |
| 37.5°  | 217.3 | 225.6 | 236.2 | 246.7 | 249.8 |
| 40°    | 207.2 | 216.8 | 228.7 | 240.2 | 244.1 |
| 42.5°  | 197.5 | 207.2 | 221.2 | 234.0 | 238.0 |
| 45°    | 186.5 | 198.4 | 213.8 | 227.4 | 231.8 |
| 47.5°  | 175.9 | 188.7 | 206.3 | 220.4 | 225.2 |
| 50°    | 164.9 | 178.6 | 198.4 | 213.3 | 218.2 |
| 52.5°  | 154.4 | 168.9 | 190.0 | 205.4 | 210.7 |
| 55°    | 142.9 | 158.8 | 181.7 | 197.5 | 203.2 |
| 57.5°  | 132.0 | 149.5 | 172.4 | 189.6 | 195.3 |
| 60°    | 120.1 | 139.0 | 164.1 | 180.8 | 186.9 |
| 62.5°  | 109.5 | 129.3 | 154.4 | 172.4 | 178.1 |
| 65°    | 97.6  | 119.2 | 145.1 | 163.2 | 168.9 |
| 67.5°  | 87.1  | 109.5 | 135.9 | 153.9 | 160.1 |
| 70°    | 75.7  | 98.5  | 125.8 | 144.7 | 150.0 |
| 72.5°  | 65.1  | 88.8  | 116.6 | 135.0 | 141.6 |
| 75°    | 54.1  | 78.7  | 106.9 | 125.8 | 131.5 |
| 77.5°  | 43.5  | 69.1  | 97.6  | 116.6 | 122.7 |
| 80°    | 33.0  | 59.8  | 88.4  | 106.9 | 113.0 |
| 82.5°  | 24.2  | 50.6  | 79.6  | 98.1  | 103.8 |
| 85°    | 15.8  | 43.1  | 71.3  | 89.7  | 95.9  |
| 87.5°  | 9.7   | 36.1  | 64.2  | 82.2  | 88.0  |
| 90°    | 5.0   | 37.3  | 78.0  | 94.4  | 100.2 |
| 92.5°  | 16.5  | 44.3  | 71.7  | 89.5  | 94.7  |
| 95°    | 33.0  | 59.4  | 87.0  | 103.7 | 107.8 |
| 97.5°  | 52.5  | 76.5  | 104.3 | 120.6 | 125.9 |
| 100°   | 75.2  | 96.1  | 122.4 | 138.7 | 142.9 |
| 102.5° | 98.6  | 116.6 | 142.6 | 159.0 | 163.3 |
| 105°   | 124.3 | 138.8 | 162.8 | 179.3 | 184.2 |
| 107.5° | 150.5 | 163.3 | 185.2 | 200.8 | 202.8 |
| 110°   | 175.1 | 187.3 | 208.8 | 222.9 | 226.0 |

TEST NUMBER: P1008884

CATALOG NUMBER: S122DIP-B290D530UB40-4F0-XX-W2A-D1

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 112.5° | 202.3 | 212.7 | 232.4 | 244.8 | 248.4 |
| 115°   | 229.0 | 237.2 | 255.9 | 268.5 | 271.6 |
| 117.5° | 255.2 | 263.3 | 278.9 | 290.4 | 293.1 |
| 120°   | 281.9 | 288.3 | 301.3 | 313.6 | 316.7 |
| 122.5° | 306.4 | 312.5 | 325.9 | 336.1 | 339.0 |
| 125°   | 331.5 | 336.6 | 349.0 | 359.1 | 362.6 |
| 127.5° | 356.5 | 362.3 | 371.9 | 380.6 | 382.9 |
| 130°   | 379.8 | 386.7 | 394.9 | 404.2 | 405.6 |
| 132.5° | 405.9 | 411.1 | 418.3 | 425.7 | 427.4 |
| 135°   | 428.2 | 434.4 | 440.0 | 448.7 | 450.5 |
| 137.5° | 453.2 | 458.3 | 461.6 | 469.4 | 470.3 |
| 140°   | 475.3 | 480.0 | 483.8 | 490.8 | 491.2 |
| 142.5° | 498.0 | 502.8 | 504.5 | 510.3 | 510.3 |
| 145°   | 519.2 | 523.2 | 526.6 | 529.8 | 529.7 |
| 147.5° | 538.5 | 543.7 | 545.9 | 547.5 | 546.6 |
| 150°   | 558.4 | 561.8 | 564.1 | 565.8 | 564.1 |
| 152.5° | 576.0 | 579.4 | 582.3 | 584.6 | 582.3 |
| 155°   | 593.6 | 595.4 | 597.1 | 599.9 | 598.2 |
| 157.5° | 609.0 | 610.1 | 611.3 | 615.2 | 612.4 |
| 160°   | 622.6 | 623.8 | 624.3 | 627.7 | 625.5 |
| 162.5° | 635.1 | 635.1 | 635.7 | 639.7 | 636.8 |
| 165°   | 645.9 | 645.3 | 645.3 | 649.3 | 646.5 |
| 167.5° | 655.6 | 653.9 | 653.9 | 657.8 | 655.0 |
| 170°   | 663.0 | 661.3 | 660.7 | 664.7 | 661.3 |
| 172.5° | 668.1 | 666.4 | 665.8 | 669.8 | 666.4 |
| 175°   | 672.0 | 670.3 | 669.2 | 673.2 | 669.8 |
| 177.5° | 674.3 | 672.6 | 671.5 | 674.9 | 671.5 |
| 180°   | 673.2 | 673.2 | 673.2 | 673.2 | 673.2 |

(END OF REPORT)