

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009367

Luminaire Tested: S122DIP-B675D725UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009367
REPORT IS A COMBINATION OF REPORTS P984638 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5270.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009367

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009367

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	60	59	51	50	49
2	89	82	76	71	82	76	71	66	65	61	57	54	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	41	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16967	16967	16967
5°	16995	16172	16058
10°	16856	15435	15129
15°	16609	14694	14152
20°	16276	13886	13227
25°	15944	13042	12304
30°	15524	12249	11334
35°	15131	11412	10383
40°	14643	10587	9482
45°	14159	9769	8599
50°	13628	8936	7684
55°	13073	8044	6817
60°	12447	7080	5915
65°	11760	6100	4967
70°	10892	5029	4010
75°	9683	3875	3097
80°	8231	2635	1993
85°	5975	1226	849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14159 cd/sqm

TEST NUMBER: P1009367

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.9
10°-20°	283.8	5.4
20°-30°	417.1	7.9
30°-40°	484.5	9.2
40°-50°	483.9	9.2
50°-60°	421.9	8.0
60°-70°	311.9	5.9
70°-80°	176.5	3.3
80°-90°	49.2	0.9
90°-100°	56.2	1.1
100°-110°	178.7	3.4
110°-120°	305.8	5.8
120°-130°	402.1	7.6
130°-140°	451.4	8.6
140°-150°	442.6	8.4
150°-160°	371.3	7.0
160°-170°	246.2	4.7
170°-180°	86.1	1.6
0°-30°	801.8	15.2
0°-40°	1286.3	24.4
0°-60°	2192.1	41.6
0°-90°	2729.6	51.8
90°-120°	540.7	10.3
90°-150°	1836.8	34.9
90°-180°	2540.0	48.2
0°-180°	5270.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1056	1065	1063	102
15°	1020	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	614	610	500
55°	491	484	472	460	454	439
65°	331	325	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	47
90°	1	10	27	25	26	5
95°	40	48	49	49	48	45
105°	165	167	169	170	170	174
115°	307	311	310	309	307	303
125°	446	453	451	449	448	399
135°	577	586	587	587	584	446
145°	701	706	711	712	708	438
155°	801	804	806	810	807	369
165°	872	871	871	876	873	246
175°	907	905	903	909	904	86
180°	909	909	909	909	909	

TEST NUMBER: P1009367

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1071.9	1071.9	1071.9	1071.9	1071.9
2.5°	1078.1	1072.9	1061.6	1071.9	1069.8
5°	1071.9	1067.7	1056.4	1064.7	1062.6
7.5°	1064.7	1058.5	1047.1	1055.4	1053.3
10°	1053.3	1046.1	1033.7	1042.0	1038.9
12.5°	1037.9	1031.7	1019.3	1024.5	1022.4
15°	1020.3	1014.2	1000.8	1004.9	999.7
17.5°	998.7	992.5	979.1	984.3	979.1
20°	975.0	968.8	954.4	957.5	953.3
22.5°	951.3	942.0	928.6	928.6	926.5
25°	923.5	915.2	897.7	899.7	897.7
27.5°	892.5	885.3	871.9	868.8	863.7
30°	861.6	853.4	837.9	834.8	830.7
32.5°	828.6	822.5	806.0	799.8	795.7
35°	796.7	786.4	769.9	763.7	758.6
37.5°	760.6	751.3	734.8	727.6	722.5
40°	723.5	715.3	698.8	689.5	685.4
42.5°	687.4	679.2	662.7	652.4	646.2
45°	648.3	641.1	625.6	614.3	610.1
47.5°	610.1	602.9	586.4	575.1	568.9
50°	569.9	564.8	550.4	535.9	530.8
52.5°	530.8	523.6	510.2	498.8	491.6
55°	490.6	484.4	472.0	459.7	454.5
57.5°	450.4	445.2	431.8	419.5	415.3
60°	410.2	406.1	391.6	380.3	377.2
62.5°	371.0	363.8	353.5	343.2	339.1
65°	330.8	324.7	314.3	305.1	299.9
67.5°	289.6	284.5	275.2	268.0	263.8
70°	251.5	247.4	238.1	230.9	226.7
72.5°	212.3	208.2	203.0	195.8	192.7
75°	173.1	171.1	165.9	159.7	161.8
77.5°	138.1	134.0	131.9	128.8	125.7
80°	103.1	102.0	100.0	96.9	94.8
82.5°	70.1	70.1	69.1	64.9	64.9
85°	42.3	41.2	40.2	37.1	36.1
87.5°	18.6	16.5	14.4	11.3	10.3
90°	0.8	10.0	26.8	25.3	26.1
92.5°	16.9	23.0	23.8	24.5	24.5
95°	39.9	47.5	49.1	49.1	47.5
97.5°	66.7	73.6	76.7	76.7	76.7
100°	97.4	103.5	105.8	105.8	105.1
102.5°	129.6	134.2	137.3	138.0	137.3
105°	164.9	167.2	168.7	170.2	170.2
107.5°	200.1	203.2	203.2	204.0	200.1
110°	233.9	238.5	238.5	238.5	236.2

TEST NUMBER: P1009367

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	270.7	275.3	274.5	272.2	270.7
115°	306.7	311.3	309.8	309.0	306.7
117.5°	342.8	348.9	345.1	342.8	340.5
120°	378.8	384.9	378.8	378.8	376.5
122.5°	411.8	419.4	415.6	413.3	411.8
125°	446.3	453.2	450.9	448.6	447.8
127.5°	480.0	488.4	485.4	482.3	480.0
130°	511.5	521.4	519.9	518.4	515.3
132.5°	546.7	554.4	555.2	551.3	549.0
135°	577.4	585.8	587.4	586.6	584.3
137.5°	611.1	618.0	619.6	618.8	615.7
140°	641.0	647.9	651.8	651.8	648.7
142.5°	671.7	678.6	680.9	681.7	678.6
145°	700.8	706.2	710.8	711.6	708.5
147.5°	726.9	733.8	736.9	738.4	735.4
150°	753.8	758.4	761.4	763.7	761.4
152.5°	777.5	782.1	786.0	789.0	786.0
155°	801.3	803.6	805.9	809.7	807.4
157.5°	822.0	823.5	825.1	830.4	826.6
160°	840.4	841.9	842.7	847.3	844.2
162.5°	857.3	857.3	858.0	863.4	859.6
165°	871.8	871.1	871.1	876.4	872.6
167.5°	884.9	882.6	882.6	887.9	884.1
170°	894.8	892.5	891.8	897.1	892.5
172.5°	901.7	899.4	898.7	904.0	899.4
175°	907.1	904.8	903.3	908.7	904.0
177.5°	910.2	907.9	906.3	911.0	906.3
180°	908.7	908.7	908.7	908.7	908.7

(END OF REPORT)