

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009395

Luminaire Tested: S122DIP-B675D925UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009395
REPORT IS A COMBINATION OF REPORTS P984666 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D925UB27-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6247.1 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009395

CATALOG NUMBER: S122DIP-B675D925UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009395

CATALOG NUMBER: S122DIP-B675D925UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20
7	57	45	37	32	52	41	34	30	35	29	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16749	16749	16749
5°	16776	15964	15853
10°	16640	15238	14936
15°	16396	14504	13971
20°	16067	13707	13057
25°	15738	12875	12146
30°	15326	12092	11188
35°	14937	11266	10249
40°	14455	10451	9361
45°	13978	9644	8489
50°	13454	8821	7586
55°	12905	7942	6730
60°	12287	6990	5840
65°	11610	6022	4904
70°	10749	4963	3959
75°	9560	3826	3057
80°	8119	2601	1968
85°	5890	1211	837

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13978 cd/sqm

TEST NUMBER: P1009395

CATALOG NUMBER: S122DIP-B675D925UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.6
10°-20°	280.2	4.5
20°-30°	411.8	6.6
30°-40°	478.3	7.7
40°-50°	477.7	7.6
50°-60°	416.5	6.7
60°-70°	307.9	4.9
70°-80°	174.2	2.8
80°-90°	49.2	0.8
90°-100°	206.5	3.3
100°-110°	698.2	11.2
110°-120°	733.9	11.7
120°-130°	603.5	9.7
130°-140°	484.9	7.8
140°-150°	366.3	5.9
150°-160°	257.5	4.1
160°-170°	151.6	2.4
170°-180°	49.3	0.8
0°-30°	791.6	12.7
0°-40°	1269.8	20.3
0°-60°	2164.0	34.6
0°-90°	2695.2	43.1
90°-120°	1638.5	26.2
90°-150°	3093.3	49.5
90°-180°	3552.0	56.9
0°-180°	6247.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1058	1058	1058	1058	1058	
5°	1058	1054	1043	1051	1049	100
15°	1007	1001	988	992	987	284
25°	912	904	886	888	886	419
35°	786	776	760	754	749	491
45°	640	633	618	606	602	494
55°	484	478	466	454	449	433
65°	327	320	310	301	296	323
75°	171	169	164	158	160	182
85°	42	41	40	37	36	46
90°	1	13	33	32	32	5
95°	34	84	384	145	112	35
105°	120	180	726	1298	1104	127
115°	211	266	607	1254	1453	209
125°	294	348	584	1015	1179	261
135°	345	412	577	853	977	266
145°	394	453	574	713	780	247
155°	448	483	557	630	655	206
165°	488	503	534	566	575	138
175°	508	509	513	520	518	48
180°	509	509	509	509	509	

TEST NUMBER: P1009395

CATALOG NUMBER: S122DIP-B675D925UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1058.1	1058.1	1058.1	1058.1	1058.1
2.5°	1064.2	1059.1	1047.9	1058.1	1056.1
5°	1058.1	1054.0	1042.8	1051.0	1049.0
7.5°	1051.0	1044.9	1033.7	1041.8	1039.8
10°	1039.8	1032.7	1020.5	1028.6	1025.6
12.5°	1024.5	1018.4	1006.2	1011.3	1009.3
15°	1007.2	1001.1	987.9	992.0	986.9
17.5°	985.9	979.8	966.5	971.6	966.5
20°	962.5	956.4	942.1	945.2	941.1
22.5°	939.1	929.9	916.7	916.7	914.7
25°	911.6	903.5	886.2	888.2	886.2
27.5°	881.1	874.0	860.7	857.7	852.6
30°	850.6	842.4	827.2	824.1	820.0
32.5°	818.0	811.9	795.6	789.5	785.4
35°	786.5	776.3	760.0	753.9	748.8
37.5°	750.9	741.7	725.4	718.3	713.2
40°	714.2	706.1	689.8	680.6	676.6
42.5°	678.6	670.5	654.2	644.0	637.9
45°	640.0	632.8	617.6	606.4	602.3
47.5°	602.3	595.2	578.9	567.7	561.6
50°	562.6	557.5	543.3	529.1	524.0
52.5°	524.0	516.8	503.6	492.4	485.3
55°	484.3	478.2	466.0	453.8	448.7
57.5°	444.6	439.5	426.3	414.1	410.0
60°	404.9	400.9	386.6	375.4	372.4
62.5°	366.3	359.1	349.0	338.8	334.7
65°	326.6	320.5	310.3	301.2	296.1
67.5°	285.9	280.8	271.6	264.5	260.5
70°	248.2	244.2	235.0	227.9	223.8
72.5°	209.6	205.5	200.4	193.3	190.3
75°	170.9	168.9	163.8	157.7	159.7
77.5°	136.3	132.3	130.2	127.2	124.1
80°	101.7	100.7	98.7	95.6	93.6
82.5°	69.2	69.2	68.2	64.1	64.1
85°	41.7	40.7	39.7	36.6	35.6
87.5°	18.3	16.3	14.2	11.2	10.2
90°	1.0	13.2	33.3	31.8	32.3
92.5°	14.7	46.5	150.9	69.6	59.8
95°	34.3	84.2	384.0	145.0	111.7
97.5°	50.9	111.2	626.0	291.0	187.1
100°	75.4	136.2	774.0	579.5	350.7
102.5°	98.0	158.7	778.8	979.7	683.8
105°	119.5	180.2	725.9	1297.6	1104.1
107.5°	143.0	201.8	677.0	1412.7	1387.2
110°	166.5	223.9	643.7	1394.1	1502.8

TEST NUMBER: P1009395

CATALOG NUMBER: S122DIP-B675D925UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.1	244.9	622.1	1330.9	1500.9
115°	210.6	266.0	607.4	1253.6	1452.9
117.5°	234.1	287.0	599.6	1179.5	1380.4
120°	255.7	307.6	592.7	1113.4	1310.8
122.5°	276.3	328.7	588.8	1062.0	1238.3
125°	293.9	347.8	583.9	1015.4	1178.6
127.5°	308.6	365.9	581.0	975.8	1122.7
130°	321.3	382.1	579.0	935.6	1076.7
132.5°	333.1	397.8	578.0	894.0	1028.7
135°	344.8	411.5	577.0	853.3	976.7
137.5°	355.6	423.2	577.0	812.2	926.8
140°	368.4	434.0	576.1	776.0	874.9
142.5°	381.1	442.8	576.1	741.2	822.9
145°	393.8	452.6	574.1	712.7	779.8
147.5°	407.5	460.4	571.2	687.8	741.6
150°	421.3	468.3	568.2	666.2	708.3
152.5°	435.0	476.2	563.3	648.0	679.9
155°	447.7	483.4	557.4	630.4	655.4
157.5°	458.5	489.4	551.6	613.8	633.9
160°	469.3	495.2	545.7	597.1	613.3
162.5°	480.0	499.6	540.8	581.4	593.7
165°	487.9	502.6	533.9	566.2	575.1
167.5°	494.7	505.6	528.1	552.6	557.4
170°	501.6	507.0	523.2	539.8	541.8
172.5°	505.5	508.4	517.3	528.6	529.0
175°	508.5	509.0	513.4	519.7	518.3
177.5°	510.4	509.4	509.4	513.4	510.4
180°	509.4	509.4	509.4	509.4	509.4

(END OF REPORT)