

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008923

Luminaire Tested: S122DIP-B290D725UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008923
REPORT IS A COMBINATION OF REPORTS P984038 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3718.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008923

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008923

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	53	50	43	40	38	30	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7310	7310	7310
5°	7322	6969	6918
10°	7262	6651	6518
15°	7156	6331	6099
20°	7013	5983	5700
25°	6870	5619	5302
30°	6688	5277	4883
35°	6520	4917	4473
40°	6309	4562	4085
45°	6100	4210	3706
50°	5873	3850	3311
55°	5633	3467	2937
60°	5362	3050	2548
65°	5066	2628	2140
70°	4694	2167	1728
75°	4173	1670	1334
80°	3545	1136	860
85°	2571	528	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6100 cd/sqm

TEST NUMBER: P1008923

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	1.2
10°-20°	122.3	3.3
20°-30°	179.7	4.8
30°-40°	208.7	5.6
40°-50°	208.5	5.6
50°-60°	181.8	4.9
60°-70°	134.4	3.6
70°-80°	76.0	2.0
80°-90°	22.7	0.6
90°-100°	56.2	1.5
100°-110°	178.7	4.8
110°-120°	305.8	8.2
120°-130°	402.1	10.8
130°-140°	451.4	12.1
140°-150°	442.6	11.9
150°-160°	371.3	10.0
160°-170°	246.2	6.6
170°-180°	86.1	2.3
0°-30°	345.5	9.3
0°-40°	554.2	14.9
0°-60°	944.5	25.4
0°-90°	1177.6	31.7
90°-120°	540.7	14.5
90°-150°	1836.8	49.4
90°-180°	2540.0	68.3
0°-180°	3718.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	462	460	455	459	458	44
15°	440	437	431	433	431	124
25°	398	394	387	388	387	183
35°	343	339	332	329	327	214
45°	279	276	270	265	263	216
55°	211	209	203	198	196	189
65°	142	140	135	131	129	141
75°	75	74	72	69	70	80
85°	18	18	17	16	16	20
90°	1	10	27	25	26	4
95°	40	48	49	49	48	45
105°	165	167	169	170	170	174
115°	307	311	310	309	307	303
125°	446	453	451	449	448	399
135°	577	586	587	587	584	446
145°	701	706	711	712	708	438
155°	801	804	806	810	807	369
165°	872	871	871	876	873	246
175°	907	905	903	909	904	86
180°	909	909	909	909	909	

TEST NUMBER: P1008923

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	461.8	461.8	461.8	461.8	461.8
2.5°	464.5	462.3	457.4	461.8	461.0
5°	461.8	460.1	455.2	458.7	457.8
7.5°	458.7	456.1	451.2	454.7	453.8
10°	453.8	450.7	445.4	449.0	447.6
12.5°	447.2	444.5	439.2	441.4	440.5
15°	439.6	437.0	431.2	433.0	430.8
17.5°	430.3	427.6	421.9	424.1	421.9
20°	420.1	417.4	411.2	412.5	410.8
22.5°	409.9	405.9	400.1	400.1	399.2
25°	397.9	394.3	386.8	387.7	386.8
27.5°	384.6	381.5	375.7	374.4	372.1
30°	371.2	367.7	361.0	359.7	357.9
32.5°	357.0	354.4	347.3	344.6	342.8
35°	343.3	338.8	331.7	329.1	326.8
37.5°	327.7	323.7	316.6	313.5	311.3
40°	311.7	308.2	301.1	297.1	295.3
42.5°	296.2	292.6	285.5	281.1	278.4
45°	279.3	276.2	269.6	264.7	262.9
47.5°	262.9	259.8	252.7	247.8	245.1
50°	245.6	243.4	237.1	230.9	228.7
52.5°	228.7	225.6	219.8	214.9	211.8
55°	211.4	208.7	203.4	198.1	195.8
57.5°	194.1	191.8	186.1	180.7	179.0
60°	176.7	175.0	168.7	163.9	162.5
62.5°	159.9	156.8	152.3	147.9	146.1
65°	142.5	139.9	135.4	131.4	129.2
67.5°	124.8	122.6	118.6	115.5	113.7
70°	108.4	106.6	102.6	99.5	97.7
72.5°	91.5	89.7	87.5	84.4	83.0
75°	74.6	73.7	71.5	68.8	69.7
77.5°	59.5	57.7	56.8	55.5	54.2
80°	44.4	44.0	43.1	41.7	40.9
82.5°	30.2	30.2	29.8	28.0	28.0
85°	18.2	17.8	17.3	16.0	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	0.8	10.0	26.8	25.3	26.1
92.5°	16.9	23.0	23.8	24.5	24.5
95°	39.9	47.5	49.1	49.1	47.5
97.5°	66.7	73.6	76.7	76.7	76.7
100°	97.4	103.5	105.8	105.8	105.1
102.5°	129.6	134.2	137.3	138.0	137.3
105°	164.9	167.2	168.7	170.2	170.2
107.5°	200.1	203.2	203.2	204.0	200.1
110°	233.9	238.5	238.5	238.5	236.2

TEST NUMBER: P1008923

CATALOG NUMBER: S122DIP-B290D725UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	270.7	275.3	274.5	272.2	270.7
115°	306.7	311.3	309.8	309.0	306.7
117.5°	342.8	348.9	345.1	342.8	340.5
120°	378.8	384.9	378.8	378.8	376.5
122.5°	411.8	419.4	415.6	413.3	411.8
125°	446.3	453.2	450.9	448.6	447.8
127.5°	480.0	488.4	485.4	482.3	480.0
130°	511.5	521.4	519.9	518.4	515.3
132.5°	546.7	554.4	555.2	551.3	549.0
135°	577.4	585.8	587.4	586.6	584.3
137.5°	611.1	618.0	619.6	618.8	615.7
140°	641.0	647.9	651.8	651.8	648.7
142.5°	671.7	678.6	680.9	681.7	678.6
145°	700.8	706.2	710.8	711.6	708.5
147.5°	726.9	733.8	736.9	738.4	735.4
150°	753.8	758.4	761.4	763.7	761.4
152.5°	777.5	782.1	786.0	789.0	786.0
155°	801.3	803.6	805.9	809.7	807.4
157.5°	822.0	823.5	825.1	830.4	826.6
160°	840.4	841.9	842.7	847.3	844.2
162.5°	857.3	857.3	858.0	863.4	859.6
165°	871.8	871.1	871.1	876.4	872.6
167.5°	884.9	882.6	882.6	887.9	884.1
170°	894.8	892.5	891.8	897.1	892.5
172.5°	901.7	899.4	898.7	904.0	899.4
175°	907.1	904.8	903.3	908.7	904.0
177.5°	910.2	907.9	906.3	911.0	906.3
180°	908.7	908.7	908.7	908.7	908.7

(END OF REPORT)