

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009412

Luminaire Tested: S122DIP-B675D925UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009412
REPORT IS A COMBINATION OF REPORTS P984698 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D925UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6018.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009412

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009412

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44
2	88	81	75	69	80	74	69	64	62	58	55	51	48	46	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	36	33	31
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16967	16967	16967
5°	16995	16172	16058
10°	16856	15435	15129
15°	16609	14694	14152
20°	16276	13886	13227
25°	15944	13042	12304
30°	15524	12249	11334
35°	15131	11412	10383
40°	14643	10587	9482
45°	14159	9769	8599
50°	13628	8936	7684
55°	13073	8044	6817
60°	12447	7080	5915
65°	11760	6100	4967
70°	10892	5029	4010
75°	9683	3875	3097
80°	8231	2635	1993
85°	5975	1226	849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14159 cd/sqm

TEST NUMBER: P1009412

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.7
10°-20°	283.8	4.7
20°-30°	417.1	6.9
30°-40°	484.5	8.1
40°-50°	483.9	8.0
50°-60°	421.9	7.0
60°-70°	311.9	5.2
70°-80°	176.5	2.9
80°-90°	49.9	0.8
90°-100°	72.7	1.2
100°-110°	231.3	3.8
110°-120°	395.7	6.6
120°-130°	520.4	8.6
130°-140°	584.1	9.7
140°-150°	572.8	9.5
150°-160°	480.5	8.0
160°-170°	318.7	5.3
170°-180°	111.4	1.9
0°-30°	801.8	13.3
0°-40°	1286.3	21.4
0°-60°	2192.1	36.4
0°-90°	2730.3	45.4
90°-120°	699.7	11.6
90°-150°	2377.1	39.5
90°-180°	3288.0	54.6
0°-180°	6018.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1056	1065	1063	102
15°	1020	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	614	610	500
55°	491	484	472	460	454	439
65°	331	325	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	47
90°	1	13	35	33	34	6
95°	52	62	64	64	62	58
105°	213	216	218	220	220	225
115°	397	403	401	400	397	393
125°	578	586	584	580	580	516
135°	747	758	760	759	756	577
145°	907	914	920	921	917	567
155°	1037	1040	1043	1048	1045	477
165°	1128	1127	1127	1134	1129	318
175°	1174	1171	1169	1176	1170	112
180°	1176	1176	1176	1176	1176	

TEST NUMBER: P1009412

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1071.9	1071.9	1071.9	1071.9	1071.9
2.5°	1078.1	1072.9	1061.6	1071.9	1069.8
5°	1071.9	1067.7	1056.4	1064.7	1062.6
7.5°	1064.7	1058.5	1047.1	1055.4	1053.3
10°	1053.3	1046.1	1033.7	1042.0	1038.9
12.5°	1037.9	1031.7	1019.3	1024.5	1022.4
15°	1020.3	1014.2	1000.8	1004.9	999.7
17.5°	998.7	992.5	979.1	984.3	979.1
20°	975.0	968.8	954.4	957.5	953.3
22.5°	951.3	942.0	928.6	928.6	926.5
25°	923.5	915.2	897.7	899.7	897.7
27.5°	892.5	885.3	871.9	868.8	863.7
30°	861.6	853.4	837.9	834.8	830.7
32.5°	828.6	822.5	806.0	799.8	795.7
35°	796.7	786.4	769.9	763.7	758.6
37.5°	760.6	751.3	734.8	727.6	722.5
40°	723.5	715.3	698.8	689.5	685.4
42.5°	687.4	679.2	662.7	652.4	646.2
45°	648.3	641.1	625.6	614.3	610.1
47.5°	610.1	602.9	586.4	575.1	568.9
50°	569.9	564.8	550.4	535.9	530.8
52.5°	530.8	523.6	510.2	498.8	491.6
55°	490.6	484.4	472.0	459.7	454.5
57.5°	450.4	445.2	431.8	419.5	415.3
60°	410.2	406.1	391.6	380.3	377.2
62.5°	371.0	363.8	353.5	343.2	339.1
65°	330.8	324.7	314.3	305.1	299.9
67.5°	289.6	284.5	275.2	268.0	263.8
70°	251.5	247.4	238.1	230.9	226.7
72.5°	212.3	208.2	203.0	195.8	192.7
75°	173.1	171.1	165.9	159.7	161.8
77.5°	138.1	134.0	131.9	128.8	125.7
80°	103.1	102.0	100.0	96.9	94.8
82.5°	70.1	70.1	69.1	64.9	64.9
85°	42.3	41.2	40.2	37.1	36.1
87.5°	18.6	16.5	14.4	11.3	10.3
90°	1.0	12.9	34.7	32.7	33.7
92.5°	21.8	29.8	30.8	31.8	31.8
95°	51.6	61.5	63.5	63.5	61.5
97.5°	86.3	95.3	99.2	99.2	99.2
100°	126.0	134.0	136.9	136.9	136.0
102.5°	167.7	173.7	177.6	178.6	177.6
105°	213.4	216.3	218.3	220.3	220.3
107.5°	259.0	263.0	263.0	264.0	259.0
110°	302.7	308.6	308.6	308.6	305.6

TEST NUMBER: P1009412

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.3	356.2	355.3	352.3	350.3
115°	396.9	402.9	400.9	399.9	396.9
117.5°	443.6	451.5	446.6	443.6	440.6
120°	490.2	498.2	490.2	490.2	487.2
122.5°	532.9	542.8	537.8	534.9	532.9
125°	577.5	586.5	583.5	580.5	579.5
127.5°	621.2	632.1	628.2	624.2	621.2
130°	661.9	674.8	672.8	670.8	666.9
132.5°	707.5	717.5	718.5	713.5	710.5
135°	747.2	758.1	760.1	759.1	756.2
137.5°	790.9	799.8	801.8	800.8	796.8
140°	829.6	838.5	843.5	843.5	839.5
142.5°	869.3	878.2	881.2	882.2	878.2
145°	907.0	913.9	919.9	920.9	916.9
147.5°	940.7	949.7	953.6	955.6	951.7
150°	975.5	981.4	985.4	988.4	985.4
152.5°	1006.2	1012.2	1017.1	1021.1	1017.1
155°	1037.0	1040.0	1042.9	1047.9	1044.9
157.5°	1063.8	1065.8	1067.8	1074.7	1069.7
160°	1087.6	1089.6	1090.6	1096.5	1092.6
162.5°	1109.4	1109.4	1110.4	1117.4	1112.4
165°	1128.3	1127.3	1127.3	1134.2	1129.3
167.5°	1145.2	1142.2	1142.2	1149.1	1144.2
170°	1158.1	1155.1	1154.1	1161.0	1155.1
172.5°	1167.0	1164.0	1163.0	1170.0	1164.0
175°	1173.9	1171.0	1169.0	1175.9	1170.0
177.5°	1177.9	1174.9	1172.9	1178.9	1172.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9

(END OF REPORT)