

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008942

Luminaire Tested: S122DIP-B290D725UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008942
REPORT IS A COMBINATION OF REPORTS P984057 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D725UB50-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3789.0 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008942

CATALOG NUMBER: S122DIP-B290D725UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008942

CATALOG NUMBER: S122DIP-B290D725UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32
2	85	78	72	67	76	70	65	61	55	52	49	42	39	37	29	28	27
3	77	68	61	56	69	61	55	51	49	44	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	38	35	33	30	27	23	21	19
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	21	19	17
6	60	48	40	34	53	43	37	32	35	30	26	26	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	18	16	16	13	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	32	25	21	40	29	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7000	7000	7000
5°	7011	6672	6625
10°	6953	6368	6242
15°	6852	6062	5838
20°	6714	5728	5457
25°	6578	5380	5075
30°	6405	5054	4676
35°	6243	4708	4283
40°	6041	4368	3911
45°	5840	4030	3548
50°	5622	3686	3170
55°	5393	3318	2812
60°	5134	2922	2440
65°	4852	2517	2049
70°	4491	2074	1654
75°	3994	1600	1279
80°	3393	1086	822
85°	2458	506	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5840 cd/sqm

TEST NUMBER: P1008942

CATALOG NUMBER: S122DIP-B290D725UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	1.1
10°-20°	117.1	3.1
20°-30°	172.1	4.5
30°-40°	199.9	5.3
40°-50°	199.6	5.3
50°-60°	174.1	4.6
60°-70°	128.7	3.4
70°-80°	72.8	1.9
80°-90°	21.7	0.6
90°-100°	154.7	4.1
100°-110°	523.2	13.8
110°-120°	549.9	14.5
120°-130°	452.2	11.9
130°-140°	363.4	9.6
140°-150°	274.5	7.2
150°-160°	193.0	5.1
160°-170°	113.6	3.0
170°-180°	37.0	1.0
0°-30°	330.8	8.7
0°-40°	530.7	14.0
0°-60°	904.3	23.9
0°-90°	1127.4	29.8
90°-120°	1227.9	32.4
90°-150°	2318.0	61.2
90°-180°	2662.0	70.3
0°-180°	3789.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	439	438	42
15°	421	418	413	415	412	119
25°	381	378	370	371	370	175
35°	329	324	318	315	313	205
45°	267	264	258	253	252	206
55°	202	200	195	190	188	181
65°	136	134	130	126	124	135
75°	71	71	68	66	67	76
85°	17	17	17	15	15	19
90°	1	10	25	24	24	3
95°	26	63	288	109	84	27
105°	90	135	544	972	827	95
115°	158	199	455	939	1089	157
125°	220	261	438	761	883	196
135°	258	308	432	639	732	200
145°	295	339	430	534	584	185
155°	336	362	418	472	491	154
165°	366	377	400	424	431	103
175°	381	381	385	390	388	36
180°	382	382	382	382	382	

TEST NUMBER: P1008942

CATALOG NUMBER: S122DIP-B290D725UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	442.2	442.2	442.2	442.2	442.2
2.5°	444.7	442.6	437.9	442.2	441.3
5°	442.2	440.5	435.8	439.2	438.4
7.5°	439.2	436.7	432.0	435.4	434.5
10°	434.5	431.6	426.5	429.9	428.6
12.5°	428.2	425.6	420.5	422.6	421.8
15°	420.9	418.4	412.9	414.6	412.4
17.5°	412.0	409.5	403.9	406.0	403.9
20°	402.2	399.7	393.7	395.0	393.3
22.5°	392.4	388.6	383.1	383.1	382.2
25°	381.0	377.6	370.3	371.2	370.3
27.5°	368.2	365.2	359.7	358.4	356.3
30°	355.5	352.1	345.7	344.4	342.7
32.5°	341.8	339.3	332.5	329.9	328.2
35°	328.7	324.4	317.6	315.1	312.9
37.5°	313.8	310.0	303.2	300.2	298.1
40°	298.5	295.1	288.3	284.4	282.7
42.5°	283.6	280.2	273.4	269.1	266.6
45°	267.4	264.5	258.1	253.4	251.7
47.5°	251.7	248.7	241.9	237.3	234.7
50°	235.1	233.0	227.0	221.1	219.0
52.5°	219.0	216.0	210.5	205.8	202.8
55°	202.4	199.8	194.7	189.6	187.5
57.5°	185.8	183.7	178.2	173.0	171.3
60°	169.2	167.5	161.6	156.9	155.6
62.5°	153.1	150.1	145.8	141.6	139.9
65°	136.5	133.9	129.7	125.9	123.7
67.5°	119.5	117.4	113.5	110.5	108.8
70°	103.7	102.0	98.2	95.2	93.5
72.5°	87.6	85.9	83.8	80.8	79.5
75°	71.4	70.6	68.5	65.9	66.8
77.5°	57.0	55.3	54.4	53.1	51.9
80°	42.5	42.1	41.2	40.0	39.1
82.5°	28.9	28.9	28.5	26.8	26.8
85°	17.4	17.0	16.6	15.3	14.9
87.5°	7.7	6.8	6.0	4.7	4.3
90°	0.7	9.9	25.0	23.8	24.2
92.5°	11.0	34.8	113.1	52.2	44.8
95°	25.7	63.1	287.8	108.6	83.7
97.5°	38.2	83.3	469.1	218.0	140.2
100°	56.5	102.0	580.0	434.2	262.8
102.5°	73.4	119.0	583.6	734.2	512.4
105°	89.6	135.1	544.0	972.4	827.4
107.5°	107.2	151.2	507.3	1058.6	1039.5
110°	124.8	167.8	482.3	1044.7	1126.2

TEST NUMBER: P1008942

CATALOG NUMBER: S122DIP-B290D725UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.0	183.5	466.2	997.3	1124.7
115°	157.8	199.3	455.2	939.3	1088.7
117.5°	175.5	215.1	449.3	883.9	1034.4
120°	191.6	230.5	444.2	834.4	982.3
122.5°	207.0	246.3	441.2	795.8	928.0
125°	220.2	260.6	437.5	761.0	883.2
127.5°	231.3	274.2	435.3	731.2	841.3
130°	240.8	286.3	433.9	701.1	806.8
132.5°	249.6	298.0	433.1	669.9	770.8
135°	258.4	308.4	432.4	639.4	731.9
137.5°	266.5	317.2	432.4	608.6	694.5
140°	276.0	325.2	431.7	581.4	655.6
142.5°	285.6	331.8	431.7	555.4	616.7
145°	295.1	339.2	430.2	534.0	584.4
147.5°	305.4	345.0	428.0	515.4	555.7
150°	315.7	350.9	425.8	499.2	530.8
152.5°	326.0	356.8	422.1	485.6	509.5
155°	335.5	362.3	417.7	472.4	491.1
157.5°	343.6	366.7	413.3	459.9	475.0
160°	351.7	371.1	408.9	447.4	459.6
162.5°	359.7	374.4	405.2	435.7	444.9
165°	365.6	376.6	400.1	424.4	430.9
167.5°	370.7	378.8	395.7	414.0	417.7
170°	375.9	379.9	392.0	404.5	406.0
172.5°	378.8	381.0	387.6	396.0	396.4
175°	381.0	381.4	384.7	389.5	388.4
177.5°	382.5	381.8	381.8	384.7	382.5
180°	381.8	381.8	381.8	381.8	381.8

(END OF REPORT)