

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009425

Luminaire Tested: S122DIP-B675D925UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009425
REPORT IS A COMBINATION OF REPORTS P984711 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D925UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6276.0 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29
5	69	57	50	44	63	53	46	41	45	40	36	37	33	30	30	28	25
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20367	21665	20445	17235
10°	20130	23650	20257	14211
15°	19642	24945	19915	11969
20°	19336	23422	19336	10403
25°	18720	20122	18804	9304
30°	17706	15818	18043	8427
35°	16808	10938	17089	7711
40°	15774	8258	15954	7139
45°	14502	6787	14738	6522
50°	13401	5956	13425	5970
55°	12145	5075	12225	5371
60°	10809	4239	10957	4687
65°	9609	3448	9787	4003
70°	8419	2705	8631	3229
75°	7065	1964	7339	2341
80°	5517	1245	5908	1390
85°	3630	626	3899	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21003 cd/sqm

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	1.9
10°-20°	355.8	5.7
20°-30°	516.4	8.2
30°-40°	544.4	8.7
40°-50°	481.8	7.7
50°-60°	384.7	6.1
60°-70°	261.3	4.2
70°-80°	133.7	2.1
80°-90°	34.8	0.6
90°-100°	192.6	3.1
100°-110°	678.3	10.8
110°-120°	712.4	11.4
120°-130°	586.1	9.3
130°-140°	470.8	7.5
140°-150°	355.6	5.7
150°-160°	250.0	4.0
160°-170°	147.2	2.3
170°-180°	47.9	0.8
0°-30°	994.6	15.8
0°-40°	1539.0	24.5
0°-60°	2405.4	38.3
0°-90°	2835.2	45.2
90°-120°	1583.3	25.2
90°-150°	2995.8	47.7
90°-180°	3441.0	54.8
0°-180°	6276.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	30
90°	1	31	1	31	1	4
95°	33	108	33	108	33	34
105°	116	1071	116	1071	116	123
115°	204	1409	204	1409	204	203
125°	285	1143	285	1143	285	253
135°	334	947	334	947	334	258
145°	382	756	382	756	382	240
155°	434	636	434	636	434	200
165°	473	558	473	558	473	133
175°	493	503	493	503	493	47
180°	494	494	494	494	494	

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	1.0	3.8	7.6	9.5	11.4	12.8	14.3	19.0	25.7	31.4	32.3
92.5°	14.3	20.0	27.6	32.3	39.9	45.2	50.4	76.0	112.1	144.4	146.3
95°	33.3	37.1	46.6	55.1	70.3	81.7	93.1	136.8	219.5	329.7	372.5
97.5°	49.4	55.1	65.6	77.9	95.0	107.8	120.7	176.7	291.7	469.4	607.2
100°	73.2	76.0	84.6	99.8	118.8	132.1	145.4	195.7	311.7	516.9	750.6
102.5°	95.0	96.9	105.5	120.7	140.6	153.9	167.2	212.8	312.6	498.8	755.4
105°	115.9	119.7	126.4	140.6	161.5	174.8	188.1	232.8	317.4	474.1	704.1
107.5°	138.7	141.6	148.2	161.5	182.4	195.7	209.0	252.7	327.8	460.8	656.6
110°	161.5	165.3	171.0	183.4	203.3	217.1	230.9	272.7	341.1	457.0	624.3

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	182.4	186.2	192.9	204.3	223.3	237.6	251.8	291.7	355.4	458.0	603.4
115°	204.3	209.0	214.7	226.1	245.1	258.0	270.8	311.7	369.6	461.8	589.1
117.5°	227.1	230.9	236.6	247.0	265.1	278.4	291.7	329.7	384.8	467.5	581.5
120°	248.0	251.8	257.5	266.0	285.0	298.4	311.7	348.7	400.0	473.2	574.8
122.5°	267.9	270.8	276.5	286.0	305.0	318.8	332.6	366.8	413.3	479.8	571.0
125°	285.0	287.9	293.6	305.0	324.0	337.3	350.6	384.8	427.6	486.5	566.3
127.5°	299.3	303.1	310.7	323.1	341.1	354.9	368.7	401.9	440.9	493.1	563.4
130°	311.7	315.5	325.0	338.3	357.3	370.6	383.9	417.1	453.2	500.7	561.5
132.5°	323.1	327.8	338.3	352.5	372.5	385.8	399.1	430.4	465.6	508.3	560.6
135°	334.5	338.3	349.7	363.9	385.8	399.1	412.4	442.8	476.0	514.0	559.6
137.5°	344.9	349.7	361.1	376.3	398.1	410.4	422.8	453.2	484.6	519.7	559.6
140°	357.3	361.1	372.5	387.7	408.6	421.0	433.3	461.8	491.2	523.5	558.7
142.5°	369.6	372.5	382.9	398.1	418.1	429.5	440.9	468.4	496.9	526.4	558.7
145°	382.0	385.8	395.3	409.5	428.5	439.0	449.4	475.1	501.7	528.3	556.8
147.5°	395.3	398.1	407.6	420.9	437.1	446.6	456.1	480.8	504.5	529.2	553.9
150°	408.6	411.4	419.0	431.4	445.6	454.2	462.7	484.6	506.4	528.3	551.1
152.5°	421.9	422.8	430.4	440.9	454.2	461.8	469.4	488.4	507.4	526.4	546.3
155°	434.2	435.2	440.9	451.3	461.8	468.9	476.0	492.2	508.3	524.5	540.6
157.5°	444.7	445.6	450.4	459.9	468.4	474.6	480.8	495.0	508.3	520.7	534.9
160°	455.1	456.1	459.9	467.5	475.1	480.3	485.5	496.9	508.3	517.8	529.2
162.5°	465.6	464.6	468.4	474.1	480.8	484.6	488.4	497.9	507.4	515.0	524.5
165°	473.2	472.2	474.1	479.8	484.6	487.4	490.3	498.8	505.5	511.2	517.8
167.5°	479.8	478.9	480.8	484.6	488.4	490.3	492.2	498.8	504.5	507.4	512.1
170°	486.5	484.6	485.5	488.4	490.3	491.7	493.1	497.9	502.6	504.5	507.4
172.5°	490.3	489.3	488.4	491.2	492.2	493.2	494.1	496.9	499.8	500.7	501.7
175°	493.1	492.2	491.2	493.1	493.1	493.6	494.1	496.0	497.9	496.9	497.9
177.5°	495.0	493.1	492.2	494.1	494.1	494.1	494.1	495.0	496.9	495.0	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	31.4	30.4	28.5	30.4	30.9	31.4	31.4	31.4	31.4	31.4	31.4
92.5°	122.6	96.0	81.7	71.3	67.5	63.7	62.7	58.9	59.9	58.0	59.9
95°	325.9	248.9	191.0	151.1	140.6	130.2	117.8	110.2	107.4	108.3	107.4
97.5°	611.9	509.3	406.7	310.7	282.2	253.7	216.6	197.6	187.2	181.5	187.2
100°	887.5	867.5	749.7	619.5	562.0	504.5	425.7	384.8	357.3	340.2	357.3
102.5°	990.1	1102.2	1098.4	1011.9	950.2	888.4	801.0	724.0	687.9	663.2	687.9
105°	956.8	1154.4	1261.8	1274.2	1258.5	1242.8	1183.9	1125.0	1084.1	1070.8	1084.1
107.5°	886.5	1098.4	1258.0	1351.1	1370.1	1389.1	1388.2	1379.6	1367.3	1345.4	1367.3
110°	820.9	1021.4	1191.5	1313.1	1352.0	1391.0	1431.9	1450.0	1458.5	1457.6	1458.5

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	775.3	951.1	1112.6	1244.7	1290.8	1336.9	1397.7	1430.9	1449.0	1455.7	1449.0
115°	739.2	896.0	1042.3	1166.8	1215.8	1264.7	1332.1	1375.8	1400.5	1409.1	1400.5
117.5°	714.5	850.4	981.5	1097.4	1144.0	1190.6	1259.9	1306.5	1332.1	1338.8	1332.1
120°	695.5	818.1	935.9	1036.6	1079.8	1123.1	1189.6	1234.3	1261.8	1271.3	1261.8
122.5°	679.4	792.4	897.9	992.0	1030.0	1068.0	1125.9	1169.7	1193.4	1201.0	1193.4
125°	664.2	767.7	865.6	949.2	984.8	1020.5	1075.6	1111.7	1135.4	1143.0	1135.4
127.5°	649.9	743.0	833.3	913.1	946.4	979.6	1028.1	1062.3	1083.2	1088.9	1083.2
130°	635.7	719.3	801.0	876.1	907.4	938.8	985.3	1017.6	1036.6	1044.2	1036.6
132.5°	624.3	696.5	770.6	838.0	867.0	896.0	941.6	973.9	991.0	997.7	991.0
135°	613.8	675.6	738.3	801.0	827.6	854.2	895.1	926.4	943.5	947.3	943.5
137.5°	606.2	658.5	712.6	763.9	787.6	811.4	850.4	878.0	893.2	898.9	893.2
140°	599.6	642.3	687.9	731.6	752.5	773.4	803.8	828.5	842.8	848.5	842.8
142.5°	592.9	629.0	666.1	702.2	718.8	735.4	763.9	785.8	798.1	798.1	798.1
145°	587.2	616.7	648.0	677.5	691.2	705.0	727.8	744.0	753.5	756.3	753.5
147.5°	581.5	607.2	632.8	656.6	667.0	677.5	697.4	710.7	717.4	719.3	717.4
150°	573.9	596.7	617.6	637.6	646.2	654.7	668.9	680.3	686.0	687.0	686.0
152.5°	567.2	586.3	605.3	621.4	628.6	635.7	646.1	655.6	659.4	659.4	659.4
155°	558.7	576.7	592.0	606.2	611.4	616.7	627.1	633.8	637.6	635.7	637.6
157.5°	551.1	565.3	578.7	591.0	595.3	599.6	607.2	612.9	614.8	614.8	614.8
160°	542.5	554.9	565.3	575.8	579.2	582.5	589.1	593.9	594.8	594.8	594.8
162.5°	534.9	544.4	553.0	561.5	563.9	566.3	572.9	575.8	576.7	575.8	576.7
165°	526.4	534.0	540.6	547.3	549.2	551.1	554.9	558.7	558.7	557.7	558.7
167.5°	517.8	523.5	529.2	534.0	535.9	537.8	539.7	541.6	541.6	540.6	541.6
170°	511.2	515.9	518.8	522.6	523.6	524.5	525.4	528.3	527.3	525.4	527.3
172.5°	504.5	507.4	509.3	512.1	512.6	513.1	514.0	515.0	514.0	513.1	514.0
175°	498.8	501.7	502.6	503.6	504.0	504.5	504.5	505.5	504.5	502.6	504.5
177.5°	495.0	496.9	496.9	497.9	497.9	497.9	497.9	497.9	496.9	495.0	496.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	31.4	31.4	31.4	30.9	30.4	28.5	30.4	31.4	32.3	31.4	25.7
92.5°	58.9	62.7	63.7	67.5	71.3	81.7	96.0	122.6	146.3	144.4	112.1
95°	110.2	117.8	130.2	140.6	151.1	191.0	248.9	325.9	372.5	329.7	219.5
97.5°	197.6	216.6	253.7	282.2	310.7	406.7	509.3	611.9	607.2	469.4	291.7
100°	384.8	425.7	504.5	562.0	619.5	749.7	867.5	887.5	750.6	516.9	311.7
102.5°	724.0	801.0	888.4	950.2	1011.9	1098.4	1102.2	990.1	755.4	498.8	312.6
105°	1125.0	1183.9	1242.8	1258.5	1274.2	1261.8	1154.4	956.8	704.1	474.1	317.4
107.5°	1379.6	1388.2	1389.1	1370.1	1351.1	1258.0	1098.4	886.5	656.6	460.8	327.8
110°	1450.0	1431.9	1391.0	1352.0	1313.1	1191.5	1021.4	820.9	624.3	457.0	341.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1430.9	1397.7	1336.9	1290.8	1244.7	1112.6	951.1	775.3	603.4	458.0	355.4
115°	1375.8	1332.1	1264.7	1215.8	1166.8	1042.3	896.0	739.2	589.1	461.8	369.6
117.5°	1306.5	1259.9	1190.6	1144.0	1097.4	981.5	850.4	714.5	581.5	467.5	384.8
120°	1234.3	1189.6	1123.1	1079.8	1036.6	935.9	818.1	695.5	574.8	473.2	400.0
122.5°	1169.7	1125.9	1068.0	1030.0	992.0	897.9	792.4	679.4	571.0	479.8	413.3
125°	1111.7	1075.6	1020.5	984.8	949.2	865.6	767.7	664.2	566.3	486.5	427.6
127.5°	1062.3	1028.1	979.6	946.4	913.1	833.3	743.0	649.9	563.4	493.1	440.9
130°	1017.6	985.3	938.8	907.4	876.1	801.0	719.3	635.7	561.5	500.7	453.2
132.5°	973.9	941.6	896.0	867.0	838.0	770.6	696.5	624.3	560.6	508.3	465.6
135°	926.4	895.1	854.2	827.6	801.0	738.3	675.6	613.8	559.6	514.0	476.0
137.5°	878.0	850.4	811.4	787.6	763.9	712.6	658.5	606.2	559.6	519.7	484.6
140°	828.5	803.8	773.4	752.5	731.6	687.9	642.3	599.6	558.7	523.5	491.2
142.5°	785.8	763.9	735.4	718.8	702.2	666.1	629.0	592.9	558.7	526.4	496.9
145°	744.0	727.8	705.0	691.2	677.5	648.0	616.7	587.2	556.8	528.3	501.7
147.5°	710.7	697.4	677.5	667.0	656.6	632.8	607.2	581.5	553.9	529.2	504.5
150°	680.3	668.9	654.7	646.2	637.6	617.6	596.7	573.9	551.1	528.3	506.4
152.5°	655.6	646.1	635.7	628.6	621.4	605.3	586.3	567.2	546.3	526.4	507.4
155°	633.8	627.1	616.7	611.4	606.2	592.0	576.7	558.7	540.6	524.5	508.3
157.5°	612.9	607.2	599.6	595.3	591.0	578.7	565.3	551.1	534.9	520.7	508.3
160°	593.9	589.1	582.5	579.2	575.8	565.3	554.9	542.5	529.2	517.8	508.3
162.5°	575.8	572.9	566.3	563.9	561.5	553.0	544.4	534.9	524.5	515.0	507.4
165°	558.7	554.9	551.1	549.2	547.3	540.6	534.0	526.4	517.8	511.2	505.5
167.5°	541.6	539.7	537.8	535.9	534.0	529.2	523.5	517.8	512.1	507.4	504.5
170°	528.3	525.4	524.5	523.6	522.6	518.8	515.9	511.2	507.4	504.5	502.6
172.5°	515.0	514.0	513.1	512.6	512.1	509.3	507.4	504.5	501.7	500.7	499.8
175°	505.5	504.5	504.5	504.0	503.6	502.6	501.7	498.8	497.9	496.9	497.9
177.5°	497.9	497.9	497.9	497.9	497.9	496.9	496.9	495.0	494.1	495.0	496.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	19.0	14.3	12.8	11.4	9.5	7.6	3.8	1.0	3.8	7.6	9.5
92.5°	76.0	50.4	45.2	39.9	32.3	27.6	20.0	14.3	20.0	27.6	32.3
95°	136.8	93.1	81.7	70.3	55.1	46.6	37.1	33.3	37.1	46.6	55.1
97.5°	176.7	120.7	107.8	95.0	77.9	65.6	55.1	49.4	55.1	65.6	77.9
100°	195.7	145.4	132.1	118.8	99.8	84.6	76.0	73.2	76.0	84.6	99.8
102.5°	212.8	167.2	153.9	140.6	120.7	105.5	96.9	95.0	96.9	105.5	120.7
105°	232.8	188.1	174.8	161.5	140.6	126.4	119.7	115.9	119.7	126.4	140.6
107.5°	252.7	209.0	195.7	182.4	161.5	148.2	141.6	138.7	141.6	148.2	161.5
110°	272.7	230.9	217.1	203.3	183.4	171.0	165.3	161.5	165.3	171.0	183.4

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	291.7	251.8	237.6	223.3	204.3	192.9	186.2	182.4	186.2	192.9	204.3
115°	311.7	270.8	258.0	245.1	226.1	214.7	209.0	204.3	209.0	214.7	226.1
117.5°	329.7	291.7	278.4	265.1	247.0	236.6	230.9	227.1	230.9	236.6	247.0
120°	348.7	311.7	298.4	285.0	266.0	257.5	251.8	248.0	251.8	257.5	266.0
122.5°	366.8	332.6	318.8	305.0	286.0	276.5	270.8	267.9	270.8	276.5	286.0
125°	384.8	350.6	337.3	324.0	305.0	293.6	287.9	285.0	287.9	293.6	305.0
127.5°	401.9	368.7	354.9	341.1	323.1	310.7	303.1	299.3	303.1	310.7	323.1
130°	417.1	383.9	370.6	357.3	338.3	325.0	315.5	311.7	315.5	325.0	338.3
132.5°	430.4	399.1	385.8	372.5	352.5	338.3	327.8	323.1	327.8	338.3	352.5
135°	442.8	412.4	399.1	385.8	363.9	349.7	338.3	334.5	338.3	349.7	363.9
137.5°	453.2	422.8	410.4	398.1	376.3	361.1	349.7	344.9	349.7	361.1	376.3
140°	461.8	433.3	421.0	408.6	387.7	372.5	361.1	357.3	361.1	372.5	387.7
142.5°	468.4	440.9	429.5	418.1	398.1	382.9	372.5	369.6	372.5	382.9	398.1
145°	475.1	449.4	439.0	428.5	409.5	395.3	385.8	382.0	385.8	395.3	409.5
147.5°	480.8	456.1	446.6	437.1	420.9	407.6	398.1	395.3	398.1	407.6	420.9
150°	484.6	462.7	454.2	445.6	431.4	419.0	411.4	408.6	411.4	419.0	431.4
152.5°	488.4	469.4	461.8	454.2	440.9	430.4	422.8	421.9	422.8	430.4	440.9
155°	492.2	476.0	468.9	461.8	451.3	440.9	435.2	434.2	435.2	440.9	451.3
157.5°	495.0	480.8	474.6	468.4	459.9	450.4	445.6	444.7	445.6	450.4	459.9
160°	496.9	485.5	480.3	475.1	467.5	459.9	456.1	455.1	456.1	459.9	467.5
162.5°	497.9	488.4	484.6	480.8	474.1	468.4	464.6	465.6	464.6	468.4	474.1
165°	498.8	490.3	487.4	484.6	479.8	474.1	472.2	473.2	472.2	474.1	479.8
167.5°	498.8	492.2	490.3	488.4	484.6	480.8	478.9	479.8	478.9	480.8	484.6
170°	497.9	493.1	491.7	490.3	488.4	485.5	484.6	486.5	484.6	485.5	488.4
172.5°	496.9	494.1	493.2	492.2	491.2	488.4	489.3	490.3	489.3	488.4	491.2
175°	496.0	494.1	493.6	493.1	493.1	491.2	492.2	493.1	492.2	491.2	493.1
177.5°	495.0	494.1	494.1	494.1	494.1	492.2	493.1	495.0	493.1	492.2	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	11.4	12.8	14.3	19.0	25.7	31.4	32.3	31.4	30.4	28.5	30.4
92.5°	39.9	45.2	50.4	76.0	112.1	144.4	146.3	122.6	96.0	81.7	71.3
95°	70.3	81.7	93.1	136.8	219.5	329.7	372.5	325.9	248.9	191.0	151.1
97.5°	95.0	107.8	120.7	176.7	291.7	469.4	607.2	611.9	509.3	406.7	310.7
100°	118.8	132.1	145.4	195.7	311.7	516.9	750.6	887.5	867.5	749.7	619.5
102.5°	140.6	153.9	167.2	212.8	312.6	498.8	755.4	990.1	1102.2	1098.4	1011.9
105°	161.5	174.8	188.1	232.8	317.4	474.1	704.1	956.8	1154.4	1261.8	1274.2
107.5°	182.4	195.7	209.0	252.7	327.8	460.8	656.6	886.5	1098.4	1258.0	1351.1
110°	203.3	217.1	230.9	272.7	341.1	457.0	624.3	820.9	1021.4	1191.5	1313.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	223.3	237.6	251.8	291.7	355.4	458.0	603.4	775.3	951.1	1112.6	1244.7
115°	245.1	258.0	270.8	311.7	369.6	461.8	589.1	739.2	896.0	1042.3	1166.8
117.5°	265.1	278.4	291.7	329.7	384.8	467.5	581.5	714.5	850.4	981.5	1097.4
120°	285.0	298.4	311.7	348.7	400.0	473.2	574.8	695.5	818.1	935.9	1036.6
122.5°	305.0	318.8	332.6	366.8	413.3	479.8	571.0	679.4	792.4	897.9	992.0
125°	324.0	337.3	350.6	384.8	427.6	486.5	566.3	664.2	767.7	865.6	949.2
127.5°	341.1	354.9	368.7	401.9	440.9	493.1	563.4	649.9	743.0	833.3	913.1
130°	357.3	370.6	383.9	417.1	453.2	500.7	561.5	635.7	719.3	801.0	876.1
132.5°	372.5	385.8	399.1	430.4	465.6	508.3	560.6	624.3	696.5	770.6	838.0
135°	385.8	399.1	412.4	442.8	476.0	514.0	559.6	613.8	675.6	738.3	801.0
137.5°	398.1	410.4	422.8	453.2	484.6	519.7	559.6	606.2	658.5	712.6	763.9
140°	408.6	421.0	433.3	461.8	491.2	523.5	558.7	599.6	642.3	687.9	731.6
142.5°	418.1	429.5	440.9	468.4	496.9	526.4	558.7	592.9	629.0	666.1	702.2
145°	428.5	439.0	449.4	475.1	501.7	528.3	556.8	587.2	616.7	648.0	677.5
147.5°	437.1	446.6	456.1	480.8	504.5	529.2	553.9	581.5	607.2	632.8	656.6
150°	445.6	454.2	462.7	484.6	506.4	528.3	551.1	573.9	596.7	617.6	637.6
152.5°	454.2	461.8	469.4	488.4	507.4	526.4	546.3	567.2	586.3	605.3	621.4
155°	461.8	468.9	476.0	492.2	508.3	524.5	540.6	558.7	576.7	592.0	606.2
157.5°	468.4	474.6	480.8	495.0	508.3	520.7	534.9	551.1	565.3	578.7	591.0
160°	475.1	480.3	485.5	496.9	508.3	517.8	529.2	542.5	554.9	565.3	575.8
162.5°	480.8	484.6	488.4	497.9	507.4	515.0	524.5	534.9	544.4	553.0	561.5
165°	484.6	487.4	490.3	498.8	505.5	511.2	517.8	526.4	534.0	540.6	547.3
167.5°	488.4	490.3	492.2	498.8	504.5	507.4	512.1	517.8	523.5	529.2	534.0
170°	490.3	491.7	493.1	497.9	502.6	504.5	507.4	511.2	515.9	518.8	522.6
172.5°	492.2	493.2	494.1	496.9	499.8	500.7	501.7	504.5	507.4	509.3	512.1
175°	493.1	493.6	494.1	496.0	497.9	496.9	497.9	498.8	501.7	502.6	503.6
177.5°	494.1	494.1	494.1	495.0	496.9	495.0	494.1	495.0	496.9	496.9	497.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	30.9	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	30.9
92.5°	67.5	63.7	62.7	58.9	59.9	58.0	59.9	58.9	62.7	63.7	67.5
95°	140.6	130.2	117.8	110.2	107.4	108.3	107.4	110.2	117.8	130.2	140.6
97.5°	282.2	253.7	216.6	197.6	187.2	181.5	187.2	197.6	216.6	253.7	282.2
100°	562.0	504.5	425.7	384.8	357.3	340.2	357.3	384.8	425.7	504.5	562.0
102.5°	950.2	888.4	801.0	724.0	687.9	663.2	687.9	724.0	801.0	888.4	950.2
105°	1258.5	1242.8	1183.9	1125.0	1084.1	1070.8	1084.1	1125.0	1183.9	1242.8	1258.5
107.5°	1370.1	1389.1	1388.2	1379.6	1367.3	1345.4	1367.3	1379.6	1388.2	1389.1	1370.1
110°	1352.0	1391.0	1431.9	1450.0	1458.5	1457.6	1458.5	1450.0	1431.9	1391.0	1352.0

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1290.8	1336.9	1397.7	1430.9	1449.0	1455.7	1449.0	1430.9	1397.7	1336.9	1290.8
115°	1215.8	1264.7	1332.1	1375.8	1400.5	1409.1	1400.5	1375.8	1332.1	1264.7	1215.8
117.5°	1144.0	1190.6	1259.9	1306.5	1332.1	1338.8	1332.1	1306.5	1259.9	1190.6	1144.0
120°	1079.8	1123.1	1189.6	1234.3	1261.8	1271.3	1261.8	1234.3	1189.6	1123.1	1079.8
122.5°	1030.0	1068.0	1125.9	1169.7	1193.4	1201.0	1193.4	1169.7	1125.9	1068.0	1030.0
125°	984.8	1020.5	1075.6	1111.7	1135.4	1143.0	1135.4	1111.7	1075.6	1020.5	984.8
127.5°	946.4	979.6	1028.1	1062.3	1083.2	1088.9	1083.2	1062.3	1028.1	979.6	946.4
130°	907.4	938.8	985.3	1017.6	1036.6	1044.2	1036.6	1017.6	985.3	938.8	907.4
132.5°	867.0	896.0	941.6	973.9	991.0	997.7	991.0	973.9	941.6	896.0	867.0
135°	827.6	854.2	895.1	926.4	943.5	947.3	943.5	926.4	895.1	854.2	827.6
137.5°	787.6	811.4	850.4	878.0	893.2	898.9	893.2	878.0	850.4	811.4	787.6
140°	752.5	773.4	803.8	828.5	842.8	848.5	842.8	828.5	803.8	773.4	752.5
142.5°	718.8	735.4	763.9	785.8	798.1	798.1	798.1	785.8	763.9	735.4	718.8
145°	691.2	705.0	727.8	744.0	753.5	756.3	753.5	744.0	727.8	705.0	691.2
147.5°	667.0	677.5	697.4	710.7	717.4	719.3	717.4	710.7	697.4	677.5	667.0
150°	646.2	654.7	668.9	680.3	686.0	687.0	686.0	680.3	668.9	654.7	646.2
152.5°	628.6	635.7	646.1	655.6	659.4	659.4	659.4	655.6	646.1	635.7	628.6
155°	611.4	616.7	627.1	633.8	637.6	635.7	637.6	633.8	627.1	616.7	611.4
157.5°	595.3	599.6	607.2	612.9	614.8	614.8	614.8	612.9	607.2	599.6	595.3
160°	579.2	582.5	589.1	593.9	594.8	594.8	594.8	593.9	589.1	582.5	579.2
162.5°	563.9	566.3	572.9	575.8	576.7	575.8	576.7	575.8	572.9	566.3	563.9
165°	549.2	551.1	554.9	558.7	558.7	557.7	558.7	558.7	554.9	551.1	549.2
167.5°	535.9	537.8	539.7	541.6	541.6	540.6	541.6	541.6	539.7	537.8	535.9
170°	523.6	524.5	525.4	528.3	527.3	525.4	527.3	528.3	525.4	524.5	523.6
172.5°	512.6	513.1	514.0	515.0	514.0	513.1	514.0	515.0	514.0	513.1	512.6
175°	504.0	504.5	504.5	505.5	504.5	502.6	504.5	505.5	504.5	504.5	504.0
177.5°	497.9	497.9	497.9	497.9	496.9	495.0	496.9	497.9	497.9	497.9	497.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	30.4	28.5	30.4	31.4	32.3	31.4	25.7	19.0	14.3	12.8	11.4
92.5°	71.3	81.7	96.0	122.6	146.3	144.4	112.1	76.0	50.4	45.2	39.9
95°	151.1	191.0	248.9	325.9	372.5	329.7	219.5	136.8	93.1	81.7	70.3
97.5°	310.7	406.7	509.3	611.9	607.2	469.4	291.7	176.7	120.7	107.8	95.0
100°	619.5	749.7	867.5	887.5	750.6	516.9	311.7	195.7	145.4	132.1	118.8
102.5°	1011.9	1098.4	1102.2	990.1	755.4	498.8	312.6	212.8	167.2	153.9	140.6
105°	1274.2	1261.8	1154.4	956.8	704.1	474.1	317.4	232.8	188.1	174.8	161.5
107.5°	1351.1	1258.0	1098.4	886.5	656.6	460.8	327.8	252.7	209.0	195.7	182.4
110°	1313.1	1191.5	1021.4	820.9	624.3	457.0	341.1	272.7	230.9	217.1	203.3

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1244.7	1112.6	951.1	775.3	603.4	458.0	355.4	291.7	251.8	237.6	223.3
115°	1166.8	1042.3	896.0	739.2	589.1	461.8	369.6	311.7	270.8	258.0	245.1
117.5°	1097.4	981.5	850.4	714.5	581.5	467.5	384.8	329.7	291.7	278.4	265.1
120°	1036.6	935.9	818.1	695.5	574.8	473.2	400.0	348.7	311.7	298.4	285.0
122.5°	992.0	897.9	792.4	679.4	571.0	479.8	413.3	366.8	332.6	318.8	305.0
125°	949.2	865.6	767.7	664.2	566.3	486.5	427.6	384.8	350.6	337.3	324.0
127.5°	913.1	833.3	743.0	649.9	563.4	493.1	440.9	401.9	368.7	354.9	341.1
130°	876.1	801.0	719.3	635.7	561.5	500.7	453.2	417.1	383.9	370.6	357.3
132.5°	838.0	770.6	696.5	624.3	560.6	508.3	465.6	430.4	399.1	385.8	372.5
135°	801.0	738.3	675.6	613.8	559.6	514.0	476.0	442.8	412.4	399.1	385.8
137.5°	763.9	712.6	658.5	606.2	559.6	519.7	484.6	453.2	422.8	410.4	398.1
140°	731.6	687.9	642.3	599.6	558.7	523.5	491.2	461.8	433.3	421.0	408.6
142.5°	702.2	666.1	629.0	592.9	558.7	526.4	496.9	468.4	440.9	429.5	418.1
145°	677.5	648.0	616.7	587.2	556.8	528.3	501.7	475.1	449.4	439.0	428.5
147.5°	656.6	632.8	607.2	581.5	553.9	529.2	504.5	480.8	456.1	446.6	437.1
150°	637.6	617.6	596.7	573.9	551.1	528.3	506.4	484.6	462.7	454.2	445.6
152.5°	621.4	605.3	586.3	567.2	546.3	526.4	507.4	488.4	469.4	461.8	454.2
155°	606.2	592.0	576.7	558.7	540.6	524.5	508.3	492.2	476.0	468.9	461.8
157.5°	591.0	578.7	565.3	551.1	534.9	520.7	508.3	495.0	480.8	474.6	468.4
160°	575.8	565.3	554.9	542.5	529.2	517.8	508.3	496.9	485.5	480.3	475.1
162.5°	561.5	553.0	544.4	534.9	524.5	515.0	507.4	497.9	488.4	484.6	480.8
165°	547.3	540.6	534.0	526.4	517.8	511.2	505.5	498.8	490.3	487.4	484.6
167.5°	534.0	529.2	523.5	517.8	512.1	507.4	504.5	498.8	492.2	490.3	488.4
170°	522.6	518.8	515.9	511.2	507.4	504.5	502.6	497.9	493.1	491.7	490.3
172.5°	512.1	509.3	507.4	504.5	501.7	500.7	499.8	496.9	494.1	493.2	492.2
175°	503.6	502.6	501.7	498.8	497.9	496.9	497.9	496.0	494.1	493.6	493.1
177.5°	497.9	496.9	496.9	495.0	494.1	495.0	496.9	495.0	494.1	494.1	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	9.5	7.6	3.8	1.0
92.5°	32.3	27.6	20.0	14.3
95°	55.1	46.6	37.1	33.3
97.5°	77.9	65.6	55.1	49.4
100°	99.8	84.6	76.0	73.2
102.5°	120.7	105.5	96.9	95.0
105°	140.6	126.4	119.7	115.9
107.5°	161.5	148.2	141.6	138.7
110°	183.4	171.0	165.3	161.5

TEST NUMBER: P1009425

CATALOG NUMBER: S122DIP-B675D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	204.3	192.9	186.2	182.4
115°	226.1	214.7	209.0	204.3
117.5°	247.0	236.6	230.9	227.1
120°	266.0	257.5	251.8	248.0
122.5°	286.0	276.5	270.8	267.9
125°	305.0	293.6	287.9	285.0
127.5°	323.1	310.7	303.1	299.3
130°	338.3	325.0	315.5	311.7
132.5°	352.5	338.3	327.8	323.1
135°	363.9	349.7	338.3	334.5
137.5°	376.3	361.1	349.7	344.9
140°	387.7	372.5	361.1	357.3
142.5°	398.1	382.9	372.5	369.6
145°	409.5	395.3	385.8	382.0
147.5°	420.9	407.6	398.1	395.3
150°	431.4	419.0	411.4	408.6
152.5°	440.9	430.4	422.8	421.9
155°	451.3	440.9	435.2	434.2
157.5°	459.9	450.4	445.6	444.7
160°	467.5	459.9	456.1	455.1
162.5°	474.1	468.4	464.6	465.6
165°	479.8	474.1	472.2	473.2
167.5°	484.6	480.8	478.9	479.8
170°	488.4	485.5	484.6	486.5
172.5°	491.2	488.4	489.3	490.3
175°	493.1	491.2	492.2	493.1
177.5°	494.1	492.2	493.1	495.0
180°	494.1	494.1	494.1	494.1

(END OF REPORT)