

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009449

Luminaire Tested: S122DIP-B865D1080UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009449
REPORT IS A COMBINATION OF REPORTS P984750 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7702.8 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009449

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009449

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44
2	88	81	75	69	80	74	69	64	62	58	55	51	48	46	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	36	33	31
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1009449

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	1.7
10°-20°	363.3	4.7
20°-30°	533.8	6.9
30°-40°	620.0	8.0
40°-50°	619.2	8.0
50°-60°	540.0	7.0
60°-70°	399.1	5.2
70°-80°	225.8	2.9
80°-90°	63.5	0.8
90°-100°	244.7	3.2
100°-110°	827.3	10.7
110°-120°	869.6	11.3
120°-130°	715.1	9.3
130°-140°	574.7	7.5
140°-150°	434.1	5.6
150°-160°	305.2	4.0
160°-170°	179.7	2.3
170°-180°	58.5	0.8
0°-30°	1026.2	13.3
0°-40°	1646.2	21.4
0°-60°	2805.4	36.4
0°-90°	3493.9	45.4
90°-120°	1941.7	25.2
90°-150°	3665.6	47.6
90°-180°	4209.0	54.6
0°-180°	7702.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	1	16	40	38	38	6
95°	41	100	455	172	132	42
105°	142	214	860	1538	1308	150
115°	250	315	720	1485	1722	248
125°	348	412	692	1203	1397	310
135°	409	488	684	1011	1158	316
145°	467	536	680	845	924	293
155°	531	573	661	747	777	244
165°	578	596	633	671	682	163
175°	602	603	608	616	614	57
180°	604	604	604	604	604	

TEST NUMBER: P1009449

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	1.2	15.6	39.5	37.8	38.3
92.5°	17.4	55.2	178.8	82.4	70.8
95°	40.6	99.8	455.1	171.8	132.3
97.5°	60.4	131.8	741.8	344.8	221.7
100°	89.4	161.4	917.1	686.7	415.6
102.5°	116.1	188.0	923.0	1161.0	810.3
105°	141.6	213.6	860.3	1537.6	1308.4
107.5°	169.5	239.2	802.2	1674.1	1643.9
110°	197.4	265.2	762.7	1652.0	1780.9

TEST NUMBER: P1009449

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.9	290.2	737.2	1577.1	1778.6
115°	249.6	315.2	719.8	1485.4	1721.7
117.5°	277.5	340.2	710.5	1397.8	1635.8
120°	303.0	364.6	702.4	1319.4	1553.3
122.5°	327.4	389.5	697.7	1258.4	1467.4
125°	348.3	412.2	691.9	1203.4	1396.6
127.5°	365.7	433.6	688.4	1156.3	1330.4
130°	380.8	452.8	686.1	1108.7	1275.9
132.5°	394.7	471.4	685.0	1059.4	1219.0
135°	408.7	487.6	683.8	1011.2	1157.5
137.5°	421.4	501.5	683.8	962.4	1098.3
140°	436.5	514.3	682.6	919.4	1036.7
142.5°	451.6	524.8	682.6	878.2	975.2
145°	466.7	536.4	680.3	844.6	924.1
147.5°	483.0	545.6	676.8	815.0	878.8
150°	499.2	555.0	673.3	789.4	839.4
152.5°	515.5	564.2	667.5	768.0	805.7
155°	530.6	572.9	660.6	747.1	776.7
157.5°	543.3	579.8	653.6	727.4	751.1
160°	556.1	586.8	646.6	707.6	726.8
162.5°	568.9	592.0	640.8	689.0	703.5
165°	578.2	595.6	632.7	671.0	681.5
167.5°	586.3	599.0	625.7	654.8	660.6
170°	594.4	600.8	619.9	639.6	642.0
172.5°	599.0	602.6	613.0	626.3	626.9
175°	602.5	603.1	608.3	615.9	614.1
177.5°	604.9	603.7	603.7	608.3	604.9
180°	603.7	603.7	603.7	603.7	603.7

(END OF REPORT)