

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008968

Luminaire Tested: S122DIP-B290D925UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008968
REPORT IS A COMBINATION OF REPORTS P984098 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4466.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008968

CATALOG NUMBER: S122DIP-B290D925UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008968

CATALOG NUMBER: S122DIP-B290D925UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7310	7310	7310
5°	7322	6969	6918
10°	7262	6651	6518
15°	7156	6331	6099
20°	7013	5983	5700
25°	6870	5619	5302
30°	6688	5277	4883
35°	6520	4917	4473
40°	6309	4562	4085
45°	6100	4210	3706
50°	5873	3850	3311
55°	5633	3467	2937
60°	5362	3050	2548
65°	5066	2628	2140
70°	4694	2167	1728
75°	4173	1670	1334
80°	3545	1136	860
85°	2571	528	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6100 cd/sqm

TEST NUMBER: P1008968

CATALOG NUMBER: S122DIP-B290D925UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	1.0
10°-20°	122.3	2.7
20°-30°	179.7	4.0
30°-40°	208.7	4.7
40°-50°	208.5	4.7
50°-60°	181.8	4.1
60°-70°	134.4	3.0
70°-80°	76.0	1.7
80°-90°	23.4	0.5
90°-100°	72.7	1.6
100°-110°	231.3	5.2
110°-120°	395.7	8.9
120°-130°	520.4	11.7
130°-140°	584.1	13.1
140°-150°	572.8	12.8
150°-160°	480.5	10.8
160°-170°	318.7	7.1
170°-180°	111.4	2.5
0°-30°	345.5	7.7
0°-40°	554.2	12.4
0°-60°	944.5	21.1
0°-90°	1178.3	26.4
90°-120°	699.7	15.7
90°-150°	2377.1	53.2
90°-180°	3288.0	73.6
0°-180°	4466.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	462	460	455	459	458	44
15°	440	437	431	433	431	124
25°	398	394	387	388	387	183
35°	343	339	332	329	327	214
45°	279	276	270	265	263	216
55°	211	209	203	198	196	189
65°	142	140	135	131	129	141
75°	75	74	72	69	70	80
85°	18	18	17	16	16	20
90°	1	13	35	33	34	4
95°	52	62	64	64	62	58
105°	213	216	218	220	220	225
115°	397	403	401	400	397	393
125°	578	586	584	580	580	516
135°	747	758	760	759	756	577
145°	907	914	920	921	917	567
155°	1037	1040	1043	1048	1045	477
165°	1128	1127	1127	1134	1129	318
175°	1174	1171	1169	1176	1170	112
180°	1176	1176	1176	1176	1176	

TEST NUMBER: P1008968

CATALOG NUMBER: S122DIP-B290D925UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	461.8	461.8	461.8	461.8	461.8
2.5°	464.5	462.3	457.4	461.8	461.0
5°	461.8	460.1	455.2	458.7	457.8
7.5°	458.7	456.1	451.2	454.7	453.8
10°	453.8	450.7	445.4	449.0	447.6
12.5°	447.2	444.5	439.2	441.4	440.5
15°	439.6	437.0	431.2	433.0	430.8
17.5°	430.3	427.6	421.9	424.1	421.9
20°	420.1	417.4	411.2	412.5	410.8
22.5°	409.9	405.9	400.1	400.1	399.2
25°	397.9	394.3	386.8	387.7	386.8
27.5°	384.6	381.5	375.7	374.4	372.1
30°	371.2	367.7	361.0	359.7	357.9
32.5°	357.0	354.4	347.3	344.6	342.8
35°	343.3	338.8	331.7	329.1	326.8
37.5°	327.7	323.7	316.6	313.5	311.3
40°	311.7	308.2	301.1	297.1	295.3
42.5°	296.2	292.6	285.5	281.1	278.4
45°	279.3	276.2	269.6	264.7	262.9
47.5°	262.9	259.8	252.7	247.8	245.1
50°	245.6	243.4	237.1	230.9	228.7
52.5°	228.7	225.6	219.8	214.9	211.8
55°	211.4	208.7	203.4	198.1	195.8
57.5°	194.1	191.8	186.1	180.7	179.0
60°	176.7	175.0	168.7	163.9	162.5
62.5°	159.9	156.8	152.3	147.9	146.1
65°	142.5	139.9	135.4	131.4	129.2
67.5°	124.8	122.6	118.6	115.5	113.7
70°	108.4	106.6	102.6	99.5	97.7
72.5°	91.5	89.7	87.5	84.4	83.0
75°	74.6	73.7	71.5	68.8	69.7
77.5°	59.5	57.7	56.8	55.5	54.2
80°	44.4	44.0	43.1	41.7	40.9
82.5°	30.2	30.2	29.8	28.0	28.0
85°	18.2	17.8	17.3	16.0	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	1.0	12.9	34.7	32.7	33.7
92.5°	21.8	29.8	30.8	31.8	31.8
95°	51.6	61.5	63.5	63.5	61.5
97.5°	86.3	95.3	99.2	99.2	99.2
100°	126.0	134.0	136.9	136.9	136.0
102.5°	167.7	173.7	177.6	178.6	177.6
105°	213.4	216.3	218.3	220.3	220.3
107.5°	259.0	263.0	263.0	264.0	259.0
110°	302.7	308.6	308.6	308.6	305.6

TEST NUMBER: P1008968

CATALOG NUMBER: S122DIP-B290D925UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.3	356.2	355.3	352.3	350.3
115°	396.9	402.9	400.9	399.9	396.9
117.5°	443.6	451.5	446.6	443.6	440.6
120°	490.2	498.2	490.2	490.2	487.2
122.5°	532.9	542.8	537.8	534.9	532.9
125°	577.5	586.5	583.5	580.5	579.5
127.5°	621.2	632.1	628.2	624.2	621.2
130°	661.9	674.8	672.8	670.8	666.9
132.5°	707.5	717.5	718.5	713.5	710.5
135°	747.2	758.1	760.1	759.1	756.2
137.5°	790.9	799.8	801.8	800.8	796.8
140°	829.6	838.5	843.5	843.5	839.5
142.5°	869.3	878.2	881.2	882.2	878.2
145°	907.0	913.9	919.9	920.9	916.9
147.5°	940.7	949.7	953.6	955.6	951.7
150°	975.5	981.4	985.4	988.4	985.4
152.5°	1006.2	1012.2	1017.1	1021.1	1017.1
155°	1037.0	1040.0	1042.9	1047.9	1044.9
157.5°	1063.8	1065.8	1067.8	1074.7	1069.7
160°	1087.6	1089.6	1090.6	1096.5	1092.6
162.5°	1109.4	1109.4	1110.4	1117.4	1112.4
165°	1128.3	1127.3	1127.3	1134.2	1129.3
167.5°	1145.2	1142.2	1142.2	1149.1	1144.2
170°	1158.1	1155.1	1154.1	1161.0	1155.1
172.5°	1167.0	1164.0	1163.0	1170.0	1164.0
175°	1173.9	1171.0	1169.0	1175.9	1170.0
177.5°	1177.9	1174.9	1172.9	1178.9	1172.9
180°	1175.9	1175.9	1175.9	1175.9	1175.9

(END OF REPORT)