

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008977

Luminaire Tested: S122DIP-B290D925UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008977
REPORT IS A COMBINATION OF REPORTS P984107 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB40-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4421.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008977

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008977

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7236	7236	7236
5°	7247	6897	6849
10°	7189	6583	6453
15°	7083	6266	6036
20°	6941	5921	5641
25°	6799	5561	5247
30°	6622	5223	4834
35°	6453	4866	4428
40°	6246	4515	4044
45°	6039	4166	3667
50°	5813	3811	3278
55°	5574	3431	2907
60°	5307	3019	2523
65°	5016	2603	2118
70°	4643	2144	1711
75°	4128	1654	1321
80°	3513	1123	849
85°	2543	521	362

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6039 cd/sqm

TEST NUMBER: P1008977

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.0	1.0
10°-20°	121.1	2.7
20°-30°	177.9	4.0
30°-40°	206.6	4.7
40°-50°	206.4	4.7
50°-60°	179.9	4.1
60°-70°	133.0	3.0
70°-80°	75.3	1.7
80°-90°	23.2	0.5
90°-100°	72.0	1.6
100°-110°	228.9	5.2
110°-120°	391.7	8.9
120°-130°	515.2	11.7
130°-140°	578.3	13.1
140°-150°	567.1	12.8
150°-160°	475.7	10.8
160°-170°	315.5	7.1
170°-180°	110.3	2.5
0°-30°	342.0	7.7
0°-40°	548.6	12.4
0°-60°	934.9	21.1
0°-90°	1166.3	26.4
90°-120°	692.7	15.7
90°-150°	2353.2	53.2
90°-180°	3255.0	73.6
0°-180°	4421.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	457	457	457	457	457	
5°	457	455	450	454	453	43
15°	435	432	427	429	426	123
25°	394	390	383	384	383	181
35°	340	335	328	326	324	212
45°	276	273	267	262	260	213
55°	209	207	201	196	194	187
65°	141	138	134	130	128	139
75°	74	73	71	68	69	79
85°	18	18	17	16	15	20
90°	1	13	34	32	33	4
95°	51	61	63	63	61	57
105°	211	214	216	218	218	223
115°	393	399	397	396	393	389
125°	572	581	578	575	574	511
135°	740	750	752	752	749	572
145°	898	905	911	912	908	561
155°	1027	1030	1032	1037	1034	473
165°	1117	1116	1116	1123	1118	315
175°	1162	1159	1157	1164	1158	110
180°	1164	1164	1164	1164	1164	

TEST NUMBER: P1008977

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	457.1	457.1	457.1	457.1	457.1
2.5°	459.8	457.6	452.7	457.1	456.2
5°	457.1	455.4	450.5	454.0	453.2
7.5°	454.0	451.4	446.6	450.1	449.2
10°	449.2	446.1	440.9	444.4	443.1
12.5°	442.6	440.0	434.7	436.9	436.0
15°	435.1	432.5	426.8	428.6	426.4
17.5°	425.9	423.3	417.6	419.8	417.6
20°	415.8	413.2	407.0	408.3	406.6
22.5°	405.7	401.7	396.0	396.0	395.1
25°	393.8	390.3	382.8	383.7	382.8
27.5°	380.6	377.6	371.9	370.5	368.3
30°	367.5	363.9	357.3	356.0	354.3
32.5°	353.4	350.8	343.7	341.1	339.3
35°	339.8	335.4	328.3	325.7	323.5
37.5°	324.4	320.4	313.4	310.3	308.1
40°	308.6	305.0	298.0	294.1	292.3
42.5°	293.2	289.7	282.6	278.2	275.6
45°	276.5	273.4	266.8	262.0	260.2
47.5°	260.2	257.1	250.1	245.3	242.6
50°	243.1	240.9	234.7	228.6	226.4
52.5°	226.4	223.3	217.6	212.7	209.7
55°	209.2	206.6	201.3	196.0	193.8
57.5°	192.1	189.9	184.2	178.9	177.1
60°	174.9	173.2	167.0	162.2	160.9
62.5°	158.2	155.2	150.8	146.4	144.6
65°	141.1	138.5	134.1	130.1	127.9
67.5°	123.5	121.3	117.4	114.3	112.5
70°	107.2	105.5	101.5	98.5	96.7
72.5°	90.5	88.8	86.6	83.5	82.2
75°	73.8	73.0	70.8	68.1	69.0
77.5°	58.9	57.1	56.3	54.9	53.6
80°	44.0	43.5	42.6	41.3	40.4
82.5°	29.9	29.9	29.4	27.7	27.7
85°	18.0	17.6	17.1	15.8	15.4
87.5°	7.9	7.0	6.2	4.8	4.4
90°	1.0	12.8	34.4	32.4	33.4
92.5°	21.6	29.5	30.5	31.4	31.4
95°	51.1	60.9	62.9	62.9	60.9
97.5°	85.5	94.3	98.2	98.2	98.2
100°	124.8	132.6	135.6	135.6	134.6
102.5°	166.0	171.9	175.8	176.8	175.8
105°	211.2	214.2	216.1	218.1	218.1
107.5°	256.4	260.3	260.3	261.3	256.4
110°	299.6	305.5	305.5	305.5	302.6

TEST NUMBER: P1008977

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	346.8	352.7	351.7	348.7	346.8
115°	393.0	398.8	396.9	395.9	393.0
117.5°	439.1	447.0	442.1	439.1	436.2
120°	485.3	493.2	485.3	485.3	482.4
122.5°	527.5	537.4	532.5	529.5	527.5
125°	571.7	580.6	577.6	574.7	573.7
127.5°	615.0	625.8	621.9	617.9	615.0
130°	655.3	668.0	666.1	664.1	660.2
132.5°	700.4	710.3	711.2	706.3	703.4
135°	739.7	750.5	752.5	751.5	748.6
137.5°	783.0	791.8	793.8	792.8	788.9
140°	821.3	830.1	835.0	835.0	831.1
142.5°	860.6	869.4	872.4	873.3	869.4
145°	897.9	904.8	910.7	911.7	907.7
147.5°	931.3	940.1	944.1	946.0	942.1
150°	965.7	971.6	975.5	978.5	975.5
152.5°	996.1	1002.0	1006.9	1010.9	1006.9
155°	1026.6	1029.5	1032.5	1037.4	1034.5
157.5°	1053.1	1055.1	1057.0	1063.9	1059.0
160°	1076.7	1078.7	1079.6	1085.5	1081.6
162.5°	1098.3	1098.3	1099.3	1106.2	1101.3
165°	1117.0	1116.0	1116.0	1122.9	1118.0
167.5°	1133.7	1130.7	1130.7	1137.6	1132.7
170°	1146.4	1143.5	1142.5	1149.4	1143.5
172.5°	1155.3	1152.3	1151.4	1158.2	1152.3
175°	1162.2	1159.2	1157.3	1164.1	1158.2
177.5°	1166.1	1163.1	1161.2	1167.1	1161.2
180°	1164.1	1164.1	1164.1	1164.1	1164.1

(END OF REPORT)