

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009458

Luminaire Tested: S122DIP-B865D1080UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009458
REPORT IS A COMBINATION OF REPORTS P984759 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB35-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7735.8 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009458

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009458

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44
2	88	81	75	69	80	74	69	64	62	58	55	51	48	46	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	36	33	31
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21808	21808	21808
5°	21844	20787	20638
10°	21665	19840	19446
15°	21348	18885	18190
20°	20918	17847	17001
25°	20491	16763	15814
30°	19953	15744	14568
35°	19447	14668	13344
40°	18820	13607	12187
45°	18197	12556	11053
50°	17517	11485	9876
55°	16800	10340	8762
60°	15998	9101	7602
65°	15116	7841	6385
70°	13997	6463	5155
75°	12447	4982	3981
80°	10578	3386	2563
85°	7670	1576	1091

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18197 cd/sqm

TEST NUMBER: P1009458

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.7	1.7
10°-20°	364.8	4.7
20°-30°	536.1	6.9
30°-40°	622.7	8.0
40°-50°	621.9	8.0
50°-60°	542.3	7.0
60°-70°	400.8	5.2
70°-80°	226.8	2.9
80°-90°	63.7	0.8
90°-100°	245.8	3.2
100°-110°	830.9	10.7
110°-120°	873.4	11.3
120°-130°	718.2	9.3
130°-140°	577.1	7.5
140°-150°	436.0	5.6
150°-160°	306.5	4.0
160°-170°	180.5	2.3
170°-180°	58.7	0.8
0°-30°	1030.6	13.3
0°-40°	1653.3	21.4
0°-60°	2817.5	36.4
0°-90°	3508.9	45.4
90°-120°	1950.0	25.2
90°-150°	3681.3	47.6
90°-180°	4227.0	54.6
0°-180°	7735.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1378	1378	1378	1378	1378	
5°	1378	1372	1358	1368	1366	131
15°	1311	1304	1286	1292	1285	369
25°	1187	1176	1154	1156	1154	546
35°	1024	1011	990	982	975	639
45°	833	824	804	790	784	643
55°	630	623	607	591	584	564
65°	425	417	404	392	386	420
75°	222	220	213	205	208	237
85°	54	53	52	48	46	61
90°	1	16	40	38	38	6
95°	41	100	457	173	133	42
105°	142	215	864	1544	1314	151
115°	251	317	723	1492	1729	249
125°	350	414	695	1208	1403	311
135°	410	490	687	1016	1162	317
145°	469	539	683	848	928	294
155°	533	575	663	750	780	245
165°	581	598	635	674	684	164
175°	605	606	611	618	617	57
180°	606	606	606	606	606	

TEST NUMBER: P1009458

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1377.7	1377.7	1377.7	1377.7	1377.7
2.5°	1385.6	1379.0	1364.4	1377.7	1375.0
5°	1377.7	1372.4	1357.8	1368.4	1365.7
7.5°	1368.4	1360.4	1345.9	1356.5	1353.8
10°	1353.8	1344.5	1328.7	1339.2	1335.3
12.5°	1334.0	1326.0	1310.1	1316.7	1314.1
15°	1311.4	1303.5	1286.3	1291.6	1284.9
17.5°	1283.6	1275.7	1258.4	1265.1	1258.4
20°	1253.1	1245.2	1226.7	1230.6	1225.3
22.5°	1222.7	1210.8	1193.5	1193.5	1190.9
25°	1186.9	1176.3	1153.8	1156.4	1153.8
27.5°	1147.2	1137.9	1120.7	1116.7	1110.1
30°	1107.4	1096.8	1077.0	1073.0	1067.7
32.5°	1065.0	1057.1	1035.9	1028.0	1022.7
35°	1024.0	1010.7	989.5	981.6	975.0
37.5°	977.6	965.7	944.5	935.2	928.6
40°	929.9	919.3	898.1	886.2	880.9
42.5°	883.6	873.0	851.8	838.5	830.6
45°	833.2	823.9	804.1	789.5	784.2
47.5°	784.2	774.9	753.7	739.2	731.2
50°	732.5	725.9	707.4	688.8	682.2
52.5°	682.2	672.9	655.7	641.1	631.9
55°	630.5	622.6	606.7	590.8	584.2
57.5°	578.9	572.3	555.0	539.1	533.8
60°	527.2	521.9	503.4	488.8	484.8
62.5°	476.9	467.6	454.4	441.1	435.8
65°	425.2	417.3	404.0	392.1	385.5
67.5°	372.2	365.6	353.7	344.4	339.1
70°	323.2	317.9	306.0	296.7	291.4
72.5°	272.9	267.6	261.0	251.7	247.7
75°	222.5	219.9	213.3	205.3	208.0
77.5°	177.5	172.2	169.6	165.6	161.6
80°	132.5	131.1	128.5	124.5	121.9
82.5°	90.1	90.1	88.8	83.5	83.5
85°	54.3	53.0	51.7	47.7	46.4
87.5°	23.8	21.2	18.5	14.6	13.2
90°	1.2	15.8	39.6	37.9	38.5
92.5°	17.5	55.4	179.6	82.8	71.1
95°	40.8	100.3	457.0	172.6	132.9
97.5°	60.6	132.4	745.0	346.3	222.7
100°	89.8	162.0	921.1	689.7	417.4
102.5°	116.6	188.9	926.9	1165.9	813.8
105°	142.2	214.6	863.9	1544.2	1314.0
107.5°	170.2	240.2	805.6	1681.2	1650.9
110°	198.2	266.4	766.0	1659.1	1788.5

TEST NUMBER: P1009458

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	291.5	740.4	1583.8	1786.2
115°	250.7	316.6	722.9	1491.8	1729.0
117.5°	278.7	341.6	713.5	1403.8	1642.8
120°	304.3	366.1	705.4	1325.0	1560.0
122.5°	328.8	391.2	700.7	1263.8	1473.7
125°	349.8	413.9	694.9	1208.4	1402.6
127.5°	367.3	435.5	691.4	1161.2	1336.1
130°	382.4	454.7	689.1	1113.4	1281.3
132.5°	396.4	473.4	687.9	1063.9	1224.2
135°	410.4	489.7	686.7	1015.6	1162.4
137.5°	423.2	503.6	686.7	966.6	1103.0
140°	438.4	516.5	685.6	923.4	1041.2
142.5°	453.5	527.0	685.6	882.0	979.4
145°	468.7	538.6	683.2	848.2	928.1
147.5°	485.0	548.0	679.7	818.4	882.6
150°	501.3	557.3	676.2	792.8	843.0
152.5°	517.7	566.6	670.4	771.2	809.1
155°	532.8	575.4	663.4	750.3	780.0
157.5°	545.6	582.4	656.4	730.4	754.3
160°	558.5	589.4	649.4	710.6	729.9
162.5°	571.3	594.6	643.6	692.0	706.5
165°	580.6	598.1	635.4	673.9	684.4
167.5°	588.8	601.6	628.4	657.6	663.4
170°	596.9	603.4	622.6	642.4	644.7
172.5°	601.6	605.1	615.6	629.0	629.6
175°	605.1	605.7	610.9	618.5	616.8
177.5°	607.4	606.3	606.3	610.9	607.4
180°	606.3	606.3	606.3	606.3	606.3

(END OF REPORT)