

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008978

Luminaire Tested: S122DIP-B290D925UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008978
REPORT IS A COMBINATION OF REPORTS P984108 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D925UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4728.0 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008978

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008978

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	84	81	82	78	75	72	61	58	57	44	43	42	29	28	28
2	84	77	71	66	74	68	64	59	53	50	47	39	37	35	25	24	23
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13
7	54	42	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	22	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7236	7236	7236
5°	7247	6897	6849
10°	7189	6583	6453
15°	7083	6266	6036
20°	6941	5921	5641
25°	6799	5561	5247
30°	6622	5223	4834
35°	6453	4866	4428
40°	6246	4515	4044
45°	6039	4166	3667
50°	5813	3811	3278
55°	5574	3431	2907
60°	5307	3019	2523
65°	5016	2603	2118
70°	4643	2144	1711
75°	4128	1654	1321
80°	3513	1123	849
85°	2543	521	362

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6039 cd/sqm

TEST NUMBER: P1008978

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.0	0.9
10°-20°	121.1	2.6
20°-30°	177.9	3.8
30°-40°	206.6	4.4
40°-50°	206.4	4.4
50°-60°	179.9	3.8
60°-70°	133.0	2.8
70°-80°	75.3	1.6
80°-90°	23.1	0.5
90°-100°	207.1	4.4
100°-110°	700.1	14.8
110°-120°	735.9	15.6
120°-130°	605.2	12.8
130°-140°	486.3	10.3
140°-150°	367.4	7.8
150°-160°	258.3	5.5
160°-170°	152.1	3.2
170°-180°	49.5	1.0
0°-30°	342.0	7.2
0°-40°	548.6	11.6
0°-60°	934.9	19.8
0°-90°	1166.3	24.7
90°-120°	1643.2	34.8
90°-150°	3102.0	65.6
90°-180°	3562.0	75.3
0°-180°	4728.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	457	457	457	457	457	
5°	457	455	450	454	453	43
15°	435	432	427	429	426	123
25°	394	390	383	384	383	181
35°	340	335	328	326	324	212
45°	276	273	267	262	260	213
55°	209	207	201	196	194	187
65°	141	138	134	130	128	139
75°	74	73	71	68	69	79
85°	18	18	17	16	15	20
90°	1	13	33	32	32	3
95°	34	84	385	145	112	36
105°	120	181	728	1301	1107	127
115°	211	267	609	1257	1457	209
125°	295	349	586	1018	1182	262
135°	346	413	579	856	980	267
145°	395	454	576	715	782	248
155°	449	485	559	632	657	207
165°	489	504	535	568	577	138
175°	510	510	515	521	520	48
180°	511	511	511	511	511	

TEST NUMBER: P1008978

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	457.1	457.1	457.1	457.1	457.1
2.5°	459.8	457.6	452.7	457.1	456.2
5°	457.1	455.4	450.5	454.0	453.2
7.5°	454.0	451.4	446.6	450.1	449.2
10°	449.2	446.1	440.9	444.4	443.1
12.5°	442.6	440.0	434.7	436.9	436.0
15°	435.1	432.5	426.8	428.6	426.4
17.5°	425.9	423.3	417.6	419.8	417.6
20°	415.8	413.2	407.0	408.3	406.6
22.5°	405.7	401.7	396.0	396.0	395.1
25°	393.8	390.3	382.8	383.7	382.8
27.5°	380.6	377.6	371.9	370.5	368.3
30°	367.5	363.9	357.3	356.0	354.3
32.5°	353.4	350.8	343.7	341.1	339.3
35°	339.8	335.4	328.3	325.7	323.5
37.5°	324.4	320.4	313.4	310.3	308.1
40°	308.6	305.0	298.0	294.1	292.3
42.5°	293.2	289.7	282.6	278.2	275.6
45°	276.5	273.4	266.8	262.0	260.2
47.5°	260.2	257.1	250.1	245.3	242.6
50°	243.1	240.9	234.7	228.6	226.4
52.5°	226.4	223.3	217.6	212.7	209.7
55°	209.2	206.6	201.3	196.0	193.8
57.5°	192.1	189.9	184.2	178.9	177.1
60°	174.9	173.2	167.0	162.2	160.9
62.5°	158.2	155.2	150.8	146.4	144.6
65°	141.1	138.5	134.1	130.1	127.9
67.5°	123.5	121.3	117.4	114.3	112.5
70°	107.2	105.5	101.5	98.5	96.7
72.5°	90.5	88.8	86.6	83.5	82.2
75°	73.8	73.0	70.8	68.1	69.0
77.5°	58.9	57.1	56.3	54.9	53.6
80°	44.0	43.5	42.6	41.3	40.4
82.5°	29.9	29.9	29.4	27.7	27.7
85°	18.0	17.6	17.1	15.8	15.4
87.5°	7.9	7.0	6.2	4.8	4.4
90°	1.0	13.2	33.4	31.9	32.4
92.5°	14.7	46.7	151.3	69.8	59.9
95°	34.4	84.5	385.1	145.4	112.0
97.5°	51.1	111.5	627.8	291.8	187.6
100°	75.6	136.6	776.1	581.2	351.7
102.5°	98.2	159.2	781.0	982.4	685.7
105°	119.9	180.8	728.0	1301.2	1107.2
107.5°	143.4	202.4	678.9	1416.6	1391.1
110°	167.0	224.4	645.5	1398.0	1507.1

TEST NUMBER: P1008978

CATALOG NUMBER: S122DIP-B290D925UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.6	245.6	623.9	1334.6	1505.1
115°	211.2	266.8	609.1	1257.0	1457.0
117.5°	234.8	287.8	601.3	1182.8	1384.3
120°	256.4	308.4	594.4	1116.5	1314.5
122.5°	277.0	329.6	590.4	1065.0	1241.8
125°	294.7	348.8	585.5	1018.3	1181.9
127.5°	309.5	367.0	582.6	978.5	1125.9
130°	322.2	383.2	580.6	938.2	1079.7
132.5°	334.0	398.8	579.6	896.4	1031.6
135°	345.8	412.6	578.7	855.7	979.5
137.5°	356.6	424.4	578.7	814.4	929.4
140°	369.4	435.2	577.7	778.1	877.3
142.5°	382.2	444.1	577.7	743.2	825.3
145°	394.9	453.9	575.7	714.8	782.0
147.5°	408.7	461.8	572.8	689.7	743.7
150°	422.5	469.6	569.8	668.0	710.3
152.5°	436.2	477.4	564.9	649.9	681.8
155°	449.0	484.8	559.0	632.2	657.3
157.5°	459.8	490.7	553.1	615.5	635.6
160°	470.6	496.6	547.2	598.8	615.0
162.5°	481.4	501.0	542.3	583.0	595.4
165°	489.3	504.0	535.4	567.8	576.7
167.5°	496.1	507.0	529.5	554.1	559.0
170°	503.0	508.4	524.6	541.3	543.3
172.5°	506.9	509.9	518.7	530.0	530.5
175°	509.9	510.4	514.8	521.2	519.7
177.5°	511.9	510.9	510.9	514.8	511.9
180°	510.9	510.9	510.9	510.9	510.9

(END OF REPORT)