

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009491

Luminaire Tested: S122DIP-B865D330UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009491
REPORT IS A COMBINATION OF REPORTS P984810 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4779.5 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009491

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009491

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40
5	72	60	52	45	68	57	50	44	52	46	41	47	42	38	43	39	35
6	67	54	46	39	63	52	44	38	47	41	36	43	38	33	39	35	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25
9	54	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1009491

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	2.7
10°-20°	363.3	7.6
20°-30°	533.8	11.2
30°-40°	620.0	13.0
40°-50°	619.2	13.0
50°-60°	540.0	11.3
60°-70°	399.1	8.4
70°-80°	225.8	4.7
80°-90°	60.8	1.3
90°-100°	74.9	1.6
100°-110°	253.2	5.3
110°-120°	266.2	5.6
120°-130°	218.9	4.6
130°-140°	175.9	3.7
140°-150°	132.9	2.8
150°-160°	93.4	2.0
160°-170°	55.0	1.2
170°-180°	17.9	0.4
0°-30°	1026.2	21.5
0°-40°	1646.2	34.4
0°-60°	2805.4	58.7
0°-90°	3491.2	73.0
90°-120°	594.3	12.4
90°-150°	1122.0	23.5
90°-180°	1288.0	26.9
0°-180°	4779.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	0	5	12	12	12	4
95°	12	31	139	53	40	13
105°	43	65	263	471	400	46
115°	76	96	220	455	527	76
125°	107	126	212	368	428	95
135°	125	149	209	310	354	97
145°	143	164	208	259	283	90
155°	162	175	202	229	238	75
165°	177	182	194	205	209	50
175°	184	185	186	188	188	18
180°	185	185	185	185	185	

TEST NUMBER: P1009491

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	0.4	4.8	12.1	11.6	11.7
92.5°	5.3	16.8	54.7	25.2	21.7
95°	12.4	30.6	139.3	52.6	40.5
97.5°	18.5	40.3	227.1	105.6	67.9
100°	27.4	49.4	280.7	210.2	127.2
102.5°	35.5	57.6	282.5	355.3	248.0
105°	43.4	65.4	263.3	470.6	400.5
107.5°	51.9	73.2	245.5	512.4	503.2
110°	60.4	81.2	233.5	505.6	545.1



TEST NUMBER: P1009491

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.2	88.8	225.6	482.8	544.4
115°	76.4	96.5	220.3	454.7	527.0
117.5°	84.9	104.1	217.5	427.8	500.7
120°	92.7	111.6	215.0	403.8	475.5
122.5°	100.2	119.2	213.6	385.2	449.2
125°	106.6	126.2	211.8	368.3	427.5
127.5°	111.9	132.8	210.7	354.0	407.2
130°	116.6	138.6	210.0	339.4	390.5
132.5°	120.8	144.2	209.7	324.2	373.1
135°	125.1	149.2	209.3	309.6	354.3
137.5°	129.0	153.5	209.3	294.6	336.2
140°	133.6	157.4	208.9	281.5	317.3
142.5°	138.2	160.6	208.9	268.8	298.5
145°	142.8	164.2	208.2	258.6	282.9
147.5°	147.8	167.0	207.2	249.4	269.0
150°	152.8	169.9	206.1	241.6	256.9
152.5°	157.8	172.7	204.3	235.0	246.6
155°	162.4	175.4	202.2	228.6	237.7
157.5°	166.3	177.5	200.1	222.6	229.9
160°	170.2	179.6	197.9	216.6	222.4
162.5°	174.1	181.2	196.2	210.9	215.3
165°	177.0	182.3	193.7	205.4	208.6
167.5°	179.4	183.4	191.5	200.4	202.2
170°	181.9	183.9	189.8	195.8	196.5
172.5°	183.4	184.4	187.6	191.7	191.9
175°	184.4	184.6	186.2	188.5	188.0
177.5°	185.1	184.8	184.8	186.2	185.1
180°	184.8	184.8	184.8	184.8	184.8

(END OF REPORT)