

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009037

Luminaire Tested: S122DIP-B485D330UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009037
REPORT IS A COMBINATION OF REPORTS P984185 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D330UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3120.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009037

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009037

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12139	12139	12139
5°	12159	11571	11488
10°	12060	11044	10825
15°	11883	10512	10125
20°	11644	9934	9464
25°	11407	9330	8802
30°	11106	8764	8109
35°	10825	8165	7428
40°	10476	7574	6783
45°	10129	6989	6152
50°	9752	6394	5497
55°	9353	5755	4877
60°	8906	5066	4232
65°	8415	4365	3554
70°	7791	3597	2869
75°	6931	2773	2216
80°	5884	1884	1425
85°	4266	878	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10129 cd/sqm

TEST NUMBER: P1009037

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	2.3
10°-20°	203.1	6.5
20°-30°	298.4	9.6
30°-40°	346.6	11.1
40°-50°	346.2	11.1
50°-60°	301.9	9.7
60°-70°	223.1	7.2
70°-80°	126.3	4.0
80°-90°	34.5	1.1
90°-100°	25.8	0.8
100°-110°	82.1	2.6
110°-120°	140.6	4.5
120°-130°	184.8	5.9
130°-140°	207.5	6.7
140°-150°	203.5	6.5
150°-160°	170.7	5.5
160°-170°	113.2	3.6
170°-180°	39.6	1.3
0°-30°	573.7	18.4
0°-40°	920.3	29.5
0°-60°	1568.3	50.3
0°-90°	1952.2	62.6
90°-120°	248.5	8.0
90°-150°	844.4	27.1
90°-180°	1168.0	37.4
0°-180°	3120.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	764	756	762	760	73
15°	730	726	716	719	715	206
25°	661	655	642	644	642	304
35°	570	563	551	546	543	356
45°	464	459	448	440	436	358
55°	351	347	338	329	325	314
65°	237	232	225	218	215	234
75°	124	122	119	114	116	132
85°	30	30	29	26	26	34
90°	0	5	12	12	12	3
95°	18	22	23	23	22	20
105°	76	77	78	78	78	80
115°	141	143	142	142	141	139
125°	205	208	207	206	206	183
135°	265	269	270	270	269	205
145°	322	325	327	327	326	201
155°	368	369	370	372	371	170
165°	401	400	400	403	401	113
175°	417	416	415	418	416	40
180°	418	418	418	418	418	

TEST NUMBER: P1009037

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.9	766.9	766.9	766.9	766.9
2.5°	771.3	767.6	759.5	766.9	765.4
5°	766.9	763.9	755.8	761.7	760.2
7.5°	761.7	757.3	749.2	755.1	753.6
10°	753.6	748.4	739.6	745.5	743.3
12.5°	742.5	738.1	729.2	732.9	731.5
15°	730.0	725.6	716.0	718.9	715.2
17.5°	714.5	710.1	700.5	704.2	700.5
20°	697.5	693.1	682.8	685.0	682.1
22.5°	680.6	673.9	664.4	664.4	662.9
25°	660.7	654.8	642.2	643.7	642.2
27.5°	638.6	633.4	623.8	621.6	617.9
30°	616.4	610.5	599.5	597.3	594.3
32.5°	592.8	588.4	576.6	572.2	569.2
35°	570.0	562.6	550.8	546.4	542.7
37.5°	544.2	537.5	525.7	520.6	516.9
40°	517.6	511.7	499.9	493.3	490.3
42.5°	491.8	485.9	474.1	466.7	462.3
45°	463.8	458.6	447.6	439.5	436.5
47.5°	436.5	431.4	419.6	411.4	407.0
50°	407.8	404.1	393.8	383.4	379.7
52.5°	379.7	374.6	365.0	356.9	351.7
55°	351.0	346.6	337.7	328.9	325.2
57.5°	322.2	318.5	309.0	300.1	297.2
60°	293.5	290.5	280.2	272.1	269.9
62.5°	265.4	260.3	252.9	245.5	242.6
65°	236.7	232.3	224.9	218.3	214.6
67.5°	207.2	203.5	196.9	191.7	188.8
70°	179.9	177.0	170.3	165.2	162.2
72.5°	151.9	148.9	145.3	140.1	137.9
75°	123.9	122.4	118.7	114.3	115.8
77.5°	98.8	95.9	94.4	92.2	90.0
80°	73.7	73.0	71.5	69.3	67.8
82.5°	50.1	50.1	49.4	46.5	46.5
85°	30.2	29.5	28.8	26.5	25.8
87.5°	13.3	11.8	10.3	8.1	7.4
90°	0.4	4.6	12.3	11.6	12.0
92.5°	7.8	10.6	10.9	11.3	11.3
95°	18.3	21.9	22.6	22.6	21.9
97.5°	30.7	33.8	35.2	35.2	35.2
100°	44.8	47.6	48.6	48.6	48.3
102.5°	59.6	61.7	63.1	63.4	63.1
105°	75.8	76.8	77.5	78.3	78.3
107.5°	92.0	93.4	93.4	93.8	92.0
110°	107.5	109.6	109.6	109.6	108.6

TEST NUMBER: P1009037

CATALOG NUMBER: S122DIP-B485D330UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	124.4	126.5	126.2	125.1	124.4
115°	141.0	143.1	142.4	142.1	141.0
117.5°	157.6	160.4	158.6	157.6	156.5
120°	174.1	176.9	174.1	174.1	173.1
122.5°	189.3	192.8	191.0	190.0	189.3
125°	205.1	208.3	207.3	206.2	205.9
127.5°	220.7	224.5	223.1	221.7	220.7
130°	235.1	239.7	239.0	238.3	236.9
132.5°	251.3	254.9	255.2	253.4	252.4
135°	265.4	269.3	270.0	269.7	268.6
137.5°	280.9	284.1	284.8	284.5	283.0
140°	294.7	297.9	299.6	299.6	298.2
142.5°	308.8	312.0	313.0	313.4	312.0
145°	322.2	324.6	326.8	327.1	325.7
147.5°	334.2	337.3	338.7	339.4	338.0
150°	346.5	348.6	350.0	351.1	350.0
152.5°	357.4	359.5	361.3	362.7	361.3
155°	368.4	369.4	370.5	372.2	371.2
157.5°	377.9	378.6	379.3	381.7	380.0
160°	386.3	387.0	387.4	389.5	388.1
162.5°	394.1	394.1	394.4	396.9	395.1
165°	400.8	400.4	400.4	402.9	401.1
167.5°	406.8	405.7	405.7	408.2	406.4
170°	411.4	410.3	409.9	412.4	410.3
172.5°	414.5	413.5	413.1	415.6	413.5
175°	417.0	415.9	415.2	417.7	415.6
177.5°	418.4	417.3	416.6	418.8	416.6
180°	417.7	417.7	417.7	417.7	417.7

(END OF REPORT)