

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009047

Luminaire Tested: S122DIP-B485D330UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009047
REPORT IS A COMBINATION OF REPORTS P984210 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D330UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3257.5 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009047

CATALOG NUMBER: S122DIP-B485D330UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009047

CATALOG NUMBER: S122DIP-B485D330UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	56
2	91	84	77	72	85	78	73	68	69	64	61	60	56	54	51	49	47
3	83	74	66	60	77	69	62	57	61	55	51	53	49	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	37	33	30
6	65	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	45	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12244	12244	12244
5°	12264	11672	11588
10°	12164	11139	10918
15°	11986	10603	10214
20°	11745	10020	9546
25°	11505	9411	8879
30°	11204	8840	8180
35°	10918	8236	7492
40°	10567	7641	6843
45°	10217	7050	6206
50°	9836	6449	5545
55°	9433	5807	4919
60°	8982	5109	4268
65°	8489	4404	3584
70°	7860	3628	2894
75°	6993	2796	2236
80°	5940	1900	1438
85°	4308	884	611

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10217 cd/sqm

TEST NUMBER: P1009047

CATALOG NUMBER: S122DIP-B485D330UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	2.2
10°-20°	204.8	6.3
20°-30°	301.0	9.2
30°-40°	349.6	10.7
40°-50°	349.2	10.7
50°-60°	304.5	9.3
60°-70°	225.1	6.9
70°-80°	127.3	3.9
80°-90°	34.8	1.1
90°-100°	74.9	2.3
100°-110°	253.2	7.8
110°-120°	266.2	8.2
120°-130°	218.9	6.7
130°-140°	175.9	5.4
140°-150°	132.9	4.1
150°-160°	93.4	2.9
160°-170°	55.0	1.7
170°-180°	17.9	0.5
0°-30°	578.7	17.8
0°-40°	928.3	28.5
0°-60°	1582.0	48.6
0°-90°	1969.2	60.5
90°-120°	594.3	18.2
90°-150°	1122.0	34.4
90°-180°	1288.0	39.5
0°-180°	3257.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	774	771	762	768	767	73
15°	736	732	722	725	722	207
25°	666	660	648	649	648	307
35°	575	568	556	551	547	359
45°	468	463	452	443	440	361
55°	354	350	341	332	328	317
65°	239	234	227	220	216	236
75°	125	124	120	115	117	133
85°	30	30	29	27	26	34
90°	0	5	12	12	12	3
95°	12	31	139	53	40	13
105°	43	65	263	471	400	46
115°	76	96	220	455	527	76
125°	107	126	212	368	428	95
135°	125	149	209	310	354	97
145°	143	164	208	259	283	90
155°	162	175	202	229	238	75
165°	177	182	194	205	209	50
175°	184	185	186	188	188	18
180°	185	185	185	185	185	

TEST NUMBER: P1009047

CATALOG NUMBER: S122DIP-B485D330UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	773.5	773.5	773.5	773.5	773.5
2.5°	778.0	774.3	766.1	773.5	772.0
5°	773.5	770.6	762.4	768.3	766.8
7.5°	768.3	763.9	755.7	761.6	760.1
10°	760.1	754.9	746.0	752.0	749.7
12.5°	749.0	744.5	735.6	739.3	737.8
15°	736.3	731.9	722.2	725.2	721.5
17.5°	720.7	716.3	706.6	710.3	706.6
20°	703.6	699.2	688.7	691.0	688.0
22.5°	686.5	679.8	670.2	670.2	668.7
25°	666.4	660.5	647.8	649.3	647.8
27.5°	644.1	638.9	629.2	627.0	623.3
30°	621.8	615.9	604.7	602.5	599.5
32.5°	598.0	593.5	581.6	577.2	574.2
35°	574.9	567.5	555.6	551.1	547.4
37.5°	548.9	542.2	530.3	525.1	521.4
40°	522.1	516.2	504.3	497.6	494.6
42.5°	496.1	490.2	478.3	470.8	466.4
45°	467.8	462.6	451.5	443.3	440.3
47.5°	440.3	435.1	423.2	415.0	410.6
50°	411.3	407.6	397.2	386.8	383.0
52.5°	383.0	377.8	368.2	360.0	354.8
55°	354.0	349.6	340.7	331.7	328.0
57.5°	325.0	321.3	311.6	302.7	299.7
60°	296.0	293.1	282.6	274.5	272.2
62.5°	267.8	262.6	255.1	247.7	244.7
65°	238.8	234.3	226.9	220.2	216.4
67.5°	209.0	205.3	198.6	193.4	190.4
70°	181.5	178.5	171.8	166.6	163.6
72.5°	153.2	150.2	146.5	141.3	139.1
75°	125.0	123.5	119.7	115.3	116.8
77.5°	99.7	96.7	95.2	93.0	90.7
80°	74.4	73.6	72.1	69.9	68.4
82.5°	50.6	50.6	49.8	46.9	46.9
85°	30.5	29.8	29.0	26.8	26.0
87.5°	13.4	11.9	10.4	8.2	7.4
90°	0.4	4.8	12.1	11.6	11.7
92.5°	5.3	16.8	54.7	25.2	21.7
95°	12.4	30.6	139.3	52.6	40.5
97.5°	18.5	40.3	227.1	105.6	67.9
100°	27.4	49.4	280.7	210.2	127.2
102.5°	35.5	57.6	282.5	355.3	248.0
105°	43.4	65.4	263.3	470.6	400.5
107.5°	51.9	73.2	245.5	512.4	503.2
110°	60.4	81.2	233.5	505.6	545.1



TEST NUMBER: P1009047

CATALOG NUMBER: S122DIP-B485D330UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.2	88.8	225.6	482.8	544.4
115°	76.4	96.5	220.3	454.7	527.0
117.5°	84.9	104.1	217.5	427.8	500.7
120°	92.7	111.6	215.0	403.8	475.5
122.5°	100.2	119.2	213.6	385.2	449.2
125°	106.6	126.2	211.8	368.3	427.5
127.5°	111.9	132.8	210.7	354.0	407.2
130°	116.6	138.6	210.0	339.4	390.5
132.5°	120.8	144.2	209.7	324.2	373.1
135°	125.1	149.2	209.3	309.6	354.3
137.5°	129.0	153.5	209.3	294.6	336.2
140°	133.6	157.4	208.9	281.5	317.3
142.5°	138.2	160.6	208.9	268.8	298.5
145°	142.8	164.2	208.2	258.6	282.9
147.5°	147.8	167.0	207.2	249.4	269.0
150°	152.8	169.9	206.1	241.6	256.9
152.5°	157.8	172.7	204.3	235.0	246.6
155°	162.4	175.4	202.2	228.6	237.7
157.5°	166.3	177.5	200.1	222.6	229.9
160°	170.2	179.6	197.9	216.6	222.4
162.5°	174.1	181.2	196.2	210.9	215.3
165°	177.0	182.3	193.7	205.4	208.6
167.5°	179.4	183.4	191.5	200.4	202.2
170°	181.9	183.9	189.8	195.8	196.5
172.5°	183.4	184.4	187.6	191.7	191.9
175°	184.4	184.6	186.2	188.5	188.0
177.5°	185.1	184.8	184.8	186.2	185.1
180°	184.8	184.8	184.8	184.8	184.8

(END OF REPORT)