

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009535

Luminaire Tested: S122DIP-B865D530UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009535
REPORT IS A COMBINATION OF REPORTS P984869 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D530UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5385.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009535

CATALOG NUMBER: S122DIP-B865D530UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009535

CATALOG NUMBER: S122DIP-B865D530UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	39	36
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32
6	65	53	44	39	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	25	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1009535

CATALOG NUMBER: S122DIP-B865D530UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	2.4
10°-20°	363.3	6.7
20°-30°	533.8	9.9
30°-40°	620.0	11.5
40°-50°	619.2	11.5
50°-60°	540.0	10.0
60°-70°	399.1	7.4
70°-80°	225.8	4.2
80°-90°	61.5	1.1
90°-100°	41.9	0.8
100°-110°	133.2	2.5
110°-120°	227.8	4.2
120°-130°	299.7	5.6
130°-140°	336.4	6.2
140°-150°	329.9	6.1
150°-160°	276.7	5.1
160°-170°	183.5	3.4
170°-180°	64.1	1.2
0°-30°	1026.2	19.1
0°-40°	1646.2	30.6
0°-60°	2805.4	52.1
0°-90°	3491.9	64.8
90°-120°	402.9	7.5
90°-150°	1368.8	25.4
90°-180°	1893.0	35.2
0°-180°	5385.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	1	7	20	19	19	5
95°	30	35	37	37	35	33
105°	123	125	126	127	127	130
115°	229	232	231	230	229	226
125°	333	338	336	334	334	297
135°	430	437	438	437	435	332
145°	522	526	530	530	528	326
155°	597	599	600	603	602	275
165°	650	649	649	653	650	183
175°	676	674	673	677	674	64
180°	677	677	677	677	677	

TEST NUMBER: P1009535

CATALOG NUMBER: S122DIP-B865D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	0.6	7.4	20.0	18.9	19.4
92.5°	12.6	17.1	17.7	18.3	18.3
95°	29.7	35.4	36.6	36.6	35.4
97.5°	49.7	54.9	57.1	57.1	57.1
100°	72.6	77.1	78.9	78.9	78.3
102.5°	96.6	100.0	102.3	102.9	102.3
105°	122.9	124.6	125.7	126.9	126.9
107.5°	149.1	151.4	151.4	152.0	149.1
110°	174.3	177.7	177.7	177.7	176.0

TEST NUMBER: P1009535

CATALOG NUMBER: S122DIP-B865D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.7	205.1	204.6	202.8	201.7
115°	228.6	232.0	230.8	230.3	228.6
117.5°	255.4	260.0	257.1	255.4	253.7
120°	282.3	286.8	282.3	282.3	280.6
122.5°	306.8	312.6	309.7	308.0	306.8
125°	332.6	337.7	336.0	334.3	333.7
127.5°	357.7	364.0	361.7	359.4	357.7
130°	381.1	388.6	387.4	386.3	384.0
132.5°	407.4	413.1	413.7	410.8	409.1
135°	430.3	436.6	437.7	437.1	435.4
137.5°	455.4	460.5	461.7	461.1	458.8
140°	477.7	482.8	485.7	485.7	483.4
142.5°	500.5	505.7	507.4	508.0	505.7
145°	522.3	526.3	529.7	530.3	528.0
147.5°	541.7	546.8	549.1	550.3	548.0
150°	561.7	565.1	567.4	569.1	567.4
152.5°	579.4	582.8	585.7	588.0	585.7
155°	597.1	598.8	600.5	603.4	601.7
157.5°	612.5	613.7	614.8	618.8	616.0
160°	626.3	627.4	628.0	631.4	629.1
162.5°	638.8	638.8	639.4	643.4	640.5
165°	649.7	649.1	649.1	653.1	650.3
167.5°	659.4	657.7	657.7	661.7	658.8
170°	666.8	665.1	664.5	668.5	665.1
172.5°	672.0	670.3	669.7	673.7	670.3
175°	676.0	674.3	673.1	677.1	673.7
177.5°	678.3	676.5	675.4	678.8	675.4
180°	677.1	677.1	677.1	677.1	677.1

(END OF REPORT)