

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009553

Luminaire Tested: S122DIP-B865D530UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009553
REPORT IS A COMBINATION OF REPORTS P984887 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D530UB40-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5354.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009553

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009553

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	39	36
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32
6	65	53	44	39	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	25	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21590	21590	21590
5°	21625	20578	20433
10°	21449	19641	19251
15°	21135	18696	18008
20°	20710	17668	16831
25°	20287	16595	15656
30°	19755	15586	14422
35°	19254	14522	13210
40°	18632	13472	12065
45°	18016	12431	10943
50°	17342	11370	9778
55°	16635	10236	8673
60°	15840	9011	7527
65°	14966	7763	6320
70°	13858	6397	5104
75°	12324	4931	3941
80°	10467	3352	2537
85°	7600	1558	1079

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18016 cd/sqm

TEST NUMBER: P1009553

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	2.4
10°-20°	361.2	6.7
20°-30°	530.8	9.9
30°-40°	616.5	11.5
40°-50°	615.7	11.5
50°-60°	536.9	10.0
60°-70°	396.9	7.4
70°-80°	224.5	4.2
80°-90°	61.2	1.1
90°-100°	41.6	0.8
100°-110°	132.4	2.5
110°-120°	226.5	4.2
120°-130°	297.9	5.6
130°-140°	334.4	6.2
140°-150°	327.9	6.1
150°-160°	275.1	5.1
160°-170°	182.4	3.4
170°-180°	63.8	1.2
0°-30°	1020.3	19.1
0°-40°	1636.8	30.6
0°-60°	2789.4	52.1
0°-90°	3471.9	64.8
90°-120°	400.5	7.5
90°-150°	1360.8	25.4
90°-180°	1882.0	35.2
0°-180°	5354.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1364	1364	1364	1364	1364	
5°	1364	1359	1344	1355	1352	129
15°	1298	1290	1273	1279	1272	366
25°	1175	1165	1142	1145	1142	541
35°	1014	1001	980	972	965	633
45°	825	816	796	782	776	637
55°	624	616	601	585	578	558
65°	421	413	400	388	382	416
75°	220	218	211	203	206	235
85°	54	52	51	47	46	60
90°	1	7	20	19	19	5
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	231	230	229	227	225
125°	331	336	334	332	332	295
135°	428	434	435	435	433	331
145°	519	523	527	527	525	324
155°	594	595	597	600	598	273
165°	646	645	645	649	646	182
175°	672	670	669	673	670	64
180°	673	673	673	673	673	

TEST NUMBER: P1009553

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1363.9	1363.9	1363.9	1363.9	1363.9
2.5°	1371.8	1365.2	1350.8	1363.9	1361.3
5°	1363.9	1358.7	1344.2	1354.7	1352.1
7.5°	1354.7	1346.9	1332.4	1342.9	1340.3
10°	1340.3	1331.1	1315.4	1325.9	1321.9
12.5°	1320.6	1312.8	1297.0	1303.6	1301.0
15°	1298.3	1290.5	1273.4	1278.7	1272.1
17.5°	1270.8	1262.9	1245.9	1252.4	1245.9
20°	1240.6	1232.8	1214.4	1218.3	1213.1
22.5°	1210.5	1198.7	1181.6	1181.6	1179.0
25°	1175.1	1164.6	1142.3	1144.9	1142.3
27.5°	1135.7	1126.5	1109.5	1105.6	1099.0
30°	1096.4	1085.9	1066.2	1062.3	1057.0
32.5°	1054.4	1046.5	1025.6	1017.7	1012.4
35°	1013.8	1000.6	979.7	971.8	965.2
37.5°	967.9	956.0	935.1	925.9	919.3
40°	920.6	910.1	889.2	877.4	872.1
42.5°	874.7	864.2	843.3	830.1	822.3
45°	824.9	815.7	796.1	781.6	776.4
47.5°	776.4	767.2	746.2	731.8	723.9
50°	725.2	718.7	700.3	682.0	675.4
52.5°	675.4	666.2	649.2	634.7	625.6
55°	624.3	616.4	600.6	584.9	578.3
57.5°	573.1	566.5	549.5	533.8	528.5
60°	522.0	516.7	498.4	483.9	480.0
62.5°	472.1	462.9	449.8	436.7	431.5
65°	421.0	413.1	400.0	388.2	381.6
67.5°	368.5	362.0	350.2	341.0	335.7
70°	320.0	314.7	302.9	293.8	288.5
72.5°	270.2	264.9	258.4	249.2	245.2
75°	220.3	217.7	211.1	203.3	205.9
77.5°	175.7	170.5	167.9	163.9	160.0
80°	131.1	129.8	127.2	123.3	120.7
82.5°	89.2	89.2	87.9	82.6	82.6
85°	53.8	52.5	51.1	47.2	45.9
87.5°	23.6	21.0	18.4	14.4	13.1
90°	0.6	7.4	19.9	18.7	19.3
92.5°	12.5	17.0	17.6	18.2	18.2
95°	29.5	35.2	36.4	36.4	35.2
97.5°	49.4	54.5	56.8	56.8	56.8
100°	72.1	76.7	78.4	78.4	77.8
102.5°	96.0	99.4	101.7	102.3	101.7
105°	122.1	123.8	125.0	126.1	126.1
107.5°	148.3	150.5	150.5	151.1	148.3
110°	173.3	176.7	176.7	176.7	175.0

TEST NUMBER: P1009553

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.5	203.9	203.4	201.7	200.5
115°	227.2	230.6	229.5	228.9	227.2
117.5°	253.9	258.5	255.6	253.9	252.2
120°	280.6	285.2	280.6	280.6	278.9
122.5°	305.1	310.7	307.9	306.2	305.1
125°	330.6	335.7	334.0	332.3	331.8
127.5°	355.6	361.9	359.6	357.3	355.6
130°	378.9	386.3	385.2	384.0	381.8
132.5°	405.0	410.7	411.3	408.5	406.7
135°	427.8	434.0	435.2	434.6	432.9
137.5°	452.8	457.9	459.0	458.4	456.2
140°	474.9	480.0	482.9	482.9	480.6
142.5°	497.6	502.8	504.5	505.0	502.8
145°	519.2	523.2	526.6	527.2	524.9
147.5°	538.5	543.7	545.9	547.1	544.8
150°	558.4	561.8	564.1	565.8	564.1
152.5°	576.0	579.4	582.3	584.6	582.3
155°	593.6	595.4	597.1	599.9	598.2
157.5°	609.0	610.1	611.3	615.2	612.4
160°	622.6	623.8	624.3	627.7	625.5
162.5°	635.1	635.1	635.7	639.7	636.8
165°	645.9	645.3	645.3	649.3	646.5
167.5°	655.6	653.9	653.9	657.8	655.0
170°	663.0	661.3	660.7	664.7	661.3
172.5°	668.1	666.4	665.8	669.8	666.4
175°	672.0	670.3	669.2	673.2	669.8
177.5°	674.3	672.6	671.5	674.9	671.5
180°	673.2	673.2	673.2	673.2	673.2

(END OF REPORT)