

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009554

Luminaire Tested: S122DIP-B865D530UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009554
REPORT IS A COMBINATION OF REPORTS P984888 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D530UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5532.4 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009554

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009554

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21590	21590	21590
5°	21625	20578	20433
10°	21449	19641	19251
15°	21135	18696	18008
20°	20710	17668	16831
25°	20287	16595	15656
30°	19755	15586	14422
35°	19254	14522	13210
40°	18632	13472	12065
45°	18016	12431	10943
50°	17342	11370	9778
55°	16635	10236	8673
60°	15840	9011	7527
65°	14966	7763	6320
70°	13858	6397	5104
75°	12324	4931	3941
80°	10467	3352	2537
85°	7600	1558	1079

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18016 cd/sqm

TEST NUMBER: P1009554

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	2.3
10°-20°	361.2	6.5
20°-30°	530.8	9.6
30°-40°	616.5	11.1
40°-50°	615.7	11.1
50°-60°	536.9	9.7
60°-70°	396.9	7.2
70°-80°	224.5	4.1
80°-90°	61.1	1.1
90°-100°	119.8	2.2
100°-110°	405.0	7.3
110°-120°	425.7	7.7
120°-130°	350.1	6.3
130°-140°	281.3	5.1
140°-150°	212.5	3.8
150°-160°	149.4	2.7
160°-170°	88.0	1.6
170°-180°	28.6	0.5
0°-30°	1020.3	18.4
0°-40°	1636.8	29.6
0°-60°	2789.4	50.4
0°-90°	3471.9	62.8
90°-120°	950.6	17.2
90°-150°	1794.5	32.4
90°-180°	2060.0	37.2
0°-180°	5532.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1364	1364	1364	1364	1364	
5°	1364	1359	1344	1355	1352	129
15°	1298	1290	1273	1279	1272	366
25°	1175	1165	1142	1145	1142	541
35°	1014	1001	980	972	965	633
45°	825	816	796	782	776	637
55°	624	616	601	585	578	558
65°	421	413	400	388	382	416
75°	220	218	211	203	206	235
85°	54	52	51	47	46	60
90°	1	8	19	18	19	5
95°	20	49	223	84	65	21
105°	69	105	421	753	640	74
115°	122	154	352	727	843	121
125°	170	202	339	589	684	152
135°	200	239	335	495	567	155
145°	228	263	333	413	452	143
155°	260	280	323	366	380	120
165°	283	292	310	328	334	80
175°	295	295	298	302	301	28
180°	296	296	296	296	296	

TEST NUMBER: P1009554

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1363.9	1363.9	1363.9	1363.9	1363.9
2.5°	1371.8	1365.2	1350.8	1363.9	1361.3
5°	1363.9	1358.7	1344.2	1354.7	1352.1
7.5°	1354.7	1346.9	1332.4	1342.9	1340.3
10°	1340.3	1331.1	1315.4	1325.9	1321.9
12.5°	1320.6	1312.8	1297.0	1303.6	1301.0
15°	1298.3	1290.5	1273.4	1278.7	1272.1
17.5°	1270.8	1262.9	1245.9	1252.4	1245.9
20°	1240.6	1232.8	1214.4	1218.3	1213.1
22.5°	1210.5	1198.7	1181.6	1181.6	1179.0
25°	1175.1	1164.6	1142.3	1144.9	1142.3
27.5°	1135.7	1126.5	1109.5	1105.6	1099.0
30°	1096.4	1085.9	1066.2	1062.3	1057.0
32.5°	1054.4	1046.5	1025.6	1017.7	1012.4
35°	1013.8	1000.6	979.7	971.8	965.2
37.5°	967.9	956.0	935.1	925.9	919.3
40°	920.6	910.1	889.2	877.4	872.1
42.5°	874.7	864.2	843.3	830.1	822.3
45°	824.9	815.7	796.1	781.6	776.4
47.5°	776.4	767.2	746.2	731.8	723.9
50°	725.2	718.7	700.3	682.0	675.4
52.5°	675.4	666.2	649.2	634.7	625.6
55°	624.3	616.4	600.6	584.9	578.3
57.5°	573.1	566.5	549.5	533.8	528.5
60°	522.0	516.7	498.4	483.9	480.0
62.5°	472.1	462.9	449.8	436.7	431.5
65°	421.0	413.1	400.0	388.2	381.6
67.5°	368.5	362.0	350.2	341.0	335.7
70°	320.0	314.7	302.9	293.8	288.5
72.5°	270.2	264.9	258.4	249.2	245.2
75°	220.3	217.7	211.1	203.3	205.9
77.5°	175.7	170.5	167.9	163.9	160.0
80°	131.1	129.8	127.2	123.3	120.7
82.5°	89.2	89.2	87.9	82.6	82.6
85°	53.8	52.5	51.1	47.2	45.9
87.5°	23.6	21.0	18.4	14.4	13.1
90°	0.6	7.6	19.3	18.5	18.8
92.5°	8.5	27.0	87.5	40.4	34.7
95°	19.9	48.9	222.8	84.2	64.8
97.5°	29.6	64.5	363.2	168.8	108.6
100°	43.8	79.0	449.0	336.2	203.5
102.5°	56.8	92.0	451.8	568.3	396.7
105°	69.3	104.6	421.1	752.8	640.5
107.5°	83.0	117.0	392.7	819.6	804.8
110°	96.6	129.8	373.4	808.7	871.8

TEST NUMBER: P1009554

CATALOG NUMBER: S122DIP-B865D530UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.1	142.1	360.9	772.0	870.7
115°	122.2	154.3	352.4	727.2	842.8
117.5°	135.8	166.6	347.8	684.2	800.8
120°	148.3	178.4	343.8	646.0	760.4
122.5°	160.3	190.6	341.6	616.0	718.4
125°	170.5	201.8	338.7	589.1	683.7
127.5°	179.0	212.2	337.0	566.1	651.3
130°	186.4	221.6	335.9	542.8	624.6
132.5°	193.2	230.8	335.3	518.6	596.7
135°	200.1	238.7	334.7	495.0	566.6
137.5°	206.3	245.5	334.7	471.2	537.6
140°	213.7	251.8	334.2	450.1	507.5
142.5°	221.1	256.9	334.2	430.0	477.4
145°	228.5	262.6	333.0	413.4	452.4
147.5°	236.4	267.1	331.3	399.0	430.2
150°	244.4	271.6	329.6	386.5	410.9
152.5°	252.3	276.2	326.8	376.0	394.4
155°	259.7	280.4	323.4	365.7	380.2
157.5°	266.0	283.9	320.0	356.0	367.7
160°	272.2	287.3	316.6	346.4	355.8
162.5°	278.5	289.8	313.7	337.3	344.4
165°	283.0	291.6	309.7	328.5	333.6
167.5°	287.0	293.2	306.3	320.5	323.4
170°	291.0	294.2	303.5	313.2	314.3
172.5°	293.3	295.0	300.1	306.6	306.9
175°	295.0	295.2	297.8	301.5	300.6
177.5°	296.1	295.5	295.5	297.8	296.1
180°	295.5	295.5	295.5	295.5	295.5

(END OF REPORT)