

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009562

Luminaire Tested: S122DIP-B865D530UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009562
REPORT IS A COMBINATION OF REPORTS P984896 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D530UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5178.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009562

CATALOG NUMBER: S122DIP-B865D530UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009562

CATALOG NUMBER: S122DIP-B865D530UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	39	36
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32
6	65	53	44	39	61	50	42	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	25	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20880	20880	20880
5°	20914	19903	19762
10°	20745	18996	18619
15°	20441	18082	17417
20°	20030	17088	16278
25°	19621	16049	15141
30°	19106	15074	13949
35°	18619	14045	12776
40°	18021	13030	11670
45°	17424	12022	10584
50°	16773	10997	9456
55°	16086	9900	8388
60°	15318	8714	7279
65°	14472	7509	6113
70°	13404	6188	4936
75°	11921	4770	3811
80°	10123	3241	2453
85°	7345	1509	1044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17424 cd/sqm

TEST NUMBER: P1009562

CATALOG NUMBER: S122DIP-B865D530UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	2.4
10°-20°	349.3	6.7
20°-30°	513.3	9.9
30°-40°	596.2	11.5
40°-50°	595.5	11.5
50°-60°	519.2	10.0
60°-70°	383.8	7.4
70°-80°	217.2	4.2
80°-90°	59.2	1.1
90°-100°	40.3	0.8
100°-110°	128.0	2.5
110°-120°	219.1	4.2
120°-130°	288.1	5.6
130°-140°	323.4	6.2
140°-150°	317.1	6.1
150°-160°	266.0	5.1
160°-170°	176.4	3.4
170°-180°	61.7	1.2
0°-30°	986.8	19.1
0°-40°	1583.0	30.6
0°-60°	2697.7	52.1
0°-90°	3357.8	64.8
90°-120°	387.4	7.5
90°-150°	1316.0	25.4
90°-180°	1820.0	35.1
0°-180°	5178.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1319	1314	1300	1310	1308	125
15°	1256	1248	1232	1237	1230	354
25°	1136	1126	1105	1107	1105	523
35°	980	968	948	940	934	612
45°	798	789	770	756	751	616
55°	604	596	581	566	559	540
65°	407	400	387	375	369	403
75°	213	210	204	197	199	227
85°	52	51	50	46	44	58
90°	0	7	19	18	19	5
95°	29	34	35	35	34	32
105°	118	120	121	122	122	125
115°	220	223	222	221	220	217
125°	320	325	323	321	321	286
135°	414	420	421	420	419	320
145°	502	506	509	510	508	314
155°	574	576	577	580	578	264
165°	625	624	624	628	625	176
175°	650	648	647	651	648	62
180°	651	651	651	651	651	

TEST NUMBER: P1009562

CATALOG NUMBER: S122DIP-B865D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.1	1319.1	1319.1	1319.1	1319.1
2.5°	1326.7	1320.4	1306.4	1319.1	1316.6
5°	1319.1	1314.0	1300.1	1310.2	1307.7
7.5°	1310.2	1302.6	1288.7	1298.8	1296.3
10°	1296.3	1287.4	1272.2	1282.3	1278.5
12.5°	1277.2	1269.6	1254.4	1260.8	1258.2
15°	1255.7	1248.1	1231.6	1236.7	1230.3
17.5°	1229.0	1221.4	1204.9	1211.3	1204.9
20°	1199.9	1192.3	1174.5	1178.3	1173.2
22.5°	1170.7	1159.3	1142.8	1142.8	1140.3
25°	1136.5	1126.3	1104.7	1107.3	1104.7
27.5°	1098.4	1089.5	1073.0	1069.2	1062.9
30°	1060.4	1050.2	1031.2	1027.4	1022.3
32.5°	1019.8	1012.2	991.9	984.3	979.2
35°	980.4	967.8	947.5	939.9	933.5
37.5°	936.1	924.6	904.3	895.5	889.1
40°	890.4	880.2	860.0	848.5	843.5
42.5°	846.0	835.9	815.6	802.9	795.3
45°	797.8	788.9	769.9	755.9	750.9
47.5°	750.9	742.0	721.7	707.7	700.1
50°	701.4	695.1	677.3	659.5	653.2
52.5°	653.2	644.3	627.8	613.9	605.0
55°	603.7	596.1	580.9	565.7	559.3
57.5°	554.3	547.9	531.4	516.2	511.2
60°	504.8	499.7	482.0	468.0	464.2
62.5°	456.6	447.7	435.0	422.4	417.3
65°	407.1	399.5	386.9	375.4	369.1
67.5°	356.4	350.1	338.7	329.8	324.7
70°	309.5	304.4	293.0	284.1	279.0
72.5°	261.3	256.2	249.9	241.0	237.2
75°	213.1	210.5	204.2	196.6	199.1
77.5°	170.0	164.9	162.4	158.5	154.7
80°	126.8	125.6	123.0	119.2	116.7
82.5°	86.2	86.2	85.0	79.9	79.9
85°	52.0	50.7	49.5	45.7	44.4
87.5°	22.8	20.3	17.8	14.0	12.7
90°	0.5	7.1	19.2	18.1	18.7
92.5°	12.1	16.5	17.0	17.6	17.6
95°	28.6	34.1	35.2	35.2	34.1
97.5°	47.8	52.7	54.9	54.9	54.9
100°	69.8	74.2	75.8	75.8	75.3
102.5°	92.8	96.1	98.3	98.9	98.3
105°	118.1	119.8	120.9	122.0	122.0
107.5°	143.4	145.6	145.6	146.1	143.4
110°	167.6	170.9	170.9	170.9	169.2

TEST NUMBER: P1009562

CATALOG NUMBER: S122DIP-B865D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	193.9	197.2	196.7	195.0	193.9
115°	219.8	223.1	222.0	221.4	219.8
117.5°	245.6	250.0	247.2	245.6	243.9
120°	271.4	275.8	271.4	271.4	269.8
122.5°	295.0	300.5	297.8	296.1	295.0
125°	319.7	324.7	323.0	321.4	320.8
127.5°	343.9	350.0	347.8	345.6	343.9
130°	366.4	373.6	372.5	371.4	369.2
132.5°	391.7	397.2	397.8	395.0	393.4
135°	413.7	419.7	420.8	420.3	418.6
137.5°	437.9	442.8	443.9	443.4	441.2
140°	459.3	464.2	467.0	467.0	464.8
142.5°	481.3	486.2	487.9	488.4	486.2
145°	502.1	506.0	509.3	509.8	507.6
147.5°	520.8	525.8	528.0	529.1	526.9
150°	540.1	543.3	545.5	547.2	545.5
152.5°	557.1	560.4	563.1	565.3	563.1
155°	574.1	575.8	577.4	580.2	578.5
157.5°	588.9	590.0	591.1	595.0	592.2
160°	602.1	603.2	603.8	607.1	604.9
162.5°	614.2	614.2	614.8	618.6	615.9
165°	624.7	624.1	624.1	628.0	625.2
167.5°	634.0	632.3	632.3	636.2	633.4
170°	641.1	639.5	638.9	642.8	639.5
172.5°	646.1	644.4	643.9	647.7	644.4
175°	649.9	648.3	647.2	651.0	647.7
177.5°	652.1	650.5	649.4	652.7	649.4
180°	651.0	651.0	651.0	651.0	651.0

(END OF REPORT)