

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009100

Luminaire Tested: S122DIP-B485D530UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009100
REPORT IS A COMBINATION OF REPORTS P984278 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D530UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3879.0 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009100

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009100

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	50	49	48
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	28	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12295	12295	12295
5°	12315	11719	11636
10°	12213	11184	10963
15°	12035	10647	10255
20°	11794	10061	9585
25°	11552	9451	8916
30°	11249	8876	8212
35°	10964	8270	7524
40°	10611	7671	6870
45°	10258	7078	6231
50°	9876	6475	5568
55°	9473	5829	4939
60°	9018	5131	4286
65°	8521	4421	3599
70°	7891	3643	2907
75°	7021	2808	2243
80°	5964	1908	1444
85°	4322	887	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10258 cd/sqm

TEST NUMBER: P1009100

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.1	1.9
10°-20°	205.7	5.3
20°-30°	302.3	7.8
30°-40°	351.0	9.0
40°-50°	350.6	9.0
50°-60°	305.7	7.9
60°-70°	226.0	5.8
70°-80°	127.9	3.3
80°-90°	35.7	0.9
90°-100°	42.1	1.1
100°-110°	133.7	3.4
110°-120°	228.8	5.9
120°-130°	300.9	7.8
130°-140°	337.8	8.7
140°-150°	331.2	8.5
150°-160°	277.9	7.2
160°-170°	184.3	4.8
170°-180°	64.4	1.7
0°-30°	581.0	15.0
0°-40°	932.1	24.0
0°-60°	1588.4	40.9
0°-90°	1977.9	51.0
90°-120°	404.6	10.4
90°-150°	1374.5	35.4
90°-180°	1901.0	49.0
0°-180°	3879.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	774	766	772	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	363
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	34
90°	1	8	20	19	20	4
95°	30	36	37	37	36	33
105°	123	125	126	127	127	130
115°	230	233	232	231	230	227
125°	334	339	337	336	335	298
135°	432	438	440	439	437	334
145°	524	528	532	532	530	328
155°	600	601	603	606	604	276
165°	652	652	652	656	653	184
175°	679	677	676	680	676	64
180°	680	680	680	680	680	

TEST NUMBER: P1009100

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	776.7	776.7	776.7	776.7	776.7
2.5°	781.2	777.4	769.2	776.7	775.2
5°	776.7	773.7	765.5	771.5	770.0
7.5°	771.5	767.0	758.8	764.7	763.2
10°	763.2	758.0	749.0	755.0	752.8
12.5°	752.0	747.6	738.6	742.3	740.8
15°	739.3	734.9	725.2	728.1	724.4
17.5°	723.7	719.2	709.5	713.2	709.5
20°	706.5	702.0	691.5	693.8	690.8
22.5°	689.3	682.6	672.9	672.9	671.4
25°	669.1	663.2	650.5	652.0	650.5
27.5°	646.7	641.5	631.8	629.6	625.8
30°	624.3	618.4	607.2	604.9	601.9
32.5°	600.4	596.0	584.0	579.5	576.5
35°	577.3	569.8	557.9	553.4	549.7
37.5°	551.1	544.4	532.5	527.2	523.5
40°	524.3	518.3	506.3	499.6	496.6
42.5°	498.1	492.1	480.2	472.7	468.2
45°	469.7	464.5	453.3	445.1	442.1
47.5°	442.1	436.9	424.9	416.7	412.2
50°	413.0	409.3	398.8	388.3	384.6
52.5°	384.6	379.4	369.7	361.5	356.2
55°	355.5	351.0	342.0	333.1	329.3
57.5°	326.4	322.6	312.9	304.0	301.0
60°	297.2	294.2	283.8	275.6	273.3
62.5°	268.9	263.6	256.2	248.7	245.7
65°	239.7	235.2	227.8	221.1	217.3
67.5°	209.9	206.1	199.4	194.2	191.2
70°	182.2	179.2	172.5	167.3	164.3
72.5°	153.8	150.9	147.1	141.9	139.7
75°	125.5	124.0	120.2	115.8	117.2
77.5°	100.1	97.1	95.6	93.4	91.1
80°	74.7	73.9	72.4	70.2	68.7
82.5°	50.8	50.8	50.0	47.0	47.0
85°	30.6	29.9	29.1	26.9	26.1
87.5°	13.4	11.9	10.5	8.2	7.5
90°	0.6	7.5	20.1	18.9	19.5
92.5°	12.6	17.2	17.8	18.4	18.4
95°	29.8	35.6	36.7	36.7	35.6
97.5°	49.9	55.1	57.4	57.4	57.4
100°	72.9	77.5	79.2	79.2	78.6
102.5°	97.0	100.4	102.7	103.3	102.7
105°	123.4	125.1	126.2	127.4	127.4
107.5°	149.8	152.1	152.1	152.6	149.8
110°	175.0	178.5	178.5	178.5	176.7

TEST NUMBER: P1009100

CATALOG NUMBER: S122DIP-B485D530UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	202.6	206.0	205.4	203.7	202.6
115°	229.5	233.0	231.8	231.2	229.5
117.5°	256.5	261.1	258.2	256.5	254.8
120°	283.5	288.1	283.5	283.5	281.7
122.5°	308.1	313.9	311.0	309.3	308.1
125°	334.0	339.1	337.4	335.7	335.1
127.5°	359.2	365.5	363.2	360.9	359.2
130°	382.7	390.2	389.0	387.9	385.6
132.5°	409.1	414.9	415.4	412.6	410.9
135°	432.1	438.4	439.5	439.0	437.2
137.5°	457.3	462.5	463.6	463.1	460.8
140°	479.7	484.9	487.7	487.7	485.4
142.5°	502.7	507.8	509.5	510.1	507.8
145°	524.5	528.5	531.9	532.5	530.2
147.5°	544.0	549.1	551.4	552.6	550.3
150°	564.1	567.5	569.8	571.5	569.8
152.5°	581.8	585.3	588.2	590.5	588.2
155°	599.6	601.4	603.1	605.9	604.2
157.5°	615.1	616.3	617.4	621.4	618.6
160°	628.9	630.0	630.6	634.1	631.8
162.5°	641.5	641.5	642.1	646.1	643.2
165°	652.4	651.9	651.9	655.9	653.0
167.5°	662.2	660.5	660.5	664.5	661.6
170°	669.6	667.9	667.3	671.4	667.9
172.5°	674.8	673.1	672.5	676.5	673.1
175°	678.8	677.1	676.0	680.0	676.5
177.5°	681.1	679.4	678.2	681.7	678.2
180°	680.0	680.0	680.0	680.0	680.0

(END OF REPORT)