

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009581

Luminaire Tested: S122DIP-B865D725UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009581
REPORT IS A COMBINATION OF REPORTS P984930 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D725UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6260.2 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009581

CATALOG NUMBER: S122DIP-B865D725UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009581

CATALOG NUMBER: S122DIP-B865D725UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	54	53	52
2	90	83	77	71	84	77	72	67	67	62	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	50	46	43	42	40	37
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	20	18
10	48	36	28	23	44	33	27	22	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1009581

CATALOG NUMBER: S122DIP-B865D725UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	2.1
10°-20°	363.3	5.8
20°-30°	533.8	8.5
30°-40°	620.0	9.9
40°-50°	619.2	9.9
50°-60°	540.0	8.6
60°-70°	399.1	6.4
70°-80°	225.8	3.6
80°-90°	62.1	1.0
90°-100°	160.9	2.6
100°-110°	544.0	8.7
110°-120°	571.8	9.1
120°-130°	470.2	7.5
130°-140°	377.9	6.0
140°-150°	285.5	4.6
150°-160°	200.7	3.2
160°-170°	118.2	1.9
170°-180°	38.4	0.6
0°-30°	1026.2	16.4
0°-40°	1646.2	26.3
0°-60°	2805.4	44.8
0°-90°	3492.5	55.8
90°-120°	1276.8	20.4
90°-150°	2410.4	38.5
90°-180°	2768.0	44.2
0°-180°	6260.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	1	10	26	25	25	5
95°	27	66	299	113	87	28
105°	93	140	566	1011	860	99
115°	164	207	473	977	1132	163
125°	229	271	455	791	918	204
135°	269	321	450	665	761	208
145°	307	353	447	555	608	193
155°	349	377	434	491	511	161
165°	380	392	416	441	448	107
175°	396	397	400	405	404	38
180°	397	397	397	397	397	

TEST NUMBER: P1009581

CATALOG NUMBER: S122DIP-B865D725UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	0.8	10.4	26.0	24.8	25.2
92.5°	11.5	36.3	117.6	54.2	46.6
95°	26.7	65.6	299.2	113.0	87.0
97.5°	39.7	86.6	487.8	226.7	145.8
100°	58.8	106.1	603.1	451.6	273.3
102.5°	76.3	123.7	606.9	763.4	532.8
105°	93.1	140.5	565.7	1011.1	860.3
107.5°	111.5	157.2	527.5	1100.8	1081.0
110°	129.8	174.4	501.5	1086.3	1171.0



TEST NUMBER: P1009581

CATALOG NUMBER: S122DIP-B865D725UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	146.6	190.9	484.8	1037.0	1169.5
115°	164.1	207.3	473.3	976.8	1132.1
117.5°	182.4	223.7	467.2	919.1	1075.6
120°	199.2	239.7	461.8	867.6	1021.4
122.5°	215.3	256.1	458.8	827.5	964.9
125°	229.0	271.0	455.0	791.2	918.4
127.5°	240.5	285.2	452.7	760.4	874.8
130°	250.4	297.7	451.2	729.0	839.0
132.5°	259.6	309.9	450.4	696.6	801.6
135°	268.7	320.6	449.6	664.9	761.1
137.5°	277.1	329.8	449.6	632.8	722.2
140°	287.0	338.2	448.9	604.6	681.7
142.5°	297.0	345.0	448.9	577.5	641.2
145°	306.9	352.7	447.3	555.3	607.7
147.5°	317.6	358.8	445.1	535.9	577.9
150°	328.3	364.9	442.8	519.1	551.9
152.5°	338.9	371.0	438.9	505.0	529.8
155°	348.9	376.8	434.4	491.2	510.7
157.5°	357.3	381.3	429.8	478.2	493.9
160°	365.7	385.9	425.2	465.3	477.9
162.5°	374.1	389.4	421.4	453.1	462.6
165°	380.2	391.6	416.0	441.2	448.1
167.5°	385.5	393.9	411.5	430.6	434.4
170°	390.9	395.0	407.6	420.6	422.2
172.5°	393.9	396.2	403.1	411.8	412.2
175°	396.2	396.6	400.0	405.0	403.8
177.5°	397.7	397.0	397.0	400.0	397.7
180°	397.0	397.0	397.0	397.0	397.0

(END OF REPORT)