

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009127

Luminaire Tested: S122DIP-B485D725UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009127
REPORT IS A COMBINATION OF REPORTS P984305 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D725UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4461.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009127

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009127

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30
4	73	63	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12139	12139	12139
5°	12159	11571	11488
10°	12060	11044	10825
15°	11883	10512	10125
20°	11644	9934	9464
25°	11407	9330	8802
30°	11106	8764	8109
35°	10825	8165	7428
40°	10476	7574	6783
45°	10129	6989	6152
50°	9752	6394	5497
55°	9353	5755	4877
60°	8906	5066	4232
65°	8415	4365	3554
70°	7791	3597	2869
75°	6931	2773	2216
80°	5884	1884	1425
85°	4266	878	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10129 cd/sqm

TEST NUMBER: P1009127

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	1.6
10°-20°	203.1	4.6
20°-30°	298.4	6.7
30°-40°	346.6	7.8
40°-50°	346.2	7.8
50°-60°	301.9	6.8
60°-70°	223.1	5.0
70°-80°	126.3	2.8
80°-90°	35.9	0.8
90°-100°	55.5	1.2
100°-110°	176.4	4.0
110°-120°	301.8	6.8
120°-130°	396.9	8.9
130°-140°	445.5	10.0
140°-150°	436.9	9.8
150°-160°	366.5	8.2
160°-170°	243.1	5.4
170°-180°	84.9	1.9
0°-30°	573.7	12.9
0°-40°	920.3	20.6
0°-60°	1568.3	35.2
0°-90°	1953.6	43.8
90°-120°	533.6	12.0
90°-150°	1813.0	40.6
90°-180°	2507.0	56.2
0°-180°	4461.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	764	756	762	760	73
15°	730	726	716	719	715	206
25°	661	655	642	644	642	304
35°	570	563	551	546	543	356
45°	464	459	448	440	436	358
55°	351	347	338	329	325	314
65°	237	232	225	218	215	234
75°	124	122	119	114	116	132
85°	30	30	29	26	26	34
90°	1	10	26	25	26	4
95°	39	47	48	48	47	44
105°	163	165	166	168	168	172
115°	303	307	306	305	303	300
125°	440	447	445	443	442	394
135°	570	578	580	579	577	440
145°	692	697	702	702	699	432
155°	791	793	795	799	797	364
165°	860	860	860	865	861	243
175°	895	893	892	897	892	85
180°	897	897	897	897	897	

TEST NUMBER: P1009127

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.9	766.9	766.9	766.9	766.9
2.5°	771.3	767.6	759.5	766.9	765.4
5°	766.9	763.9	755.8	761.7	760.2
7.5°	761.7	757.3	749.2	755.1	753.6
10°	753.6	748.4	739.6	745.5	743.3
12.5°	742.5	738.1	729.2	732.9	731.5
15°	730.0	725.6	716.0	718.9	715.2
17.5°	714.5	710.1	700.5	704.2	700.5
20°	697.5	693.1	682.8	685.0	682.1
22.5°	680.6	673.9	664.4	664.4	662.9
25°	660.7	654.8	642.2	643.7	642.2
27.5°	638.6	633.4	623.8	621.6	617.9
30°	616.4	610.5	599.5	597.3	594.3
32.5°	592.8	588.4	576.6	572.2	569.2
35°	570.0	562.6	550.8	546.4	542.7
37.5°	544.2	537.5	525.7	520.6	516.9
40°	517.6	511.7	499.9	493.3	490.3
42.5°	491.8	485.9	474.1	466.7	462.3
45°	463.8	458.6	447.6	439.5	436.5
47.5°	436.5	431.4	419.6	411.4	407.0
50°	407.8	404.1	393.8	383.4	379.7
52.5°	379.7	374.6	365.0	356.9	351.7
55°	351.0	346.6	337.7	328.9	325.2
57.5°	322.2	318.5	309.0	300.1	297.2
60°	293.5	290.5	280.2	272.1	269.9
62.5°	265.4	260.3	252.9	245.5	242.6
65°	236.7	232.3	224.9	218.3	214.6
67.5°	207.2	203.5	196.9	191.7	188.8
70°	179.9	177.0	170.3	165.2	162.2
72.5°	151.9	148.9	145.3	140.1	137.9
75°	123.9	122.4	118.7	114.3	115.8
77.5°	98.8	95.9	94.4	92.2	90.0
80°	73.7	73.0	71.5	69.3	67.8
82.5°	50.1	50.1	49.4	46.5	46.5
85°	30.2	29.5	28.8	26.5	25.8
87.5°	13.3	11.8	10.3	8.1	7.4
90°	0.8	9.8	26.5	25.0	25.7
92.5°	16.7	22.7	23.5	24.2	24.2
95°	39.4	46.9	48.4	48.4	46.9
97.5°	65.8	72.7	75.7	75.7	75.7
100°	96.1	102.2	104.4	104.4	103.7
102.5°	127.9	132.4	135.5	136.2	135.5
105°	162.7	165.0	166.5	168.0	168.0
107.5°	197.5	200.6	200.6	201.3	197.5
110°	230.8	235.4	235.4	235.4	233.1

TEST NUMBER: P1009127

CATALOG NUMBER: S122DIP-B485D725UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.2	271.7	270.9	268.7	267.2
115°	302.7	307.3	305.8	305.0	302.7
117.5°	338.3	344.4	340.6	338.3	336.0
120°	373.9	379.9	373.9	373.9	371.6
122.5°	406.4	414.0	410.2	407.9	406.4
125°	440.5	447.3	445.0	442.8	442.0
127.5°	473.8	482.1	479.1	476.1	473.8
130°	504.8	514.7	513.1	511.6	508.6
132.5°	539.6	547.2	548.0	544.2	541.9
135°	569.9	578.2	579.7	579.0	576.7
137.5°	603.2	610.0	611.5	610.8	607.7
140°	632.7	639.5	643.3	643.3	640.3
142.5°	663.0	669.8	672.1	672.8	669.8
145°	691.8	697.1	701.6	702.4	699.3
147.5°	717.5	724.3	727.3	728.8	725.8
150°	744.0	748.5	751.5	753.8	751.5
152.5°	767.4	772.0	775.8	778.8	775.8
155°	790.9	793.2	795.4	799.2	797.0
157.5°	811.3	812.8	814.4	819.7	815.9
160°	829.5	831.0	831.8	836.3	833.3
162.5°	846.2	846.2	846.9	852.2	848.4
165°	860.5	859.8	859.8	865.1	861.3
167.5°	873.4	871.1	871.1	876.4	872.6
170°	883.2	881.0	880.2	885.5	881.0
172.5°	890.0	887.8	887.0	892.3	887.8
175°	895.3	893.1	891.6	896.9	892.3
177.5°	898.4	896.1	894.6	899.1	894.6
180°	896.9	896.9	896.9	896.9	896.9

(END OF REPORT)