

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009626

Luminaire Tested: S122DIP-B865D925UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009626
REPORT IS A COMBINATION OF REPORTS P984990 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7075.2 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009626

CATALOG NUMBER: S122DIP-B865D925UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009626

CATALOG NUMBER: S122DIP-B865D925UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49		
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42		
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	40	35		
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	30		
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25		
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22		
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19		
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17		
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14		
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1009626

CATALOG NUMBER: S122DIP-B865D925UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	1.8
10°-20°	363.3	5.1
20°-30°	533.8	7.5
30°-40°	620.0	8.8
40°-50°	619.2	8.8
50°-60°	540.0	7.6
60°-70°	399.1	5.6
70°-80°	225.8	3.2
80°-90°	62.9	0.9
90°-100°	208.3	2.9
100°-110°	704.1	10.0
110°-120°	740.1	10.5
120°-130°	608.6	8.6
130°-140°	489.0	6.9
140°-150°	369.4	5.2
150°-160°	259.7	3.7
160°-170°	152.9	2.2
170°-180°	49.7	0.7
0°-30°	1026.2	14.5
0°-40°	1646.2	23.3
0°-60°	2805.4	39.7
0°-90°	3493.3	49.4
90°-120°	1652.4	23.4
90°-150°	3119.5	44.1
90°-180°	3582.0	50.6
0°-180°	7075.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	1	13	34	32	33	6
95°	35	85	387	146	113	36
105°	120	182	732	1309	1113	128
115°	212	268	612	1264	1465	211
125°	296	351	589	1024	1188	263
135°	348	415	582	861	985	269
145°	397	456	579	719	786	249
155°	452	488	562	636	661	208
165°	492	507	538	571	580	139
175°	513	513	518	524	523	49
180°	514	514	514	514	514	

TEST NUMBER: P1009626

CATALOG NUMBER: S122DIP-B865D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	1.0	13.4	33.6	32.1	32.6
92.5°	14.8	47.0	152.1	70.2	60.3
95°	34.6	84.9	387.3	146.2	112.6
97.5°	51.4	112.2	631.3	293.5	188.7
100°	76.1	137.4	780.5	584.4	353.7
102.5°	98.8	160.0	785.4	988.0	689.6
105°	120.5	181.8	732.1	1308.6	1113.4
107.5°	144.2	203.6	682.7	1424.6	1399.0
110°	168.0	225.8	649.1	1405.9	1515.5

TEST NUMBER: P1009626

CATALOG NUMBER: S122DIP-B865D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	189.7	247.0	627.4	1342.2	1513.6
115°	212.4	268.2	612.5	1264.1	1465.1
117.5°	236.1	289.5	604.6	1189.5	1392.0
120°	257.9	310.2	597.7	1122.8	1321.9
122.5°	278.6	331.5	593.8	1071.0	1248.8
125°	296.4	350.8	588.8	1024.0	1188.5
127.5°	311.2	369.0	585.9	984.0	1132.2
130°	324.1	385.3	583.9	943.5	1085.8
132.5°	335.9	401.1	582.9	901.5	1037.4
135°	347.8	415.0	581.9	860.6	985.0
137.5°	358.6	426.8	581.9	819.0	934.6
140°	371.5	437.6	580.9	782.4	882.2
142.5°	384.3	446.6	580.9	747.4	829.9
145°	397.2	456.4	578.9	718.8	786.4
147.5°	411.0	464.4	576.0	693.6	747.9
150°	424.8	472.2	573.0	671.8	714.3
152.5°	438.7	480.2	568.1	653.5	685.6
155°	451.5	487.6	562.2	635.8	660.9
157.5°	462.4	493.5	556.2	619.0	639.2
160°	473.2	499.4	550.3	602.2	618.5
162.5°	484.1	503.8	545.4	586.3	598.7
165°	492.0	506.8	538.4	571.0	579.9
167.5°	498.9	509.8	532.5	557.2	562.2
170°	505.8	511.3	527.6	544.4	546.3
172.5°	509.8	512.8	521.6	533.0	533.5
175°	512.8	513.2	517.7	524.1	522.6
177.5°	514.7	513.7	513.7	517.7	514.7
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)