

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009173

Luminaire Tested: S122DIP-B485D925UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009173
REPORT IS A COMBINATION OF REPORTS P984366 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B485D925UB27-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5506.1 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009173

CATALOG NUMBER: S122DIP-B485D925UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009173

CATALOG NUMBER: S122DIP-B485D925UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	90	86	83	85	82	79	76	66	64	62	51	50	48	38	37	36
2	86	79	73	68	78	71	66	62	58	54	51	45	43	40	33	32	30
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	28	26
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	21	19
6	61	49	41	35	55	44	38	32	36	31	27	29	25	22	21	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14
9	48	36	29	24	43	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12139	12139	12139
5°	12159	11571	11488
10°	12060	11044	10825
15°	11883	10512	10125
20°	11644	9934	9464
25°	11407	9330	8802
30°	11106	8764	8109
35°	10825	8165	7428
40°	10476	7574	6783
45°	10129	6989	6152
50°	9752	6394	5497
55°	9353	5755	4877
60°	8906	5066	4232
65°	8415	4365	3554
70°	7791	3597	2869
75°	6931	2773	2216
80°	5884	1884	1425
85°	4266	878	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10129 cd/sqm

TEST NUMBER: P1009173

CATALOG NUMBER: S122DIP-B485D925UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	1.3
10°-20°	203.1	3.7
20°-30°	298.4	5.4
30°-40°	346.6	6.3
40°-50°	346.2	6.3
50°-60°	301.9	5.5
60°-70°	223.1	4.1
70°-80°	126.3	2.3
80°-90°	36.6	0.7
90°-100°	206.5	3.8
100°-110°	698.2	12.7
110°-120°	733.9	13.3
120°-130°	603.5	11.0
130°-140°	484.9	8.8
140°-150°	366.3	6.7
150°-160°	257.5	4.7
160°-170°	151.6	2.8
170°-180°	49.3	0.9
0°-30°	573.7	10.4
0°-40°	920.3	16.7
0°-60°	1568.3	28.5
0°-90°	1954.3	35.5
90°-120°	1638.5	29.8
90°-150°	3093.3	56.2
90°-180°	3552.0	64.5
0°-180°	5506.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	764	756	762	760	73
15°	730	726	716	719	715	206
25°	661	655	642	644	642	304
35°	570	563	551	546	543	356
45°	464	459	448	440	436	358
55°	351	347	338	329	325	314
65°	237	232	225	218	215	234
75°	124	122	119	114	116	132
85°	30	30	29	26	26	34
90°	1	13	33	32	32	4
95°	34	84	384	145	112	35
105°	120	180	726	1298	1104	127
115°	211	266	607	1254	1453	209
125°	294	348	584	1015	1179	261
135°	345	412	577	853	977	266
145°	394	453	574	713	780	247
155°	448	483	557	630	655	206
165°	488	503	534	566	575	138
175°	508	509	513	520	518	48
180°	509	509	509	509	509	

TEST NUMBER: P1009173

CATALOG NUMBER: S122DIP-B485D925UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.9	766.9	766.9	766.9	766.9
2.5°	771.3	767.6	759.5	766.9	765.4
5°	766.9	763.9	755.8	761.7	760.2
7.5°	761.7	757.3	749.2	755.1	753.6
10°	753.6	748.4	739.6	745.5	743.3
12.5°	742.5	738.1	729.2	732.9	731.5
15°	730.0	725.6	716.0	718.9	715.2
17.5°	714.5	710.1	700.5	704.2	700.5
20°	697.5	693.1	682.8	685.0	682.1
22.5°	680.6	673.9	664.4	664.4	662.9
25°	660.7	654.8	642.2	643.7	642.2
27.5°	638.6	633.4	623.8	621.6	617.9
30°	616.4	610.5	599.5	597.3	594.3
32.5°	592.8	588.4	576.6	572.2	569.2
35°	570.0	562.6	550.8	546.4	542.7
37.5°	544.2	537.5	525.7	520.6	516.9
40°	517.6	511.7	499.9	493.3	490.3
42.5°	491.8	485.9	474.1	466.7	462.3
45°	463.8	458.6	447.6	439.5	436.5
47.5°	436.5	431.4	419.6	411.4	407.0
50°	407.8	404.1	393.8	383.4	379.7
52.5°	379.7	374.6	365.0	356.9	351.7
55°	351.0	346.6	337.7	328.9	325.2
57.5°	322.2	318.5	309.0	300.1	297.2
60°	293.5	290.5	280.2	272.1	269.9
62.5°	265.4	260.3	252.9	245.5	242.6
65°	236.7	232.3	224.9	218.3	214.6
67.5°	207.2	203.5	196.9	191.7	188.8
70°	179.9	177.0	170.3	165.2	162.2
72.5°	151.9	148.9	145.3	140.1	137.9
75°	123.9	122.4	118.7	114.3	115.8
77.5°	98.8	95.9	94.4	92.2	90.0
80°	73.7	73.0	71.5	69.3	67.8
82.5°	50.1	50.1	49.4	46.5	46.5
85°	30.2	29.5	28.8	26.5	25.8
87.5°	13.3	11.8	10.3	8.1	7.4
90°	1.0	13.2	33.3	31.8	32.3
92.5°	14.7	46.5	150.9	69.6	59.8
95°	34.3	84.2	384.0	145.0	111.7
97.5°	50.9	111.2	626.0	291.0	187.1
100°	75.4	136.2	774.0	579.5	350.7
102.5°	98.0	158.7	778.8	979.7	683.8
105°	119.5	180.2	725.9	1297.6	1104.1
107.5°	143.0	201.8	677.0	1412.7	1387.2
110°	166.5	223.9	643.7	1394.1	1502.8

TEST NUMBER: P1009173

CATALOG NUMBER: S122DIP-B485D925UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.1	244.9	622.1	1330.9	1500.9
115°	210.6	266.0	607.4	1253.6	1452.9
117.5°	234.1	287.0	599.6	1179.5	1380.4
120°	255.7	307.6	592.7	1113.4	1310.8
122.5°	276.3	328.7	588.8	1062.0	1238.3
125°	293.9	347.8	583.9	1015.4	1178.6
127.5°	308.6	365.9	581.0	975.8	1122.7
130°	321.3	382.1	579.0	935.6	1076.7
132.5°	333.1	397.8	578.0	894.0	1028.7
135°	344.8	411.5	577.0	853.3	976.7
137.5°	355.6	423.2	577.0	812.2	926.8
140°	368.4	434.0	576.1	776.0	874.9
142.5°	381.1	442.8	576.1	741.2	822.9
145°	393.8	452.6	574.1	712.7	779.8
147.5°	407.5	460.4	571.2	687.8	741.6
150°	421.3	468.3	568.2	666.2	708.3
152.5°	435.0	476.2	563.3	648.0	679.9
155°	447.7	483.4	557.4	630.4	655.4
157.5°	458.5	489.4	551.6	613.8	633.9
160°	469.3	495.2	545.7	597.1	613.3
162.5°	480.0	499.6	540.8	581.4	593.7
165°	487.9	502.6	533.9	566.2	575.1
167.5°	494.7	505.6	528.1	552.6	557.4
170°	501.6	507.0	523.2	539.8	541.8
172.5°	505.5	508.4	517.3	528.6	529.0
175°	508.5	509.0	513.4	519.7	518.3
177.5°	510.4	509.4	509.4	513.4	510.4
180°	509.4	509.4	509.4	509.4	509.4

(END OF REPORT)