

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009652

Luminaire Tested: S122DIP-B865D925UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009652
REPORT IS A COMBINATION OF REPORTS P985016 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6507.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009652

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009652

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58
1	98	94	90	86	91	87	84	80	74	71	69	62	60	59	51	50	49	49	49	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	45	43	41	41	41	36
3	82	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	35	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30	30	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	26	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23	23	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	21	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18	18	18	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	17	17	14
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20880	20880	20880
5°	20914	19903	19762
10°	20745	18996	18619
15°	20441	18082	17417
20°	20030	17088	16278
25°	19621	16049	15141
30°	19106	15074	13949
35°	18619	14045	12776
40°	18021	13030	11670
45°	17424	12022	10584
50°	16773	10997	9456
55°	16086	9900	8388
60°	15318	8714	7279
65°	14472	7509	6113
70°	13404	6188	4936
75°	11921	4770	3811
80°	10123	3241	2453
85°	7345	1509	1044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17424 cd/sqm

TEST NUMBER: P1009652

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	1.9
10°-20°	349.3	5.4
20°-30°	513.3	7.9
30°-40°	596.2	9.2
40°-50°	595.5	9.2
50°-60°	519.2	8.0
60°-70°	383.8	5.9
70°-80°	217.2	3.3
80°-90°	60.5	0.9
90°-100°	69.6	1.1
100°-110°	221.4	3.4
110°-120°	378.9	5.8
120°-130°	498.3	7.7
130°-140°	559.3	8.6
140°-150°	548.5	8.4
150°-160°	460.1	7.1
160°-170°	305.1	4.7
170°-180°	106.6	1.6
0°-30°	986.8	15.2
0°-40°	1583.0	24.3
0°-60°	2697.7	41.5
0°-90°	3359.2	51.6
90°-120°	669.9	10.3
90°-150°	2276.0	35.0
90°-180°	3148.0	48.4
0°-180°	6507.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1319	1314	1300	1310	1308	125
15°	1256	1248	1232	1237	1230	354
25°	1136	1126	1105	1107	1105	523
35°	980	968	948	940	934	612
45°	798	789	770	756	751	616
55°	604	596	581	566	559	540
65°	407	400	387	375	369	403
75°	213	210	204	197	199	227
85°	52	51	50	46	44	58
90°	1	12	33	31	32	6
95°	49	59	61	61	59	55
105°	204	207	209	211	211	216
115°	380	386	384	383	380	376
125°	553	562	559	556	555	494
135°	715	726	728	727	724	553
145°	868	875	881	882	878	543
155°	993	996	999	1003	1000	457
165°	1080	1079	1079	1086	1081	305
175°	1124	1121	1119	1126	1120	107
180°	1126	1126	1126	1126	1126	

TEST NUMBER: P1009652

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.1	1319.1	1319.1	1319.1	1319.1
2.5°	1326.7	1320.4	1306.4	1319.1	1316.6
5°	1319.1	1314.0	1300.1	1310.2	1307.7
7.5°	1310.2	1302.6	1288.7	1298.8	1296.3
10°	1296.3	1287.4	1272.2	1282.3	1278.5
12.5°	1277.2	1269.6	1254.4	1260.8	1258.2
15°	1255.7	1248.1	1231.6	1236.7	1230.3
17.5°	1229.0	1221.4	1204.9	1211.3	1204.9
20°	1199.9	1192.3	1174.5	1178.3	1173.2
22.5°	1170.7	1159.3	1142.8	1142.8	1140.3
25°	1136.5	1126.3	1104.7	1107.3	1104.7
27.5°	1098.4	1089.5	1073.0	1069.2	1062.9
30°	1060.4	1050.2	1031.2	1027.4	1022.3
32.5°	1019.8	1012.2	991.9	984.3	979.2
35°	980.4	967.8	947.5	939.9	933.5
37.5°	936.1	924.6	904.3	895.5	889.1
40°	890.4	880.2	860.0	848.5	843.5
42.5°	846.0	835.9	815.6	802.9	795.3
45°	797.8	788.9	769.9	755.9	750.9
47.5°	750.9	742.0	721.7	707.7	700.1
50°	701.4	695.1	677.3	659.5	653.2
52.5°	653.2	644.3	627.8	613.9	605.0
55°	603.7	596.1	580.9	565.7	559.3
57.5°	554.3	547.9	531.4	516.2	511.2
60°	504.8	499.7	482.0	468.0	464.2
62.5°	456.6	447.7	435.0	422.4	417.3
65°	407.1	399.5	386.9	375.4	369.1
67.5°	356.4	350.1	338.7	329.8	324.7
70°	309.5	304.4	293.0	284.1	279.0
72.5°	261.3	256.2	249.9	241.0	237.2
75°	213.1	210.5	204.2	196.6	199.1
77.5°	170.0	164.9	162.4	158.5	154.7
80°	126.8	125.6	123.0	119.2	116.7
82.5°	86.2	86.2	85.0	79.9	79.9
85°	52.0	50.7	49.5	45.7	44.4
87.5°	22.8	20.3	17.8	14.0	12.7
90°	1.0	12.4	33.3	31.4	32.3
92.5°	20.9	28.5	29.5	30.4	30.4
95°	49.4	58.9	60.8	60.8	58.9
97.5°	82.7	91.2	95.0	95.0	95.0
100°	120.7	128.3	131.1	131.1	130.2
102.5°	160.6	166.3	170.1	171.0	170.1
105°	204.3	207.1	209.0	210.9	210.9
107.5°	248.0	251.8	251.8	252.7	248.0
110°	289.8	295.5	295.5	295.5	292.6

TEST NUMBER: P1009652

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	335.4	341.1	340.1	337.3	335.4
115°	380.0	385.8	383.9	382.9	380.0
117.5°	424.7	432.3	427.6	424.7	421.9
120°	469.4	477.0	469.4	469.4	466.5
122.5°	510.2	519.7	515.0	512.1	510.2
125°	553.0	561.5	558.7	555.8	554.9
127.5°	594.8	605.2	601.4	597.6	594.8
130°	633.7	646.1	644.2	642.3	638.5
132.5°	677.4	686.9	687.9	683.1	680.3
135°	715.4	725.9	727.8	726.8	724.0
137.5°	757.2	765.8	767.7	766.8	762.9
140°	794.3	802.9	807.6	807.6	803.8
142.5°	832.3	840.9	843.7	844.7	840.9
145°	868.4	875.1	880.8	881.7	877.9
147.5°	900.7	909.3	913.1	915.0	911.2
150°	934.0	939.7	943.5	946.3	943.5
152.5°	963.4	969.1	973.9	977.7	973.9
155°	992.9	995.7	998.6	1003.3	1000.5
157.5°	1018.5	1020.4	1022.3	1029.0	1024.2
160°	1041.3	1043.2	1044.2	1049.9	1046.1
162.5°	1062.2	1062.2	1063.2	1069.8	1065.1
165°	1080.3	1079.3	1079.3	1086.0	1081.2
167.5°	1096.4	1093.6	1093.6	1100.2	1095.5
170°	1108.8	1105.9	1105.0	1111.6	1105.9
172.5°	1117.3	1114.5	1113.5	1120.2	1114.5
175°	1124.0	1121.1	1119.2	1125.9	1120.2
177.5°	1127.8	1124.9	1123.0	1128.7	1123.0
180°	1125.9	1125.9	1125.9	1125.9	1125.9

(END OF REPORT)