

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009664

Luminaire Tested: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009664
REPORT IS A COMBINATION OF REPORTS P987838 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7341.0 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009664

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009664

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48	48	48
1	98	94	90	87	90	86	83	80	73	70	68	60	58	57	48	47	46	41	41	41
2	89	82	76	71	82	76	71	67	64	60	57	53	51	48	43	41	40	35	35	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34	30	30	30
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26	26	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	32	29	26	23	23	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21	21	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17	17	17
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	23	20	17	15	15	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26869	26869	26869
5°	26912	25563	25373
10°	26648	24245	23445
15°	26282	22689	21246
20°	25798	20919	18947
25°	25301	19103	16843
30°	24634	17336	14546
35°	23981	15553	12573
40°	23317	13801	10541
45°	22545	11994	8768
50°	21747	10251	7139
55°	20917	8508	5668
60°	19952	6805	4287
65°	18841	5188	3486
70°	17496	3764	2772
75°	15814	2871	2117
80°	13365	1942	1421
85°	9337	890	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22545 cd/sqm

TEST NUMBER: P1009664

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.2
10°-20°	436.7	5.9
20°-30°	613.1	8.4
30°-40°	668.4	9.1
40°-50°	614.3	8.4
50°-60°	482.4	6.6
60°-70°	314.0	4.3
70°-80°	161.7	2.2
80°-90°	45.2	0.6
90°-100°	85.1	1.2
100°-110°	270.5	3.7
110°-120°	462.9	6.3
120°-130°	608.8	8.3
130°-140°	683.4	9.3
140°-150°	670.1	9.1
150°-160°	562.1	7.7
160°-170°	372.8	5.1
170°-180°	130.3	1.8
0°-30°	1209.0	16.5
0°-40°	1877.3	25.6
0°-60°	2974.0	40.5
0°-90°	3494.9	47.6
90°-120°	818.5	11.2
90°-150°	2780.8	37.9
90°-180°	3846.0	52.4
0°-180°	7341.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1697	1690	1670	1684	1679	161
15°	1614	1598	1545	1516	1501	455
25°	1466	1416	1315	1252	1229	674
35°	1263	1184	1049	952	919	790
45°	1032	929	768	659	622	797
55°	785	665	499	407	378	701
65°	530	406	267	215	210	525
75°	283	175	123	112	111	299
85°	66	34	29	29	29	76
90°	1	15	41	38	40	7
95°	60	72	74	74	72	67
105°	250	253	255	258	258	264
115°	464	471	469	468	464	459
125°	676	686	683	679	678	604
135°	874	887	889	888	885	675
145°	1061	1069	1076	1077	1073	663
155°	1213	1217	1220	1226	1222	558
165°	1320	1319	1319	1327	1321	372
175°	1373	1370	1368	1376	1369	130
180°	1376	1376	1376	1376	1376	

TEST NUMBER: P1009664

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.4	1697.4	1697.4	1697.4	1697.4
2.5°	1705.1	1697.4	1680.5	1695.9	1692.8
5°	1697.4	1689.8	1669.8	1683.6	1679.0
7.5°	1683.6	1674.4	1652.9	1659.0	1651.4
10°	1665.2	1654.4	1623.7	1619.1	1609.9
12.5°	1642.1	1628.3	1586.8	1577.6	1560.7
15°	1614.5	1597.6	1545.4	1516.2	1500.8
17.5°	1582.2	1557.6	1493.1	1459.3	1434.8
20°	1545.4	1514.6	1437.8	1399.4	1365.6
22.5°	1505.4	1470.1	1381.0	1328.8	1305.7
25°	1465.5	1416.3	1314.9	1252.0	1228.9
27.5°	1417.9	1365.6	1253.5	1181.3	1146.0
30°	1367.2	1308.8	1185.9	1107.6	1066.1
32.5°	1318.0	1247.3	1121.4	1029.2	990.8
35°	1262.7	1184.4	1049.2	952.4	918.6
37.5°	1208.9	1124.5	981.6	875.6	837.2
40°	1152.1	1059.9	910.9	801.9	761.9
42.5°	1093.7	995.4	840.3	726.6	688.2
45°	1032.3	929.4	768.1	659.0	622.1
47.5°	973.9	864.8	698.9	589.9	556.1
50°	909.4	800.3	631.4	525.4	493.1
52.5°	846.4	731.2	566.8	465.5	436.3
55°	785.0	665.2	499.2	407.1	377.9
57.5°	722.0	599.1	439.3	353.3	328.7
60°	657.5	534.6	376.4	298.0	273.4
62.5°	594.5	471.6	322.6	248.9	236.6
65°	530.0	405.5	267.3	215.1	210.5
67.5°	468.5	344.1	215.1	188.9	184.3
70°	404.0	284.2	178.2	162.8	156.7
72.5°	342.6	228.9	149.0	136.7	133.6
75°	282.7	175.1	122.9	112.1	110.6
77.5°	222.7	124.4	96.8	90.6	87.6
80°	167.4	89.1	73.7	67.6	67.6
82.5°	116.7	59.9	50.7	47.6	47.6
85°	66.1	33.8	29.2	29.2	29.2
87.5°	24.6	12.3	12.3	10.8	10.8
90°	1.2	15.1	40.6	38.3	39.5
92.5°	25.5	34.8	36.0	37.1	37.1
95°	60.4	72.0	74.3	74.3	72.0
97.5°	101.0	111.4	116.1	116.1	116.1
100°	147.4	156.7	160.2	160.2	159.0
102.5°	196.2	203.2	207.8	209.0	207.8
105°	249.6	253.1	255.4	257.7	257.7
107.5°	303.0	307.6	307.6	308.8	303.0
110°	354.1	361.0	361.0	361.0	357.6

TEST NUMBER: P1009664

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	409.8	416.8	415.6	412.1	409.8
115°	464.4	471.3	469.0	467.8	464.4
117.5°	518.9	528.2	522.4	518.9	515.4
120°	573.5	582.8	573.5	573.5	570.0
122.5°	623.4	635.0	629.2	625.7	623.4
125°	675.6	686.1	682.6	679.1	678.0
127.5°	726.7	739.5	734.8	730.2	726.7
130°	774.3	789.4	787.1	784.8	780.1
132.5°	827.7	839.3	840.5	834.7	831.2
135°	874.2	886.9	889.2	888.1	884.6
137.5°	925.2	935.7	938.0	936.8	932.2
140°	970.5	981.0	986.8	986.8	982.1
142.5°	1016.9	1027.4	1030.9	1032.0	1027.4
145°	1061.1	1069.2	1076.1	1077.3	1072.7
147.5°	1100.5	1111.0	1115.6	1117.9	1113.3
150°	1141.2	1148.1	1152.8	1156.3	1152.8
152.5°	1177.1	1184.1	1189.9	1194.6	1189.9
155°	1213.1	1216.6	1220.1	1225.9	1222.4
157.5°	1244.5	1246.8	1249.1	1257.2	1251.4
160°	1272.3	1274.7	1275.8	1282.8	1278.1
162.5°	1297.9	1297.9	1299.0	1307.2	1301.4
165°	1319.9	1318.8	1318.8	1326.9	1321.1
167.5°	1339.7	1336.2	1336.2	1344.3	1338.5
170°	1354.8	1351.3	1350.1	1358.2	1351.3
172.5°	1365.2	1361.7	1360.6	1368.7	1361.7
175°	1373.3	1369.9	1367.5	1375.7	1368.7
177.5°	1378.0	1374.5	1372.2	1379.1	1372.2
180°	1375.7	1375.7	1375.7	1375.7	1375.7

(END OF REPORT)