

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009665

Luminaire Tested: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009665
REPORT IS A COMBINATION OF REPORTS P987839 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7703.8 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009665

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009665

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45		
1	97	93	89	86	89	86	82	80	71	69	67	58	57	56	46	46	45	39		
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33		
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29		
4	75	64	57	51	68	59	53	48	50	45	41	41	38	35	33	31	29	25		
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	25	22		
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20		
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18		
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18	16		
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14		
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26869	26869	26869
5°	26912	25563	25373
10°	26648	24245	23445
15°	26282	22689	21246
20°	25798	20919	18947
25°	25301	19103	16843
30°	24634	17336	14546
35°	23981	15553	12573
40°	23317	13801	10541
45°	22545	11994	8768
50°	21747	10251	7139
55°	20917	8508	5668
60°	19952	6805	4287
65°	18841	5188	3486
70°	17496	3764	2772
75°	15814	2871	2117
80°	13365	1942	1421
85°	9337	890	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22545 cd/sqm

TEST NUMBER: P1009665

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	2.1
10°-20°	436.7	5.7
20°-30°	613.1	8.0
30°-40°	668.4	8.7
40°-50°	614.3	8.0
50°-60°	482.4	6.3
60°-70°	314.0	4.1
70°-80°	161.7	2.1
80°-90°	45.1	0.6
90°-100°	244.7	3.2
100°-110°	827.3	10.7
110°-120°	869.6	11.3
120°-130°	715.1	9.3
130°-140°	574.7	7.5
140°-150°	434.1	5.6
150°-160°	305.2	4.0
160°-170°	179.7	2.3
170°-180°	58.5	0.8
0°-30°	1209.0	15.7
0°-40°	1877.3	24.4
0°-60°	2974.0	38.6
0°-90°	3494.9	45.4
90°-120°	1941.7	25.2
90°-150°	3665.6	47.6
90°-180°	4209.0	54.6
0°-180°	7703.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1697	1690	1670	1684	1679	161
15°	1614	1598	1545	1516	1501	455
25°	1466	1416	1315	1252	1229	674
35°	1263	1184	1049	952	919	790
45°	1032	929	768	659	622	797
55°	785	665	499	407	378	701
65°	530	406	267	215	210	525
75°	283	175	123	112	111	299
85°	66	34	29	29	29	76
90°	1	16	40	38	38	6
95°	41	100	455	172	132	42
105°	142	214	860	1538	1308	150
115°	250	315	720	1485	1722	248
125°	348	412	692	1203	1397	310
135°	409	488	684	1011	1158	316
145°	467	536	680	845	924	293
155°	531	573	661	747	777	244
165°	578	596	633	671	682	163
175°	602	603	608	616	614	57
180°	604	604	604	604	604	

TEST NUMBER: P1009665

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.4	1697.4	1697.4	1697.4	1697.4
2.5°	1705.1	1697.4	1680.5	1695.9	1692.8
5°	1697.4	1689.8	1669.8	1683.6	1679.0
7.5°	1683.6	1674.4	1652.9	1659.0	1651.4
10°	1665.2	1654.4	1623.7	1619.1	1609.9
12.5°	1642.1	1628.3	1586.8	1577.6	1560.7
15°	1614.5	1597.6	1545.4	1516.2	1500.8
17.5°	1582.2	1557.6	1493.1	1459.3	1434.8
20°	1545.4	1514.6	1437.8	1399.4	1365.6
22.5°	1505.4	1470.1	1381.0	1328.8	1305.7
25°	1465.5	1416.3	1314.9	1252.0	1228.9
27.5°	1417.9	1365.6	1253.5	1181.3	1146.0
30°	1367.2	1308.8	1185.9	1107.6	1066.1
32.5°	1318.0	1247.3	1121.4	1029.2	990.8
35°	1262.7	1184.4	1049.2	952.4	918.6
37.5°	1208.9	1124.5	981.6	875.6	837.2
40°	1152.1	1059.9	910.9	801.9	761.9
42.5°	1093.7	995.4	840.3	726.6	688.2
45°	1032.3	929.4	768.1	659.0	622.1
47.5°	973.9	864.8	698.9	589.9	556.1
50°	909.4	800.3	631.4	525.4	493.1
52.5°	846.4	731.2	566.8	465.5	436.3
55°	785.0	665.2	499.2	407.1	377.9
57.5°	722.0	599.1	439.3	353.3	328.7
60°	657.5	534.6	376.4	298.0	273.4
62.5°	594.5	471.6	322.6	248.9	236.6
65°	530.0	405.5	267.3	215.1	210.5
67.5°	468.5	344.1	215.1	188.9	184.3
70°	404.0	284.2	178.2	162.8	156.7
72.5°	342.6	228.9	149.0	136.7	133.6
75°	282.7	175.1	122.9	112.1	110.6
77.5°	222.7	124.4	96.8	90.6	87.6
80°	167.4	89.1	73.7	67.6	67.6
82.5°	116.7	59.9	50.7	47.6	47.6
85°	66.1	33.8	29.2	29.2	29.2
87.5°	24.6	12.3	12.3	10.8	10.8
90°	1.2	15.6	39.5	37.8	38.3
92.5°	17.4	55.2	178.8	82.4	70.8
95°	40.6	99.8	455.1	171.8	132.3
97.5°	60.4	131.8	741.8	344.8	221.7
100°	89.4	161.4	917.1	686.7	415.6
102.5°	116.1	188.0	923.0	1161.0	810.3
105°	141.6	213.6	860.3	1537.6	1308.4
107.5°	169.5	239.2	802.2	1674.1	1643.9
110°	197.4	265.2	762.7	1652.0	1780.9

TEST NUMBER: P1009665

CATALOG NUMBER: S122RDIP-B1005D1080UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.9	290.2	737.2	1577.1	1778.6
115°	249.6	315.2	719.8	1485.4	1721.7
117.5°	277.5	340.2	710.5	1397.8	1635.8
120°	303.0	364.6	702.4	1319.4	1553.3
122.5°	327.4	389.5	697.7	1258.4	1467.4
125°	348.3	412.2	691.9	1203.4	1396.6
127.5°	365.7	433.6	688.4	1156.3	1330.4
130°	380.8	452.8	686.1	1108.7	1275.9
132.5°	394.7	471.4	685.0	1059.4	1219.0
135°	408.7	487.6	683.8	1011.2	1157.5
137.5°	421.4	501.5	683.8	962.4	1098.3
140°	436.5	514.3	682.6	919.4	1036.7
142.5°	451.6	524.8	682.6	878.2	975.2
145°	466.7	536.4	680.3	844.6	924.1
147.5°	483.0	545.6	676.8	815.0	878.8
150°	499.2	555.0	673.3	789.4	839.4
152.5°	515.5	564.2	667.5	768.0	805.7
155°	530.6	572.9	660.6	747.1	776.7
157.5°	543.3	579.8	653.6	727.4	751.1
160°	556.1	586.8	646.6	707.6	726.8
162.5°	568.9	592.0	640.8	689.0	703.5
165°	578.2	595.6	632.7	671.0	681.5
167.5°	586.3	599.0	625.7	654.8	660.6
170°	594.4	600.8	619.9	639.6	642.0
172.5°	599.0	602.6	613.0	626.3	626.9
175°	602.5	603.1	608.3	615.9	614.1
177.5°	604.9	603.7	603.7	608.3	604.9
180°	603.7	603.7	603.7	603.7	603.7

(END OF REPORT)