

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009677

Luminaire Tested: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009677
REPORT IS A COMBINATION OF REPORTS P987853 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7375.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	99	94	91	88	91	87	84	82	74	72	70	62	60	59	51	50	49	49	49	44
2	90	83	78	73	83	77	72	68	66	62	59	55	53	51	46	44	42	42	42	38
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37	37	37	33
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	33	33	33	29
5	70	59	52	46	65	55	49	44	48	43	39	41	37	34	34	31	29	29	29	26
6	65	54	46	41	60	50	43	38	44	38	34	37	33	30	31	28	26	26	26	23
7	61	49	41	36	56	46	39	34	40	34	31	34	30	27	29	26	24	24	24	21
8	56	45	37	32	52	42	35	31	37	31	28	32	27	24	27	24	21	21	21	19
9	53	41	34	29	49	38	32	28	34	29	25	29	25	22	25	22	20	20	20	18
10	49	38	31	26	46	36	29	25	31	26	23	27	23	20	23	20	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33644	33644	33644	33644
5°	33722	35735	33839	28548
10°	33352	37771	33587	23575
15°	32627	37783	33181	17710
20°	31757	31232	32448	14611
25°	30701	19515	31364	12430
30°	29353	12494	30153	10701
35°	27714	9603	28613	9158
40°	25888	8071	26993	8010
45°	23934	6870	24935	6725
50°	21933	5837	22959	5815
55°	19718	5072	20781	5006
60°	17749	3869	18689	3822
65°	15908	2912	16854	3303
70°	13880	2326	14967	2691
75°	11731	1782	12805	2035
80°	9317	1211	10020	1335
85°	6470	626	7091	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 30776 cd/sqm

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.6	2.7
10°-20°	562.7	7.6
20°-30°	724.2	9.8
30°-40°	687.1	9.3
40°-50°	588.8	8.0
50°-60°	448.4	6.1
60°-70°	282.8	3.8
70°-80°	141.1	1.9
80°-90°	40.0	0.5
90°-100°	81.8	1.1
100°-110°	260.1	3.5
110°-120°	445.1	6.0
120°-130°	585.4	7.9
130°-140°	657.1	8.9
140°-150°	644.4	8.7
150°-160°	540.5	7.3
160°-170°	358.5	4.9
170°-180°	125.3	1.7
0°-30°	1488.5	20.2
0°-40°	2175.6	29.5
0°-60°	3212.9	43.6
0°-90°	3676.8	49.9
90°-120°	787.1	10.7
90°-150°	2673.9	36.3
90°-180°	3698.0	50.1
0°-180°	7375.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2125	2125	2125	2125	2125	
5°	2127	2365	2134	1889	2127	202
15°	2004	2669	2038	1251	2004	564
25°	1778	1424	1817	907	1778	817
35°	1459	702	1507	669	1459	913
45°	1096	487	1142	477	1096	846
55°	740	338	780	334	740	667
65°	448	176	474	199	448	444
75°	210	93	229	106	210	227
85°	46	27	50	28	46	52
90°	1	38	1	38	1	7
95°	58	69	58	69	58	65
105°	240	248	240	248	240	253
115°	446	446	446	446	446	442
125°	650	652	650	652	650	581
135°	840	851	840	851	840	650
145°	1020	1031	1020	1031	1020	637
155°	1166	1175	1166	1175	1166	537
165°	1269	1270	1269	1270	1269	358
175°	1320	1316	1320	1316	1320	125
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2138.7	2147.6	2152.0	2157.9	2171.2	2180.1	2193.4	2196.3	2194.8	2200.8	2184.5
5°	2126.9	2146.1	2163.8	2178.6	2202.2	2217.0	2233.2	2252.4	2256.9	2279.0	2265.7
7.5°	2110.7	2138.7	2163.8	2193.4	2228.8	2248.0	2273.1	2302.7	2316.0	2342.5	2349.9
10°	2084.1	2123.9	2166.8	2197.8	2246.5	2280.5	2304.1	2351.4	2382.4	2422.3	2416.4
12.5°	2041.2	2092.9	2150.5	2202.2	2265.7	2287.9	2332.2	2380.9	2420.8	2457.8	2490.2
15°	2004.3	2063.4	2126.9	2190.4	2262.8	2304.1	2348.5	2412.0	2454.8	2519.8	2547.9
17.5°	1954.1	2029.4	2104.7	2175.6	2261.3	2308.6	2363.2	2425.3	2488.8	2550.8	2573.0
20°	1902.4	1983.6	2064.9	2160.9	2258.4	2304.1	2360.3	2437.1	2499.1	2547.9	2547.9
22.5°	1840.4	1939.3	2032.4	2123.9	2230.3	2296.8	2354.4	2444.5	2488.8	2499.1	2459.2
25°	1778.3	1877.3	1979.2	2092.9	2214.0	2273.1	2338.1	2422.3	2437.1	2395.7	2292.3
27.5°	1704.5	1815.3	1930.5	2053.1	2180.1	2253.9	2313.0	2369.1	2341.1	2230.3	2069.3
30°	1629.1	1748.8	1878.8	1995.4	2149.1	2217.0	2267.2	2283.5	2194.8	2014.6	1806.4
32.5°	1550.9	1667.6	1804.9	1945.2	2100.3	2165.3	2197.8	2155.0	1992.5	1765.0	1511.0
35°	1459.3	1590.7	1734.0	1880.2	2033.9	2082.6	2101.8	1996.9	1788.7	1494.7	1242.2
37.5°	1376.6	1508.0	1661.6	1810.8	1960.0	1986.6	1967.4	1803.4	1539.1	1248.1	1001.4
40°	1279.1	1419.4	1570.1	1737.0	1859.6	1866.9	1819.7	1607.0	1279.1	1005.8	853.7
42.5°	1189.0	1330.8	1481.4	1651.3	1744.4	1719.2	1655.7	1376.6	1067.9	867.0	744.4
45°	1095.9	1230.4	1392.8	1543.5	1609.9	1550.9	1454.9	1158.0	896.5	745.9	651.4
47.5°	1005.8	1131.4	1292.4	1437.1	1449.0	1382.5	1268.8	970.4	776.9	655.8	579.0
50°	917.2	1042.8	1193.4	1313.1	1301.3	1209.7	1081.2	843.4	675.0	579.0	515.5
52.5°	828.6	942.3	1088.6	1183.1	1132.9	1044.3	917.2	714.9	589.3	505.1	456.4
55°	740.0	846.3	971.9	1050.2	970.4	868.5	778.4	613.0	511.0	443.1	406.2
57.5°	666.1	750.3	865.5	912.8	816.8	737.0	658.7	527.3	443.1	394.4	351.5
60°	584.9	661.7	756.2	784.3	685.3	620.3	553.9	446.1	379.6	336.8	308.7
62.5°	515.5	579.0	651.4	651.4	564.2	515.5	465.3	373.7	319.0	285.1	271.8
65°	447.5	493.3	545.0	539.1	465.3	422.4	382.5	308.7	267.3	243.7	230.4
67.5°	381.1	416.5	450.5	429.8	376.6	339.7	302.8	249.6	221.6	205.3	187.6
70°	320.5	348.6	366.3	347.1	293.9	262.9	236.3	200.9	178.7	158.0	147.7
72.5°	268.8	280.6	286.5	262.9	218.6	200.9	181.7	156.6	137.4	127.0	124.1
75°	209.7	220.1	215.6	197.9	161.0	147.7	132.9	115.2	110.8	104.9	101.9
77.5°	163.9	163.9	156.6	140.3	115.2	104.9	99.0	90.1	85.7	84.2	81.2
80°	116.7	115.2	110.8	93.1	78.3	72.4	72.4	66.5	65.0	62.0	62.0
82.5°	76.8	76.8	70.9	56.1	51.7	50.2	48.7	45.8	45.8	44.3	44.3
85°	45.8	42.8	35.4	31.0	29.5	29.5	28.1	26.6	28.1	26.6	26.6
87.5°	20.7	16.2	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8
90°	1.1	4.1	7.1	10.0	13.0	14.5	17.2	22.7	28.2	33.6	39.1
92.5°	24.6	26.6	28.6	30.5	32.5	33.5	33.6	33.9	34.1	34.4	34.6
95°	58.0	60.5	63.0	65.5	68.0	69.2	69.4	69.9	70.4	70.9	71.4
97.5°	97.1	99.3	101.6	103.8	106.1	107.2	107.7	108.7	109.6	110.6	111.6
100°	141.8	143.8	145.8	147.7	149.7	150.7	151.1	151.8	152.5	153.3	154.0
102.5°	188.6	190.1	191.6	193.1	194.6	195.3	195.8	196.8	197.8	198.8	199.8
105°	240.0	240.7	241.5	242.2	242.9	243.3	243.6	244.1	244.6	245.1	245.6
107.5°	291.3	292.3	293.3	294.3	295.3	295.8	295.8	295.8	295.8	295.8	295.8
110°	340.5	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	394.0	395.5	397.0	398.5	400.0	400.7	400.6	400.3	400.1	399.8	399.6
115°	446.5	448.0	449.5	451.0	452.5	453.2	453.0	452.5	452.0	451.5	451.0
117.5°	499.0	501.0	503.0	504.9	506.9	507.9	507.3	506.0	504.8	503.5	502.3
120°	551.4	553.4	555.4	557.4	559.4	560.4	559.4	557.4	555.4	553.4	551.4
122.5°	599.4	601.9	604.4	606.9	609.4	610.6	610.0	608.7	607.5	606.2	605.0
125°	649.7	651.9	654.1	656.4	658.6	659.7	659.3	658.6	657.9	657.1	656.4
127.5°	698.8	701.5	704.3	707.0	709.7	711.1	710.6	709.6	708.6	707.6	706.6
130°	744.6	747.8	751.0	754.3	757.5	759.1	758.8	758.3	757.8	757.3	756.8
132.5°	795.9	798.4	800.9	803.4	805.9	807.1	807.2	807.5	807.7	808.0	808.2
135°	840.5	843.2	846.0	848.7	851.4	852.8	853.1	853.6	854.1	854.6	855.1
137.5°	889.7	891.9	894.1	896.4	898.6	899.7	899.9	900.4	900.9	901.4	901.9
140°	933.2	935.4	937.6	939.9	942.1	943.2	943.8	945.1	946.3	947.6	948.8
142.5°	977.9	980.1	982.3	984.6	986.8	987.9	988.3	989.0	989.7	990.5	991.2
145°	1020.3	1022.0	1023.8	1025.5	1027.2	1028.1	1028.8	1030.3	1031.8	1033.3	1034.8
147.5°	1058.2	1060.4	1062.7	1064.9	1067.2	1068.3	1068.8	1069.8	1070.7	1071.7	1072.7
150°	1097.3	1098.8	1100.3	1101.8	1103.3	1104.0	1104.5	1105.5	1106.5	1107.5	1108.5
152.5°	1131.9	1133.4	1134.9	1136.4	1137.9	1138.6	1139.2	1140.5	1141.7	1143.0	1144.2
155°	1166.5	1167.2	1168.0	1168.7	1169.4	1169.8	1170.2	1170.9	1171.7	1172.4	1173.2
157.5°	1196.6	1197.1	1197.6	1198.1	1198.6	1198.9	1199.1	1199.6	1200.1	1200.6	1201.1
160°	1223.4	1223.9	1224.4	1224.9	1225.4	1225.7	1225.8	1226.1	1226.3	1226.6	1226.8
162.5°	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.1	1248.4	1248.6	1248.9	1249.1
165°	1269.2	1269.0	1268.7	1268.5	1268.2	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1
167.5°	1288.2	1287.4	1286.7	1285.9	1285.2	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8
170°	1302.7	1301.9	1301.2	1300.4	1299.7	1299.3	1299.2	1298.9	1298.7	1298.4	1298.2
172.5°	1312.7	1312.0	1311.2	1310.5	1309.8	1309.4	1309.3	1309.0	1308.8	1308.5	1308.3
175°	1320.5	1319.8	1319.0	1318.3	1317.6	1317.2	1317.0	1316.5	1316.0	1315.5	1315.0
177.5°	1325.0	1324.3	1323.5	1322.8	1322.1	1321.7	1321.4	1320.9	1320.4	1319.9	1319.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2200.8	2203.7	2208.1	2228.8	2231.8	2237.7	2234.7	2234.7	2236.2	2233.2	2234.7
5°	2295.3	2299.7	2321.9	2347.0	2352.9	2347.0	2354.4	2364.7	2364.7	2364.7	2361.7
7.5°	2383.9	2400.2	2425.3	2462.2	2469.6	2477.0	2490.2	2481.4	2484.3	2497.6	2493.2
10°	2469.6	2493.2	2521.3	2552.3	2568.5	2578.9	2584.8	2598.1	2629.1	2593.6	2606.9
12.5°	2550.8	2584.8	2614.3	2648.3	2660.1	2673.4	2677.8	2689.6	2689.6	2688.2	2698.5
15°	2604.0	2635.0	2661.6	2683.7	2686.7	2683.7	2680.8	2682.3	2686.7	2669.0	2679.3
17.5°	2615.8	2618.7	2627.6	2618.7	2620.2	2589.2	2571.5	2567.1	2525.7	2527.2	2561.1
20°	2558.2	2508.0	2494.7	2445.9	2416.4	2336.6	2333.7	2311.5	2224.4	2251.0	2245.1
22.5°	2400.2	2314.5	2200.8	2144.6	2116.6	2032.4	1967.4	1921.6	1890.6	1859.6	1846.3
25°	2191.9	2053.1	1892.1	1781.3	1765.0	1686.8	1567.1	1511.0	1444.5	1423.8	1459.3
27.5°	1923.1	1742.9	1561.2	1391.3	1360.3	1289.4	1228.9	1189.0	1112.2	1107.8	1110.7
30°	1558.3	1376.6	1224.4	1113.7	1036.9	1004.4	964.5	935.0	903.9	915.7	918.7
32.5°	1280.6	1107.8	966.0	906.9	871.4	850.8	816.8	797.6	784.3	779.9	778.4
35°	1017.7	902.5	838.9	781.3	760.7	745.9	720.8	711.9	700.1	701.6	701.6
37.5°	871.4	775.4	728.2	698.6	679.4	672.0	655.8	646.9	639.5	636.6	641.0
40°	751.8	685.3	655.8	629.2	613.0	610.0	601.1	590.8	581.9	583.4	587.9
42.5°	664.7	626.3	590.8	570.1	558.3	553.9	546.5	539.1	539.1	534.7	533.2
45°	595.2	564.2	534.7	515.5	508.1	502.2	493.3	491.8	485.9	487.4	488.9
47.5°	533.2	508.1	485.9	466.7	459.4	457.9	449.0	443.1	443.1	441.6	440.2
50°	477.1	452.0	432.8	422.4	412.1	409.1	407.7	406.2	403.2	403.2	404.7
52.5°	431.3	406.2	391.4	382.5	376.6	373.7	373.7	372.2	372.2	372.2	370.7
55°	381.1	360.4	348.6	345.6	342.7	341.2	339.7	336.8	335.3	338.2	335.3
57.5°	333.8	326.4	316.1	313.1	305.7	305.7	301.3	298.4	295.4	298.4	298.4
60°	296.9	286.5	280.6	271.8	265.9	260.0	252.6	251.1	248.1	246.7	245.2
62.5°	258.5	249.6	234.8	221.6	212.7	206.8	203.8	202.4	202.4	200.9	200.9
65°	215.6	195.0	187.6	183.1	181.7	180.2	177.2	175.8	177.2	175.8	177.2
67.5°	168.4	165.4	161.0	158.0	156.6	155.1	155.1	153.6	153.6	153.6	153.6
70°	146.2	138.8	137.4	134.4	134.4	132.9	132.9	132.9	132.9	131.5	134.4
72.5°	121.1	116.7	115.2	113.7	113.7	113.7	112.3	112.3	112.3	110.8	112.3
75°	99.0	97.5	94.5	94.5	93.1	94.5	93.1	93.1	91.6	93.1	93.1
77.5°	79.8	78.3	76.8	76.8	75.3	75.3	75.3	75.3	75.3	75.3	76.8
80°	60.6	59.1	57.6	59.1	57.6	59.1	57.6	57.6	59.1	57.6	57.6
82.5°	44.3	42.8	42.8	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4
85°	26.6	25.1	25.1	26.6	25.1	26.6	25.1	25.1	25.1	26.6	26.6
87.5°	11.8	13.3	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.3
90°	38.6	38.1	37.6	37.1	36.8	36.9	37.2	37.5	37.7	38.0	37.7
92.5°	34.8	35.1	35.3	35.6	35.7	35.7	35.7	35.7	35.7	35.7	35.7
95°	71.4	71.4	71.4	71.4	71.4	71.2	70.7	70.2	69.7	69.2	69.7
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
100°	154.0	154.0	154.0	154.0	154.0	153.9	153.6	153.4	153.1	152.9	153.1
102.5°	200.0	200.3	200.5	200.8	200.9	200.8	200.5	200.3	200.0	199.8	200.0
105°	246.1	246.6	247.1	247.6	247.8	247.8	247.8	247.8	247.8	247.8	247.8
107.5°	296.0	296.3	296.5	296.8	296.9	296.3	295.0	293.8	292.5	291.3	292.5
110°	347.2	347.2	347.2	347.2	347.2	346.8	346.1	345.3	344.6	343.8	344.6

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	398.9	398.1	397.4	396.7	396.3	396.0	395.5	395.0	394.5	394.0	394.5
115°	450.8	450.5	450.3	450.0	449.9	449.5	448.8	448.0	447.3	446.5	447.3
117.5°	501.6	500.8	500.1	499.4	499.0	498.6	497.9	497.1	496.4	495.6	496.4
120°	551.4	551.4	551.4	551.4	551.4	551.0	550.3	549.6	548.8	548.1	548.8
122.5°	604.3	603.5	602.8	602.1	601.7	601.4	600.9	600.4	599.9	599.4	599.9
125°	655.6	654.9	654.1	653.4	653.0	652.9	652.6	652.4	652.1	651.9	652.1
127.5°	705.6	704.6	703.6	702.6	702.1	701.7	701.0	700.3	699.5	698.8	699.5
130°	756.3	755.8	755.3	754.8	754.6	754.1	753.1	752.1	751.1	750.1	751.1
132.5°	807.0	805.7	804.5	803.2	802.6	802.2	801.5	800.7	800.0	799.2	800.0
135°	854.8	854.6	854.3	854.0	853.9	853.5	852.8	852.1	851.3	850.6	851.3
137.5°	901.7	901.4	901.2	900.9	900.8	900.3	899.3	898.4	897.4	896.4	897.4
140°	948.8	948.8	948.8	948.8	948.8	948.3	947.3	946.4	945.4	944.4	945.4
142.5°	991.5	991.7	992.0	992.3	992.4	991.9	990.9	989.9	988.9	987.9	988.9
145°	1035.0	1035.3	1035.5	1035.8	1035.9	1035.4	1034.4	1033.4	1032.4	1031.4	1032.4
147.5°	1073.2	1073.7	1074.2	1074.7	1075.0	1074.5	1073.5	1072.5	1071.5	1070.5	1071.5
150°	1109.2	1110.0	1110.7	1111.4	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1109.2
152.5°	1145.2	1146.2	1147.1	1148.1	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1145.2
155°	1174.4	1175.7	1176.9	1178.2	1178.8	1178.4	1177.7	1176.9	1176.2	1175.4	1176.2
157.5°	1202.8	1204.6	1206.3	1208.0	1208.9	1208.3	1207.0	1205.8	1204.5	1203.3	1204.5
160°	1228.3	1229.8	1231.3	1232.8	1233.5	1233.0	1232.0	1231.0	1230.0	1229.0	1230.0
162.5°	1250.8	1252.6	1254.3	1256.0	1256.9	1256.3	1255.0	1253.8	1252.5	1251.3	1252.5
165°	1269.8	1271.6	1273.3	1275.0	1275.9	1275.3	1274.0	1272.8	1271.5	1270.3	1271.5
167.5°	1286.5	1288.3	1290.0	1291.7	1292.6	1292.0	1290.8	1289.5	1288.3	1287.1	1288.3
170°	1299.9	1301.7	1303.4	1305.1	1306.0	1305.3	1303.8	1302.3	1300.8	1299.3	1300.8
172.5°	1310.0	1311.8	1313.5	1315.2	1316.1	1315.4	1313.9	1312.4	1310.9	1309.4	1310.9
175°	1316.7	1318.5	1320.2	1321.9	1322.8	1322.1	1320.6	1319.1	1317.6	1316.1	1317.6
177.5°	1320.9	1322.4	1323.9	1325.4	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1320.9
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2240.6	2230.3	2227.3	2230.3	2227.3	2228.8	2218.5	2180.1	2190.4	2174.2	2183.0
5°	2367.7	2358.8	2339.6	2336.6	2333.7	2330.7	2316.0	2282.0	2268.7	2246.5	2245.1
7.5°	2488.8	2488.8	2474.0	2463.7	2450.4	2440.0	2420.8	2370.6	2349.9	2323.3	2308.6
10°	2608.4	2570.0	2586.3	2575.9	2543.4	2537.5	2502.1	2472.5	2432.6	2406.1	2382.4
12.5°	2694.1	2682.3	2667.5	2658.6	2649.8	2630.6	2606.9	2531.6	2510.9	2457.8	2431.2
15°	2691.1	2683.7	2688.2	2688.2	2685.2	2680.8	2661.6	2606.9	2571.5	2519.8	2474.0
17.5°	2546.4	2565.6	2584.8	2598.1	2627.6	2640.9	2658.6	2626.1	2604.0	2559.7	2510.9
20°	2293.8	2341.1	2397.2	2409.0	2435.6	2513.9	2549.3	2577.4	2586.3	2571.5	2531.6
22.5°	1942.3	1982.2	2118.0	2115.1	2153.5	2246.5	2349.9	2434.1	2500.6	2537.5	2522.7
25°	1521.3	1577.5	1649.8	1704.5	1830.0	1968.9	2097.4	2231.8	2347.0	2448.9	2474.0
27.5°	1150.6	1224.4	1282.0	1354.4	1417.9	1581.9	1747.3	1957.0	2091.5	2284.9	2385.4
30°	930.5	964.5	1022.1	1056.1	1087.1	1212.6	1400.2	1607.0	1843.3	2066.3	2239.2
32.5°	794.6	818.3	861.1	875.9	908.4	992.6	1110.7	1299.8	1543.5	1813.8	2041.2
35°	713.4	738.5	747.4	760.7	787.2	840.4	921.7	1059.0	1279.1	1543.5	1815.3
37.5°	644.0	657.3	682.4	691.2	700.1	740.0	794.6	890.6	1036.9	1254.0	1555.3
40°	595.2	602.6	615.9	623.3	629.2	657.3	706.0	771.0	878.8	1044.3	1321.9
42.5°	543.5	552.4	561.3	570.1	577.5	599.7	629.2	691.2	763.6	889.2	1090.0
45°	493.3	499.2	509.6	515.5	525.8	543.5	570.1	613.0	678.0	757.7	920.2
47.5°	447.5	454.9	459.4	466.7	474.1	493.3	518.4	546.5	599.7	678.0	796.1
50°	406.2	415.0	420.9	422.4	428.3	446.1	466.7	497.8	531.7	592.3	695.7
52.5°	376.6	378.1	382.5	388.5	387.0	397.3	416.5	440.2	475.6	524.3	599.7
55°	342.7	347.1	350.1	351.5	351.5	360.4	370.7	392.9	420.9	460.8	524.3
57.5°	299.8	304.3	313.1	316.1	320.5	324.9	329.4	344.1	367.8	406.2	457.9
60°	255.5	258.5	267.3	273.2	276.2	288.0	293.9	305.7	319.0	347.1	395.8
62.5°	205.3	208.3	212.7	218.6	224.5	242.2	257.0	268.8	279.2	298.4	338.2
65°	178.7	180.2	183.1	184.6	186.1	193.5	206.8	223.0	242.2	257.0	280.6
67.5°	155.1	156.6	158.0	161.0	162.5	163.9	169.9	174.3	193.5	214.2	231.9
70°	132.9	135.9	137.4	137.4	138.8	141.8	144.7	150.7	156.6	166.9	189.1
72.5°	112.3	113.7	116.7	116.7	116.7	119.6	122.6	125.5	128.5	134.4	143.3
75°	93.1	96.0	96.0	96.0	97.5	97.5	100.4	103.4	106.3	110.8	113.7
77.5°	76.8	76.8	76.8	76.8	78.3	78.3	79.8	82.7	84.2	85.7	88.6
80°	57.6	59.1	59.1	59.1	60.6	60.6	60.6	63.5	65.0	65.0	67.9
82.5°	42.8	42.8	42.8	44.3	42.8	44.3	44.3	45.8	44.3	45.8	47.3
85°	26.6	26.6	26.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1	29.5
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	14.8	13.3	13.3
90°	37.5	37.2	36.9	36.8	37.1	37.6	38.1	38.6	39.1	33.6	28.2
92.5°	35.7	35.7	35.7	35.7	35.6	35.3	35.1	34.8	34.6	34.4	34.1
95°	70.2	70.7	71.2	71.4	71.4	71.4	71.4	71.4	71.4	70.9	70.4
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	110.6	109.6
100°	153.4	153.6	153.9	154.0	154.0	154.0	154.0	154.0	154.0	153.3	152.5
102.5°	200.3	200.5	200.8	200.9	200.8	200.5	200.3	200.0	199.8	198.8	197.8
105°	247.8	247.8	247.8	247.8	247.6	247.1	246.6	246.1	245.6	245.1	244.6
107.5°	293.8	295.0	296.3	296.9	296.8	296.5	296.3	296.0	295.8	295.8	295.8
110°	345.3	346.1	346.8	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	395.0	395.5	396.0	396.3	396.7	397.4	398.1	398.9	399.6	399.8	400.1
115°	448.0	448.8	449.5	449.9	450.0	450.3	450.5	450.8	451.0	451.5	452.0
117.5°	497.1	497.9	498.6	499.0	499.4	500.1	500.8	501.6	502.3	503.5	504.8
120°	549.6	550.3	551.0	551.4	551.4	551.4	551.4	551.4	551.4	553.4	555.4
122.5°	600.4	600.9	601.4	601.7	602.1	602.8	603.5	604.3	605.0	606.2	607.5
125°	652.4	652.6	652.9	653.0	653.4	654.1	654.9	655.6	656.4	657.1	657.9
127.5°	700.3	701.0	701.7	702.1	702.6	703.6	704.6	705.6	706.6	707.6	708.6
130°	752.1	753.1	754.1	754.6	754.8	755.3	755.8	756.3	756.8	757.3	757.8
132.5°	800.7	801.5	802.2	802.6	803.2	804.5	805.7	807.0	808.2	808.0	807.7
135°	852.1	852.8	853.5	853.9	854.0	854.3	854.6	854.8	855.1	854.6	854.1
137.5°	898.4	899.3	900.3	900.8	900.9	901.2	901.4	901.7	901.9	901.4	900.9
140°	946.4	947.3	948.3	948.8	948.8	948.8	948.8	948.8	948.8	947.6	946.3
142.5°	989.9	990.9	991.9	992.4	992.3	992.0	991.7	991.5	991.2	990.5	989.7
145°	1033.4	1034.4	1035.4	1035.9	1035.8	1035.5	1035.3	1035.0	1034.8	1033.3	1031.8
147.5°	1072.5	1073.5	1074.5	1075.0	1074.7	1074.2	1073.7	1073.2	1072.7	1071.7	1070.7
150°	1110.0	1110.7	1111.4	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1107.5	1106.5
152.5°	1146.2	1147.1	1148.1	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1143.0	1141.7
155°	1176.9	1177.7	1178.4	1178.8	1178.2	1176.9	1175.7	1174.4	1173.2	1172.4	1171.7
157.5°	1205.8	1207.0	1208.3	1208.9	1208.0	1206.3	1204.6	1202.8	1201.1	1200.6	1200.1
160°	1231.0	1232.0	1233.0	1233.5	1232.8	1231.3	1229.8	1228.3	1226.8	1226.6	1226.3
162.5°	1253.8	1255.0	1256.3	1256.9	1256.0	1254.3	1252.6	1250.8	1249.1	1248.9	1248.6
165°	1272.8	1274.0	1275.3	1275.9	1275.0	1273.3	1271.6	1269.8	1268.1	1268.1	1268.1
167.5°	1289.5	1290.8	1292.0	1292.6	1291.7	1290.0	1288.3	1286.5	1284.8	1284.8	1284.8
170°	1302.3	1303.8	1305.3	1306.0	1305.1	1303.4	1301.7	1299.9	1298.2	1298.4	1298.7
172.5°	1312.4	1313.9	1315.4	1316.1	1315.2	1313.5	1311.8	1310.0	1308.3	1308.5	1308.8
175°	1319.1	1320.6	1322.1	1322.8	1321.9	1320.2	1318.5	1316.7	1315.0	1315.5	1316.0
177.5°	1322.4	1323.9	1325.4	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1319.9	1320.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2169.7	2162.4	2162.4	2157.9	2157.9	2134.3	2134.3	2141.7	2132.8	2122.5	2107.7
5°	2225.9	2209.6	2205.2	2199.3	2180.1	2150.5	2138.7	2134.3	2116.6	2094.4	2069.3
7.5°	2279.0	2252.4	2239.2	2225.9	2200.8	2159.4	2135.8	2119.5	2092.9	2059.0	2026.5
10°	2330.7	2296.8	2262.8	2246.5	2211.1	2159.4	2125.4	2098.8	2060.4	2014.6	1968.9
12.5°	2378.0	2307.1	2301.2	2268.7	2217.0	2157.9	2106.2	2067.8	2019.1	1965.9	1912.7
15°	2419.4	2347.0	2311.5	2282.0	2214.0	2140.2	2085.5	2038.3	1973.3	1912.7	1847.7
17.5°	2440.0	2361.7	2338.1	2289.4	2220.0	2123.9	2050.1	1992.5	1921.6	1849.2	1775.4
20°	2460.7	2369.1	2330.7	2296.8	2202.2	2092.9	2010.2	1943.8	1865.5	1779.8	1698.6
22.5°	2471.0	2369.1	2323.3	2276.1	2184.5	2059.0	1961.5	1883.2	1791.6	1704.5	1607.0
25°	2453.3	2360.3	2305.6	2256.9	2153.5	2017.6	1905.4	1816.7	1719.2	1620.3	1521.3
27.5°	2409.0	2339.6	2276.1	2225.9	2110.7	1964.4	1846.3	1745.8	1645.4	1534.6	1434.2
30°	2326.3	2295.3	2245.1	2188.9	2063.4	1917.2	1776.9	1673.5	1562.7	1451.9	1347.0
32.5°	2197.8	2224.4	2191.9	2143.2	2007.3	1852.2	1703.0	1598.1	1477.0	1357.4	1261.4
35°	2041.2	2135.8	2118.0	2084.1	1948.2	1782.8	1633.6	1506.6	1385.4	1264.3	1168.3
37.5°	1869.9	2013.2	2027.9	2007.3	1880.2	1711.9	1547.9	1423.8	1299.8	1177.2	1079.7
40°	1635.1	1855.1	1902.4	1911.3	1809.3	1626.2	1454.9	1333.7	1211.2	1091.5	973.4
42.5°	1419.4	1697.1	1756.2	1793.1	1719.2	1542.0	1369.2	1234.8	1113.7	1005.8	887.7
45°	1217.1	1506.6	1602.6	1649.8	1617.3	1446.0	1267.3	1141.7	1031.0	932.0	818.3
47.5°	1008.8	1299.8	1434.2	1509.5	1509.5	1348.5	1169.8	1045.7	939.4	855.2	754.8
50°	870.0	1112.2	1251.0	1350.0	1376.6	1249.6	1081.2	960.1	859.6	768.0	691.2
52.5°	741.5	958.6	1073.8	1177.2	1254.0	1143.2	982.2	872.9	774.0	688.3	627.7
55°	641.0	803.5	908.4	1022.1	1107.8	1035.4	886.2	779.9	694.2	623.3	571.6
57.5°	545.0	686.8	772.5	872.9	964.5	909.8	790.2	698.6	623.3	561.3	515.5
60°	463.8	579.0	645.5	723.7	837.5	799.1	700.1	615.9	555.4	499.2	460.8
62.5°	394.4	485.9	542.1	598.2	701.6	683.9	607.1	542.1	490.4	443.1	410.6
65°	323.5	398.8	443.1	491.8	574.6	581.9	519.9	474.1	426.9	385.5	356.0
67.5°	261.4	320.5	360.4	401.7	468.2	488.9	446.1	407.7	367.8	333.8	307.2
70°	211.2	252.6	282.1	314.6	369.3	394.4	372.2	345.6	313.1	285.1	261.4
72.5°	166.9	193.5	211.2	236.3	280.6	305.7	304.3	280.6	257.0	237.8	218.6
75°	122.6	143.3	158.0	174.3	209.7	233.4	239.3	228.9	205.3	190.5	175.8
77.5°	93.1	104.9	112.3	124.1	149.2	169.9	178.7	175.8	159.5	147.7	137.4
80°	70.9	73.9	76.8	81.2	101.9	121.1	127.0	125.5	116.7	112.3	100.4
82.5°	50.2	51.7	53.2	54.6	62.0	78.3	84.2	87.1	79.8	75.3	65.0
85°	29.5	31.0	31.0	34.0	35.4	39.9	50.2	50.2	48.7	42.8	41.4
87.5°	14.8	14.8	13.3	13.3	14.8	16.2	19.2	22.2	19.2	17.7	16.2
90°	22.7	17.2	14.5	13.0	10.0	7.1	4.1	1.1	4.1	7.1	10.0
92.5°	33.9	33.6	33.5	32.5	30.5	28.6	26.6	24.6	26.6	28.6	30.5
95°	69.9	69.4	69.2	68.0	65.5	63.0	60.5	58.0	60.5	63.0	65.5
97.5°	108.7	107.7	107.2	106.1	103.8	101.6	99.3	97.1	99.3	101.6	103.8
100°	151.8	151.1	150.7	149.7	147.7	145.8	143.8	141.8	143.8	145.8	147.7
102.5°	196.8	195.8	195.3	194.6	193.1	191.6	190.1	188.6	190.1	191.6	193.1
105°	244.1	243.6	243.3	242.9	242.2	241.5	240.7	240.0	240.7	241.5	242.2
107.5°	295.8	295.8	295.8	295.3	294.3	293.3	292.3	291.3	292.3	293.3	294.3
110°	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5	342.0	343.5	345.0

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	400.3	400.6	400.7	400.0	398.5	397.0	395.5	394.0	395.5	397.0	398.5
115°	452.5	453.0	453.2	452.5	451.0	449.5	448.0	446.5	448.0	449.5	451.0
117.5°	506.0	507.3	507.9	506.9	504.9	503.0	501.0	499.0	501.0	503.0	504.9
120°	557.4	559.4	560.4	559.4	557.4	555.4	553.4	551.4	553.4	555.4	557.4
122.5°	608.7	610.0	610.6	609.4	606.9	604.4	601.9	599.4	601.9	604.4	606.9
125°	658.6	659.3	659.7	658.6	656.4	654.1	651.9	649.7	651.9	654.1	656.4
127.5°	709.6	710.6	711.1	709.7	707.0	704.3	701.5	698.8	701.5	704.3	707.0
130°	758.3	758.8	759.1	757.5	754.3	751.0	747.8	744.6	747.8	751.0	754.3
132.5°	807.5	807.2	807.1	805.9	803.4	800.9	798.4	795.9	798.4	800.9	803.4
135°	853.6	853.1	852.8	851.4	848.7	846.0	843.2	840.5	843.2	846.0	848.7
137.5°	900.4	899.9	899.7	898.6	896.4	894.1	891.9	889.7	891.9	894.1	896.4
140°	945.1	943.8	943.2	942.1	939.9	937.6	935.4	933.2	935.4	937.6	939.9
142.5°	989.0	988.3	987.9	986.8	984.6	982.3	980.1	977.9	980.1	982.3	984.6
145°	1030.3	1028.8	1028.1	1027.2	1025.5	1023.8	1022.0	1020.3	1022.0	1023.8	1025.5
147.5°	1069.8	1068.8	1068.3	1067.2	1064.9	1062.7	1060.4	1058.2	1060.4	1062.7	1064.9
150°	1105.5	1104.5	1104.0	1103.3	1101.8	1100.3	1098.8	1097.3	1098.8	1100.3	1101.8
152.5°	1140.5	1139.2	1138.6	1137.9	1136.4	1134.9	1133.4	1131.9	1133.4	1134.9	1136.4
155°	1170.9	1170.2	1169.8	1169.4	1168.7	1168.0	1167.2	1166.5	1167.2	1168.0	1168.7
157.5°	1199.6	1199.1	1198.9	1198.6	1198.1	1197.6	1197.1	1196.6	1197.1	1197.6	1198.1
160°	1226.1	1225.8	1225.7	1225.4	1224.9	1224.4	1223.9	1223.4	1223.9	1224.4	1224.9
162.5°	1248.4	1248.1	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0	1248.0
165°	1268.1	1268.1	1268.1	1268.2	1268.5	1268.7	1269.0	1269.2	1269.0	1268.7	1268.5
167.5°	1284.8	1284.8	1284.8	1285.2	1285.9	1286.7	1287.4	1288.2	1287.4	1286.7	1285.9
170°	1298.9	1299.2	1299.3	1299.7	1300.4	1301.2	1301.9	1302.7	1301.9	1301.2	1300.4
172.5°	1309.0	1309.3	1309.4	1309.8	1310.5	1311.2	1312.0	1312.7	1312.0	1311.2	1310.5
175°	1316.5	1317.0	1317.2	1317.6	1318.3	1319.0	1319.8	1320.5	1319.8	1319.0	1318.3
177.5°	1320.9	1321.4	1321.7	1322.1	1322.8	1323.5	1324.3	1325.0	1324.3	1323.5	1322.8
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2101.8	2103.3	2107.7	2094.4	2073.7	2064.9	2038.3	2033.9	2029.4	2029.4	2033.9
5°	2054.5	2048.6	2050.1	2025.0	1995.4	1977.7	1940.8	1946.7	1927.5	1915.7	1918.6
7.5°	2002.8	1986.6	1985.1	1952.6	1915.7	1883.2	1844.8	1835.9	1818.2	1797.5	1788.7
10°	1937.8	1926.0	1903.9	1866.9	1819.7	1793.1	1741.4	1710.4	1706.0	1674.9	1663.1
12.5°	1871.4	1850.7	1828.5	1776.9	1723.7	1680.8	1642.4	1608.5	1584.8	1558.3	1540.5
15°	1794.6	1769.5	1744.4	1689.7	1627.7	1584.8	1527.2	1477.0	1407.6	1352.9	1321.9
17.5°	1710.4	1682.3	1648.3	1587.8	1527.2	1468.2	1361.8	1302.7	1254.0	1221.5	1202.3
20°	1623.2	1592.2	1558.3	1497.7	1392.8	1289.4	1230.4	1184.6	1155.0	1122.5	1098.9
22.5°	1531.7	1499.2	1462.2	1367.7	1256.9	1184.6	1138.8	1095.9	1053.1	1035.4	1023.6
25°	1446.0	1416.5	1369.2	1240.7	1153.5	1087.1	1035.4	1007.3	985.2	961.5	939.4
27.5°	1357.4	1302.7	1236.3	1128.4	1073.8	1005.8	968.9	948.2	909.8	893.6	883.3
30°	1251.0	1190.5	1127.0	1050.2	986.6	939.4	905.4	871.4	849.3	833.0	815.3
32.5°	1143.2	1085.6	1045.7	966.0	918.7	870.0	837.5	816.8	784.3	774.0	766.6
35°	1050.2	1001.4	966.0	901.0	856.7	812.4	788.7	757.7	737.0	717.8	706.0
37.5°	958.6	932.0	895.1	840.4	793.2	757.7	725.2	714.9	686.8	676.5	664.7
40°	895.1	855.2	824.2	776.9	737.0	698.6	678.0	654.3	635.1	618.9	614.4
42.5°	818.3	788.7	771.0	719.3	678.0	655.8	630.7	604.1	589.3	576.0	559.8
45°	760.7	734.1	709.0	667.6	630.7	602.6	580.5	562.7	537.6	531.7	506.6
47.5°	700.1	673.5	654.3	613.0	579.0	552.4	536.2	512.5	491.8	478.6	466.7
50°	639.5	617.4	599.7	564.2	534.7	506.6	484.5	460.8	452.0	429.8	422.4
52.5°	581.9	567.2	548.0	514.0	484.5	460.8	437.2	418.0	404.7	392.9	384.0
55°	533.2	509.6	500.7	463.8	438.7	413.6	392.9	381.1	364.8	357.4	350.1
57.5°	478.6	465.3	450.5	422.4	394.4	370.7	356.0	338.2	329.4	320.5	314.6
60°	431.3	412.1	400.3	376.6	351.5	329.4	316.1	302.8	291.0	283.6	271.8
62.5°	376.6	361.9	354.5	329.4	308.7	288.0	276.2	262.9	254.0	240.8	226.0
65°	329.4	317.6	308.7	288.0	268.8	249.6	237.8	221.6	209.7	202.4	200.9
67.5°	288.0	279.2	265.9	246.7	227.5	212.7	199.4	186.1	184.6	181.7	181.7
70°	242.2	233.4	226.0	205.3	189.1	172.8	169.9	165.4	161.0	159.5	156.6
72.5°	202.4	195.0	186.1	168.4	152.1	147.7	144.7	141.8	137.4	135.9	134.4
75°	163.9	153.6	147.7	131.5	127.0	124.1	121.1	116.7	113.7	112.3	109.3
77.5°	125.5	115.2	115.2	106.3	103.4	99.0	96.0	93.1	91.6	88.6	88.6
80°	88.6	88.6	85.7	81.2	76.8	75.3	70.9	69.4	67.9	69.4	66.5
82.5°	65.0	59.1	59.1	56.1	53.2	51.7	48.7	48.7	47.3	47.3	47.3
85°	36.9	36.9	35.4	32.5	31.0	31.0	29.5	29.5	28.1	28.1	26.6
87.5°	14.8	13.3	14.8	13.3	13.3	11.8	11.8	11.8	10.3	11.8	10.3
90°	13.0	14.5	17.2	22.7	28.2	33.6	39.1	38.6	38.1	37.6	37.1
92.5°	32.5	33.5	33.6	33.9	34.1	34.4	34.6	34.8	35.1	35.3	35.6
95°	68.0	69.2	69.4	69.9	70.4	70.9	71.4	71.4	71.4	71.4	71.4
97.5°	106.1	107.2	107.7	108.7	109.6	110.6	111.6	111.6	111.6	111.6	111.6
100°	149.7	150.7	151.1	151.8	152.5	153.3	154.0	154.0	154.0	154.0	154.0
102.5°	194.6	195.3	195.8	196.8	197.8	198.8	199.8	200.0	200.3	200.5	200.8
105°	242.9	243.3	243.6	244.1	244.6	245.1	245.6	246.1	246.6	247.1	247.6
107.5°	295.3	295.8	295.8	295.8	295.8	295.8	295.8	296.0	296.3	296.5	296.8
110°	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	400.0	400.7	400.6	400.3	400.1	399.8	399.6	398.9	398.1	397.4	396.7
115°	452.5	453.2	453.0	452.5	452.0	451.5	451.0	450.8	450.5	450.3	450.0
117.5°	506.9	507.9	507.3	506.0	504.8	503.5	502.3	501.6	500.8	500.1	499.4
120°	559.4	560.4	559.4	557.4	555.4	553.4	551.4	551.4	551.4	551.4	551.4
122.5°	609.4	610.6	610.0	608.7	607.5	606.2	605.0	604.3	603.5	602.8	602.1
125°	658.6	659.7	659.3	658.6	657.9	657.1	656.4	655.6	654.9	654.1	653.4
127.5°	709.7	711.1	710.6	709.6	708.6	707.6	706.6	705.6	704.6	703.6	702.6
130°	757.5	759.1	758.8	758.3	757.8	757.3	756.8	756.3	755.8	755.3	754.8
132.5°	805.9	807.1	807.2	807.5	807.7	808.0	808.2	807.0	805.7	804.5	803.2
135°	851.4	852.8	853.1	853.6	854.1	854.6	855.1	854.8	854.6	854.3	854.0
137.5°	898.6	899.7	899.9	900.4	900.9	901.4	901.9	901.7	901.4	901.2	900.9
140°	942.1	943.2	943.8	945.1	946.3	947.6	948.8	948.8	948.8	948.8	948.8
142.5°	986.8	987.9	988.3	989.0	989.7	990.5	991.2	991.5	991.7	992.0	992.3
145°	1027.2	1028.1	1028.8	1030.3	1031.8	1033.3	1034.8	1035.0	1035.3	1035.5	1035.8
147.5°	1067.2	1068.3	1068.8	1069.8	1070.7	1071.7	1072.7	1073.2	1073.7	1074.2	1074.7
150°	1103.3	1104.0	1104.5	1105.5	1106.5	1107.5	1108.5	1109.2	1110.0	1110.7	1111.4
152.5°	1137.9	1138.6	1139.2	1140.5	1141.7	1143.0	1144.2	1145.2	1146.2	1147.1	1148.1
155°	1169.4	1169.8	1170.2	1170.9	1171.7	1172.4	1173.2	1174.4	1175.7	1176.9	1178.2
157.5°	1198.6	1198.9	1199.1	1199.6	1200.1	1200.6	1201.1	1202.8	1204.6	1206.3	1208.0
160°	1225.4	1225.7	1225.8	1226.1	1226.3	1226.6	1226.8	1228.3	1229.8	1231.3	1232.8
162.5°	1248.0	1248.0	1248.1	1248.4	1248.6	1248.9	1249.1	1250.8	1252.6	1254.3	1256.0
165°	1268.2	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1	1269.8	1271.6	1273.3	1275.0
167.5°	1285.2	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8	1286.5	1288.3	1290.0	1291.7
170°	1299.7	1299.3	1299.2	1298.9	1298.7	1298.4	1298.2	1299.9	1301.7	1303.4	1305.1
172.5°	1309.8	1309.4	1309.3	1309.0	1308.8	1308.5	1308.3	1310.0	1311.8	1313.5	1315.2
175°	1317.6	1317.2	1317.0	1316.5	1316.0	1315.5	1315.0	1316.7	1318.5	1320.2	1321.9
177.5°	1322.1	1321.7	1321.4	1320.9	1320.4	1319.9	1319.4	1320.9	1322.4	1323.9	1325.4
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2033.9	2030.9	2022.0	2025.0	2020.6	2020.6	2017.6	2017.6	2017.6	2025.0	2020.6
5°	1923.1	1912.7	1902.4	1898.0	1893.5	1889.1	1889.1	1887.6	1900.9	1898.0	1909.8
7.5°	1785.7	1782.8	1762.1	1762.1	1754.7	1751.7	1759.1	1760.6	1762.1	1765.0	1772.4
10°	1663.1	1655.7	1626.2	1629.1	1624.7	1618.8	1623.2	1620.3	1630.6	1633.6	1630.6
12.5°	1518.4	1505.1	1472.6	1456.3	1438.6	1425.3	1441.6	1429.8	1471.1	1482.9	1515.4
15°	1326.4	1301.3	1279.1	1279.1	1262.8	1251.0	1258.4	1271.7	1280.6	1293.9	1299.8
17.5°	1197.9	1187.5	1169.8	1159.5	1155.0	1150.6	1150.6	1156.5	1175.7	1174.2	1186.0
20°	1088.6	1082.7	1073.8	1060.5	1056.1	1053.1	1053.1	1053.1	1066.4	1078.2	1085.6
22.5°	1013.2	1008.8	1002.9	985.2	976.3	973.4	980.7	985.2	995.5	1004.4	1011.8
25°	937.9	927.6	917.2	911.3	906.9	906.9	909.8	911.3	915.7	920.2	929.0
27.5°	875.9	868.5	853.7	837.5	837.5	833.0	836.0	838.9	849.3	864.1	871.4
30°	806.5	805.0	799.1	793.2	787.2	784.3	790.2	794.6	796.1	803.5	803.5
32.5°	756.2	745.9	735.6	729.6	726.7	725.2	726.7	732.6	732.6	741.5	751.8
35°	706.0	700.1	689.8	679.4	676.5	669.1	675.0	680.9	691.2	695.7	700.1
37.5°	651.4	644.0	639.5	636.6	630.7	632.2	627.7	636.6	645.5	644.0	646.9
40°	610.0	596.7	583.4	581.9	580.5	579.0	579.0	580.5	586.4	592.3	601.1
42.5°	556.8	552.4	540.6	528.8	525.8	522.9	519.9	525.8	537.6	548.0	552.4
45°	502.2	496.3	493.3	484.5	478.6	477.1	474.1	481.5	491.8	496.3	499.2
47.5°	452.0	450.5	441.6	443.1	438.7	440.2	438.7	443.1	443.1	447.5	450.5
50°	418.0	413.6	409.1	406.2	401.7	401.7	400.3	401.7	407.7	413.6	412.1
52.5°	384.0	376.6	375.2	373.7	370.7	373.7	369.3	370.7	376.6	379.6	378.1
55°	344.1	342.7	339.7	336.8	335.3	333.8	333.8	333.8	339.7	344.1	345.6
57.5°	313.1	305.7	299.8	299.8	293.9	292.4	295.4	296.9	301.3	304.3	307.2
60°	270.3	267.3	258.5	254.0	245.2	243.7	243.7	249.6	257.0	267.3	270.3
62.5°	224.5	220.1	218.6	218.6	218.6	218.6	218.6	218.6	218.6	220.1	220.1
65°	199.4	200.9	199.4	197.9	199.4	199.4	197.9	197.9	197.9	199.4	200.9
67.5°	178.7	177.2	178.7	177.2	175.8	175.8	174.3	175.8	177.2	178.7	178.7
70°	155.1	155.1	153.6	155.1	153.6	152.1	150.7	150.7	153.6	155.1	155.1
72.5°	132.9	132.9	131.5	131.5	128.5	128.5	130.0	128.5	128.5	132.9	132.9
75°	110.8	109.3	107.8	107.8	106.3	106.3	106.3	104.9	107.8	107.8	109.3
77.5°	87.1	87.1	87.1	85.7	85.7	84.2	84.2	85.7	85.7	85.7	87.1
80°	66.5	66.5	66.5	65.0	63.5	63.5	63.5	63.5	63.5	65.0	63.5
82.5°	45.8	45.8	45.8	45.8	45.8	44.3	44.3	44.3	45.8	45.8	44.3
85°	28.1	26.6	28.1	28.1	26.6	28.1	26.6	26.6	25.1	25.1	26.6
87.5°	11.8	10.3	8.9	8.9	10.3	8.9	8.9	8.9	10.3	8.9	8.9
90°	36.8	36.9	37.2	37.5	37.7	38.0	37.7	37.5	37.2	36.9	36.8
92.5°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7	35.7
95°	71.4	71.2	70.7	70.2	69.7	69.2	69.7	70.2	70.7	71.2	71.4
97.5°	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6
100°	154.0	153.9	153.6	153.4	153.1	152.9	153.1	153.4	153.6	153.9	154.0
102.5°	200.9	200.8	200.5	200.3	200.0	199.8	200.0	200.3	200.5	200.8	200.9
105°	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8	247.8
107.5°	296.9	296.3	295.0	293.8	292.5	291.3	292.5	293.8	295.0	296.3	296.9
110°	347.2	346.8	346.1	345.3	344.6	343.8	344.6	345.3	346.1	346.8	347.2

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	396.3	396.0	395.5	395.0	394.5	394.0	394.5	395.0	395.5	396.0	396.3
115°	449.9	449.5	448.8	448.0	447.3	446.5	447.3	448.0	448.8	449.5	449.9
117.5°	499.0	498.6	497.9	497.1	496.4	495.6	496.4	497.1	497.9	498.6	499.0
120°	551.4	551.0	550.3	549.6	548.8	548.1	548.8	549.6	550.3	551.0	551.4
122.5°	601.7	601.4	600.9	600.4	599.9	599.4	599.9	600.4	600.9	601.4	601.7
125°	653.0	652.9	652.6	652.4	652.1	651.9	652.1	652.4	652.6	652.9	653.0
127.5°	702.1	701.7	701.0	700.3	699.5	698.8	699.5	700.3	701.0	701.7	702.1
130°	754.6	754.1	753.1	752.1	751.1	750.1	751.1	752.1	753.1	754.1	754.6
132.5°	802.6	802.2	801.5	800.7	800.0	799.2	800.0	800.7	801.5	802.2	802.6
135°	853.9	853.5	852.8	852.1	851.3	850.6	851.3	852.1	852.8	853.5	853.9
137.5°	900.8	900.3	899.3	898.4	897.4	896.4	897.4	898.4	899.3	900.3	900.8
140°	948.8	948.3	947.3	946.4	945.4	944.4	945.4	946.4	947.3	948.3	948.8
142.5°	992.4	991.9	990.9	989.9	988.9	987.9	988.9	989.9	990.9	991.9	992.4
145°	1035.9	1035.4	1034.4	1033.4	1032.4	1031.4	1032.4	1033.4	1034.4	1035.4	1035.9
147.5°	1075.0	1074.5	1073.5	1072.5	1071.5	1070.5	1071.5	1072.5	1073.5	1074.5	1075.0
150°	1111.8	1111.4	1110.7	1110.0	1109.2	1108.5	1109.2	1110.0	1110.7	1111.4	1111.8
152.5°	1148.6	1148.1	1147.1	1146.2	1145.2	1144.2	1145.2	1146.2	1147.1	1148.1	1148.6
155°	1178.8	1178.4	1177.7	1176.9	1176.2	1175.4	1176.2	1176.9	1177.7	1178.4	1178.8
157.5°	1208.9	1208.3	1207.0	1205.8	1204.5	1203.3	1204.5	1205.8	1207.0	1208.3	1208.9
160°	1233.5	1233.0	1232.0	1231.0	1230.0	1229.0	1230.0	1231.0	1232.0	1233.0	1233.5
162.5°	1256.9	1256.3	1255.0	1253.8	1252.5	1251.3	1252.5	1253.8	1255.0	1256.3	1256.9
165°	1275.9	1275.3	1274.0	1272.8	1271.5	1270.3	1271.5	1272.8	1274.0	1275.3	1275.9
167.5°	1292.6	1292.0	1290.8	1289.5	1288.3	1287.1	1288.3	1289.5	1290.8	1292.0	1292.6
170°	1306.0	1305.3	1303.8	1302.3	1300.8	1299.3	1300.8	1302.3	1303.8	1305.3	1306.0
172.5°	1316.1	1315.4	1313.9	1312.4	1310.9	1309.4	1310.9	1312.4	1313.9	1315.4	1316.1
175°	1322.8	1322.1	1320.6	1319.1	1317.6	1316.1	1317.6	1319.1	1320.6	1322.1	1322.8
177.5°	1326.1	1325.4	1323.9	1322.4	1320.9	1319.4	1320.9	1322.4	1323.9	1325.4	1326.1
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2025.0	2032.4	2029.4	2013.2	2029.4	2033.9	2042.7	2051.6	2057.5	2066.3	2073.7
5°	1898.0	1912.7	1921.6	1912.7	1942.3	1946.7	1967.4	1979.2	1996.9	2011.7	2023.5
7.5°	1778.3	1790.1	1807.9	1810.8	1828.5	1849.2	1878.8	1908.3	1936.4	1951.1	1964.4
10°	1649.8	1670.5	1697.1	1691.2	1717.8	1750.3	1781.3	1828.5	1852.2	1878.8	1902.4
12.5°	1521.3	1534.6	1570.1	1581.9	1620.3	1645.4	1688.2	1717.8	1776.9	1807.9	1828.5
15°	1296.8	1351.5	1395.8	1449.0	1499.2	1546.4	1584.8	1638.0	1689.7	1713.3	1747.3
17.5°	1194.9	1220.0	1246.6	1273.2	1338.2	1422.4	1490.3	1547.9	1592.2	1623.2	1663.1
20°	1088.6	1113.7	1143.2	1168.3	1208.2	1268.8	1352.9	1451.9	1505.1	1537.6	1576.0
22.5°	1013.2	1036.9	1056.1	1078.2	1109.2	1153.5	1217.1	1339.7	1410.6	1450.4	1484.4
25°	932.0	961.5	982.2	998.5	1023.6	1072.3	1124.0	1193.4	1320.5	1351.5	1398.7
27.5°	875.9	884.7	908.4	933.5	958.6	985.2	1038.3	1097.4	1183.1	1251.0	1308.6
30°	809.4	831.6	853.7	864.1	886.2	924.6	957.1	1020.6	1087.1	1140.3	1209.7
32.5°	759.2	772.5	787.2	812.4	833.0	859.6	892.1	945.3	1001.4	1035.4	1088.6
35°	703.1	711.9	742.9	753.3	774.0	800.5	833.0	874.4	935.0	961.5	999.9
37.5°	649.9	670.6	679.4	703.1	722.3	748.8	772.5	819.7	859.6	890.6	926.1
40°	608.5	617.4	633.6	654.3	670.6	691.2	720.8	754.8	797.6	822.7	853.7
42.5°	558.3	565.7	586.4	598.2	624.8	644.0	661.7	703.1	741.5	760.7	791.7
45°	503.7	521.4	534.7	558.3	573.1	596.7	618.9	648.4	683.9	706.0	723.7
47.5°	456.4	474.1	487.4	509.6	533.2	543.5	567.2	598.2	630.7	648.4	673.5
50°	418.0	423.9	449.0	459.4	484.5	505.1	521.4	548.0	583.4	593.8	614.4
52.5°	381.1	385.5	401.7	415.0	437.2	454.9	475.6	500.7	530.2	546.5	562.7
55°	348.6	351.5	358.9	373.7	388.5	410.6	429.8	453.4	478.6	496.3	511.0
57.5°	311.7	317.6	323.5	332.3	347.1	367.8	388.5	410.6	431.3	443.1	462.3
60°	268.8	277.7	288.0	298.4	308.7	323.5	347.1	367.8	387.0	397.3	412.1
62.5°	223.0	240.8	249.6	261.4	270.3	283.6	301.3	324.9	338.2	351.5	363.3
65°	200.9	202.4	203.8	215.6	231.9	245.2	261.4	279.2	299.8	308.7	317.6
67.5°	178.7	180.2	183.1	184.6	190.5	205.3	223.0	242.2	258.5	264.4	273.2
70°	156.6	156.6	162.5	163.9	165.4	166.9	181.7	200.9	215.6	223.0	233.4
72.5°	132.9	134.4	137.4	138.8	141.8	144.7	149.2	159.5	177.2	184.6	196.4
75°	109.3	110.8	112.3	113.7	118.2	119.6	124.1	130.0	137.4	146.2	153.6
77.5°	87.1	87.1	88.6	91.6	94.5	96.0	100.4	103.4	106.3	110.8	116.7
80°	65.0	66.5	66.5	69.4	69.4	70.9	72.4	76.8	79.8	82.7	85.7
82.5°	44.3	47.3	47.3	47.3	48.7	50.2	51.7	51.7	54.6	56.1	60.6
85°	26.6	28.1	28.1	28.1	26.6	29.5	29.5	31.0	31.0	31.0	32.5
87.5°	10.3	8.9	10.3	10.3	10.3	11.8	10.3	10.3	11.8	13.3	13.3
90°	37.1	37.6	38.1	38.6	39.1	33.6	28.2	22.7	17.2	14.5	13.0
92.5°	35.6	35.3	35.1	34.8	34.6	34.4	34.1	33.9	33.6	33.5	32.5
95°	71.4	71.4	71.4	71.4	71.4	70.9	70.4	69.9	69.4	69.2	68.0
97.5°	111.6	111.6	111.6	111.6	111.6	110.6	109.6	108.7	107.7	107.2	106.1
100°	154.0	154.0	154.0	154.0	154.0	153.3	152.5	151.8	151.1	150.7	149.7
102.5°	200.8	200.5	200.3	200.0	199.8	198.8	197.8	196.8	195.8	195.3	194.6
105°	247.6	247.1	246.6	246.1	245.6	245.1	244.6	244.1	243.6	243.3	242.9
107.5°	296.8	296.5	296.3	296.0	295.8	295.8	295.8	295.8	295.8	295.8	295.3
110°	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	346.5

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	396.7	397.4	398.1	398.9	399.6	399.8	400.1	400.3	400.6	400.7	400.0
115°	450.0	450.3	450.5	450.8	451.0	451.5	452.0	452.5	453.0	453.2	452.5
117.5°	499.4	500.1	500.8	501.6	502.3	503.5	504.8	506.0	507.3	507.9	506.9
120°	551.4	551.4	551.4	551.4	551.4	553.4	555.4	557.4	559.4	560.4	559.4
122.5°	602.1	602.8	603.5	604.3	605.0	606.2	607.5	608.7	610.0	610.6	609.4
125°	653.4	654.1	654.9	655.6	656.4	657.1	657.9	658.6	659.3	659.7	658.6
127.5°	702.6	703.6	704.6	705.6	706.6	707.6	708.6	709.6	710.6	711.1	709.7
130°	754.8	755.3	755.8	756.3	756.8	757.3	757.8	758.3	758.8	759.1	757.5
132.5°	803.2	804.5	805.7	807.0	808.2	808.0	807.7	807.5	807.2	807.1	805.9
135°	854.0	854.3	854.6	854.8	855.1	854.6	854.1	853.6	853.1	852.8	851.4
137.5°	900.9	901.2	901.4	901.7	901.9	901.4	900.9	900.4	899.9	899.7	898.6
140°	948.8	948.8	948.8	948.8	948.8	947.6	946.3	945.1	943.8	943.2	942.1
142.5°	992.3	992.0	991.7	991.5	991.2	990.5	989.7	989.0	988.3	987.9	986.8
145°	1035.8	1035.5	1035.3	1035.0	1034.8	1033.3	1031.8	1030.3	1028.8	1028.1	1027.2
147.5°	1074.7	1074.2	1073.7	1073.2	1072.7	1071.7	1070.7	1069.8	1068.8	1068.3	1067.2
150°	1111.4	1110.7	1110.0	1109.2	1108.5	1107.5	1106.5	1105.5	1104.5	1104.0	1103.3
152.5°	1148.1	1147.1	1146.2	1145.2	1144.2	1143.0	1141.7	1140.5	1139.2	1138.6	1137.9
155°	1178.2	1176.9	1175.7	1174.4	1173.2	1172.4	1171.7	1170.9	1170.2	1169.8	1169.4
157.5°	1208.0	1206.3	1204.6	1202.8	1201.1	1200.6	1200.1	1199.6	1199.1	1198.9	1198.6
160°	1232.8	1231.3	1229.8	1228.3	1226.8	1226.6	1226.3	1226.1	1225.8	1225.7	1225.4
162.5°	1256.0	1254.3	1252.6	1250.8	1249.1	1248.9	1248.6	1248.4	1248.1	1248.0	1248.0
165°	1275.0	1273.3	1271.6	1269.8	1268.1	1268.1	1268.1	1268.1	1268.1	1268.1	1268.2
167.5°	1291.7	1290.0	1288.3	1286.5	1284.8	1284.8	1284.8	1284.8	1284.8	1284.8	1285.2
170°	1305.1	1303.4	1301.7	1299.9	1298.2	1298.4	1298.7	1298.9	1299.2	1299.3	1299.7
172.5°	1315.2	1313.5	1311.8	1310.0	1308.3	1308.5	1308.8	1309.0	1309.3	1309.4	1309.8
175°	1321.9	1320.2	1318.5	1316.7	1315.0	1315.5	1316.0	1316.5	1317.0	1317.2	1317.6
177.5°	1325.4	1323.9	1322.4	1320.9	1319.4	1319.9	1320.4	1320.9	1321.4	1321.7	1322.1
180°	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8	1322.8

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2125.4	2125.4	2125.4	2125.4
2.5°	2087.0	2082.6	2109.2	2138.7
5°	2044.2	2051.6	2085.5	2126.9
7.5°	1999.9	2016.1	2056.0	2110.7
10°	1937.8	1967.4	2027.9	2084.1
12.5°	1877.3	1917.2	1974.8	2041.2
15°	1809.3	1853.7	1924.6	2004.3
17.5°	1734.0	1784.2	1866.9	1954.1
20°	1654.3	1720.7	1807.9	1902.4
22.5°	1565.6	1645.4	1735.5	1840.4
25°	1480.0	1567.1	1657.2	1778.3
27.5°	1395.8	1481.4	1581.9	1704.5
30°	1311.6	1389.9	1497.7	1629.1
32.5°	1221.5	1302.7	1416.5	1550.9
35°	1138.8	1220.0	1326.4	1459.3
37.5°	1050.2	1137.3	1239.2	1376.6
40°	946.8	1048.7	1147.6	1279.1
42.5°	861.1	968.9	1064.9	1189.0
45°	793.2	895.1	974.8	1095.9
47.5°	729.6	812.4	893.6	1005.8
50°	669.1	732.6	816.8	917.2
52.5°	607.1	661.7	734.1	828.6
55°	550.9	602.6	667.6	740.0
57.5°	499.2	536.2	601.1	666.1
60°	441.6	480.0	530.2	584.9
62.5°	392.9	422.4	469.7	515.5
65°	341.2	369.3	404.7	447.5
67.5°	293.9	319.0	347.1	381.1
70°	251.1	270.3	291.0	320.5
72.5°	205.3	226.0	245.2	268.8
75°	168.4	177.2	193.5	209.7
77.5°	130.0	141.8	150.7	163.9
80°	93.1	103.4	106.3	116.7
82.5°	62.0	67.9	73.9	76.8
85°	35.4	38.4	44.3	45.8
87.5°	13.3	14.8	17.7	20.7
90°	10.0	7.1	4.1	1.1
92.5°	30.5	28.6	26.6	24.6
95°	65.5	63.0	60.5	58.0
97.5°	103.8	101.6	99.3	97.1
100°	147.7	145.8	143.8	141.8
102.5°	193.1	191.6	190.1	188.6
105°	242.2	241.5	240.7	240.0
107.5°	294.3	293.3	292.3	291.3
110°	345.0	343.5	342.0	340.5

TEST NUMBER: P1009677

CATALOG NUMBER: S122RDIP-B1005D1080UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	398.5	397.0	395.5	394.0
115°	451.0	449.5	448.0	446.5
117.5°	504.9	503.0	501.0	499.0
120°	557.4	555.4	553.4	551.4
122.5°	606.9	604.4	601.9	599.4
125°	656.4	654.1	651.9	649.7
127.5°	707.0	704.3	701.5	698.8
130°	754.3	751.0	747.8	744.6
132.5°	803.4	800.9	798.4	795.9
135°	848.7	846.0	843.2	840.5
137.5°	896.4	894.1	891.9	889.7
140°	939.9	937.6	935.4	933.2
142.5°	984.6	982.3	980.1	977.9
145°	1025.5	1023.8	1022.0	1020.3
147.5°	1064.9	1062.7	1060.4	1058.2
150°	1101.8	1100.3	1098.8	1097.3
152.5°	1136.4	1134.9	1133.4	1131.9
155°	1168.7	1168.0	1167.2	1166.5
157.5°	1198.1	1197.6	1197.1	1196.6
160°	1224.9	1224.4	1223.9	1223.4
162.5°	1248.0	1248.0	1248.0	1248.0
165°	1268.5	1268.7	1269.0	1269.2
167.5°	1285.9	1286.7	1287.4	1288.2
170°	1300.4	1301.2	1301.9	1302.7
172.5°	1310.5	1311.2	1312.0	1312.7
175°	1318.3	1319.0	1319.8	1320.5
177.5°	1322.8	1323.5	1324.3	1325.0
180°	1322.8	1322.8	1322.8	1322.8

(END OF REPORT)