

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009722

Luminaire Tested: S122RDIP-B1005D530UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009722
REPORT IS A COMBINATION OF REPORTS P987918 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D530UB30-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5386.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009722

CATALOG NUMBER: S122RDIP-B1005D530UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009722

CATALOG NUMBER: S122RDIP-B1005D530UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	102	98	94	90	96	92	89	86	81	79	77	72	70	68	63	61	60
2	93	86	80	75	87	81	76	71	72	68	64	64	61	58	56	54	52
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45
4	79	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39
5	72	61	53	47	68	58	51	45	52	46	41	46	42	38	41	37	34
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	38	34	31
7	62	50	42	36	58	47	40	35	43	37	33	39	34	30	34	31	28
8	58	46	38	33	54	43	36	31	39	33	29	35	31	27	32	28	25
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	29	26	23
10	51	39	31	27	48	37	30	26	34	28	24	30	26	22	27	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26869	26869	26869
5°	26912	25563	25373
10°	26648	24245	23445
15°	26282	22689	21246
20°	25798	20919	18947
25°	25301	19103	16843
30°	24634	17336	14546
35°	23981	15553	12573
40°	23317	13801	10541
45°	22545	11994	8768
50°	21747	10251	7139
55°	20917	8508	5668
60°	19952	6805	4287
65°	18841	5188	3486
70°	17496	3764	2772
75°	15814	2871	2117
80°	13365	1942	1421
85°	9337	890	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22545 cd/sqm

TEST NUMBER: P1009722

CATALOG NUMBER: S122RDIP-B1005D530UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	3.0
10°-20°	436.7	8.1
20°-30°	613.1	11.4
30°-40°	668.4	12.4
40°-50°	614.3	11.4
50°-60°	482.4	9.0
60°-70°	314.0	5.8
70°-80°	161.7	3.0
80°-90°	43.2	0.8
90°-100°	41.9	0.8
100°-110°	133.2	2.5
110°-120°	227.8	4.2
120°-130°	299.7	5.6
130°-140°	336.4	6.2
140°-150°	329.9	6.1
150°-160°	276.7	5.1
160°-170°	183.5	3.4
170°-180°	64.1	1.2
0°-30°	1209.0	22.4
0°-40°	1877.3	34.9
0°-60°	2974.0	55.2
0°-90°	3492.9	64.9
90°-120°	402.9	7.5
90°-150°	1368.8	25.4
90°-180°	1893.0	35.1
0°-180°	5386.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1697	1690	1670	1684	1679	161
15°	1614	1598	1545	1516	1501	455
25°	1466	1416	1315	1252	1229	674
35°	1263	1184	1049	952	919	790
45°	1032	929	768	659	622	797
55°	785	665	499	407	378	701
65°	530	406	267	215	210	525
75°	283	175	123	112	111	299
85°	66	34	29	29	29	76
90°	1	7	20	19	19	5
95°	30	35	37	37	35	33
105°	123	125	126	127	127	130
115°	229	232	231	230	229	226
125°	333	338	336	334	334	297
135°	430	437	438	437	435	332
145°	522	526	530	530	528	326
155°	597	599	600	603	602	275
165°	650	649	649	653	650	183
175°	676	674	673	677	674	64
180°	677	677	677	677	677	

TEST NUMBER: P1009722

CATALOG NUMBER: S122RDIP-B1005D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.4	1697.4	1697.4	1697.4	1697.4
2.5°	1705.1	1697.4	1680.5	1695.9	1692.8
5°	1697.4	1689.8	1669.8	1683.6	1679.0
7.5°	1683.6	1674.4	1652.9	1659.0	1651.4
10°	1665.2	1654.4	1623.7	1619.1	1609.9
12.5°	1642.1	1628.3	1586.8	1577.6	1560.7
15°	1614.5	1597.6	1545.4	1516.2	1500.8
17.5°	1582.2	1557.6	1493.1	1459.3	1434.8
20°	1545.4	1514.6	1437.8	1399.4	1365.6
22.5°	1505.4	1470.1	1381.0	1328.8	1305.7
25°	1465.5	1416.3	1314.9	1252.0	1228.9
27.5°	1417.9	1365.6	1253.5	1181.3	1146.0
30°	1367.2	1308.8	1185.9	1107.6	1066.1
32.5°	1318.0	1247.3	1121.4	1029.2	990.8
35°	1262.7	1184.4	1049.2	952.4	918.6
37.5°	1208.9	1124.5	981.6	875.6	837.2
40°	1152.1	1059.9	910.9	801.9	761.9
42.5°	1093.7	995.4	840.3	726.6	688.2
45°	1032.3	929.4	768.1	659.0	622.1
47.5°	973.9	864.8	698.9	589.9	556.1
50°	909.4	800.3	631.4	525.4	493.1
52.5°	846.4	731.2	566.8	465.5	436.3
55°	785.0	665.2	499.2	407.1	377.9
57.5°	722.0	599.1	439.3	353.3	328.7
60°	657.5	534.6	376.4	298.0	273.4
62.5°	594.5	471.6	322.6	248.9	236.6
65°	530.0	405.5	267.3	215.1	210.5
67.5°	468.5	344.1	215.1	188.9	184.3
70°	404.0	284.2	178.2	162.8	156.7
72.5°	342.6	228.9	149.0	136.7	133.6
75°	282.7	175.1	122.9	112.1	110.6
77.5°	222.7	124.4	96.8	90.6	87.6
80°	167.4	89.1	73.7	67.6	67.6
82.5°	116.7	59.9	50.7	47.6	47.6
85°	66.1	33.8	29.2	29.2	29.2
87.5°	24.6	12.3	12.3	10.8	10.8
90°	0.6	7.4	20.0	18.9	19.4
92.5°	12.6	17.1	17.7	18.3	18.3
95°	29.7	35.4	36.6	36.6	35.4
97.5°	49.7	54.9	57.1	57.1	57.1
100°	72.6	77.1	78.9	78.9	78.3
102.5°	96.6	100.0	102.3	102.9	102.3
105°	122.9	124.6	125.7	126.9	126.9
107.5°	149.1	151.4	151.4	152.0	149.1
110°	174.3	177.7	177.7	177.7	176.0

TEST NUMBER: P1009722

CATALOG NUMBER: S122RDIP-B1005D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.7	205.1	204.6	202.8	201.7
115°	228.6	232.0	230.8	230.3	228.6
117.5°	255.4	260.0	257.1	255.4	253.7
120°	282.3	286.8	282.3	282.3	280.6
122.5°	306.8	312.6	309.7	308.0	306.8
125°	332.6	337.7	336.0	334.3	333.7
127.5°	357.7	364.0	361.7	359.4	357.7
130°	381.1	388.6	387.4	386.3	384.0
132.5°	407.4	413.1	413.7	410.8	409.1
135°	430.3	436.6	437.7	437.1	435.4
137.5°	455.4	460.5	461.7	461.1	458.8
140°	477.7	482.8	485.7	485.7	483.4
142.5°	500.5	505.7	507.4	508.0	505.7
145°	522.3	526.3	529.7	530.3	528.0
147.5°	541.7	546.8	549.1	550.3	548.0
150°	561.7	565.1	567.4	569.1	567.4
152.5°	579.4	582.8	585.7	588.0	585.7
155°	597.1	598.8	600.5	603.4	601.7
157.5°	612.5	613.7	614.8	618.8	616.0
160°	626.3	627.4	628.0	631.4	629.1
162.5°	638.8	638.8	639.4	643.4	640.5
165°	649.7	649.1	649.1	653.1	650.3
167.5°	659.4	657.7	657.7	661.7	658.8
170°	666.8	665.1	664.5	668.5	665.1
172.5°	672.0	670.3	669.7	673.7	670.3
175°	676.0	674.3	673.1	677.1	673.7
177.5°	678.3	676.5	675.4	678.8	675.4
180°	677.1	677.1	677.1	677.1	677.1

(END OF REPORT)