

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009780

Luminaire Tested: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1009780  
REPORT IS A COMBINATION OF REPORTS P987996 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4  
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}  
{m-EER=0.647}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7400.0 lumens  
Efficiency: N/A  
Efficacy: 82.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 89.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

### Luminous Intensity Polar Plot



TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |  |    |    |    |  |    |    |    |  |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|--|----|----|----|--|----|----|----|--|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    |  | 20 |    |    |  |    | 20 |    |  |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    |  | 50 |    |    |  |    | 30 |    |  |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 |  | 50 | 30 | 10 |  | 50 | 30 | 10 |  | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |  |    |    |    |  |    |    |    |  |    |    |    |
| 0   | 108 | 108 | 108 | 108 | 99 | 99 | 99 | 99 |  | 84 | 84 | 84 |  | 70 | 70 | 70 |  | 58 | 58 | 58 |
| 1   | 99  | 95  | 91  | 88  | 91 | 88 | 85 | 82 |  | 75 | 73 | 71 |  | 63 | 62 | 60 |  | 52 | 51 | 50 |
| 2   | 91  | 84  | 78  | 73  | 84 | 78 | 73 | 69 |  | 67 | 63 | 60 |  | 56 | 54 | 52 |  | 47 | 45 | 44 |
| 3   | 83  | 75  | 68  | 62  | 77 | 69 | 63 | 59 |  | 60 | 55 | 52 |  | 51 | 47 | 45 |  | 42 | 40 | 38 |
| 4   | 77  | 67  | 59  | 53  | 71 | 62 | 56 | 50 |  | 54 | 49 | 45 |  | 46 | 42 | 39 |  | 39 | 36 | 34 |
| 5   | 71  | 60  | 52  | 46  | 66 | 56 | 49 | 44 |  | 49 | 43 | 39 |  | 42 | 38 | 35 |  | 35 | 32 | 30 |
| 6   | 66  | 54  | 46  | 41  | 61 | 51 | 44 | 39 |  | 44 | 39 | 35 |  | 38 | 34 | 31 |  | 32 | 29 | 27 |
| 7   | 61  | 49  | 42  | 36  | 56 | 46 | 39 | 35 |  | 40 | 35 | 31 |  | 35 | 31 | 28 |  | 30 | 27 | 24 |
| 8   | 57  | 45  | 38  | 32  | 53 | 42 | 36 | 31 |  | 37 | 32 | 28 |  | 32 | 28 | 25 |  | 28 | 25 | 22 |
| 9   | 53  | 41  | 34  | 29  | 49 | 39 | 32 | 28 |  | 34 | 29 | 25 |  | 30 | 26 | 23 |  | 26 | 23 | 20 |
| 10  | 50  | 38  | 31  | 27  | 46 | 36 | 30 | 25 |  | 32 | 27 | 23 |  | 28 | 24 | 21 |  | 24 | 21 | 19 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 90°   | 180°  | 270°  |
|-----|-------|-------|-------|-------|
| 0°  | 34981 | 34981 | 34981 | 34981 |
| 5°  | 35062 | 37156 | 35184 | 29683 |
| 10° | 34677 | 39272 | 34923 | 24512 |
| 15° | 33925 | 39285 | 34499 | 18415 |
| 20° | 33019 | 32472 | 33737 | 15193 |
| 25° | 31922 | 20291 | 32611 | 12923 |
| 30° | 30521 | 12992 | 31351 | 11127 |
| 35° | 28816 | 9984  | 29748 | 9522  |
| 40° | 26916 | 8392  | 28068 | 8329  |
| 45° | 24887 | 7143  | 25926 | 6991  |
| 50° | 22806 | 6070  | 23870 | 6047  |
| 55° | 20502 | 5275  | 21607 | 5206  |
| 60° | 18453 | 4022  | 19433 | 3974  |
| 65° | 16541 | 3028  | 17526 | 3433  |
| 70° | 14434 | 2418  | 15565 | 2799  |
| 75° | 12201 | 1853  | 13314 | 2117  |
| 80° | 9684  | 1259  | 10419 | 1388  |
| 85° | 6724  | 649   | 7374  | 687   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 32000 cd/sqm

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 209.6  | 2.8       |
| 10°-20°   | 585.1  | 7.9       |
| 20°-30°   | 753.0  | 10.2      |
| 30°-40°   | 714.4  | 9.7       |
| 40°-50°   | 612.2  | 8.3       |
| 50°-60°   | 466.2  | 6.3       |
| 60°-70°   | 294.0  | 4.0       |
| 70°-80°   | 146.7  | 2.0       |
| 80°-90°   | 41.0   | 0.6       |
| 90°-100°  | 200.3  | 2.7       |
| 100°-110° | 705.3  | 9.5       |
| 110°-120° | 740.7  | 10.0      |
| 120°-130° | 609.4  | 8.2       |
| 130°-140° | 489.5  | 6.6       |
| 140°-150° | 369.8  | 5.0       |
| 150°-160° | 260.0  | 3.5       |
| 160°-170° | 153.0  | 2.1       |
| 170°-180° | 49.8   | 0.7       |
| 0°-30°    | 1547.7 | 20.9      |
| 0°-40°    | 2262.1 | 30.6      |
| 0°-60°    | 3340.6 | 45.1      |
| 0°-90°    | 3822.3 | 51.7      |
| 90°-120°  | 1646.3 | 22.2      |
| 90°-150°  | 3115.0 | 42.1      |
| 90°-180°  | 3578.0 | 48.4      |
| 0°-180°   | 7400.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 90°  | 180° | 270° | 360° | Flux |
|------|------|------|------|------|------|------|
| 0°   | 2210 | 2210 | 2210 | 2210 | 2210 |      |
| 5°   | 2211 | 2459 | 2219 | 1964 | 2211 | 210  |
| 15°  | 2084 | 2775 | 2119 | 1301 | 2084 | 586  |
| 25°  | 1849 | 1480 | 1889 | 943  | 1849 | 849  |
| 35°  | 1517 | 730  | 1566 | 696  | 1517 | 949  |
| 45°  | 1140 | 507  | 1187 | 496  | 1140 | 880  |
| 55°  | 769  | 352  | 811  | 347  | 769  | 693  |
| 65°  | 465  | 183  | 493  | 207  | 465  | 462  |
| 75°  | 218  | 97   | 238  | 111  | 218  | 236  |
| 85°  | 48   | 28   | 52   | 29   | 48   | 54   |
| 90°  | 1    | 33   | 1    | 33   | 1    | 5    |
| 95°  | 35   | 113  | 35   | 113  | 35   | 36   |
| 105° | 120  | 1113 | 120  | 1113 | 120  | 128  |
| 115° | 212  | 1465 | 212  | 1465 | 212  | 211  |
| 125° | 296  | 1188 | 296  | 1188 | 296  | 263  |
| 135° | 348  | 985  | 348  | 985  | 348  | 269  |
| 145° | 397  | 786  | 397  | 786  | 397  | 249  |
| 155° | 452  | 661  | 452  | 661  | 452  | 208  |
| 165° | 492  | 580  | 492  | 580  | 492  | 139  |
| 175° | 513  | 523  | 513  | 523  | 513  | 49   |
| 180° | 514  | 514  | 514  | 514  | 514  |      |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 5°     | 10°    | 15°    | 20°    | 22.5°  | 25°    | 30°    | 35°    | 40°    | 45°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 |
| 2.5°   | 2223.7 | 2232.9 | 2237.6 | 2243.7 | 2257.5 | 2266.7 | 2280.6 | 2283.6 | 2282.1 | 2288.2 | 2271.3 |
| 5°     | 2211.4 | 2231.4 | 2249.8 | 2265.2 | 2289.8 | 2305.1 | 2322.0 | 2342.0 | 2346.6 | 2369.6 | 2355.8 |
| 7.5°   | 2194.6 | 2223.7 | 2249.8 | 2280.6 | 2317.4 | 2337.4 | 2363.5 | 2394.2 | 2408.0 | 2435.7 | 2443.3 |
| 10°    | 2166.9 | 2208.4 | 2252.9 | 2285.2 | 2335.8 | 2371.2 | 2395.7 | 2444.9 | 2477.1 | 2518.6 | 2512.4 |
| 12.5°  | 2122.4 | 2176.1 | 2236.0 | 2289.8 | 2355.8 | 2378.8 | 2424.9 | 2475.6 | 2517.1 | 2555.4 | 2589.2 |
| 15°    | 2084.0 | 2145.4 | 2211.4 | 2277.5 | 2352.7 | 2395.7 | 2441.8 | 2507.8 | 2552.4 | 2619.9 | 2649.1 |
| 17.5°  | 2031.8 | 2110.1 | 2188.4 | 2262.1 | 2351.2 | 2400.3 | 2457.2 | 2521.7 | 2587.7 | 2652.2 | 2675.2 |
| 20°    | 1978.0 | 2062.5 | 2146.9 | 2246.8 | 2348.1 | 2395.7 | 2454.1 | 2533.9 | 2598.4 | 2649.1 | 2649.1 |
| 22.5°  | 1913.5 | 2016.4 | 2113.2 | 2208.4 | 2318.9 | 2388.1 | 2447.9 | 2541.6 | 2587.7 | 2598.4 | 2557.0 |
| 25°    | 1849.0 | 1951.9 | 2057.9 | 2176.1 | 2302.1 | 2363.5 | 2431.1 | 2518.6 | 2533.9 | 2490.9 | 2383.4 |
| 27.5°  | 1772.2 | 1887.4 | 2007.2 | 2134.7 | 2266.7 | 2343.5 | 2404.9 | 2463.3 | 2434.1 | 2318.9 | 2151.6 |
| 30°    | 1693.9 | 1818.3 | 1953.4 | 2074.8 | 2234.5 | 2305.1 | 2357.3 | 2374.2 | 2282.1 | 2094.7 | 1878.2 |
| 32.5°  | 1612.5 | 1733.8 | 1876.7 | 2022.6 | 2183.8 | 2251.4 | 2285.2 | 2240.6 | 2071.7 | 1835.2 | 1571.0 |
| 35°    | 1517.3 | 1654.0 | 1802.9 | 1955.0 | 2114.7 | 2165.4 | 2185.3 | 2076.3 | 1859.8 | 1554.2 | 1291.5 |
| 37.5°  | 1431.3 | 1568.0 | 1727.7 | 1882.8 | 2037.9 | 2065.6 | 2045.6 | 1875.1 | 1600.2 | 1297.7 | 1041.2 |
| 40°    | 1329.9 | 1475.8 | 1632.5 | 1806.0 | 1933.5 | 1941.2 | 1892.0 | 1670.9 | 1329.9 | 1045.8 | 887.7  |
| 42.5°  | 1236.3 | 1383.7 | 1540.3 | 1716.9 | 1813.7 | 1787.6 | 1721.5 | 1431.3 | 1110.3 | 901.5  | 774.0  |
| 45°    | 1139.5 | 1279.3 | 1448.2 | 1604.8 | 1673.9 | 1612.5 | 1512.7 | 1204.0 | 932.2  | 775.5  | 677.3  |
| 47.5°  | 1045.8 | 1176.4 | 1343.8 | 1494.3 | 1506.5 | 1437.4 | 1319.2 | 1009.0 | 807.8  | 681.9  | 602.0  |
| 50°    | 953.7  | 1084.2 | 1240.9 | 1365.3 | 1353.0 | 1257.8 | 1124.2 | 876.9  | 701.8  | 602.0  | 536.0  |
| 52.5°  | 861.5  | 979.8  | 1131.8 | 1230.1 | 1177.9 | 1085.8 | 953.7  | 743.3  | 612.8  | 525.2  | 474.5  |
| 55°    | 769.4  | 880.0  | 1010.5 | 1091.9 | 1009.0 | 903.0  | 809.3  | 637.3  | 531.4  | 460.7  | 422.3  |
| 57.5°  | 692.6  | 780.1  | 899.9  | 949.1  | 849.3  | 766.3  | 684.9  | 548.3  | 460.7  | 410.0  | 365.5  |
| 60°    | 608.1  | 688.0  | 786.3  | 815.5  | 712.6  | 645.0  | 575.9  | 463.8  | 394.7  | 350.1  | 321.0  |
| 62.5°  | 536.0  | 602.0  | 677.3  | 677.3  | 586.6  | 536.0  | 483.8  | 388.5  | 331.7  | 296.4  | 282.6  |
| 65°    | 465.3  | 512.9  | 566.7  | 560.5  | 483.8  | 439.2  | 397.8  | 321.0  | 278.0  | 253.4  | 239.6  |
| 67.5°  | 396.2  | 433.1  | 468.4  | 446.9  | 391.6  | 353.2  | 314.8  | 259.5  | 230.4  | 213.5  | 195.0  |
| 70°    | 333.3  | 362.4  | 380.9  | 360.9  | 305.6  | 273.4  | 245.7  | 208.9  | 185.8  | 164.3  | 153.6  |
| 72.5°  | 279.5  | 291.8  | 297.9  | 273.4  | 227.3  | 208.9  | 188.9  | 162.8  | 142.8  | 132.1  | 129.0  |
| 75°    | 218.1  | 228.8  | 224.2  | 205.8  | 167.4  | 153.6  | 138.2  | 119.8  | 115.2  | 109.0  | 106.0  |
| 77.5°  | 170.5  | 170.5  | 162.8  | 145.9  | 119.8  | 109.0  | 102.9  | 93.7   | 89.1   | 87.5   | 84.5   |
| 80°    | 121.3  | 119.8  | 115.2  | 96.8   | 81.4   | 75.3   | 75.3   | 69.1   | 67.6   | 64.5   | 64.5   |
| 82.5°  | 79.9   | 79.9   | 73.7   | 58.4   | 53.8   | 52.2   | 50.7   | 47.6   | 47.6   | 46.1   | 46.1   |
| 85°    | 47.6   | 44.5   | 36.9   | 32.3   | 30.7   | 30.7   | 29.2   | 27.6   | 29.2   | 27.6   | 27.6   |
| 87.5°  | 21.5   | 16.9   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   |
| 90°    | 1.0    | 4.0    | 7.9    | 9.9    | 11.9   | 13.4   | 14.8   | 19.8   | 26.7   | 32.6   | 33.6   |
| 92.5°  | 14.8   | 20.7   | 28.7   | 33.6   | 41.5   | 47.0   | 52.4   | 79.0   | 116.6  | 150.2  | 152.1  |
| 95°    | 34.6   | 38.5   | 48.4   | 57.3   | 73.1   | 84.9   | 96.8   | 142.3  | 228.2  | 342.8  | 387.3  |
| 97.5°  | 51.4   | 57.3   | 68.2   | 81.0   | 98.8   | 112.2  | 125.5  | 183.8  | 303.3  | 488.1  | 631.3  |
| 100°   | 76.1   | 79.0   | 87.9   | 103.7  | 123.5  | 137.4  | 151.2  | 203.5  | 324.1  | 537.5  | 780.5  |
| 102.5° | 98.8   | 100.8  | 109.7  | 125.5  | 146.2  | 160.0  | 173.9  | 221.3  | 325.0  | 518.7  | 785.4  |
| 105°   | 120.5  | 124.5  | 131.4  | 146.2  | 168.0  | 181.8  | 195.6  | 242.1  | 330.0  | 493.0  | 732.1  |
| 107.5° | 144.2  | 147.2  | 154.1  | 168.0  | 189.7  | 203.6  | 217.4  | 262.8  | 340.8  | 479.2  | 682.7  |
| 110°   | 168.0  | 171.9  | 177.8  | 190.7  | 211.4  | 225.8  | 240.1  | 283.5  | 354.7  | 475.2  | 649.1  |



TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 5°    | 10°   | 15°   | 20°   | 22.5° | 25°   | 30°   | 35°   | 40°   | 45°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 189.7 | 193.6 | 200.6 | 212.4 | 232.2 | 247.0 | 261.8 | 303.3 | 369.5 | 476.2 | 627.4 |
| 115°   | 212.4 | 217.4 | 223.3 | 235.1 | 254.9 | 268.2 | 281.6 | 324.1 | 384.3 | 480.1 | 612.5 |
| 117.5° | 236.1 | 240.1 | 246.0 | 256.9 | 275.6 | 289.5 | 303.3 | 342.8 | 400.1 | 486.1 | 604.6 |
| 120°   | 257.9 | 261.8 | 267.7 | 276.6 | 296.4 | 310.2 | 324.1 | 362.6 | 415.9 | 492.0 | 597.7 |
| 122.5° | 278.6 | 281.6 | 287.5 | 297.4 | 317.1 | 331.5 | 345.8 | 381.4 | 429.8 | 498.9 | 593.8 |
| 125°   | 296.4 | 299.4 | 305.3 | 317.1 | 336.9 | 350.8 | 364.6 | 400.1 | 444.6 | 505.8 | 588.8 |
| 127.5° | 311.2 | 315.2 | 323.1 | 335.9 | 354.7 | 369.0 | 383.3 | 417.9 | 458.4 | 512.8 | 585.9 |
| 130°   | 324.1 | 328.0 | 337.9 | 351.7 | 371.5 | 385.3 | 399.1 | 433.7 | 471.3 | 520.7 | 583.9 |
| 132.5° | 335.9 | 340.8 | 351.7 | 366.5 | 387.3 | 401.1 | 414.9 | 447.5 | 484.1 | 528.6 | 582.9 |
| 135°   | 347.8 | 351.7 | 363.6 | 378.4 | 401.1 | 415.0 | 428.8 | 460.4 | 495.0 | 534.5 | 581.9 |
| 137.5° | 358.6 | 363.6 | 375.4 | 391.2 | 414.0 | 426.8 | 439.6 | 471.3 | 503.9 | 540.4 | 581.9 |
| 140°   | 371.5 | 375.4 | 387.3 | 403.1 | 424.8 | 437.6 | 450.5 | 480.1 | 510.8 | 544.4 | 580.9 |
| 142.5° | 384.3 | 387.3 | 398.1 | 414.0 | 434.7 | 446.6 | 458.4 | 487.1 | 516.7 | 547.3 | 580.9 |
| 145°   | 397.2 | 401.1 | 411.0 | 425.8 | 445.6 | 456.4 | 467.3 | 494.0 | 521.6 | 549.3 | 578.9 |
| 147.5° | 411.0 | 414.0 | 423.8 | 437.7 | 454.5 | 464.4 | 474.2 | 499.9 | 524.6 | 550.3 | 576.0 |
| 150°   | 424.8 | 427.8 | 435.7 | 448.5 | 463.4 | 472.2 | 481.1 | 503.9 | 526.6 | 549.3 | 573.0 |
| 152.5° | 438.7 | 439.6 | 447.5 | 458.4 | 472.2 | 480.2 | 488.1 | 507.8 | 527.6 | 547.3 | 568.1 |
| 155°   | 451.5 | 452.5 | 458.4 | 469.3 | 480.1 | 487.6 | 495.0 | 511.8 | 528.6 | 545.4 | 562.2 |
| 157.5° | 462.4 | 463.4 | 468.3 | 478.2 | 487.1 | 493.5 | 499.9 | 514.7 | 528.6 | 541.4 | 556.2 |
| 160°   | 473.2 | 474.2 | 478.2 | 486.1 | 494.0 | 499.4 | 504.8 | 516.7 | 528.6 | 538.4 | 550.3 |
| 162.5° | 484.1 | 483.1 | 487.1 | 493.0 | 499.9 | 503.8 | 507.8 | 517.7 | 527.6 | 535.5 | 545.4 |
| 165°   | 492.0 | 491.0 | 493.0 | 498.9 | 503.9 | 506.8 | 509.8 | 518.7 | 525.6 | 531.5 | 538.4 |
| 167.5° | 498.9 | 497.9 | 499.9 | 503.9 | 507.8 | 509.8 | 511.8 | 518.7 | 524.6 | 527.6 | 532.5 |
| 170°   | 505.8 | 503.9 | 504.8 | 507.8 | 509.8 | 511.3 | 512.8 | 517.7 | 522.6 | 524.6 | 527.6 |
| 172.5° | 509.8 | 508.8 | 507.8 | 510.8 | 511.8 | 512.8 | 513.7 | 516.7 | 519.7 | 520.7 | 521.6 |
| 175°   | 512.8 | 511.8 | 510.8 | 512.8 | 512.8 | 513.2 | 513.7 | 515.7 | 517.7 | 516.7 | 517.7 |
| 177.5° | 514.7 | 512.8 | 511.8 | 513.7 | 513.7 | 513.7 | 513.7 | 514.7 | 516.7 | 514.7 | 513.7 |
| 180°   | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 50°    | 55°    | 60°    | 65°    | 67.5°  | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 |
| 2.5°   | 2288.2 | 2291.3 | 2295.9 | 2317.4 | 2320.5 | 2326.6 | 2323.6 | 2323.6 | 2325.1 | 2322.0 | 2323.6 |
| 5°     | 2386.5 | 2391.1 | 2414.2 | 2440.3 | 2446.4 | 2440.3 | 2447.9 | 2458.7 | 2458.7 | 2458.7 | 2455.6 |
| 7.5°   | 2478.7 | 2495.6 | 2521.7 | 2560.1 | 2567.7 | 2575.4 | 2589.2 | 2580.0 | 2583.1 | 2596.9 | 2592.3 |
| 10°    | 2567.7 | 2592.3 | 2621.5 | 2653.7 | 2670.6 | 2681.4 | 2687.5 | 2701.3 | 2733.6 | 2696.7 | 2710.6 |
| 12.5°  | 2652.2 | 2687.5 | 2718.2 | 2753.6 | 2765.8 | 2779.7 | 2784.3 | 2796.6 | 2796.6 | 2795.0 | 2805.8 |
| 15°    | 2707.5 | 2739.7 | 2767.4 | 2790.4 | 2793.5 | 2790.4 | 2787.3 | 2788.9 | 2793.5 | 2775.1 | 2785.8 |
| 17.5°  | 2719.8 | 2722.8 | 2732.1 | 2722.8 | 2724.4 | 2692.1 | 2673.7 | 2669.1 | 2626.1 | 2627.6 | 2663.0 |
| 20°    | 2659.9 | 2607.7 | 2593.8 | 2543.2 | 2512.4 | 2429.5 | 2426.4 | 2403.4 | 2312.8 | 2340.4 | 2334.3 |
| 22.5°  | 2495.6 | 2406.5 | 2288.2 | 2229.9 | 2200.7 | 2113.2 | 2045.6 | 1998.0 | 1965.7 | 1933.5 | 1919.7 |
| 25°    | 2279.0 | 2134.7 | 1967.3 | 1852.1 | 1835.2 | 1753.8 | 1629.4 | 1571.0 | 1501.9 | 1480.4 | 1517.3 |
| 27.5°  | 1999.5 | 1812.2 | 1623.3 | 1446.7 | 1414.4 | 1340.7 | 1277.7 | 1236.3 | 1156.4 | 1151.8 | 1154.9 |
| 30°    | 1620.2 | 1431.3 | 1273.1 | 1157.9 | 1078.1 | 1044.3 | 1002.8 | 972.1  | 939.9  | 952.2  | 955.2  |
| 32.5°  | 1331.5 | 1151.8 | 1004.4 | 942.9  | 906.1  | 884.6  | 849.3  | 829.3  | 815.5  | 810.9  | 809.3  |
| 35°    | 1058.1 | 938.3  | 872.3  | 812.4  | 790.9  | 775.5  | 749.4  | 740.2  | 727.9  | 729.5  | 729.5  |
| 37.5°  | 906.1  | 806.3  | 757.1  | 726.4  | 706.4  | 698.8  | 681.9  | 672.6  | 665.0  | 661.9  | 666.5  |
| 40°    | 781.7  | 712.6  | 681.9  | 654.2  | 637.3  | 634.3  | 625.0  | 614.3  | 605.1  | 606.6  | 611.2  |
| 42.5°  | 691.1  | 651.1  | 614.3  | 592.8  | 580.5  | 575.9  | 568.2  | 560.5  | 560.5  | 555.9  | 554.4  |
| 45°    | 618.9  | 586.6  | 555.9  | 536.0  | 528.3  | 522.1  | 512.9  | 511.4  | 505.3  | 506.8  | 508.3  |
| 47.5°  | 554.4  | 528.3  | 505.3  | 485.3  | 477.6  | 476.1  | 466.9  | 460.7  | 460.7  | 459.2  | 457.6  |
| 50°    | 496.0  | 469.9  | 450.0  | 439.2  | 428.5  | 425.4  | 423.9  | 422.3  | 419.3  | 419.3  | 420.8  |
| 52.5°  | 448.4  | 422.3  | 407.0  | 397.8  | 391.6  | 388.5  | 388.5  | 387.0  | 387.0  | 387.0  | 385.5  |
| 55°    | 396.2  | 374.7  | 362.4  | 359.4  | 356.3  | 354.8  | 353.2  | 350.1  | 348.6  | 351.7  | 348.6  |
| 57.5°  | 347.1  | 339.4  | 328.6  | 325.6  | 317.9  | 317.9  | 313.3  | 310.2  | 307.1  | 310.2  | 310.2  |
| 60°    | 308.7  | 297.9  | 291.8  | 282.6  | 276.4  | 270.3  | 262.6  | 261.1  | 258.0  | 256.5  | 254.9  |
| 62.5°  | 268.8  | 259.5  | 244.2  | 230.4  | 221.1  | 215.0  | 211.9  | 210.4  | 210.4  | 208.9  | 208.9  |
| 65°    | 224.2  | 202.7  | 195.0  | 190.4  | 188.9  | 187.4  | 184.3  | 182.8  | 184.3  | 182.8  | 184.3  |
| 67.5°  | 175.1  | 172.0  | 167.4  | 164.3  | 162.8  | 161.3  | 161.3  | 159.7  | 159.7  | 159.7  | 159.7  |
| 70°    | 152.0  | 144.4  | 142.8  | 139.8  | 139.8  | 138.2  | 138.2  | 138.2  | 138.2  | 136.7  | 139.8  |
| 72.5°  | 125.9  | 121.3  | 119.8  | 118.3  | 118.3  | 118.3  | 116.7  | 116.7  | 116.7  | 115.2  | 116.7  |
| 75°    | 102.9  | 101.4  | 98.3   | 98.3   | 96.8   | 98.3   | 96.8   | 96.8   | 95.2   | 96.8   | 96.8   |
| 77.5°  | 82.9   | 81.4   | 79.9   | 79.9   | 78.3   | 78.3   | 78.3   | 78.3   | 78.3   | 78.3   | 79.9   |
| 80°    | 63.0   | 61.4   | 59.9   | 61.4   | 59.9   | 61.4   | 59.9   | 59.9   | 61.4   | 59.9   | 59.9   |
| 82.5°  | 46.1   | 44.5   | 44.5   | 43.0   | 43.0   | 43.0   | 43.0   | 43.0   | 43.0   | 43.0   | 43.0   |
| 85°    | 27.6   | 26.1   | 26.1   | 27.6   | 26.1   | 27.6   | 26.1   | 26.1   | 26.1   | 27.6   | 27.6   |
| 87.5°  | 12.3   | 13.8   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   | 12.3   | 13.8   |
| 90°    | 32.6   | 31.6   | 29.6   | 31.6   | 32.1   | 32.6   | 32.6   | 32.6   | 32.6   | 32.6   | 32.6   |
| 92.5°  | 127.4  | 99.8   | 85.0   | 74.1   | 70.2   | 66.2   | 65.2   | 61.3   | 62.2   | 60.3   | 62.2   |
| 95°    | 338.9  | 258.8  | 198.6  | 157.1  | 146.2  | 135.4  | 122.5  | 114.6  | 111.6  | 112.6  | 111.6  |
| 97.5°  | 636.2  | 529.5  | 422.8  | 323.1  | 293.5  | 263.8  | 225.3  | 205.5  | 194.6  | 188.7  | 194.6  |
| 100°   | 922.8  | 902.0  | 779.5  | 644.2  | 584.4  | 524.6  | 442.6  | 400.1  | 371.5  | 353.7  | 371.5  |
| 102.5° | 1029.5 | 1146.0 | 1142.1 | 1052.2 | 988.0  | 923.7  | 832.9  | 752.8  | 715.3  | 689.6  | 715.3  |
| 105°   | 994.9  | 1200.4 | 1312.0 | 1324.9 | 1308.6 | 1292.3 | 1231.0 | 1169.7 | 1127.3 | 1113.4 | 1127.3 |
| 107.5° | 921.8  | 1142.1 | 1308.1 | 1404.9 | 1424.6 | 1444.4 | 1443.4 | 1434.5 | 1421.7 | 1399.0 | 1421.7 |
| 110°   | 853.6  | 1062.1 | 1238.9 | 1365.4 | 1405.9 | 1446.4 | 1488.9 | 1507.6 | 1516.5 | 1515.5 | 1516.5 |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 50°   | 55°   | 60°    | 65°    | 67.5°  | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    |
|--------|-------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 806.2 | 988.9 | 1156.9 | 1294.2 | 1342.2 | 1390.1 | 1453.3 | 1487.9 | 1506.6 | 1513.6 | 1506.6 |
| 115°   | 768.6 | 931.6 | 1083.8 | 1213.2 | 1264.1 | 1315.0 | 1385.1 | 1430.6 | 1456.3 | 1465.1 | 1456.3 |
| 117.5° | 742.9 | 884.2 | 1020.6 | 1141.1 | 1189.5 | 1237.9 | 1310.0 | 1358.4 | 1385.1 | 1392.0 | 1385.1 |
| 120°   | 723.2 | 850.6 | 973.1  | 1077.9 | 1122.8 | 1167.8 | 1236.9 | 1283.4 | 1312.0 | 1321.9 | 1312.0 |
| 122.5° | 706.4 | 824.0 | 933.6  | 1031.4 | 1071.0 | 1110.5 | 1170.7 | 1216.2 | 1240.9 | 1248.8 | 1240.9 |
| 125°   | 690.6 | 798.3 | 900.0  | 987.0  | 1024.0 | 1061.1 | 1118.4 | 1155.9 | 1180.6 | 1188.5 | 1180.6 |
| 127.5° | 675.8 | 772.6 | 866.4  | 949.4  | 984.0  | 1018.6 | 1069.0 | 1104.5 | 1126.3 | 1132.2 | 1126.3 |
| 130°   | 660.9 | 747.9 | 832.9  | 910.9  | 943.5  | 976.1  | 1024.5 | 1058.1 | 1077.9 | 1085.8 | 1077.9 |
| 132.5° | 649.1 | 724.2 | 801.2  | 871.4  | 901.5  | 931.6  | 979.1  | 1012.7 | 1030.4 | 1037.4 | 1030.4 |
| 135°   | 638.2 | 702.4 | 767.6  | 832.9  | 860.6  | 888.2  | 930.7  | 963.3  | 981.0  | 985.0  | 981.0  |
| 137.5° | 630.3 | 684.7 | 741.0  | 794.3  | 819.0  | 843.7  | 884.2  | 912.9  | 928.7  | 934.6  | 928.7  |
| 140°   | 623.4 | 667.9 | 715.3  | 760.7  | 782.4  | 804.2  | 835.8  | 861.5  | 876.3  | 882.2  | 876.3  |
| 142.5° | 616.5 | 654.0 | 692.6  | 730.1  | 747.4  | 764.7  | 794.3  | 817.0  | 829.9  | 829.9  | 829.9  |
| 145°   | 610.6 | 641.2 | 673.8  | 704.4  | 718.8  | 733.1  | 756.8  | 773.6  | 783.5  | 786.4  | 783.5  |
| 147.5° | 604.6 | 631.3 | 658.0  | 682.7  | 693.6  | 704.4  | 725.2  | 739.0  | 745.9  | 747.9  | 745.9  |
| 150°   | 596.7 | 620.4 | 642.2  | 662.9  | 671.8  | 680.7  | 695.5  | 707.4  | 713.3  | 714.3  | 713.3  |
| 152.5° | 589.8 | 609.6 | 629.3  | 646.1  | 653.5  | 660.9  | 671.8  | 681.7  | 685.6  | 685.6  | 685.6  |
| 155°   | 580.9 | 599.7 | 615.5  | 630.3  | 635.8  | 641.2  | 652.1  | 659.0  | 662.9  | 660.9  | 662.9  |
| 157.5° | 573.0 | 587.8 | 601.7  | 614.5  | 619.0  | 623.4  | 631.3  | 637.2  | 639.2  | 639.2  | 639.2  |
| 160°   | 564.1 | 577.0 | 587.8  | 598.7  | 602.2  | 605.6  | 612.5  | 617.5  | 618.5  | 618.5  | 618.5  |
| 162.5° | 556.2 | 566.1 | 575.0  | 583.9  | 586.3  | 588.8  | 595.7  | 598.7  | 599.7  | 598.7  | 599.7  |
| 165°   | 547.3 | 555.2 | 562.2  | 569.1  | 571.0  | 573.0  | 577.0  | 580.9  | 580.9  | 579.9  | 580.9  |
| 167.5° | 538.4 | 544.4 | 550.3  | 555.2  | 557.2  | 559.2  | 561.2  | 563.1  | 563.1  | 562.2  | 563.1  |
| 170°   | 531.5 | 536.5 | 539.4  | 543.4  | 544.4  | 545.4  | 546.3  | 549.3  | 548.3  | 546.3  | 548.3  |
| 172.5° | 524.6 | 527.6 | 529.5  | 532.5  | 533.0  | 533.5  | 534.5  | 535.5  | 534.5  | 533.5  | 534.5  |
| 175°   | 518.7 | 521.6 | 522.6  | 523.6  | 524.1  | 524.6  | 524.6  | 525.6  | 524.6  | 522.6  | 524.6  |
| 177.5° | 514.7 | 516.7 | 516.7  | 517.7  | 517.7  | 517.7  | 517.7  | 517.7  | 516.7  | 514.7  | 516.7  |
| 180°   | 513.7 | 513.7 | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 100°   | 105°   | 110°   | 112.5° | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 |
| 2.5°   | 2329.7 | 2318.9 | 2315.9 | 2318.9 | 2315.9 | 2317.4 | 2306.7 | 2266.7 | 2277.5 | 2260.6 | 2269.8 |
| 5°     | 2461.8 | 2452.6 | 2432.6 | 2429.5 | 2426.4 | 2423.4 | 2408.0 | 2372.7 | 2358.9 | 2335.8 | 2334.3 |
| 7.5°   | 2587.7 | 2587.7 | 2572.3 | 2561.6 | 2547.8 | 2537.0 | 2517.1 | 2464.8 | 2443.3 | 2415.7 | 2400.3 |
| 10°    | 2712.1 | 2672.2 | 2689.1 | 2678.3 | 2644.5 | 2638.4 | 2601.5 | 2570.8 | 2529.3 | 2501.7 | 2477.1 |
| 12.5°  | 2801.2 | 2788.9 | 2773.5 | 2764.3 | 2755.1 | 2735.1 | 2710.6 | 2632.2 | 2610.7 | 2555.4 | 2527.8 |
| 15°    | 2798.1 | 2790.4 | 2795.0 | 2795.0 | 2792.0 | 2787.3 | 2767.4 | 2710.6 | 2673.7 | 2619.9 | 2572.3 |
| 17.5°  | 2647.6 | 2667.6 | 2687.5 | 2701.3 | 2732.1 | 2745.9 | 2764.3 | 2730.5 | 2707.5 | 2661.4 | 2610.7 |
| 20°    | 2385.0 | 2434.1 | 2492.5 | 2504.8 | 2532.4 | 2613.8 | 2650.7 | 2679.8 | 2689.1 | 2673.7 | 2632.2 |
| 22.5°  | 2019.5 | 2060.9 | 2202.2 | 2199.2 | 2239.1 | 2335.8 | 2443.3 | 2530.9 | 2600.0 | 2638.4 | 2623.0 |
| 25°    | 1581.8 | 1640.2 | 1715.4 | 1772.2 | 1902.8 | 2047.1 | 2180.7 | 2320.5 | 2440.3 | 2546.2 | 2572.3 |
| 27.5°  | 1196.3 | 1273.1 | 1333.0 | 1408.3 | 1474.3 | 1644.8 | 1816.8 | 2034.8 | 2174.6 | 2375.8 | 2480.2 |
| 30°    | 967.5  | 1002.8 | 1062.7 | 1098.0 | 1130.3 | 1260.8 | 1455.9 | 1670.9 | 1916.6 | 2148.5 | 2328.2 |
| 32.5°  | 826.2  | 850.8  | 895.3  | 910.7  | 944.5  | 1032.0 | 1154.9 | 1351.4 | 1604.8 | 1885.9 | 2122.4 |
| 35°    | 741.8  | 767.9  | 777.1  | 790.9  | 818.5  | 873.8  | 958.3  | 1101.1 | 1329.9 | 1604.8 | 1887.4 |
| 37.5°  | 669.6  | 683.4  | 709.5  | 718.7  | 727.9  | 769.4  | 826.2  | 926.0  | 1078.1 | 1303.8 | 1617.1 |
| 40°    | 618.9  | 626.6  | 640.4  | 648.1  | 654.2  | 683.4  | 734.1  | 801.6  | 913.8  | 1085.8 | 1374.5 |
| 42.5°  | 565.1  | 574.4  | 583.6  | 592.8  | 600.5  | 623.5  | 654.2  | 718.7  | 794.0  | 924.5  | 1133.4 |
| 45°    | 512.9  | 519.1  | 529.8  | 536.0  | 546.7  | 565.1  | 592.8  | 637.3  | 704.9  | 787.8  | 956.8  |
| 47.5°  | 465.3  | 473.0  | 477.6  | 485.3  | 493.0  | 512.9  | 539.0  | 568.2  | 623.5  | 704.9  | 827.8  |
| 50°    | 422.3  | 431.5  | 437.7  | 439.2  | 445.4  | 463.8  | 485.3  | 517.5  | 552.9  | 615.8  | 723.3  |
| 52.5°  | 391.6  | 393.1  | 397.8  | 403.9  | 402.4  | 413.1  | 433.1  | 457.6  | 494.5  | 545.2  | 623.5  |
| 55°    | 356.3  | 360.9  | 364.0  | 365.5  | 365.5  | 374.7  | 385.5  | 408.5  | 437.7  | 479.1  | 545.2  |
| 57.5°  | 311.8  | 316.4  | 325.6  | 328.6  | 333.3  | 337.9  | 342.5  | 357.8  | 382.4  | 422.3  | 476.1  |
| 60°    | 265.7  | 268.8  | 278.0  | 284.1  | 287.2  | 299.5  | 305.6  | 317.9  | 331.7  | 360.9  | 411.6  |
| 62.5°  | 213.5  | 216.5  | 221.1  | 227.3  | 233.4  | 251.9  | 267.2  | 279.5  | 290.3  | 310.2  | 351.7  |
| 65°    | 185.8  | 187.4  | 190.4  | 192.0  | 193.5  | 201.2  | 215.0  | 231.9  | 251.9  | 267.2  | 291.8  |
| 67.5°  | 161.3  | 162.8  | 164.3  | 167.4  | 168.9  | 170.5  | 176.6  | 181.2  | 201.2  | 222.7  | 241.1  |
| 70°    | 138.2  | 141.3  | 142.8  | 142.8  | 144.4  | 147.4  | 150.5  | 156.6  | 162.8  | 173.5  | 196.6  |
| 72.5°  | 116.7  | 118.3  | 121.3  | 121.3  | 121.3  | 124.4  | 127.5  | 130.5  | 133.6  | 139.8  | 149.0  |
| 75°    | 96.8   | 99.8   | 99.8   | 99.8   | 101.4  | 101.4  | 104.4  | 107.5  | 110.6  | 115.2  | 118.3  |
| 77.5°  | 79.9   | 79.9   | 79.9   | 79.9   | 81.4   | 81.4   | 82.9   | 86.0   | 87.5   | 89.1   | 92.1   |
| 80°    | 59.9   | 61.4   | 61.4   | 61.4   | 63.0   | 63.0   | 63.0   | 66.0   | 67.6   | 67.6   | 70.6   |
| 82.5°  | 44.5   | 44.5   | 44.5   | 46.1   | 44.5   | 46.1   | 46.1   | 47.6   | 46.1   | 47.6   | 49.1   |
| 85°    | 27.6   | 27.6   | 27.6   | 29.2   | 29.2   | 29.2   | 29.2   | 29.2   | 29.2   | 29.2   | 30.7   |
| 87.5°  | 13.8   | 13.8   | 13.8   | 13.8   | 13.8   | 13.8   | 13.8   | 13.8   | 15.4   | 13.8   | 13.8   |
| 90°    | 32.6   | 32.6   | 32.6   | 32.1   | 31.6   | 29.6   | 31.6   | 32.6   | 33.6   | 32.6   | 26.7   |
| 92.5°  | 61.3   | 65.2   | 66.2   | 70.2   | 74.1   | 85.0   | 99.8   | 127.4  | 152.1  | 150.2  | 116.6  |
| 95°    | 114.6  | 122.5  | 135.4  | 146.2  | 157.1  | 198.6  | 258.8  | 338.9  | 387.3  | 342.8  | 228.2  |
| 97.5°  | 205.5  | 225.3  | 263.8  | 293.5  | 323.1  | 422.8  | 529.5  | 636.2  | 631.3  | 488.1  | 303.3  |
| 100°   | 400.1  | 442.6  | 524.6  | 584.4  | 644.2  | 779.5  | 902.0  | 922.8  | 780.5  | 537.5  | 324.1  |
| 102.5° | 752.8  | 832.9  | 923.7  | 988.0  | 1052.2 | 1142.1 | 1146.0 | 1029.5 | 785.4  | 518.7  | 325.0  |
| 105°   | 1169.7 | 1231.0 | 1292.3 | 1308.6 | 1324.9 | 1312.0 | 1200.4 | 994.9  | 732.1  | 493.0  | 330.0  |
| 107.5° | 1434.5 | 1443.4 | 1444.4 | 1424.6 | 1404.9 | 1308.1 | 1142.1 | 921.8  | 682.7  | 479.2  | 340.8  |
| 110°   | 1507.6 | 1488.9 | 1446.4 | 1405.9 | 1365.4 | 1238.9 | 1062.1 | 853.6  | 649.1  | 475.2  | 354.7  |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 100°   | 105°   | 110°   | 112.5° | 115°   | 120°   | 125°  | 130°  | 135°  | 140°  | 145°  |
|--------|--------|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|
| 112.5° | 1487.9 | 1453.3 | 1390.1 | 1342.2 | 1294.2 | 1156.9 | 988.9 | 806.2 | 627.4 | 476.2 | 369.5 |
| 115°   | 1430.6 | 1385.1 | 1315.0 | 1264.1 | 1213.2 | 1083.8 | 931.6 | 768.6 | 612.5 | 480.1 | 384.3 |
| 117.5° | 1358.4 | 1310.0 | 1237.9 | 1189.5 | 1141.1 | 1020.6 | 884.2 | 742.9 | 604.6 | 486.1 | 400.1 |
| 120°   | 1283.4 | 1236.9 | 1167.8 | 1122.8 | 1077.9 | 973.1  | 850.6 | 723.2 | 597.7 | 492.0 | 415.9 |
| 122.5° | 1216.2 | 1170.7 | 1110.5 | 1071.0 | 1031.4 | 933.6  | 824.0 | 706.4 | 593.8 | 498.9 | 429.8 |
| 125°   | 1155.9 | 1118.4 | 1061.1 | 1024.0 | 987.0  | 900.0  | 798.3 | 690.6 | 588.8 | 505.8 | 444.6 |
| 127.5° | 1104.5 | 1069.0 | 1018.6 | 984.0  | 949.4  | 866.4  | 772.6 | 675.8 | 585.9 | 512.8 | 458.4 |
| 130°   | 1058.1 | 1024.5 | 976.1  | 943.5  | 910.9  | 832.9  | 747.9 | 660.9 | 583.9 | 520.7 | 471.3 |
| 132.5° | 1012.7 | 979.1  | 931.6  | 901.5  | 871.4  | 801.2  | 724.2 | 649.1 | 582.9 | 528.6 | 484.1 |
| 135°   | 963.3  | 930.7  | 888.2  | 860.6  | 832.9  | 767.6  | 702.4 | 638.2 | 581.9 | 534.5 | 495.0 |
| 137.5° | 912.9  | 884.2  | 843.7  | 819.0  | 794.3  | 741.0  | 684.7 | 630.3 | 581.9 | 540.4 | 503.9 |
| 140°   | 861.5  | 835.8  | 804.2  | 782.4  | 760.7  | 715.3  | 667.9 | 623.4 | 580.9 | 544.4 | 510.8 |
| 142.5° | 817.0  | 794.3  | 764.7  | 747.4  | 730.1  | 692.6  | 654.0 | 616.5 | 580.9 | 547.3 | 516.7 |
| 145°   | 773.6  | 756.8  | 733.1  | 718.8  | 704.4  | 673.8  | 641.2 | 610.6 | 578.9 | 549.3 | 521.6 |
| 147.5° | 739.0  | 725.2  | 704.4  | 693.6  | 682.7  | 658.0  | 631.3 | 604.6 | 576.0 | 550.3 | 524.6 |
| 150°   | 707.4  | 695.5  | 680.7  | 671.8  | 662.9  | 642.2  | 620.4 | 596.7 | 573.0 | 549.3 | 526.6 |
| 152.5° | 681.7  | 671.8  | 660.9  | 653.5  | 646.1  | 629.3  | 609.6 | 589.8 | 568.1 | 547.3 | 527.6 |
| 155°   | 659.0  | 652.1  | 641.2  | 635.8  | 630.3  | 615.5  | 599.7 | 580.9 | 562.2 | 545.4 | 528.6 |
| 157.5° | 637.2  | 631.3  | 623.4  | 619.0  | 614.5  | 601.7  | 587.8 | 573.0 | 556.2 | 541.4 | 528.6 |
| 160°   | 617.5  | 612.5  | 605.6  | 602.2  | 598.7  | 587.8  | 577.0 | 564.1 | 550.3 | 538.4 | 528.6 |
| 162.5° | 598.7  | 595.7  | 588.8  | 586.3  | 583.9  | 575.0  | 566.1 | 556.2 | 545.4 | 535.5 | 527.6 |
| 165°   | 580.9  | 577.0  | 573.0  | 571.0  | 569.1  | 562.2  | 555.2 | 547.3 | 538.4 | 531.5 | 525.6 |
| 167.5° | 563.1  | 561.2  | 559.2  | 557.2  | 555.2  | 550.3  | 544.4 | 538.4 | 532.5 | 527.6 | 524.6 |
| 170°   | 549.3  | 546.3  | 545.4  | 544.4  | 543.4  | 539.4  | 536.5 | 531.5 | 527.6 | 524.6 | 522.6 |
| 172.5° | 535.5  | 534.5  | 533.5  | 533.0  | 532.5  | 529.5  | 527.6 | 524.6 | 521.6 | 520.7 | 519.7 |
| 175°   | 525.6  | 524.6  | 524.6  | 524.1  | 523.6  | 522.6  | 521.6 | 518.7 | 517.7 | 516.7 | 517.7 |
| 177.5° | 517.7  | 517.7  | 517.7  | 517.7  | 517.7  | 516.7  | 516.7 | 514.7 | 513.7 | 514.7 | 516.7 |
| 180°   | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 150°   | 155°   | 157.5° | 160°   | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 |
| 2.5°   | 2256.0 | 2248.3 | 2248.3 | 2243.7 | 2243.7 | 2219.1 | 2219.1 | 2226.8 | 2217.6 | 2206.8 | 2191.5 |
| 5°     | 2314.3 | 2297.4 | 2292.8 | 2286.7 | 2266.7 | 2236.0 | 2223.7 | 2219.1 | 2200.7 | 2177.7 | 2151.6 |
| 7.5°   | 2369.6 | 2342.0 | 2328.2 | 2314.3 | 2288.2 | 2245.2 | 2220.7 | 2203.8 | 2176.1 | 2140.8 | 2107.0 |
| 10°    | 2423.4 | 2388.1 | 2352.7 | 2335.8 | 2299.0 | 2245.2 | 2209.9 | 2182.3 | 2142.3 | 2094.7 | 2047.1 |
| 12.5°  | 2472.5 | 2398.8 | 2392.7 | 2358.9 | 2305.1 | 2243.7 | 2189.9 | 2150.0 | 2099.3 | 2044.1 | 1988.8 |
| 15°    | 2515.5 | 2440.3 | 2403.4 | 2372.7 | 2302.1 | 2225.3 | 2168.4 | 2119.3 | 2051.7 | 1988.8 | 1921.2 |
| 17.5°  | 2537.0 | 2455.6 | 2431.1 | 2380.4 | 2308.2 | 2208.4 | 2131.6 | 2071.7 | 1998.0 | 1922.7 | 1845.9 |
| 20°    | 2558.5 | 2463.3 | 2423.4 | 2388.1 | 2289.8 | 2176.1 | 2090.1 | 2021.0 | 1939.6 | 1850.6 | 1766.1 |
| 22.5°  | 2569.3 | 2463.3 | 2415.7 | 2366.6 | 2271.3 | 2140.8 | 2039.4 | 1958.1 | 1862.8 | 1772.2 | 1670.9 |
| 25°    | 2550.8 | 2454.1 | 2397.3 | 2346.6 | 2239.1 | 2097.8 | 1981.1 | 1888.9 | 1787.6 | 1684.7 | 1581.8 |
| 27.5°  | 2504.8 | 2432.6 | 2366.6 | 2314.3 | 2194.6 | 2042.5 | 1919.7 | 1815.2 | 1710.8 | 1595.6 | 1491.2 |
| 30°    | 2418.8 | 2386.5 | 2334.3 | 2275.9 | 2145.4 | 1993.4 | 1847.5 | 1740.0 | 1624.8 | 1509.6 | 1400.6 |
| 32.5°  | 2285.2 | 2312.8 | 2279.0 | 2228.3 | 2087.1 | 1925.8 | 1770.7 | 1661.7 | 1535.7 | 1411.3 | 1311.5 |
| 35°    | 2122.4 | 2220.7 | 2202.2 | 2166.9 | 2025.6 | 1853.6 | 1698.5 | 1566.4 | 1440.5 | 1314.6 | 1214.8 |
| 37.5°  | 1944.2 | 2093.2 | 2108.6 | 2087.1 | 1955.0 | 1779.9 | 1609.4 | 1480.4 | 1351.4 | 1224.0 | 1122.6 |
| 40°    | 1700.0 | 1928.9 | 1978.0 | 1987.2 | 1881.3 | 1690.8 | 1512.7 | 1386.8 | 1259.3 | 1134.9 | 1012.0 |
| 42.5°  | 1475.8 | 1764.5 | 1826.0 | 1864.4 | 1787.6 | 1603.3 | 1423.6 | 1283.9 | 1157.9 | 1045.8 | 923.0  |
| 45°    | 1265.4 | 1566.4 | 1666.3 | 1715.4 | 1681.6 | 1503.5 | 1317.7 | 1187.1 | 1071.9 | 969.0  | 850.8  |
| 47.5°  | 1048.9 | 1351.4 | 1491.2 | 1569.5 | 1569.5 | 1402.1 | 1216.3 | 1087.3 | 976.7  | 889.2  | 784.8  |
| 50°    | 904.5  | 1156.4 | 1300.8 | 1403.7 | 1431.3 | 1299.2 | 1124.2 | 998.2  | 893.8  | 798.6  | 718.7  |
| 52.5°  | 770.9  | 996.7  | 1116.5 | 1224.0 | 1303.8 | 1188.7 | 1021.3 | 907.6  | 804.7  | 715.6  | 652.7  |
| 55°    | 666.5  | 835.4  | 944.5  | 1062.7 | 1151.8 | 1076.5 | 921.4  | 810.9  | 721.8  | 648.1  | 594.3  |
| 57.5°  | 566.7  | 714.1  | 803.2  | 907.6  | 1002.8 | 946.0  | 821.6  | 726.4  | 648.1  | 583.6  | 536.0  |
| 60°    | 482.2  | 602.0  | 671.1  | 752.5  | 870.8  | 830.8  | 727.9  | 640.4  | 577.4  | 519.1  | 479.1  |
| 62.5°  | 410.0  | 505.3  | 563.6  | 622.0  | 729.5  | 711.0  | 631.2  | 563.6  | 509.9  | 460.7  | 426.9  |
| 65°    | 336.3  | 414.6  | 460.7  | 511.4  | 597.4  | 605.1  | 540.6  | 493.0  | 443.8  | 400.8  | 370.1  |
| 67.5°  | 271.8  | 333.3  | 374.7  | 417.7  | 486.8  | 508.3  | 463.8  | 423.9  | 382.4  | 347.1  | 319.4  |
| 70°    | 219.6  | 262.6  | 293.3  | 327.1  | 383.9  | 410.0  | 387.0  | 359.4  | 325.6  | 296.4  | 271.8  |
| 72.5°  | 173.5  | 201.2  | 219.6  | 245.7  | 291.8  | 317.9  | 316.4  | 291.8  | 267.2  | 247.3  | 227.3  |
| 75°    | 127.5  | 149.0  | 164.3  | 181.2  | 218.1  | 242.6  | 248.8  | 238.0  | 213.5  | 198.1  | 182.8  |
| 77.5°  | 96.8   | 109.0  | 116.7  | 129.0  | 155.1  | 176.6  | 185.8  | 182.8  | 165.9  | 153.6  | 142.8  |
| 80°    | 73.7   | 76.8   | 79.9   | 84.5   | 106.0  | 125.9  | 132.1  | 130.5  | 121.3  | 116.7  | 104.4  |
| 82.5°  | 52.2   | 53.8   | 55.3   | 56.8   | 64.5   | 81.4   | 87.5   | 90.6   | 82.9   | 78.3   | 67.6   |
| 85°    | 30.7   | 32.3   | 32.3   | 35.3   | 36.9   | 41.5   | 52.2   | 52.2   | 50.7   | 44.5   | 43.0   |
| 87.5°  | 15.4   | 15.4   | 13.8   | 13.8   | 15.4   | 16.9   | 20.0   | 23.0   | 20.0   | 18.4   | 16.9   |
| 90°    | 19.8   | 14.8   | 13.4   | 11.9   | 9.9    | 7.9    | 4.0    | 1.0    | 4.0    | 7.9    | 9.9    |
| 92.5°  | 79.0   | 52.4   | 47.0   | 41.5   | 33.6   | 28.7   | 20.7   | 14.8   | 20.7   | 28.7   | 33.6   |
| 95°    | 142.3  | 96.8   | 84.9   | 73.1   | 57.3   | 48.4   | 38.5   | 34.6   | 38.5   | 48.4   | 57.3   |
| 97.5°  | 183.8  | 125.5  | 112.2  | 98.8   | 81.0   | 68.2   | 57.3   | 51.4   | 57.3   | 68.2   | 81.0   |
| 100°   | 203.5  | 151.2  | 137.4  | 123.5  | 103.7  | 87.9   | 79.0   | 76.1   | 79.0   | 87.9   | 103.7  |
| 102.5° | 221.3  | 173.9  | 160.0  | 146.2  | 125.5  | 109.7  | 100.8  | 98.8   | 100.8  | 109.7  | 125.5  |
| 105°   | 242.1  | 195.6  | 181.8  | 168.0  | 146.2  | 131.4  | 124.5  | 120.5  | 124.5  | 131.4  | 146.2  |
| 107.5° | 262.8  | 217.4  | 203.6  | 189.7  | 168.0  | 154.1  | 147.2  | 144.2  | 147.2  | 154.1  | 168.0  |
| 110°   | 283.5  | 240.1  | 225.8  | 211.4  | 190.7  | 177.8  | 171.9  | 168.0  | 171.9  | 177.8  | 190.7  |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 150°  | 155°  | 157.5° | 160°  | 165°  | 170°  | 175°  | 180°  | 185°  | 190°  | 195°  |
|--------|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 303.3 | 261.8 | 247.0  | 232.2 | 212.4 | 200.6 | 193.6 | 189.7 | 193.6 | 200.6 | 212.4 |
| 115°   | 324.1 | 281.6 | 268.2  | 254.9 | 235.1 | 223.3 | 217.4 | 212.4 | 217.4 | 223.3 | 235.1 |
| 117.5° | 342.8 | 303.3 | 289.5  | 275.6 | 256.9 | 246.0 | 240.1 | 236.1 | 240.1 | 246.0 | 256.9 |
| 120°   | 362.6 | 324.1 | 310.2  | 296.4 | 276.6 | 267.7 | 261.8 | 257.9 | 261.8 | 267.7 | 276.6 |
| 122.5° | 381.4 | 345.8 | 331.5  | 317.1 | 297.4 | 287.5 | 281.6 | 278.6 | 281.6 | 287.5 | 297.4 |
| 125°   | 400.1 | 364.6 | 350.8  | 336.9 | 317.1 | 305.3 | 299.4 | 296.4 | 299.4 | 305.3 | 317.1 |
| 127.5° | 417.9 | 383.3 | 369.0  | 354.7 | 335.9 | 323.1 | 315.2 | 311.2 | 315.2 | 323.1 | 335.9 |
| 130°   | 433.7 | 399.1 | 385.3  | 371.5 | 351.7 | 337.9 | 328.0 | 324.1 | 328.0 | 337.9 | 351.7 |
| 132.5° | 447.5 | 414.9 | 401.1  | 387.3 | 366.5 | 351.7 | 340.8 | 335.9 | 340.8 | 351.7 | 366.5 |
| 135°   | 460.4 | 428.8 | 415.0  | 401.1 | 378.4 | 363.6 | 351.7 | 347.8 | 351.7 | 363.6 | 378.4 |
| 137.5° | 471.3 | 439.6 | 426.8  | 414.0 | 391.2 | 375.4 | 363.6 | 358.6 | 363.6 | 375.4 | 391.2 |
| 140°   | 480.1 | 450.5 | 437.6  | 424.8 | 403.1 | 387.3 | 375.4 | 371.5 | 375.4 | 387.3 | 403.1 |
| 142.5° | 487.1 | 458.4 | 446.6  | 434.7 | 414.0 | 398.1 | 387.3 | 384.3 | 387.3 | 398.1 | 414.0 |
| 145°   | 494.0 | 467.3 | 456.4  | 445.6 | 425.8 | 411.0 | 401.1 | 397.2 | 401.1 | 411.0 | 425.8 |
| 147.5° | 499.9 | 474.2 | 464.4  | 454.5 | 437.7 | 423.8 | 414.0 | 411.0 | 414.0 | 423.8 | 437.7 |
| 150°   | 503.9 | 481.1 | 472.2  | 463.4 | 448.5 | 435.7 | 427.8 | 424.8 | 427.8 | 435.7 | 448.5 |
| 152.5° | 507.8 | 488.1 | 480.2  | 472.2 | 458.4 | 447.5 | 439.6 | 438.7 | 439.6 | 447.5 | 458.4 |
| 155°   | 511.8 | 495.0 | 487.6  | 480.1 | 469.3 | 458.4 | 452.5 | 451.5 | 452.5 | 458.4 | 469.3 |
| 157.5° | 514.7 | 499.9 | 493.5  | 487.1 | 478.2 | 468.3 | 463.4 | 462.4 | 463.4 | 468.3 | 478.2 |
| 160°   | 516.7 | 504.8 | 499.4  | 494.0 | 486.1 | 478.2 | 474.2 | 473.2 | 474.2 | 478.2 | 486.1 |
| 162.5° | 517.7 | 507.8 | 503.8  | 499.9 | 493.0 | 487.1 | 483.1 | 484.1 | 483.1 | 487.1 | 493.0 |
| 165°   | 518.7 | 509.8 | 506.8  | 503.9 | 498.9 | 493.0 | 491.0 | 492.0 | 491.0 | 493.0 | 498.9 |
| 167.5° | 518.7 | 511.8 | 509.8  | 507.8 | 503.9 | 499.9 | 497.9 | 498.9 | 497.9 | 499.9 | 503.9 |
| 170°   | 517.7 | 512.8 | 511.3  | 509.8 | 507.8 | 504.8 | 503.9 | 505.8 | 503.9 | 504.8 | 507.8 |
| 172.5° | 516.7 | 513.7 | 512.8  | 511.8 | 510.8 | 507.8 | 508.8 | 509.8 | 508.8 | 507.8 | 510.8 |
| 175°   | 515.7 | 513.7 | 513.2  | 512.8 | 512.8 | 510.8 | 511.8 | 512.8 | 511.8 | 510.8 | 512.8 |
| 177.5° | 514.7 | 513.7 | 513.7  | 513.7 | 513.7 | 511.8 | 512.8 | 514.7 | 512.8 | 511.8 | 513.7 |
| 180°   | 513.7 | 513.7 | 513.7  | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 200°   | 202.5° | 205°   | 210°   | 215°   | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 |
| 2.5°   | 2185.3 | 2186.9 | 2191.5 | 2177.7 | 2156.2 | 2146.9 | 2119.3 | 2114.7 | 2110.1 | 2110.1 | 2114.7 |
| 5°     | 2136.2 | 2130.1 | 2131.6 | 2105.5 | 2074.8 | 2056.3 | 2017.9 | 2024.1 | 2004.1 | 1991.8 | 1994.9 |
| 7.5°   | 2082.4 | 2065.6 | 2064.0 | 2030.2 | 1991.8 | 1958.1 | 1918.1 | 1908.9 | 1890.5 | 1869.0 | 1859.8 |
| 10°    | 2014.9 | 2002.6 | 1979.6 | 1941.2 | 1892.0 | 1864.4 | 1810.6 | 1778.4 | 1773.8 | 1741.5 | 1729.2 |
| 12.5°  | 1945.8 | 1924.3 | 1901.2 | 1847.5 | 1792.2 | 1747.7 | 1707.7 | 1672.4 | 1647.8 | 1620.2 | 1601.8 |
| 15°    | 1865.9 | 1839.8 | 1813.7 | 1756.9 | 1692.4 | 1647.8 | 1587.9 | 1535.7 | 1463.5 | 1406.7 | 1374.5 |
| 17.5°  | 1778.4 | 1749.2 | 1713.9 | 1650.9 | 1587.9 | 1526.5 | 1415.9 | 1354.5 | 1303.8 | 1270.0 | 1250.1 |
| 20°    | 1687.8 | 1655.5 | 1620.2 | 1557.2 | 1448.2 | 1340.7 | 1279.3 | 1231.7 | 1200.9 | 1167.2 | 1142.6 |
| 22.5°  | 1592.5 | 1558.8 | 1520.4 | 1422.1 | 1306.9 | 1231.7 | 1184.0 | 1139.5 | 1095.0 | 1076.5 | 1064.3 |
| 25°    | 1503.5 | 1472.8 | 1423.6 | 1290.0 | 1199.4 | 1130.3 | 1076.5 | 1047.4 | 1024.3 | 999.8  | 976.7  |
| 27.5°  | 1411.3 | 1354.5 | 1285.4 | 1173.3 | 1116.5 | 1045.8 | 1007.4 | 985.9  | 946.0  | 929.1  | 918.4  |
| 30°    | 1300.8 | 1237.8 | 1171.8 | 1091.9 | 1025.9 | 976.7  | 941.4  | 906.1  | 883.0  | 866.1  | 847.7  |
| 32.5°  | 1188.7 | 1128.8 | 1087.3 | 1004.4 | 955.2  | 904.5  | 870.8  | 849.3  | 815.5  | 804.7  | 797.0  |
| 35°    | 1091.9 | 1041.2 | 1004.4 | 936.8  | 890.7  | 844.6  | 820.1  | 787.8  | 766.3  | 746.4  | 734.1  |
| 37.5°  | 996.7  | 969.0  | 930.7  | 873.8  | 824.7  | 787.8  | 754.0  | 743.3  | 714.1  | 703.4  | 691.1  |
| 40°    | 930.7  | 889.2  | 856.9  | 807.8  | 766.3  | 726.4  | 704.9  | 680.3  | 660.4  | 643.5  | 638.9  |
| 42.5°  | 850.8  | 820.1  | 801.6  | 747.9  | 704.9  | 681.9  | 655.8  | 628.1  | 612.8  | 598.9  | 582.0  |
| 45°    | 790.9  | 763.3  | 737.1  | 694.1  | 655.8  | 626.6  | 603.5  | 585.1  | 559.0  | 552.9  | 526.8  |
| 47.5°  | 727.9  | 700.3  | 680.3  | 637.3  | 602.0  | 574.4  | 557.5  | 532.9  | 511.4  | 497.6  | 485.3  |
| 50°    | 665.0  | 641.9  | 623.5  | 586.6  | 555.9  | 526.8  | 503.7  | 479.1  | 469.9  | 446.9  | 439.2  |
| 52.5°  | 605.1  | 589.7  | 569.8  | 534.4  | 503.7  | 479.1  | 454.6  | 434.6  | 420.8  | 408.5  | 399.3  |
| 55°    | 554.4  | 529.8  | 520.6  | 482.2  | 456.1  | 430.0  | 408.5  | 396.2  | 379.3  | 371.6  | 364.0  |
| 57.5°  | 497.6  | 483.8  | 468.4  | 439.2  | 410.0  | 385.5  | 370.1  | 351.7  | 342.5  | 333.3  | 327.1  |
| 60°    | 448.4  | 428.5  | 416.2  | 391.6  | 365.5  | 342.5  | 328.6  | 314.8  | 302.5  | 294.9  | 282.6  |
| 62.5°  | 391.6  | 376.3  | 368.6  | 342.5  | 321.0  | 299.5  | 287.2  | 273.4  | 264.1  | 250.3  | 235.0  |
| 65°    | 342.5  | 330.2  | 321.0  | 299.5  | 279.5  | 259.5  | 247.3  | 230.4  | 218.1  | 210.4  | 208.9  |
| 67.5°  | 299.5  | 290.3  | 276.4  | 256.5  | 236.5  | 221.1  | 207.3  | 193.5  | 192.0  | 188.9  | 188.9  |
| 70°    | 251.9  | 242.6  | 235.0  | 213.5  | 196.6  | 179.7  | 176.6  | 172.0  | 167.4  | 165.9  | 162.8  |
| 72.5°  | 210.4  | 202.7  | 193.5  | 175.1  | 158.2  | 153.6  | 150.5  | 147.4  | 142.8  | 141.3  | 139.8  |
| 75°    | 170.5  | 159.7  | 153.6  | 136.7  | 132.1  | 129.0  | 125.9  | 121.3  | 118.3  | 116.7  | 113.6  |
| 77.5°  | 130.5  | 119.8  | 119.8  | 110.6  | 107.5  | 102.9  | 99.8   | 96.8   | 95.2   | 92.1   | 92.1   |
| 80°    | 92.1   | 92.1   | 89.1   | 84.5   | 79.9   | 78.3   | 73.7   | 72.2   | 70.6   | 72.2   | 69.1   |
| 82.5°  | 67.6   | 61.4   | 61.4   | 58.4   | 55.3   | 53.8   | 50.7   | 50.7   | 49.1   | 49.1   | 49.1   |
| 85°    | 38.4   | 38.4   | 36.9   | 33.8   | 32.3   | 32.3   | 30.7   | 30.7   | 29.2   | 29.2   | 27.6   |
| 87.5°  | 15.4   | 13.8   | 15.4   | 13.8   | 13.8   | 12.3   | 12.3   | 12.3   | 10.8   | 12.3   | 10.8   |
| 90°    | 11.9   | 13.4   | 14.8   | 19.8   | 26.7   | 32.6   | 33.6   | 32.6   | 31.6   | 29.6   | 31.6   |
| 92.5°  | 41.5   | 47.0   | 52.4   | 79.0   | 116.6  | 150.2  | 152.1  | 127.4  | 99.8   | 85.0   | 74.1   |
| 95°    | 73.1   | 84.9   | 96.8   | 142.3  | 228.2  | 342.8  | 387.3  | 338.9  | 258.8  | 198.6  | 157.1  |
| 97.5°  | 98.8   | 112.2  | 125.5  | 183.8  | 303.3  | 488.1  | 631.3  | 636.2  | 529.5  | 422.8  | 323.1  |
| 100°   | 123.5  | 137.4  | 151.2  | 203.5  | 324.1  | 537.5  | 780.5  | 922.8  | 902.0  | 779.5  | 644.2  |
| 102.5° | 146.2  | 160.0  | 173.9  | 221.3  | 325.0  | 518.7  | 785.4  | 1029.5 | 1146.0 | 1142.1 | 1052.2 |
| 105°   | 168.0  | 181.8  | 195.6  | 242.1  | 330.0  | 493.0  | 732.1  | 994.9  | 1200.4 | 1312.0 | 1324.9 |
| 107.5° | 189.7  | 203.6  | 217.4  | 262.8  | 340.8  | 479.2  | 682.7  | 921.8  | 1142.1 | 1308.1 | 1404.9 |
| 110°   | 211.4  | 225.8  | 240.1  | 283.5  | 354.7  | 475.2  | 649.1  | 853.6  | 1062.1 | 1238.9 | 1365.4 |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 200°  | 202.5° | 205°  | 210°  | 215°  | 220°  | 225°  | 230°  | 235°  | 240°   | 245°   |
|--------|-------|--------|-------|-------|-------|-------|-------|-------|-------|--------|--------|
| 112.5° | 232.2 | 247.0  | 261.8 | 303.3 | 369.5 | 476.2 | 627.4 | 806.2 | 988.9 | 1156.9 | 1294.2 |
| 115°   | 254.9 | 268.2  | 281.6 | 324.1 | 384.3 | 480.1 | 612.5 | 768.6 | 931.6 | 1083.8 | 1213.2 |
| 117.5° | 275.6 | 289.5  | 303.3 | 342.8 | 400.1 | 486.1 | 604.6 | 742.9 | 884.2 | 1020.6 | 1141.1 |
| 120°   | 296.4 | 310.2  | 324.1 | 362.6 | 415.9 | 492.0 | 597.7 | 723.2 | 850.6 | 973.1  | 1077.9 |
| 122.5° | 317.1 | 331.5  | 345.8 | 381.4 | 429.8 | 498.9 | 593.8 | 706.4 | 824.0 | 933.6  | 1031.4 |
| 125°   | 336.9 | 350.8  | 364.6 | 400.1 | 444.6 | 505.8 | 588.8 | 690.6 | 798.3 | 900.0  | 987.0  |
| 127.5° | 354.7 | 369.0  | 383.3 | 417.9 | 458.4 | 512.8 | 585.9 | 675.8 | 772.6 | 866.4  | 949.4  |
| 130°   | 371.5 | 385.3  | 399.1 | 433.7 | 471.3 | 520.7 | 583.9 | 660.9 | 747.9 | 832.9  | 910.9  |
| 132.5° | 387.3 | 401.1  | 414.9 | 447.5 | 484.1 | 528.6 | 582.9 | 649.1 | 724.2 | 801.2  | 871.4  |
| 135°   | 401.1 | 415.0  | 428.8 | 460.4 | 495.0 | 534.5 | 581.9 | 638.2 | 702.4 | 767.6  | 832.9  |
| 137.5° | 414.0 | 426.8  | 439.6 | 471.3 | 503.9 | 540.4 | 581.9 | 630.3 | 684.7 | 741.0  | 794.3  |
| 140°   | 424.8 | 437.6  | 450.5 | 480.1 | 510.8 | 544.4 | 580.9 | 623.4 | 667.9 | 715.3  | 760.7  |
| 142.5° | 434.7 | 446.6  | 458.4 | 487.1 | 516.7 | 547.3 | 580.9 | 616.5 | 654.0 | 692.6  | 730.1  |
| 145°   | 445.6 | 456.4  | 467.3 | 494.0 | 521.6 | 549.3 | 578.9 | 610.6 | 641.2 | 673.8  | 704.4  |
| 147.5° | 454.5 | 464.4  | 474.2 | 499.9 | 524.6 | 550.3 | 576.0 | 604.6 | 631.3 | 658.0  | 682.7  |
| 150°   | 463.4 | 472.2  | 481.1 | 503.9 | 526.6 | 549.3 | 573.0 | 596.7 | 620.4 | 642.2  | 662.9  |
| 152.5° | 472.2 | 480.2  | 488.1 | 507.8 | 527.6 | 547.3 | 568.1 | 589.8 | 609.6 | 629.3  | 646.1  |
| 155°   | 480.1 | 487.6  | 495.0 | 511.8 | 528.6 | 545.4 | 562.2 | 580.9 | 599.7 | 615.5  | 630.3  |
| 157.5° | 487.1 | 493.5  | 499.9 | 514.7 | 528.6 | 541.4 | 556.2 | 573.0 | 587.8 | 601.7  | 614.5  |
| 160°   | 494.0 | 499.4  | 504.8 | 516.7 | 528.6 | 538.4 | 550.3 | 564.1 | 577.0 | 587.8  | 598.7  |
| 162.5° | 499.9 | 503.8  | 507.8 | 517.7 | 527.6 | 535.5 | 545.4 | 556.2 | 566.1 | 575.0  | 583.9  |
| 165°   | 503.9 | 506.8  | 509.8 | 518.7 | 525.6 | 531.5 | 538.4 | 547.3 | 555.2 | 562.2  | 569.1  |
| 167.5° | 507.8 | 509.8  | 511.8 | 518.7 | 524.6 | 527.6 | 532.5 | 538.4 | 544.4 | 550.3  | 555.2  |
| 170°   | 509.8 | 511.3  | 512.8 | 517.7 | 522.6 | 524.6 | 527.6 | 531.5 | 536.5 | 539.4  | 543.4  |
| 172.5° | 511.8 | 512.8  | 513.7 | 516.7 | 519.7 | 520.7 | 521.6 | 524.6 | 527.6 | 529.5  | 532.5  |
| 175°   | 512.8 | 513.2  | 513.7 | 515.7 | 517.7 | 516.7 | 517.7 | 518.7 | 521.6 | 522.6  | 523.6  |
| 177.5° | 513.7 | 513.7  | 513.7 | 514.7 | 516.7 | 514.7 | 513.7 | 514.7 | 516.7 | 516.7  | 517.7  |
| 180°   | 513.7 | 513.7  | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7  | 513.7  |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 255°   | 260°   | 265°   | 270°   | 275°   | 280°   | 285°   | 290°   | 292.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 |
| 2.5°   | 2114.7 | 2111.6 | 2102.4 | 2105.5 | 2100.9 | 2100.9 | 2097.8 | 2097.8 | 2097.8 | 2105.5 | 2100.9 |
| 5°     | 1999.5 | 1988.8 | 1978.0 | 1973.4 | 1968.8 | 1964.2 | 1964.2 | 1962.7 | 1976.5 | 1973.4 | 1985.7 |
| 7.5°   | 1856.7 | 1853.6 | 1832.1 | 1832.1 | 1824.4 | 1821.4 | 1829.1 | 1830.6 | 1832.1 | 1835.2 | 1842.9 |
| 10°    | 1729.2 | 1721.5 | 1690.8 | 1693.9 | 1689.3 | 1683.2 | 1687.8 | 1684.7 | 1695.4 | 1698.5 | 1695.4 |
| 12.5°  | 1578.7 | 1564.9 | 1531.1 | 1514.2 | 1495.8 | 1482.0 | 1498.9 | 1486.6 | 1529.6 | 1541.9 | 1575.7 |
| 15°    | 1379.1 | 1353.0 | 1329.9 | 1329.9 | 1313.0 | 1300.8 | 1308.4 | 1322.3 | 1331.5 | 1345.3 | 1351.4 |
| 17.5°  | 1245.5 | 1234.7 | 1216.3 | 1205.5 | 1200.9 | 1196.3 | 1196.3 | 1202.5 | 1222.4 | 1220.9 | 1233.2 |
| 20°    | 1131.8 | 1125.7 | 1116.5 | 1102.7 | 1098.0 | 1095.0 | 1095.0 | 1095.0 | 1108.8 | 1121.1 | 1128.8 |
| 22.5°  | 1053.5 | 1048.9 | 1042.8 | 1024.3 | 1015.1 | 1012.0 | 1019.7 | 1024.3 | 1035.1 | 1044.3 | 1052.0 |
| 25°    | 975.2  | 964.4  | 953.7  | 947.5  | 942.9  | 942.9  | 946.0  | 947.5  | 952.2  | 956.8  | 966.0  |
| 27.5°  | 910.7  | 903.0  | 887.7  | 870.8  | 870.8  | 866.1  | 869.2  | 872.3  | 883.0  | 898.4  | 906.1  |
| 30°    | 838.5  | 837.0  | 830.8  | 824.7  | 818.5  | 815.5  | 821.6  | 826.2  | 827.8  | 835.4  | 835.4  |
| 32.5°  | 786.3  | 775.5  | 764.8  | 758.6  | 755.6  | 754.0  | 755.6  | 761.7  | 761.7  | 770.9  | 781.7  |
| 35°    | 734.1  | 727.9  | 717.2  | 706.4  | 703.4  | 695.7  | 701.8  | 708.0  | 718.7  | 723.3  | 727.9  |
| 37.5°  | 677.3  | 669.6  | 665.0  | 661.9  | 655.8  | 657.3  | 652.7  | 661.9  | 671.1  | 669.6  | 672.6  |
| 40°    | 634.3  | 620.4  | 606.6  | 605.1  | 603.5  | 602.0  | 602.0  | 603.5  | 609.7  | 615.8  | 625.0  |
| 42.5°  | 579.0  | 574.4  | 562.1  | 549.8  | 546.7  | 543.6  | 540.6  | 546.7  | 559.0  | 569.8  | 574.4  |
| 45°    | 522.1  | 516.0  | 512.9  | 503.7  | 497.6  | 496.0  | 493.0  | 500.6  | 511.4  | 516.0  | 519.1  |
| 47.5°  | 469.9  | 468.4  | 459.2  | 460.7  | 456.1  | 457.6  | 456.1  | 460.7  | 460.7  | 465.3  | 468.4  |
| 50°    | 434.6  | 430.0  | 425.4  | 422.3  | 417.7  | 417.7  | 416.2  | 417.7  | 423.9  | 430.0  | 428.5  |
| 52.5°  | 399.3  | 391.6  | 390.1  | 388.5  | 385.5  | 388.5  | 383.9  | 385.5  | 391.6  | 394.7  | 393.1  |
| 55°    | 357.8  | 356.3  | 353.2  | 350.1  | 348.6  | 347.1  | 347.1  | 347.1  | 353.2  | 357.8  | 359.4  |
| 57.5°  | 325.6  | 317.9  | 311.8  | 311.8  | 305.6  | 304.1  | 307.1  | 308.7  | 313.3  | 316.4  | 319.4  |
| 60°    | 281.0  | 278.0  | 268.8  | 264.1  | 254.9  | 253.4  | 253.4  | 259.5  | 267.2  | 278.0  | 281.0  |
| 62.5°  | 233.4  | 228.8  | 227.3  | 227.3  | 227.3  | 227.3  | 227.3  | 227.3  | 227.3  | 228.8  | 228.8  |
| 65°    | 207.3  | 208.9  | 207.3  | 205.8  | 207.3  | 207.3  | 205.8  | 205.8  | 205.8  | 207.3  | 208.9  |
| 67.5°  | 185.8  | 184.3  | 185.8  | 184.3  | 182.8  | 182.8  | 181.2  | 182.8  | 184.3  | 185.8  | 185.8  |
| 70°    | 161.3  | 161.3  | 159.7  | 161.3  | 159.7  | 158.2  | 156.6  | 156.6  | 159.7  | 161.3  | 161.3  |
| 72.5°  | 138.2  | 138.2  | 136.7  | 136.7  | 133.6  | 133.6  | 135.1  | 133.6  | 133.6  | 138.2  | 138.2  |
| 75°    | 115.2  | 113.6  | 112.1  | 112.1  | 110.6  | 110.6  | 110.6  | 109.0  | 112.1  | 112.1  | 113.6  |
| 77.5°  | 90.6   | 90.6   | 90.6   | 89.1   | 89.1   | 87.5   | 87.5   | 89.1   | 89.1   | 89.1   | 90.6   |
| 80°    | 69.1   | 69.1   | 69.1   | 67.6   | 66.0   | 66.0   | 66.0   | 66.0   | 66.0   | 67.6   | 66.0   |
| 82.5°  | 47.6   | 47.6   | 47.6   | 47.6   | 47.6   | 46.1   | 46.1   | 46.1   | 47.6   | 47.6   | 46.1   |
| 85°    | 29.2   | 27.6   | 29.2   | 29.2   | 27.6   | 29.2   | 27.6   | 27.6   | 26.1   | 26.1   | 27.6   |
| 87.5°  | 12.3   | 10.8   | 9.2    | 9.2    | 10.8   | 9.2    | 9.2    | 9.2    | 10.8   | 9.2    | 9.2    |
| 90°    | 32.1   | 32.6   | 32.6   | 32.6   | 32.6   | 32.6   | 32.6   | 32.6   | 32.6   | 32.6   | 32.1   |
| 92.5°  | 70.2   | 66.2   | 65.2   | 61.3   | 62.2   | 60.3   | 62.2   | 61.3   | 65.2   | 66.2   | 70.2   |
| 95°    | 146.2  | 135.4  | 122.5  | 114.6  | 111.6  | 112.6  | 111.6  | 114.6  | 122.5  | 135.4  | 146.2  |
| 97.5°  | 293.5  | 263.8  | 225.3  | 205.5  | 194.6  | 188.7  | 194.6  | 205.5  | 225.3  | 263.8  | 293.5  |
| 100°   | 584.4  | 524.6  | 442.6  | 400.1  | 371.5  | 353.7  | 371.5  | 400.1  | 442.6  | 524.6  | 584.4  |
| 102.5° | 988.0  | 923.7  | 832.9  | 752.8  | 715.3  | 689.6  | 715.3  | 752.8  | 832.9  | 923.7  | 988.0  |
| 105°   | 1308.6 | 1292.3 | 1231.0 | 1169.7 | 1127.3 | 1113.4 | 1127.3 | 1169.7 | 1231.0 | 1292.3 | 1308.6 |
| 107.5° | 1424.6 | 1444.4 | 1443.4 | 1434.5 | 1421.7 | 1399.0 | 1421.7 | 1434.5 | 1443.4 | 1444.4 | 1424.6 |
| 110°   | 1405.9 | 1446.4 | 1488.9 | 1507.6 | 1516.5 | 1515.5 | 1516.5 | 1507.6 | 1488.9 | 1446.4 | 1405.9 |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 255°   | 260°   | 265°   | 270°   | 275°   | 280°   | 285°   | 290°   | 292.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 1342.2 | 1390.1 | 1453.3 | 1487.9 | 1506.6 | 1513.6 | 1506.6 | 1487.9 | 1453.3 | 1390.1 | 1342.2 |
| 115°   | 1264.1 | 1315.0 | 1385.1 | 1430.6 | 1456.3 | 1465.1 | 1456.3 | 1430.6 | 1385.1 | 1315.0 | 1264.1 |
| 117.5° | 1189.5 | 1237.9 | 1310.0 | 1358.4 | 1385.1 | 1392.0 | 1385.1 | 1358.4 | 1310.0 | 1237.9 | 1189.5 |
| 120°   | 1122.8 | 1167.8 | 1236.9 | 1283.4 | 1312.0 | 1321.9 | 1312.0 | 1283.4 | 1236.9 | 1167.8 | 1122.8 |
| 122.5° | 1071.0 | 1110.5 | 1170.7 | 1216.2 | 1240.9 | 1248.8 | 1240.9 | 1216.2 | 1170.7 | 1110.5 | 1071.0 |
| 125°   | 1024.0 | 1061.1 | 1118.4 | 1155.9 | 1180.6 | 1188.5 | 1180.6 | 1155.9 | 1118.4 | 1061.1 | 1024.0 |
| 127.5° | 984.0  | 1018.6 | 1069.0 | 1104.5 | 1126.3 | 1132.2 | 1126.3 | 1104.5 | 1069.0 | 1018.6 | 984.0  |
| 130°   | 943.5  | 976.1  | 1024.5 | 1058.1 | 1077.9 | 1085.8 | 1077.9 | 1058.1 | 1024.5 | 976.1  | 943.5  |
| 132.5° | 901.5  | 931.6  | 979.1  | 1012.7 | 1030.4 | 1037.4 | 1030.4 | 1012.7 | 979.1  | 931.6  | 901.5  |
| 135°   | 860.6  | 888.2  | 930.7  | 963.3  | 981.0  | 985.0  | 981.0  | 963.3  | 930.7  | 888.2  | 860.6  |
| 137.5° | 819.0  | 843.7  | 884.2  | 912.9  | 928.7  | 934.6  | 928.7  | 912.9  | 884.2  | 843.7  | 819.0  |
| 140°   | 782.4  | 804.2  | 835.8  | 861.5  | 876.3  | 882.2  | 876.3  | 861.5  | 835.8  | 804.2  | 782.4  |
| 142.5° | 747.4  | 764.7  | 794.3  | 817.0  | 829.9  | 829.9  | 829.9  | 817.0  | 794.3  | 764.7  | 747.4  |
| 145°   | 718.8  | 733.1  | 756.8  | 773.6  | 783.5  | 786.4  | 783.5  | 773.6  | 756.8  | 733.1  | 718.8  |
| 147.5° | 693.6  | 704.4  | 725.2  | 739.0  | 745.9  | 747.9  | 745.9  | 739.0  | 725.2  | 704.4  | 693.6  |
| 150°   | 671.8  | 680.7  | 695.5  | 707.4  | 713.3  | 714.3  | 713.3  | 707.4  | 695.5  | 680.7  | 671.8  |
| 152.5° | 653.5  | 660.9  | 671.8  | 681.7  | 685.6  | 685.6  | 685.6  | 681.7  | 671.8  | 660.9  | 653.5  |
| 155°   | 635.8  | 641.2  | 652.1  | 659.0  | 662.9  | 660.9  | 662.9  | 659.0  | 652.1  | 641.2  | 635.8  |
| 157.5° | 619.0  | 623.4  | 631.3  | 637.2  | 639.2  | 639.2  | 639.2  | 637.2  | 631.3  | 623.4  | 619.0  |
| 160°   | 602.2  | 605.6  | 612.5  | 617.5  | 618.5  | 618.5  | 618.5  | 617.5  | 612.5  | 605.6  | 602.2  |
| 162.5° | 586.3  | 588.8  | 595.7  | 598.7  | 599.7  | 598.7  | 599.7  | 598.7  | 595.7  | 588.8  | 586.3  |
| 165°   | 571.0  | 573.0  | 577.0  | 580.9  | 580.9  | 579.9  | 580.9  | 580.9  | 577.0  | 573.0  | 571.0  |
| 167.5° | 557.2  | 559.2  | 561.2  | 563.1  | 563.1  | 562.2  | 563.1  | 563.1  | 561.2  | 559.2  | 557.2  |
| 170°   | 544.4  | 545.4  | 546.3  | 549.3  | 548.3  | 546.3  | 548.3  | 549.3  | 546.3  | 545.4  | 544.4  |
| 172.5° | 533.0  | 533.5  | 534.5  | 535.5  | 534.5  | 533.5  | 534.5  | 535.5  | 534.5  | 533.5  | 533.0  |
| 175°   | 524.1  | 524.6  | 524.6  | 525.6  | 524.6  | 522.6  | 524.6  | 525.6  | 524.6  | 524.6  | 524.1  |
| 177.5° | 517.7  | 517.7  | 517.7  | 517.7  | 516.7  | 514.7  | 516.7  | 517.7  | 517.7  | 517.7  | 517.7  |
| 180°   | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  | 513.7  |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   | 325°   | 330°   | 335°   | 337.5° | 340°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 | 2209.9 |
| 2.5°   | 2105.5 | 2113.2 | 2110.1 | 2093.2 | 2110.1 | 2114.7 | 2123.9 | 2133.1 | 2139.3 | 2148.5 | 2156.2 |
| 5°     | 1973.4 | 1988.8 | 1998.0 | 1988.8 | 2019.5 | 2024.1 | 2045.6 | 2057.9 | 2076.3 | 2091.7 | 2103.9 |
| 7.5°   | 1849.0 | 1861.3 | 1879.7 | 1882.8 | 1901.2 | 1922.7 | 1953.4 | 1984.2 | 2013.3 | 2028.7 | 2042.5 |
| 10°    | 1715.4 | 1736.9 | 1764.5 | 1758.4 | 1786.1 | 1819.8 | 1852.1 | 1901.2 | 1925.8 | 1953.4 | 1978.0 |
| 12.5°  | 1581.8 | 1595.6 | 1632.5 | 1644.8 | 1684.7 | 1710.8 | 1755.3 | 1786.1 | 1847.5 | 1879.7 | 1901.2 |
| 15°    | 1348.4 | 1405.2 | 1451.3 | 1506.5 | 1558.8 | 1607.9 | 1647.8 | 1703.1 | 1756.9 | 1781.4 | 1816.8 |
| 17.5°  | 1242.4 | 1268.5 | 1296.2 | 1323.8 | 1391.4 | 1478.9 | 1549.5 | 1609.4 | 1655.5 | 1687.8 | 1729.2 |
| 20°    | 1131.8 | 1157.9 | 1188.7 | 1214.8 | 1256.2 | 1319.2 | 1406.7 | 1509.6 | 1564.9 | 1598.7 | 1638.6 |
| 22.5°  | 1053.5 | 1078.1 | 1098.0 | 1121.1 | 1153.3 | 1199.4 | 1265.4 | 1392.9 | 1466.6 | 1508.1 | 1543.4 |
| 25°    | 969.0  | 999.8  | 1021.3 | 1038.2 | 1064.3 | 1114.9 | 1168.7 | 1240.9 | 1372.9 | 1405.2 | 1454.3 |
| 27.5°  | 910.7  | 919.9  | 944.5  | 970.6  | 996.7  | 1024.3 | 1079.6 | 1141.0 | 1230.1 | 1300.8 | 1360.7 |
| 30°    | 841.6  | 864.6  | 887.7  | 898.4  | 921.4  | 961.4  | 995.2  | 1061.2 | 1130.3 | 1185.6 | 1257.8 |
| 32.5°  | 789.4  | 803.2  | 818.5  | 844.6  | 866.1  | 893.8  | 927.6  | 982.9  | 1041.2 | 1076.5 | 1131.8 |
| 35°    | 731.0  | 740.2  | 772.5  | 783.2  | 804.7  | 832.4  | 866.1  | 909.2  | 972.1  | 999.8  | 1039.7 |
| 37.5°  | 675.7  | 697.2  | 706.4  | 731.0  | 751.0  | 778.6  | 803.2  | 852.3  | 893.8  | 926.0  | 962.9  |
| 40°    | 632.7  | 641.9  | 658.8  | 680.3  | 697.2  | 718.7  | 749.4  | 784.8  | 829.3  | 855.4  | 887.7  |
| 42.5°  | 580.5  | 588.2  | 609.7  | 622.0  | 649.6  | 669.6  | 688.0  | 731.0  | 770.9  | 790.9  | 823.1  |
| 45°    | 523.7  | 542.1  | 555.9  | 580.5  | 595.9  | 620.4  | 643.5  | 674.2  | 711.0  | 734.1  | 752.5  |
| 47.5°  | 474.5  | 493.0  | 506.8  | 529.8  | 554.4  | 565.1  | 589.7  | 622.0  | 655.8  | 674.2  | 700.3  |
| 50°    | 434.6  | 440.8  | 466.9  | 477.6  | 503.7  | 525.2  | 542.1  | 569.8  | 606.6  | 617.4  | 638.9  |
| 52.5°  | 396.2  | 400.8  | 417.7  | 431.5  | 454.6  | 473.0  | 494.5  | 520.6  | 551.3  | 568.2  | 585.1  |
| 55°    | 362.4  | 365.5  | 373.2  | 388.5  | 403.9  | 426.9  | 446.9  | 471.5  | 497.6  | 516.0  | 531.4  |
| 57.5°  | 324.0  | 330.2  | 336.3  | 345.5  | 360.9  | 382.4  | 403.9  | 426.9  | 448.4  | 460.7  | 480.7  |
| 60°    | 279.5  | 288.7  | 299.5  | 310.2  | 321.0  | 336.3  | 360.9  | 382.4  | 402.4  | 413.1  | 428.5  |
| 62.5°  | 231.9  | 250.3  | 259.5  | 271.8  | 281.0  | 294.9  | 313.3  | 337.9  | 351.7  | 365.5  | 377.8  |
| 65°    | 208.9  | 210.4  | 211.9  | 224.2  | 241.1  | 254.9  | 271.8  | 290.3  | 311.8  | 321.0  | 330.2  |
| 67.5°  | 185.8  | 187.4  | 190.4  | 192.0  | 198.1  | 213.5  | 231.9  | 251.9  | 268.8  | 274.9  | 284.1  |
| 70°    | 162.8  | 162.8  | 168.9  | 170.5  | 172.0  | 173.5  | 188.9  | 208.9  | 224.2  | 231.9  | 242.6  |
| 72.5°  | 138.2  | 139.8  | 142.8  | 144.4  | 147.4  | 150.5  | 155.1  | 165.9  | 184.3  | 192.0  | 204.3  |
| 75°    | 113.6  | 115.2  | 116.7  | 118.3  | 122.9  | 124.4  | 129.0  | 135.1  | 142.8  | 152.0  | 159.7  |
| 77.5°  | 90.6   | 90.6   | 92.1   | 95.2   | 98.3   | 99.8   | 104.4  | 107.5  | 110.6  | 115.2  | 121.3  |
| 80°    | 67.6   | 69.1   | 69.1   | 72.2   | 72.2   | 73.7   | 75.3   | 79.9   | 82.9   | 86.0   | 89.1   |
| 82.5°  | 46.1   | 49.1   | 49.1   | 49.1   | 50.7   | 52.2   | 53.8   | 53.8   | 56.8   | 58.4   | 63.0   |
| 85°    | 27.6   | 29.2   | 29.2   | 29.2   | 27.6   | 30.7   | 30.7   | 32.3   | 32.3   | 32.3   | 33.8   |
| 87.5°  | 10.8   | 9.2    | 10.8   | 10.8   | 10.8   | 12.3   | 10.8   | 10.8   | 12.3   | 13.8   | 13.8   |
| 90°    | 31.6   | 29.6   | 31.6   | 32.6   | 33.6   | 32.6   | 26.7   | 19.8   | 14.8   | 13.4   | 11.9   |
| 92.5°  | 74.1   | 85.0   | 99.8   | 127.4  | 152.1  | 150.2  | 116.6  | 79.0   | 52.4   | 47.0   | 41.5   |
| 95°    | 157.1  | 198.6  | 258.8  | 338.9  | 387.3  | 342.8  | 228.2  | 142.3  | 96.8   | 84.9   | 73.1   |
| 97.5°  | 323.1  | 422.8  | 529.5  | 636.2  | 631.3  | 488.1  | 303.3  | 183.8  | 125.5  | 112.2  | 98.8   |
| 100°   | 644.2  | 779.5  | 902.0  | 922.8  | 780.5  | 537.5  | 324.1  | 203.5  | 151.2  | 137.4  | 123.5  |
| 102.5° | 1052.2 | 1142.1 | 1146.0 | 1029.5 | 785.4  | 518.7  | 325.0  | 221.3  | 173.9  | 160.0  | 146.2  |
| 105°   | 1324.9 | 1312.0 | 1200.4 | 994.9  | 732.1  | 493.0  | 330.0  | 242.1  | 195.6  | 181.8  | 168.0  |
| 107.5° | 1404.9 | 1308.1 | 1142.1 | 921.8  | 682.7  | 479.2  | 340.8  | 262.8  | 217.4  | 203.6  | 189.7  |
| 110°   | 1365.4 | 1238.9 | 1062.1 | 853.6  | 649.1  | 475.2  | 354.7  | 283.5  | 240.1  | 225.8  | 211.4  |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 295°   | 300°   | 305°  | 310°  | 315°  | 320°  | 325°  | 330°  | 335°  | 337.5° | 340°  |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 112.5° | 1294.2 | 1156.9 | 988.9 | 806.2 | 627.4 | 476.2 | 369.5 | 303.3 | 261.8 | 247.0  | 232.2 |
| 115°   | 1213.2 | 1083.8 | 931.6 | 768.6 | 612.5 | 480.1 | 384.3 | 324.1 | 281.6 | 268.2  | 254.9 |
| 117.5° | 1141.1 | 1020.6 | 884.2 | 742.9 | 604.6 | 486.1 | 400.1 | 342.8 | 303.3 | 289.5  | 275.6 |
| 120°   | 1077.9 | 973.1  | 850.6 | 723.2 | 597.7 | 492.0 | 415.9 | 362.6 | 324.1 | 310.2  | 296.4 |
| 122.5° | 1031.4 | 933.6  | 824.0 | 706.4 | 593.8 | 498.9 | 429.8 | 381.4 | 345.8 | 331.5  | 317.1 |
| 125°   | 987.0  | 900.0  | 798.3 | 690.6 | 588.8 | 505.8 | 444.6 | 400.1 | 364.6 | 350.8  | 336.9 |
| 127.5° | 949.4  | 866.4  | 772.6 | 675.8 | 585.9 | 512.8 | 458.4 | 417.9 | 383.3 | 369.0  | 354.7 |
| 130°   | 910.9  | 832.9  | 747.9 | 660.9 | 583.9 | 520.7 | 471.3 | 433.7 | 399.1 | 385.3  | 371.5 |
| 132.5° | 871.4  | 801.2  | 724.2 | 649.1 | 582.9 | 528.6 | 484.1 | 447.5 | 414.9 | 401.1  | 387.3 |
| 135°   | 832.9  | 767.6  | 702.4 | 638.2 | 581.9 | 534.5 | 495.0 | 460.4 | 428.8 | 415.0  | 401.1 |
| 137.5° | 794.3  | 741.0  | 684.7 | 630.3 | 581.9 | 540.4 | 503.9 | 471.3 | 439.6 | 426.8  | 414.0 |
| 140°   | 760.7  | 715.3  | 667.9 | 623.4 | 580.9 | 544.4 | 510.8 | 480.1 | 450.5 | 437.6  | 424.8 |
| 142.5° | 730.1  | 692.6  | 654.0 | 616.5 | 580.9 | 547.3 | 516.7 | 487.1 | 458.4 | 446.6  | 434.7 |
| 145°   | 704.4  | 673.8  | 641.2 | 610.6 | 578.9 | 549.3 | 521.6 | 494.0 | 467.3 | 456.4  | 445.6 |
| 147.5° | 682.7  | 658.0  | 631.3 | 604.6 | 576.0 | 550.3 | 524.6 | 499.9 | 474.2 | 464.4  | 454.5 |
| 150°   | 662.9  | 642.2  | 620.4 | 596.7 | 573.0 | 549.3 | 526.6 | 503.9 | 481.1 | 472.2  | 463.4 |
| 152.5° | 646.1  | 629.3  | 609.6 | 589.8 | 568.1 | 547.3 | 527.6 | 507.8 | 488.1 | 480.2  | 472.2 |
| 155°   | 630.3  | 615.5  | 599.7 | 580.9 | 562.2 | 545.4 | 528.6 | 511.8 | 495.0 | 487.6  | 480.1 |
| 157.5° | 614.5  | 601.7  | 587.8 | 573.0 | 556.2 | 541.4 | 528.6 | 514.7 | 499.9 | 493.5  | 487.1 |
| 160°   | 598.7  | 587.8  | 577.0 | 564.1 | 550.3 | 538.4 | 528.6 | 516.7 | 504.8 | 499.4  | 494.0 |
| 162.5° | 583.9  | 575.0  | 566.1 | 556.2 | 545.4 | 535.5 | 527.6 | 517.7 | 507.8 | 503.8  | 499.9 |
| 165°   | 569.1  | 562.2  | 555.2 | 547.3 | 538.4 | 531.5 | 525.6 | 518.7 | 509.8 | 506.8  | 503.9 |
| 167.5° | 555.2  | 550.3  | 544.4 | 538.4 | 532.5 | 527.6 | 524.6 | 518.7 | 511.8 | 509.8  | 507.8 |
| 170°   | 543.4  | 539.4  | 536.5 | 531.5 | 527.6 | 524.6 | 522.6 | 517.7 | 512.8 | 511.3  | 509.8 |
| 172.5° | 532.5  | 529.5  | 527.6 | 524.6 | 521.6 | 520.7 | 519.7 | 516.7 | 513.7 | 512.8  | 511.8 |
| 175°   | 523.6  | 522.6  | 521.6 | 518.7 | 517.7 | 516.7 | 517.7 | 515.7 | 513.7 | 513.2  | 512.8 |
| 177.5° | 517.7  | 516.7  | 516.7 | 514.7 | 513.7 | 514.7 | 516.7 | 514.7 | 513.7 | 513.7  | 513.7 |
| 180°   | 513.7  | 513.7  | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7 | 513.7  | 513.7 |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 345°   | 350°   | 355°   | 360°   |
|--------|--------|--------|--------|--------|
| 0°     | 2209.9 | 2209.9 | 2209.9 | 2209.9 |
| 2.5°   | 2170.0 | 2165.4 | 2193.0 | 2223.7 |
| 5°     | 2125.4 | 2133.1 | 2168.4 | 2211.4 |
| 7.5°   | 2079.4 | 2096.3 | 2137.7 | 2194.6 |
| 10°    | 2014.9 | 2045.6 | 2108.6 | 2166.9 |
| 12.5°  | 1951.9 | 1993.4 | 2053.3 | 2122.4 |
| 15°    | 1881.3 | 1927.3 | 2001.1 | 2084.0 |
| 17.5°  | 1802.9 | 1855.2 | 1941.2 | 2031.8 |
| 20°    | 1720.0 | 1789.1 | 1879.7 | 1978.0 |
| 22.5°  | 1627.9 | 1710.8 | 1804.5 | 1913.5 |
| 25°    | 1538.8 | 1629.4 | 1723.1 | 1849.0 |
| 27.5°  | 1451.3 | 1540.3 | 1644.8 | 1772.2 |
| 30°    | 1363.7 | 1445.1 | 1557.2 | 1693.9 |
| 32.5°  | 1270.0 | 1354.5 | 1472.8 | 1612.5 |
| 35°    | 1184.0 | 1268.5 | 1379.1 | 1517.3 |
| 37.5°  | 1091.9 | 1182.5 | 1288.5 | 1431.3 |
| 40°    | 984.4  | 1090.4 | 1193.3 | 1329.9 |
| 42.5°  | 895.3  | 1007.4 | 1107.3 | 1236.3 |
| 45°    | 824.7  | 930.7  | 1013.6 | 1139.5 |
| 47.5°  | 758.6  | 844.6  | 929.1  | 1045.8 |
| 50°    | 695.7  | 761.7  | 849.3  | 953.7  |
| 52.5°  | 631.2  | 688.0  | 763.3  | 861.5  |
| 55°    | 572.8  | 626.6  | 694.1  | 769.4  |
| 57.5°  | 519.1  | 557.5  | 625.0  | 692.6  |
| 60°    | 459.2  | 499.1  | 551.3  | 608.1  |
| 62.5°  | 408.5  | 439.2  | 488.4  | 536.0  |
| 65°    | 354.8  | 383.9  | 420.8  | 465.3  |
| 67.5°  | 305.6  | 331.7  | 360.9  | 396.2  |
| 70°    | 261.1  | 281.0  | 302.5  | 333.3  |
| 72.5°  | 213.5  | 235.0  | 254.9  | 279.5  |
| 75°    | 175.1  | 184.3  | 201.2  | 218.1  |
| 77.5°  | 135.1  | 147.4  | 156.6  | 170.5  |
| 80°    | 96.8   | 107.5  | 110.6  | 121.3  |
| 82.5°  | 64.5   | 70.6   | 76.8   | 79.9   |
| 85°    | 36.9   | 39.9   | 46.1   | 47.6   |
| 87.5°  | 13.8   | 15.4   | 18.4   | 21.5   |
| 90°    | 9.9    | 7.9    | 4.0    | 1.0    |
| 92.5°  | 33.6   | 28.7   | 20.7   | 14.8   |
| 95°    | 57.3   | 48.4   | 38.5   | 34.6   |
| 97.5°  | 81.0   | 68.2   | 57.3   | 51.4   |
| 100°   | 103.7  | 87.9   | 79.0   | 76.1   |
| 102.5° | 125.5  | 109.7  | 100.8  | 98.8   |
| 105°   | 146.2  | 131.4  | 124.5  | 120.5  |
| 107.5° | 168.0  | 154.1  | 147.2  | 144.2  |
| 110°   | 190.7  | 177.8  | 171.9  | 168.0  |

TEST NUMBER: P1009780

CATALOG NUMBER: S122RDIP-B1005D925UB30-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 345°  | 350°  | 355°  | 360°  |
|--------|-------|-------|-------|-------|
| 112.5° | 212.4 | 200.6 | 193.6 | 189.7 |
| 115°   | 235.1 | 223.3 | 217.4 | 212.4 |
| 117.5° | 256.9 | 246.0 | 240.1 | 236.1 |
| 120°   | 276.6 | 267.7 | 261.8 | 257.9 |
| 122.5° | 297.4 | 287.5 | 281.6 | 278.6 |
| 125°   | 317.1 | 305.3 | 299.4 | 296.4 |
| 127.5° | 335.9 | 323.1 | 315.2 | 311.2 |
| 130°   | 351.7 | 337.9 | 328.0 | 324.1 |
| 132.5° | 366.5 | 351.7 | 340.8 | 335.9 |
| 135°   | 378.4 | 363.6 | 351.7 | 347.8 |
| 137.5° | 391.2 | 375.4 | 363.6 | 358.6 |
| 140°   | 403.1 | 387.3 | 375.4 | 371.5 |
| 142.5° | 414.0 | 398.1 | 387.3 | 384.3 |
| 145°   | 425.8 | 411.0 | 401.1 | 397.2 |
| 147.5° | 437.7 | 423.8 | 414.0 | 411.0 |
| 150°   | 448.5 | 435.7 | 427.8 | 424.8 |
| 152.5° | 458.4 | 447.5 | 439.6 | 438.7 |
| 155°   | 469.3 | 458.4 | 452.5 | 451.5 |
| 157.5° | 478.2 | 468.3 | 463.4 | 462.4 |
| 160°   | 486.1 | 478.2 | 474.2 | 473.2 |
| 162.5° | 493.0 | 487.1 | 483.1 | 484.1 |
| 165°   | 498.9 | 493.0 | 491.0 | 492.0 |
| 167.5° | 503.9 | 499.9 | 497.9 | 498.9 |
| 170°   | 507.8 | 504.8 | 503.9 | 505.8 |
| 172.5° | 510.8 | 507.8 | 508.8 | 509.8 |
| 175°   | 512.8 | 510.8 | 511.8 | 512.8 |
| 177.5° | 513.7 | 511.8 | 512.8 | 514.7 |
| 180°   | 513.7 | 513.7 | 513.7 | 513.7 |

(END OF REPORT)