

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009798

Luminaire Tested: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009798
REPORT IS A COMBINATION OF REPORTS P988014 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7117.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	50	50	45
2	91	84	78	73	84	78	73	69	67	63	60	56	54	52	47	45	44	44	44	39
3	83	75	68	62	77	69	63	59	60	55	52	51	47	45	42	40	38	38	38	34
4	77	67	59	53	71	62	56	50	54	49	45	46	42	39	39	36	34	34	34	30
5	71	60	52	46	66	56	49	44	49	43	39	42	38	35	35	32	30	30	30	27
6	66	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27	27	27	24
7	61	49	42	36	56	46	39	35	40	35	31	35	31	28	30	27	24	24	24	22
8	57	45	38	32	53	42	36	31	37	32	28	32	28	25	28	25	22	22	22	20
9	53	41	34	29	49	39	32	28	34	29	25	30	26	23	26	23	20	20	20	18
10	50	38	31	27	46	36	30	25	32	27	23	28	24	21	24	21	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33644	33644	33644	33644
5°	33722	35735	33839	28548
10°	33352	37771	33587	23575
15°	32627	37783	33181	17710
20°	31757	31232	32448	14611
25°	30701	19515	31364	12430
30°	29353	12494	30153	10701
35°	27714	9603	28613	9158
40°	25888	8071	26993	8010
45°	23934	6870	24935	6725
50°	21933	5837	22959	5815
55°	19718	5072	20781	5006
60°	17749	3869	18689	3822
65°	15908	2912	16854	3303
70°	13880	2326	14967	2691
75°	11731	1782	12805	2035
80°	9317	1211	10020	1335
85°	6470	626	7091	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 30776 cd/sqm

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.6	2.8
10°-20°	562.7	7.9
20°-30°	724.2	10.2
30°-40°	687.1	9.7
40°-50°	588.8	8.3
50°-60°	448.4	6.3
60°-70°	282.8	4.0
70°-80°	141.1	2.0
80°-90°	39.4	0.6
90°-100°	192.6	2.7
100°-110°	678.3	9.5
110°-120°	712.4	10.0
120°-130°	586.1	8.2
130°-140°	470.8	6.6
140°-150°	355.6	5.0
150°-160°	250.0	3.5
160°-170°	147.2	2.1
170°-180°	47.9	0.7
0°-30°	1488.5	20.9
0°-40°	2175.6	30.6
0°-60°	3212.9	45.1
0°-90°	3676.2	51.7
90°-120°	1583.3	22.2
90°-150°	2995.8	42.1
90°-180°	3441.0	48.3
0°-180°	7117.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2125	2125	2125	2125	2125	
5°	2127	2365	2134	1889	2127	202
15°	2004	2669	2038	1251	2004	564
25°	1778	1424	1817	907	1778	817
35°	1459	702	1507	669	1459	913
45°	1096	487	1142	477	1096	846
55°	740	338	780	334	740	667
65°	448	176	474	199	448	444
75°	210	93	229	106	210	227
85°	46	27	50	28	46	52
90°	1	31	1	31	1	5
95°	33	108	33	108	33	34
105°	116	1071	116	1071	116	123
115°	204	1409	204	1409	204	203
125°	285	1143	285	1143	285	253
135°	334	947	334	947	334	258
145°	382	756	382	756	382	240
155°	434	636	434	636	434	200
165°	473	558	473	558	473	133
175°	493	503	493	503	493	47
180°	494	494	494	494	494	

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2138.7	2147.6	2152.0	2157.9	2171.2	2180.1	2193.4	2196.3	2194.8	2200.8	2184.5
5°	2126.9	2146.1	2163.8	2178.6	2202.2	2217.0	2233.2	2252.4	2256.9	2279.0	2265.7
7.5°	2110.7	2138.7	2163.8	2193.4	2228.8	2248.0	2273.1	2302.7	2316.0	2342.5	2349.9
10°	2084.1	2123.9	2166.8	2197.8	2246.5	2280.5	2304.1	2351.4	2382.4	2422.3	2416.4
12.5°	2041.2	2092.9	2150.5	2202.2	2265.7	2287.9	2332.2	2380.9	2420.8	2457.8	2490.2
15°	2004.3	2063.4	2126.9	2190.4	2262.8	2304.1	2348.5	2412.0	2454.8	2519.8	2547.9
17.5°	1954.1	2029.4	2104.7	2175.6	2261.3	2308.6	2363.2	2425.3	2488.8	2550.8	2573.0
20°	1902.4	1983.6	2064.9	2160.9	2258.4	2304.1	2360.3	2437.1	2499.1	2547.9	2547.9
22.5°	1840.4	1939.3	2032.4	2123.9	2230.3	2296.8	2354.4	2444.5	2488.8	2499.1	2459.2
25°	1778.3	1877.3	1979.2	2092.9	2214.0	2273.1	2338.1	2422.3	2437.1	2395.7	2292.3
27.5°	1704.5	1815.3	1930.5	2053.1	2180.1	2253.9	2313.0	2369.1	2341.1	2230.3	2069.3
30°	1629.1	1748.8	1878.8	1995.4	2149.1	2217.0	2267.2	2283.5	2194.8	2014.6	1806.4
32.5°	1550.9	1667.6	1804.9	1945.2	2100.3	2165.3	2197.8	2155.0	1992.5	1765.0	1511.0
35°	1459.3	1590.7	1734.0	1880.2	2033.9	2082.6	2101.8	1996.9	1788.7	1494.7	1242.2
37.5°	1376.6	1508.0	1661.6	1810.8	1960.0	1986.6	1967.4	1803.4	1539.1	1248.1	1001.4
40°	1279.1	1419.4	1570.1	1737.0	1859.6	1866.9	1819.7	1607.0	1279.1	1005.8	853.7
42.5°	1189.0	1330.8	1481.4	1651.3	1744.4	1719.2	1655.7	1376.6	1067.9	867.0	744.4
45°	1095.9	1230.4	1392.8	1543.5	1609.9	1550.9	1454.9	1158.0	896.5	745.9	651.4
47.5°	1005.8	1131.4	1292.4	1437.1	1449.0	1382.5	1268.8	970.4	776.9	655.8	579.0
50°	917.2	1042.8	1193.4	1313.1	1301.3	1209.7	1081.2	843.4	675.0	579.0	515.5
52.5°	828.6	942.3	1088.6	1183.1	1132.9	1044.3	917.2	714.9	589.3	505.1	456.4
55°	740.0	846.3	971.9	1050.2	970.4	868.5	778.4	613.0	511.0	443.1	406.2
57.5°	666.1	750.3	865.5	912.8	816.8	737.0	658.7	527.3	443.1	394.4	351.5
60°	584.9	661.7	756.2	784.3	685.3	620.3	553.9	446.1	379.6	336.8	308.7
62.5°	515.5	579.0	651.4	651.4	564.2	515.5	465.3	373.7	319.0	285.1	271.8
65°	447.5	493.3	545.0	539.1	465.3	422.4	382.5	308.7	267.3	243.7	230.4
67.5°	381.1	416.5	450.5	429.8	376.6	339.7	302.8	249.6	221.6	205.3	187.6
70°	320.5	348.6	366.3	347.1	293.9	262.9	236.3	200.9	178.7	158.0	147.7
72.5°	268.8	280.6	286.5	262.9	218.6	200.9	181.7	156.6	137.4	127.0	124.1
75°	209.7	220.1	215.6	197.9	161.0	147.7	132.9	115.2	110.8	104.9	101.9
77.5°	163.9	163.9	156.6	140.3	115.2	104.9	99.0	90.1	85.7	84.2	81.2
80°	116.7	115.2	110.8	93.1	78.3	72.4	72.4	66.5	65.0	62.0	62.0
82.5°	76.8	76.8	70.9	56.1	51.7	50.2	48.7	45.8	45.8	44.3	44.3
85°	45.8	42.8	35.4	31.0	29.5	29.5	28.1	26.6	28.1	26.6	26.6
87.5°	20.7	16.2	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8
90°	1.0	3.8	7.6	9.5	11.4	12.8	14.3	19.0	25.7	31.4	32.3
92.5°	14.3	20.0	27.6	32.3	39.9	45.2	50.4	76.0	112.1	144.4	146.3
95°	33.3	37.1	46.6	55.1	70.3	81.7	93.1	136.8	219.5	329.7	372.5
97.5°	49.4	55.1	65.6	77.9	95.0	107.8	120.7	176.7	291.7	469.4	607.2
100°	73.2	76.0	84.6	99.8	118.8	132.1	145.4	195.7	311.7	516.9	750.6
102.5°	95.0	96.9	105.5	120.7	140.6	153.9	167.2	212.8	312.6	498.8	755.4
105°	115.9	119.7	126.4	140.6	161.5	174.8	188.1	232.8	317.4	474.1	704.1
107.5°	138.7	141.6	148.2	161.5	182.4	195.7	209.0	252.7	327.8	460.8	656.6
110°	161.5	165.3	171.0	183.4	203.3	217.1	230.9	272.7	341.1	457.0	624.3

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	182.4	186.2	192.9	204.3	223.3	237.6	251.8	291.7	355.4	458.0	603.4
115°	204.3	209.0	214.7	226.1	245.1	258.0	270.8	311.7	369.6	461.8	589.1
117.5°	227.1	230.9	236.6	247.0	265.1	278.4	291.7	329.7	384.8	467.5	581.5
120°	248.0	251.8	257.5	266.0	285.0	298.4	311.7	348.7	400.0	473.2	574.8
122.5°	267.9	270.8	276.5	286.0	305.0	318.8	332.6	366.8	413.3	479.8	571.0
125°	285.0	287.9	293.6	305.0	324.0	337.3	350.6	384.8	427.6	486.5	566.3
127.5°	299.3	303.1	310.7	323.1	341.1	354.9	368.7	401.9	440.9	493.1	563.4
130°	311.7	315.5	325.0	338.3	357.3	370.6	383.9	417.1	453.2	500.7	561.5
132.5°	323.1	327.8	338.3	352.5	372.5	385.8	399.1	430.4	465.6	508.3	560.6
135°	334.5	338.3	349.7	363.9	385.8	399.1	412.4	442.8	476.0	514.0	559.6
137.5°	344.9	349.7	361.1	376.3	398.1	410.4	422.8	453.2	484.6	519.7	559.6
140°	357.3	361.1	372.5	387.7	408.6	421.0	433.3	461.8	491.2	523.5	558.7
142.5°	369.6	372.5	382.9	398.1	418.1	429.5	440.9	468.4	496.9	526.4	558.7
145°	382.0	385.8	395.3	409.5	428.5	439.0	449.4	475.1	501.7	528.3	556.8
147.5°	395.3	398.1	407.6	420.9	437.1	446.6	456.1	480.8	504.5	529.2	553.9
150°	408.6	411.4	419.0	431.4	445.6	454.2	462.7	484.6	506.4	528.3	551.1
152.5°	421.9	422.8	430.4	440.9	454.2	461.8	469.4	488.4	507.4	526.4	546.3
155°	434.2	435.2	440.9	451.3	461.8	468.9	476.0	492.2	508.3	524.5	540.6
157.5°	444.7	445.6	450.4	459.9	468.4	474.6	480.8	495.0	508.3	520.7	534.9
160°	455.1	456.1	459.9	467.5	475.1	480.3	485.5	496.9	508.3	517.8	529.2
162.5°	465.6	464.6	468.4	474.1	480.8	484.6	488.4	497.9	507.4	515.0	524.5
165°	473.2	472.2	474.1	479.8	484.6	487.4	490.3	498.8	505.5	511.2	517.8
167.5°	479.8	478.9	480.8	484.6	488.4	490.3	492.2	498.8	504.5	507.4	512.1
170°	486.5	484.6	485.5	488.4	490.3	491.7	493.1	497.9	502.6	504.5	507.4
172.5°	490.3	489.3	488.4	491.2	492.2	493.2	494.1	496.9	499.8	500.7	501.7
175°	493.1	492.2	491.2	493.1	493.1	493.6	494.1	496.0	497.9	496.9	497.9
177.5°	495.0	493.1	492.2	494.1	494.1	494.1	494.1	495.0	496.9	495.0	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2200.8	2203.7	2208.1	2228.8	2231.8	2237.7	2234.7	2234.7	2236.2	2233.2	2234.7
5°	2295.3	2299.7	2321.9	2347.0	2352.9	2347.0	2354.4	2364.7	2364.7	2364.7	2361.7
7.5°	2383.9	2400.2	2425.3	2462.2	2469.6	2477.0	2490.2	2481.4	2484.3	2497.6	2493.2
10°	2469.6	2493.2	2521.3	2552.3	2568.5	2578.9	2584.8	2598.1	2629.1	2593.6	2606.9
12.5°	2550.8	2584.8	2614.3	2648.3	2660.1	2673.4	2677.8	2689.6	2689.6	2688.2	2698.5
15°	2604.0	2635.0	2661.6	2683.7	2686.7	2683.7	2680.8	2682.3	2686.7	2669.0	2679.3
17.5°	2615.8	2618.7	2627.6	2618.7	2620.2	2589.2	2571.5	2567.1	2525.7	2527.2	2561.1
20°	2558.2	2508.0	2494.7	2445.9	2416.4	2336.6	2333.7	2311.5	2224.4	2251.0	2245.1
22.5°	2400.2	2314.5	2200.8	2144.6	2116.6	2032.4	1967.4	1921.6	1890.6	1859.6	1846.3
25°	2191.9	2053.1	1892.1	1781.3	1765.0	1686.8	1567.1	1511.0	1444.5	1423.8	1459.3
27.5°	1923.1	1742.9	1561.2	1391.3	1360.3	1289.4	1228.9	1189.0	1112.2	1107.8	1110.7
30°	1558.3	1376.6	1224.4	1113.7	1036.9	1004.4	964.5	935.0	903.9	915.7	918.7
32.5°	1280.6	1107.8	966.0	906.9	871.4	850.8	816.8	797.6	784.3	779.9	778.4
35°	1017.7	902.5	838.9	781.3	760.7	745.9	720.8	711.9	700.1	701.6	701.6
37.5°	871.4	775.4	728.2	698.6	679.4	672.0	655.8	646.9	639.5	636.6	641.0
40°	751.8	685.3	655.8	629.2	613.0	610.0	601.1	590.8	581.9	583.4	587.9
42.5°	664.7	626.3	590.8	570.1	558.3	553.9	546.5	539.1	539.1	534.7	533.2
45°	595.2	564.2	534.7	515.5	508.1	502.2	493.3	491.8	485.9	487.4	488.9
47.5°	533.2	508.1	485.9	466.7	459.4	457.9	449.0	443.1	443.1	441.6	440.2
50°	477.1	452.0	432.8	422.4	412.1	409.1	407.7	406.2	403.2	403.2	404.7
52.5°	431.3	406.2	391.4	382.5	376.6	373.7	373.7	372.2	372.2	372.2	370.7
55°	381.1	360.4	348.6	345.6	342.7	341.2	339.7	336.8	335.3	338.2	335.3
57.5°	333.8	326.4	316.1	313.1	305.7	305.7	301.3	298.4	295.4	298.4	298.4
60°	296.9	286.5	280.6	271.8	265.9	260.0	252.6	251.1	248.1	246.7	245.2
62.5°	258.5	249.6	234.8	221.6	212.7	206.8	203.8	202.4	202.4	200.9	200.9
65°	215.6	195.0	187.6	183.1	181.7	180.2	177.2	175.8	177.2	175.8	177.2
67.5°	168.4	165.4	161.0	158.0	156.6	155.1	155.1	153.6	153.6	153.6	153.6
70°	146.2	138.8	137.4	134.4	134.4	132.9	132.9	132.9	132.9	131.5	134.4
72.5°	121.1	116.7	115.2	113.7	113.7	113.7	112.3	112.3	112.3	110.8	112.3
75°	99.0	97.5	94.5	94.5	93.1	94.5	93.1	93.1	91.6	93.1	93.1
77.5°	79.8	78.3	76.8	76.8	75.3	75.3	75.3	75.3	75.3	75.3	76.8
80°	60.6	59.1	57.6	59.1	57.6	59.1	57.6	57.6	59.1	57.6	57.6
82.5°	44.3	42.8	42.8	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4
85°	26.6	25.1	25.1	26.6	25.1	26.6	25.1	25.1	25.1	26.6	26.6
87.5°	11.8	13.3	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.3
90°	31.4	30.4	28.5	30.4	30.9	31.4	31.4	31.4	31.4	31.4	31.4
92.5°	122.6	96.0	81.7	71.3	67.5	63.7	62.7	58.9	59.9	58.0	59.9
95°	325.9	248.9	191.0	151.1	140.6	130.2	117.8	110.2	107.4	108.3	107.4
97.5°	611.9	509.3	406.7	310.7	282.2	253.7	216.6	197.6	187.2	181.5	187.2
100°	887.5	867.5	749.7	619.5	562.0	504.5	425.7	384.8	357.3	340.2	357.3
102.5°	990.1	1102.2	1098.4	1011.9	950.2	888.4	801.0	724.0	687.9	663.2	687.9
105°	956.8	1154.4	1261.8	1274.2	1258.5	1242.8	1183.9	1125.0	1084.1	1070.8	1084.1
107.5°	886.5	1098.4	1258.0	1351.1	1370.1	1389.1	1388.2	1379.6	1367.3	1345.4	1367.3
110°	820.9	1021.4	1191.5	1313.1	1352.0	1391.0	1431.9	1450.0	1458.5	1457.6	1458.5

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	775.3	951.1	1112.6	1244.7	1290.8	1336.9	1397.7	1430.9	1449.0	1455.7	1449.0
115°	739.2	896.0	1042.3	1166.8	1215.8	1264.7	1332.1	1375.8	1400.5	1409.1	1400.5
117.5°	714.5	850.4	981.5	1097.4	1144.0	1190.6	1259.9	1306.5	1332.1	1338.8	1332.1
120°	695.5	818.1	935.9	1036.6	1079.8	1123.1	1189.6	1234.3	1261.8	1271.3	1261.8
122.5°	679.4	792.4	897.9	992.0	1030.0	1068.0	1125.9	1169.7	1193.4	1201.0	1193.4
125°	664.2	767.7	865.6	949.2	984.8	1020.5	1075.6	1111.7	1135.4	1143.0	1135.4
127.5°	649.9	743.0	833.3	913.1	946.4	979.6	1028.1	1062.3	1083.2	1088.9	1083.2
130°	635.7	719.3	801.0	876.1	907.4	938.8	985.3	1017.6	1036.6	1044.2	1036.6
132.5°	624.3	696.5	770.6	838.0	867.0	896.0	941.6	973.9	991.0	997.7	991.0
135°	613.8	675.6	738.3	801.0	827.6	854.2	895.1	926.4	943.5	947.3	943.5
137.5°	606.2	658.5	712.6	763.9	787.6	811.4	850.4	878.0	893.2	898.9	893.2
140°	599.6	642.3	687.9	731.6	752.5	773.4	803.8	828.5	842.8	848.5	842.8
142.5°	592.9	629.0	666.1	702.2	718.8	735.4	763.9	785.8	798.1	798.1	798.1
145°	587.2	616.7	648.0	677.5	691.2	705.0	727.8	744.0	753.5	756.3	753.5
147.5°	581.5	607.2	632.8	656.6	667.0	677.5	697.4	710.7	717.4	719.3	717.4
150°	573.9	596.7	617.6	637.6	646.2	654.7	668.9	680.3	686.0	687.0	686.0
152.5°	567.2	586.3	605.3	621.4	628.6	635.7	646.1	655.6	659.4	659.4	659.4
155°	558.7	576.7	592.0	606.2	611.4	616.7	627.1	633.8	637.6	635.7	637.6
157.5°	551.1	565.3	578.7	591.0	595.3	599.6	607.2	612.9	614.8	614.8	614.8
160°	542.5	554.9	565.3	575.8	579.2	582.5	589.1	593.9	594.8	594.8	594.8
162.5°	534.9	544.4	553.0	561.5	563.9	566.3	572.9	575.8	576.7	575.8	576.7
165°	526.4	534.0	540.6	547.3	549.2	551.1	554.9	558.7	558.7	557.7	558.7
167.5°	517.8	523.5	529.2	534.0	535.9	537.8	539.7	541.6	541.6	540.6	541.6
170°	511.2	515.9	518.8	522.6	523.6	524.5	525.4	528.3	527.3	525.4	527.3
172.5°	504.5	507.4	509.3	512.1	512.6	513.1	514.0	515.0	514.0	513.1	514.0
175°	498.8	501.7	502.6	503.6	504.0	504.5	504.5	505.5	504.5	502.6	504.5
177.5°	495.0	496.9	496.9	497.9	497.9	497.9	497.9	497.9	496.9	495.0	496.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2240.6	2230.3	2227.3	2230.3	2227.3	2228.8	2218.5	2180.1	2190.4	2174.2	2183.0
5°	2367.7	2358.8	2339.6	2336.6	2333.7	2330.7	2316.0	2282.0	2268.7	2246.5	2245.1
7.5°	2488.8	2488.8	2474.0	2463.7	2450.4	2440.0	2420.8	2370.6	2349.9	2323.3	2308.6
10°	2608.4	2570.0	2586.3	2575.9	2543.4	2537.5	2502.1	2472.5	2432.6	2406.1	2382.4
12.5°	2694.1	2682.3	2667.5	2658.6	2649.8	2630.6	2606.9	2531.6	2510.9	2457.8	2431.2
15°	2691.1	2683.7	2688.2	2688.2	2685.2	2680.8	2661.6	2606.9	2571.5	2519.8	2474.0
17.5°	2546.4	2565.6	2584.8	2598.1	2627.6	2640.9	2658.6	2626.1	2604.0	2559.7	2510.9
20°	2293.8	2341.1	2397.2	2409.0	2435.6	2513.9	2549.3	2577.4	2586.3	2571.5	2531.6
22.5°	1942.3	1982.2	2118.0	2115.1	2153.5	2246.5	2349.9	2434.1	2500.6	2537.5	2522.7
25°	1521.3	1577.5	1649.8	1704.5	1830.0	1968.9	2097.4	2231.8	2347.0	2448.9	2474.0
27.5°	1150.6	1224.4	1282.0	1354.4	1417.9	1581.9	1747.3	1957.0	2091.5	2284.9	2385.4
30°	930.5	964.5	1022.1	1056.1	1087.1	1212.6	1400.2	1607.0	1843.3	2066.3	2239.2
32.5°	794.6	818.3	861.1	875.9	908.4	992.6	1110.7	1299.8	1543.5	1813.8	2041.2
35°	713.4	738.5	747.4	760.7	787.2	840.4	921.7	1059.0	1279.1	1543.5	1815.3
37.5°	644.0	657.3	682.4	691.2	700.1	740.0	794.6	890.6	1036.9	1254.0	1555.3
40°	595.2	602.6	615.9	623.3	629.2	657.3	706.0	771.0	878.8	1044.3	1321.9
42.5°	543.5	552.4	561.3	570.1	577.5	599.7	629.2	691.2	763.6	889.2	1090.0
45°	493.3	499.2	509.6	515.5	525.8	543.5	570.1	613.0	678.0	757.7	920.2
47.5°	447.5	454.9	459.4	466.7	474.1	493.3	518.4	546.5	599.7	678.0	796.1
50°	406.2	415.0	420.9	422.4	428.3	446.1	466.7	497.8	531.7	592.3	695.7
52.5°	376.6	378.1	382.5	388.5	387.0	397.3	416.5	440.2	475.6	524.3	599.7
55°	342.7	347.1	350.1	351.5	351.5	360.4	370.7	392.9	420.9	460.8	524.3
57.5°	299.8	304.3	313.1	316.1	320.5	324.9	329.4	344.1	367.8	406.2	457.9
60°	255.5	258.5	267.3	273.2	276.2	288.0	293.9	305.7	319.0	347.1	395.8
62.5°	205.3	208.3	212.7	218.6	224.5	242.2	257.0	268.8	279.2	298.4	338.2
65°	178.7	180.2	183.1	184.6	186.1	193.5	206.8	223.0	242.2	257.0	280.6
67.5°	155.1	156.6	158.0	161.0	162.5	163.9	169.9	174.3	193.5	214.2	231.9
70°	132.9	135.9	137.4	137.4	138.8	141.8	144.7	150.7	156.6	166.9	189.1
72.5°	112.3	113.7	116.7	116.7	116.7	119.6	122.6	125.5	128.5	134.4	143.3
75°	93.1	96.0	96.0	96.0	97.5	97.5	100.4	103.4	106.3	110.8	113.7
77.5°	76.8	76.8	76.8	76.8	78.3	78.3	79.8	82.7	84.2	85.7	88.6
80°	57.6	59.1	59.1	59.1	60.6	60.6	60.6	63.5	65.0	65.0	67.9
82.5°	42.8	42.8	42.8	44.3	42.8	44.3	44.3	45.8	44.3	45.8	47.3
85°	26.6	26.6	26.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1	29.5
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	14.8	13.3	13.3
90°	31.4	31.4	31.4	30.9	30.4	28.5	30.4	31.4	32.3	31.4	25.7
92.5°	58.9	62.7	63.7	67.5	71.3	81.7	96.0	122.6	146.3	144.4	112.1
95°	110.2	117.8	130.2	140.6	151.1	191.0	248.9	325.9	372.5	329.7	219.5
97.5°	197.6	216.6	253.7	282.2	310.7	406.7	509.3	611.9	607.2	469.4	291.7
100°	384.8	425.7	504.5	562.0	619.5	749.7	867.5	887.5	750.6	516.9	311.7
102.5°	724.0	801.0	888.4	950.2	1011.9	1098.4	1102.2	990.1	755.4	498.8	312.6
105°	1125.0	1183.9	1242.8	1258.5	1274.2	1261.8	1154.4	956.8	704.1	474.1	317.4
107.5°	1379.6	1388.2	1389.1	1370.1	1351.1	1258.0	1098.4	886.5	656.6	460.8	327.8
110°	1450.0	1431.9	1391.0	1352.0	1313.1	1191.5	1021.4	820.9	624.3	457.0	341.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1430.9	1397.7	1336.9	1290.8	1244.7	1112.6	951.1	775.3	603.4	458.0	355.4
115°	1375.8	1332.1	1264.7	1215.8	1166.8	1042.3	896.0	739.2	589.1	461.8	369.6
117.5°	1306.5	1259.9	1190.6	1144.0	1097.4	981.5	850.4	714.5	581.5	467.5	384.8
120°	1234.3	1189.6	1123.1	1079.8	1036.6	935.9	818.1	695.5	574.8	473.2	400.0
122.5°	1169.7	1125.9	1068.0	1030.0	992.0	897.9	792.4	679.4	571.0	479.8	413.3
125°	1111.7	1075.6	1020.5	984.8	949.2	865.6	767.7	664.2	566.3	486.5	427.6
127.5°	1062.3	1028.1	979.6	946.4	913.1	833.3	743.0	649.9	563.4	493.1	440.9
130°	1017.6	985.3	938.8	907.4	876.1	801.0	719.3	635.7	561.5	500.7	453.2
132.5°	973.9	941.6	896.0	867.0	838.0	770.6	696.5	624.3	560.6	508.3	465.6
135°	926.4	895.1	854.2	827.6	801.0	738.3	675.6	613.8	559.6	514.0	476.0
137.5°	878.0	850.4	811.4	787.6	763.9	712.6	658.5	606.2	559.6	519.7	484.6
140°	828.5	803.8	773.4	752.5	731.6	687.9	642.3	599.6	558.7	523.5	491.2
142.5°	785.8	763.9	735.4	718.8	702.2	666.1	629.0	592.9	558.7	526.4	496.9
145°	744.0	727.8	705.0	691.2	677.5	648.0	616.7	587.2	556.8	528.3	501.7
147.5°	710.7	697.4	677.5	667.0	656.6	632.8	607.2	581.5	553.9	529.2	504.5
150°	680.3	668.9	654.7	646.2	637.6	617.6	596.7	573.9	551.1	528.3	506.4
152.5°	655.6	646.1	635.7	628.6	621.4	605.3	586.3	567.2	546.3	526.4	507.4
155°	633.8	627.1	616.7	611.4	606.2	592.0	576.7	558.7	540.6	524.5	508.3
157.5°	612.9	607.2	599.6	595.3	591.0	578.7	565.3	551.1	534.9	520.7	508.3
160°	593.9	589.1	582.5	579.2	575.8	565.3	554.9	542.5	529.2	517.8	508.3
162.5°	575.8	572.9	566.3	563.9	561.5	553.0	544.4	534.9	524.5	515.0	507.4
165°	558.7	554.9	551.1	549.2	547.3	540.6	534.0	526.4	517.8	511.2	505.5
167.5°	541.6	539.7	537.8	535.9	534.0	529.2	523.5	517.8	512.1	507.4	504.5
170°	528.3	525.4	524.5	523.6	522.6	518.8	515.9	511.2	507.4	504.5	502.6
172.5°	515.0	514.0	513.1	512.6	512.1	509.3	507.4	504.5	501.7	500.7	499.8
175°	505.5	504.5	504.5	504.0	503.6	502.6	501.7	498.8	497.9	496.9	497.9
177.5°	497.9	497.9	497.9	497.9	497.9	496.9	496.9	495.0	494.1	495.0	496.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2169.7	2162.4	2162.4	2157.9	2157.9	2134.3	2134.3	2141.7	2132.8	2122.5	2107.7
5°	2225.9	2209.6	2205.2	2199.3	2180.1	2150.5	2138.7	2134.3	2116.6	2094.4	2069.3
7.5°	2279.0	2252.4	2239.2	2225.9	2200.8	2159.4	2135.8	2119.5	2092.9	2059.0	2026.5
10°	2330.7	2296.8	2262.8	2246.5	2211.1	2159.4	2125.4	2098.8	2060.4	2014.6	1968.9
12.5°	2378.0	2307.1	2301.2	2268.7	2217.0	2157.9	2106.2	2067.8	2019.1	1965.9	1912.7
15°	2419.4	2347.0	2311.5	2282.0	2214.0	2140.2	2085.5	2038.3	1973.3	1912.7	1847.7
17.5°	2440.0	2361.7	2338.1	2289.4	2220.0	2123.9	2050.1	1992.5	1921.6	1849.2	1775.4
20°	2460.7	2369.1	2330.7	2296.8	2202.2	2092.9	2010.2	1943.8	1865.5	1779.8	1698.6
22.5°	2471.0	2369.1	2323.3	2276.1	2184.5	2059.0	1961.5	1883.2	1791.6	1704.5	1607.0
25°	2453.3	2360.3	2305.6	2256.9	2153.5	2017.6	1905.4	1816.7	1719.2	1620.3	1521.3
27.5°	2409.0	2339.6	2276.1	2225.9	2110.7	1964.4	1846.3	1745.8	1645.4	1534.6	1434.2
30°	2326.3	2295.3	2245.1	2188.9	2063.4	1917.2	1776.9	1673.5	1562.7	1451.9	1347.0
32.5°	2197.8	2224.4	2191.9	2143.2	2007.3	1852.2	1703.0	1598.1	1477.0	1357.4	1261.4
35°	2041.2	2135.8	2118.0	2084.1	1948.2	1782.8	1633.6	1506.6	1385.4	1264.3	1168.3
37.5°	1869.9	2013.2	2027.9	2007.3	1880.2	1711.9	1547.9	1423.8	1299.8	1177.2	1079.7
40°	1635.1	1855.1	1902.4	1911.3	1809.3	1626.2	1454.9	1333.7	1211.2	1091.5	973.4
42.5°	1419.4	1697.1	1756.2	1793.1	1719.2	1542.0	1369.2	1234.8	1113.7	1005.8	887.7
45°	1217.1	1506.6	1602.6	1649.8	1617.3	1446.0	1267.3	1141.7	1031.0	932.0	818.3
47.5°	1008.8	1299.8	1434.2	1509.5	1509.5	1348.5	1169.8	1045.7	939.4	855.2	754.8
50°	870.0	1112.2	1251.0	1350.0	1376.6	1249.6	1081.2	960.1	859.6	768.0	691.2
52.5°	741.5	958.6	1073.8	1177.2	1254.0	1143.2	982.2	872.9	774.0	688.3	627.7
55°	641.0	803.5	908.4	1022.1	1107.8	1035.4	886.2	779.9	694.2	623.3	571.6
57.5°	545.0	686.8	772.5	872.9	964.5	909.8	790.2	698.6	623.3	561.3	515.5
60°	463.8	579.0	645.5	723.7	837.5	799.1	700.1	615.9	555.4	499.2	460.8
62.5°	394.4	485.9	542.1	598.2	701.6	683.9	607.1	542.1	490.4	443.1	410.6
65°	323.5	398.8	443.1	491.8	574.6	581.9	519.9	474.1	426.9	385.5	356.0
67.5°	261.4	320.5	360.4	401.7	468.2	488.9	446.1	407.7	367.8	333.8	307.2
70°	211.2	252.6	282.1	314.6	369.3	394.4	372.2	345.6	313.1	285.1	261.4
72.5°	166.9	193.5	211.2	236.3	280.6	305.7	304.3	280.6	257.0	237.8	218.6
75°	122.6	143.3	158.0	174.3	209.7	233.4	239.3	228.9	205.3	190.5	175.8
77.5°	93.1	104.9	112.3	124.1	149.2	169.9	178.7	175.8	159.5	147.7	137.4
80°	70.9	73.9	76.8	81.2	101.9	121.1	127.0	125.5	116.7	112.3	100.4
82.5°	50.2	51.7	53.2	54.6	62.0	78.3	84.2	87.1	79.8	75.3	65.0
85°	29.5	31.0	31.0	34.0	35.4	39.9	50.2	50.2	48.7	42.8	41.4
87.5°	14.8	14.8	13.3	13.3	14.8	16.2	19.2	22.2	19.2	17.7	16.2
90°	19.0	14.3	12.8	11.4	9.5	7.6	3.8	1.0	3.8	7.6	9.5
92.5°	76.0	50.4	45.2	39.9	32.3	27.6	20.0	14.3	20.0	27.6	32.3
95°	136.8	93.1	81.7	70.3	55.1	46.6	37.1	33.3	37.1	46.6	55.1
97.5°	176.7	120.7	107.8	95.0	77.9	65.6	55.1	49.4	55.1	65.6	77.9
100°	195.7	145.4	132.1	118.8	99.8	84.6	76.0	73.2	76.0	84.6	99.8
102.5°	212.8	167.2	153.9	140.6	120.7	105.5	96.9	95.0	96.9	105.5	120.7
105°	232.8	188.1	174.8	161.5	140.6	126.4	119.7	115.9	119.7	126.4	140.6
107.5°	252.7	209.0	195.7	182.4	161.5	148.2	141.6	138.7	141.6	148.2	161.5
110°	272.7	230.9	217.1	203.3	183.4	171.0	165.3	161.5	165.3	171.0	183.4

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	291.7	251.8	237.6	223.3	204.3	192.9	186.2	182.4	186.2	192.9	204.3
115°	311.7	270.8	258.0	245.1	226.1	214.7	209.0	204.3	209.0	214.7	226.1
117.5°	329.7	291.7	278.4	265.1	247.0	236.6	230.9	227.1	230.9	236.6	247.0
120°	348.7	311.7	298.4	285.0	266.0	257.5	251.8	248.0	251.8	257.5	266.0
122.5°	366.8	332.6	318.8	305.0	286.0	276.5	270.8	267.9	270.8	276.5	286.0
125°	384.8	350.6	337.3	324.0	305.0	293.6	287.9	285.0	287.9	293.6	305.0
127.5°	401.9	368.7	354.9	341.1	323.1	310.7	303.1	299.3	303.1	310.7	323.1
130°	417.1	383.9	370.6	357.3	338.3	325.0	315.5	311.7	315.5	325.0	338.3
132.5°	430.4	399.1	385.8	372.5	352.5	338.3	327.8	323.1	327.8	338.3	352.5
135°	442.8	412.4	399.1	385.8	363.9	349.7	338.3	334.5	338.3	349.7	363.9
137.5°	453.2	422.8	410.4	398.1	376.3	361.1	349.7	344.9	349.7	361.1	376.3
140°	461.8	433.3	421.0	408.6	387.7	372.5	361.1	357.3	361.1	372.5	387.7
142.5°	468.4	440.9	429.5	418.1	398.1	382.9	372.5	369.6	372.5	382.9	398.1
145°	475.1	449.4	439.0	428.5	409.5	395.3	385.8	382.0	385.8	395.3	409.5
147.5°	480.8	456.1	446.6	437.1	420.9	407.6	398.1	395.3	398.1	407.6	420.9
150°	484.6	462.7	454.2	445.6	431.4	419.0	411.4	408.6	411.4	419.0	431.4
152.5°	488.4	469.4	461.8	454.2	440.9	430.4	422.8	421.9	422.8	430.4	440.9
155°	492.2	476.0	468.9	461.8	451.3	440.9	435.2	434.2	435.2	440.9	451.3
157.5°	495.0	480.8	474.6	468.4	459.9	450.4	445.6	444.7	445.6	450.4	459.9
160°	496.9	485.5	480.3	475.1	467.5	459.9	456.1	455.1	456.1	459.9	467.5
162.5°	497.9	488.4	484.6	480.8	474.1	468.4	464.6	465.6	464.6	468.4	474.1
165°	498.8	490.3	487.4	484.6	479.8	474.1	472.2	473.2	472.2	474.1	479.8
167.5°	498.8	492.2	490.3	488.4	484.6	480.8	478.9	479.8	478.9	480.8	484.6
170°	497.9	493.1	491.7	490.3	488.4	485.5	484.6	486.5	484.6	485.5	488.4
172.5°	496.9	494.1	493.2	492.2	491.2	488.4	489.3	490.3	489.3	488.4	491.2
175°	496.0	494.1	493.6	493.1	493.1	491.2	492.2	493.1	492.2	491.2	493.1
177.5°	495.0	494.1	494.1	494.1	494.1	492.2	493.1	495.0	493.1	492.2	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2101.8	2103.3	2107.7	2094.4	2073.7	2064.9	2038.3	2033.9	2029.4	2029.4	2033.9
5°	2054.5	2048.6	2050.1	2025.0	1995.4	1977.7	1940.8	1946.7	1927.5	1915.7	1918.6
7.5°	2002.8	1986.6	1985.1	1952.6	1915.7	1883.2	1844.8	1835.9	1818.2	1797.5	1788.7
10°	1937.8	1926.0	1903.9	1866.9	1819.7	1793.1	1741.4	1710.4	1706.0	1674.9	1663.1
12.5°	1871.4	1850.7	1828.5	1776.9	1723.7	1680.8	1642.4	1608.5	1584.8	1558.3	1540.5
15°	1794.6	1769.5	1744.4	1689.7	1627.7	1584.8	1527.2	1477.0	1407.6	1352.9	1321.9
17.5°	1710.4	1682.3	1648.3	1587.8	1527.2	1468.2	1361.8	1302.7	1254.0	1221.5	1202.3
20°	1623.2	1592.2	1558.3	1497.7	1392.8	1289.4	1230.4	1184.6	1155.0	1122.5	1098.9
22.5°	1531.7	1499.2	1462.2	1367.7	1256.9	1184.6	1138.8	1095.9	1053.1	1035.4	1023.6
25°	1446.0	1416.5	1369.2	1240.7	1153.5	1087.1	1035.4	1007.3	985.2	961.5	939.4
27.5°	1357.4	1302.7	1236.3	1128.4	1073.8	1005.8	968.9	948.2	909.8	893.6	883.3
30°	1251.0	1190.5	1127.0	1050.2	986.6	939.4	905.4	871.4	849.3	833.0	815.3
32.5°	1143.2	1085.6	1045.7	966.0	918.7	870.0	837.5	816.8	784.3	774.0	766.6
35°	1050.2	1001.4	966.0	901.0	856.7	812.4	788.7	757.7	737.0	717.8	706.0
37.5°	958.6	932.0	895.1	840.4	793.2	757.7	725.2	714.9	686.8	676.5	664.7
40°	895.1	855.2	824.2	776.9	737.0	698.6	678.0	654.3	635.1	618.9	614.4
42.5°	818.3	788.7	771.0	719.3	678.0	655.8	630.7	604.1	589.3	576.0	559.8
45°	760.7	734.1	709.0	667.6	630.7	602.6	580.5	562.7	537.6	531.7	506.6
47.5°	700.1	673.5	654.3	613.0	579.0	552.4	536.2	512.5	491.8	478.6	466.7
50°	639.5	617.4	599.7	564.2	534.7	506.6	484.5	460.8	452.0	429.8	422.4
52.5°	581.9	567.2	548.0	514.0	484.5	460.8	437.2	418.0	404.7	392.9	384.0
55°	533.2	509.6	500.7	463.8	438.7	413.6	392.9	381.1	364.8	357.4	350.1
57.5°	478.6	465.3	450.5	422.4	394.4	370.7	356.0	338.2	329.4	320.5	314.6
60°	431.3	412.1	400.3	376.6	351.5	329.4	316.1	302.8	291.0	283.6	271.8
62.5°	376.6	361.9	354.5	329.4	308.7	288.0	276.2	262.9	254.0	240.8	226.0
65°	329.4	317.6	308.7	288.0	268.8	249.6	237.8	221.6	209.7	202.4	200.9
67.5°	288.0	279.2	265.9	246.7	227.5	212.7	199.4	186.1	184.6	181.7	181.7
70°	242.2	233.4	226.0	205.3	189.1	172.8	169.9	165.4	161.0	159.5	156.6
72.5°	202.4	195.0	186.1	168.4	152.1	147.7	144.7	141.8	137.4	135.9	134.4
75°	163.9	153.6	147.7	131.5	127.0	124.1	121.1	116.7	113.7	112.3	109.3
77.5°	125.5	115.2	115.2	106.3	103.4	99.0	96.0	93.1	91.6	88.6	88.6
80°	88.6	88.6	85.7	81.2	76.8	75.3	70.9	69.4	67.9	69.4	66.5
82.5°	65.0	59.1	59.1	56.1	53.2	51.7	48.7	48.7	47.3	47.3	47.3
85°	36.9	36.9	35.4	32.5	31.0	31.0	29.5	29.5	28.1	28.1	26.6
87.5°	14.8	13.3	14.8	13.3	13.3	11.8	11.8	11.8	10.3	11.8	10.3
90°	11.4	12.8	14.3	19.0	25.7	31.4	32.3	31.4	30.4	28.5	30.4
92.5°	39.9	45.2	50.4	76.0	112.1	144.4	146.3	122.6	96.0	81.7	71.3
95°	70.3	81.7	93.1	136.8	219.5	329.7	372.5	325.9	248.9	191.0	151.1
97.5°	95.0	107.8	120.7	176.7	291.7	469.4	607.2	611.9	509.3	406.7	310.7
100°	118.8	132.1	145.4	195.7	311.7	516.9	750.6	887.5	867.5	749.7	619.5
102.5°	140.6	153.9	167.2	212.8	312.6	498.8	755.4	990.1	1102.2	1098.4	1011.9
105°	161.5	174.8	188.1	232.8	317.4	474.1	704.1	956.8	1154.4	1261.8	1274.2
107.5°	182.4	195.7	209.0	252.7	327.8	460.8	656.6	886.5	1098.4	1258.0	1351.1
110°	203.3	217.1	230.9	272.7	341.1	457.0	624.3	820.9	1021.4	1191.5	1313.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	223.3	237.6	251.8	291.7	355.4	458.0	603.4	775.3	951.1	1112.6	1244.7
115°	245.1	258.0	270.8	311.7	369.6	461.8	589.1	739.2	896.0	1042.3	1166.8
117.5°	265.1	278.4	291.7	329.7	384.8	467.5	581.5	714.5	850.4	981.5	1097.4
120°	285.0	298.4	311.7	348.7	400.0	473.2	574.8	695.5	818.1	935.9	1036.6
122.5°	305.0	318.8	332.6	366.8	413.3	479.8	571.0	679.4	792.4	897.9	992.0
125°	324.0	337.3	350.6	384.8	427.6	486.5	566.3	664.2	767.7	865.6	949.2
127.5°	341.1	354.9	368.7	401.9	440.9	493.1	563.4	649.9	743.0	833.3	913.1
130°	357.3	370.6	383.9	417.1	453.2	500.7	561.5	635.7	719.3	801.0	876.1
132.5°	372.5	385.8	399.1	430.4	465.6	508.3	560.6	624.3	696.5	770.6	838.0
135°	385.8	399.1	412.4	442.8	476.0	514.0	559.6	613.8	675.6	738.3	801.0
137.5°	398.1	410.4	422.8	453.2	484.6	519.7	559.6	606.2	658.5	712.6	763.9
140°	408.6	421.0	433.3	461.8	491.2	523.5	558.7	599.6	642.3	687.9	731.6
142.5°	418.1	429.5	440.9	468.4	496.9	526.4	558.7	592.9	629.0	666.1	702.2
145°	428.5	439.0	449.4	475.1	501.7	528.3	556.8	587.2	616.7	648.0	677.5
147.5°	437.1	446.6	456.1	480.8	504.5	529.2	553.9	581.5	607.2	632.8	656.6
150°	445.6	454.2	462.7	484.6	506.4	528.3	551.1	573.9	596.7	617.6	637.6
152.5°	454.2	461.8	469.4	488.4	507.4	526.4	546.3	567.2	586.3	605.3	621.4
155°	461.8	468.9	476.0	492.2	508.3	524.5	540.6	558.7	576.7	592.0	606.2
157.5°	468.4	474.6	480.8	495.0	508.3	520.7	534.9	551.1	565.3	578.7	591.0
160°	475.1	480.3	485.5	496.9	508.3	517.8	529.2	542.5	554.9	565.3	575.8
162.5°	480.8	484.6	488.4	497.9	507.4	515.0	524.5	534.9	544.4	553.0	561.5
165°	484.6	487.4	490.3	498.8	505.5	511.2	517.8	526.4	534.0	540.6	547.3
167.5°	488.4	490.3	492.2	498.8	504.5	507.4	512.1	517.8	523.5	529.2	534.0
170°	490.3	491.7	493.1	497.9	502.6	504.5	507.4	511.2	515.9	518.8	522.6
172.5°	492.2	493.2	494.1	496.9	499.8	500.7	501.7	504.5	507.4	509.3	512.1
175°	493.1	493.6	494.1	496.0	497.9	496.9	497.9	498.8	501.7	502.6	503.6
177.5°	494.1	494.1	494.1	495.0	496.9	495.0	494.1	495.0	496.9	496.9	497.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2033.9	2030.9	2022.0	2025.0	2020.6	2020.6	2017.6	2017.6	2017.6	2025.0	2020.6
5°	1923.1	1912.7	1902.4	1898.0	1893.5	1889.1	1889.1	1887.6	1900.9	1898.0	1909.8
7.5°	1785.7	1782.8	1762.1	1762.1	1754.7	1751.7	1759.1	1760.6	1762.1	1765.0	1772.4
10°	1663.1	1655.7	1626.2	1629.1	1624.7	1618.8	1623.2	1620.3	1630.6	1633.6	1630.6
12.5°	1518.4	1505.1	1472.6	1456.3	1438.6	1425.3	1441.6	1429.8	1471.1	1482.9	1515.4
15°	1326.4	1301.3	1279.1	1279.1	1262.8	1251.0	1258.4	1271.7	1280.6	1293.9	1299.8
17.5°	1197.9	1187.5	1169.8	1159.5	1155.0	1150.6	1150.6	1156.5	1175.7	1174.2	1186.0
20°	1088.6	1082.7	1073.8	1060.5	1056.1	1053.1	1053.1	1053.1	1066.4	1078.2	1085.6
22.5°	1013.2	1008.8	1002.9	985.2	976.3	973.4	980.7	985.2	995.5	1004.4	1011.8
25°	937.9	927.6	917.2	911.3	906.9	906.9	909.8	911.3	915.7	920.2	929.0
27.5°	875.9	868.5	853.7	837.5	837.5	833.0	836.0	838.9	849.3	864.1	871.4
30°	806.5	805.0	799.1	793.2	787.2	784.3	790.2	794.6	796.1	803.5	803.5
32.5°	756.2	745.9	735.6	729.6	726.7	725.2	726.7	732.6	732.6	741.5	751.8
35°	706.0	700.1	689.8	679.4	676.5	669.1	675.0	680.9	691.2	695.7	700.1
37.5°	651.4	644.0	639.5	636.6	630.7	632.2	627.7	636.6	645.5	644.0	646.9
40°	610.0	596.7	583.4	581.9	580.5	579.0	579.0	580.5	586.4	592.3	601.1
42.5°	556.8	552.4	540.6	528.8	525.8	522.9	519.9	525.8	537.6	548.0	552.4
45°	502.2	496.3	493.3	484.5	478.6	477.1	474.1	481.5	491.8	496.3	499.2
47.5°	452.0	450.5	441.6	443.1	438.7	440.2	438.7	443.1	443.1	447.5	450.5
50°	418.0	413.6	409.1	406.2	401.7	401.7	400.3	401.7	407.7	413.6	412.1
52.5°	384.0	376.6	375.2	373.7	370.7	373.7	369.3	370.7	376.6	379.6	378.1
55°	344.1	342.7	339.7	336.8	335.3	333.8	333.8	333.8	339.7	344.1	345.6
57.5°	313.1	305.7	299.8	299.8	293.9	292.4	295.4	296.9	301.3	304.3	307.2
60°	270.3	267.3	258.5	254.0	245.2	243.7	243.7	249.6	257.0	267.3	270.3
62.5°	224.5	220.1	218.6	218.6	218.6	218.6	218.6	218.6	218.6	220.1	220.1
65°	199.4	200.9	199.4	197.9	199.4	199.4	197.9	197.9	197.9	199.4	200.9
67.5°	178.7	177.2	178.7	177.2	175.8	175.8	174.3	175.8	177.2	178.7	178.7
70°	155.1	155.1	153.6	155.1	153.6	152.1	150.7	150.7	153.6	155.1	155.1
72.5°	132.9	132.9	131.5	131.5	128.5	128.5	130.0	128.5	128.5	132.9	132.9
75°	110.8	109.3	107.8	107.8	106.3	106.3	106.3	104.9	107.8	107.8	109.3
77.5°	87.1	87.1	87.1	85.7	85.7	84.2	84.2	85.7	85.7	85.7	87.1
80°	66.5	66.5	66.5	65.0	63.5	63.5	63.5	63.5	63.5	65.0	63.5
82.5°	45.8	45.8	45.8	45.8	45.8	44.3	44.3	44.3	45.8	45.8	44.3
85°	28.1	26.6	28.1	28.1	26.6	28.1	26.6	26.6	25.1	25.1	26.6
87.5°	11.8	10.3	8.9	8.9	10.3	8.9	8.9	8.9	10.3	8.9	8.9
90°	30.9	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	31.4	30.9
92.5°	67.5	63.7	62.7	58.9	59.9	58.0	59.9	58.9	62.7	63.7	67.5
95°	140.6	130.2	117.8	110.2	107.4	108.3	107.4	110.2	117.8	130.2	140.6
97.5°	282.2	253.7	216.6	197.6	187.2	181.5	187.2	197.6	216.6	253.7	282.2
100°	562.0	504.5	425.7	384.8	357.3	340.2	357.3	384.8	425.7	504.5	562.0
102.5°	950.2	888.4	801.0	724.0	687.9	663.2	687.9	724.0	801.0	888.4	950.2
105°	1258.5	1242.8	1183.9	1125.0	1084.1	1070.8	1084.1	1125.0	1183.9	1242.8	1258.5
107.5°	1370.1	1389.1	1388.2	1379.6	1367.3	1345.4	1367.3	1379.6	1388.2	1389.1	1370.1
110°	1352.0	1391.0	1431.9	1450.0	1458.5	1457.6	1458.5	1450.0	1431.9	1391.0	1352.0

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1290.8	1336.9	1397.7	1430.9	1449.0	1455.7	1449.0	1430.9	1397.7	1336.9	1290.8
115°	1215.8	1264.7	1332.1	1375.8	1400.5	1409.1	1400.5	1375.8	1332.1	1264.7	1215.8
117.5°	1144.0	1190.6	1259.9	1306.5	1332.1	1338.8	1332.1	1306.5	1259.9	1190.6	1144.0
120°	1079.8	1123.1	1189.6	1234.3	1261.8	1271.3	1261.8	1234.3	1189.6	1123.1	1079.8
122.5°	1030.0	1068.0	1125.9	1169.7	1193.4	1201.0	1193.4	1169.7	1125.9	1068.0	1030.0
125°	984.8	1020.5	1075.6	1111.7	1135.4	1143.0	1135.4	1111.7	1075.6	1020.5	984.8
127.5°	946.4	979.6	1028.1	1062.3	1083.2	1088.9	1083.2	1062.3	1028.1	979.6	946.4
130°	907.4	938.8	985.3	1017.6	1036.6	1044.2	1036.6	1017.6	985.3	938.8	907.4
132.5°	867.0	896.0	941.6	973.9	991.0	997.7	991.0	973.9	941.6	896.0	867.0
135°	827.6	854.2	895.1	926.4	943.5	947.3	943.5	926.4	895.1	854.2	827.6
137.5°	787.6	811.4	850.4	878.0	893.2	898.9	893.2	878.0	850.4	811.4	787.6
140°	752.5	773.4	803.8	828.5	842.8	848.5	842.8	828.5	803.8	773.4	752.5
142.5°	718.8	735.4	763.9	785.8	798.1	798.1	798.1	785.8	763.9	735.4	718.8
145°	691.2	705.0	727.8	744.0	753.5	756.3	753.5	744.0	727.8	705.0	691.2
147.5°	667.0	677.5	697.4	710.7	717.4	719.3	717.4	710.7	697.4	677.5	667.0
150°	646.2	654.7	668.9	680.3	686.0	687.0	686.0	680.3	668.9	654.7	646.2
152.5°	628.6	635.7	646.1	655.6	659.4	659.4	659.4	655.6	646.1	635.7	628.6
155°	611.4	616.7	627.1	633.8	637.6	635.7	637.6	633.8	627.1	616.7	611.4
157.5°	595.3	599.6	607.2	612.9	614.8	614.8	614.8	612.9	607.2	599.6	595.3
160°	579.2	582.5	589.1	593.9	594.8	594.8	594.8	593.9	589.1	582.5	579.2
162.5°	563.9	566.3	572.9	575.8	576.7	575.8	576.7	575.8	572.9	566.3	563.9
165°	549.2	551.1	554.9	558.7	558.7	557.7	558.7	558.7	554.9	551.1	549.2
167.5°	535.9	537.8	539.7	541.6	541.6	540.6	541.6	541.6	539.7	537.8	535.9
170°	523.6	524.5	525.4	528.3	527.3	525.4	527.3	528.3	525.4	524.5	523.6
172.5°	512.6	513.1	514.0	515.0	514.0	513.1	514.0	515.0	514.0	513.1	512.6
175°	504.0	504.5	504.5	505.5	504.5	502.6	504.5	505.5	504.5	504.5	504.0
177.5°	497.9	497.9	497.9	497.9	496.9	495.0	496.9	497.9	497.9	497.9	497.9
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2025.0	2032.4	2029.4	2013.2	2029.4	2033.9	2042.7	2051.6	2057.5	2066.3	2073.7
5°	1898.0	1912.7	1921.6	1912.7	1942.3	1946.7	1967.4	1979.2	1996.9	2011.7	2023.5
7.5°	1778.3	1790.1	1807.9	1810.8	1828.5	1849.2	1878.8	1908.3	1936.4	1951.1	1964.4
10°	1649.8	1670.5	1697.1	1691.2	1717.8	1750.3	1781.3	1828.5	1852.2	1878.8	1902.4
12.5°	1521.3	1534.6	1570.1	1581.9	1620.3	1645.4	1688.2	1717.8	1776.9	1807.9	1828.5
15°	1296.8	1351.5	1395.8	1449.0	1499.2	1546.4	1584.8	1638.0	1689.7	1713.3	1747.3
17.5°	1194.9	1220.0	1246.6	1273.2	1338.2	1422.4	1490.3	1547.9	1592.2	1623.2	1663.1
20°	1088.6	1113.7	1143.2	1168.3	1208.2	1268.8	1352.9	1451.9	1505.1	1537.6	1576.0
22.5°	1013.2	1036.9	1056.1	1078.2	1109.2	1153.5	1217.1	1339.7	1410.6	1450.4	1484.4
25°	932.0	961.5	982.2	998.5	1023.6	1072.3	1124.0	1193.4	1320.5	1351.5	1398.7
27.5°	875.9	884.7	908.4	933.5	958.6	985.2	1038.3	1097.4	1183.1	1251.0	1308.6
30°	809.4	831.6	853.7	864.1	886.2	924.6	957.1	1020.6	1087.1	1140.3	1209.7
32.5°	759.2	772.5	787.2	812.4	833.0	859.6	892.1	945.3	1001.4	1035.4	1088.6
35°	703.1	711.9	742.9	753.3	774.0	800.5	833.0	874.4	935.0	961.5	999.9
37.5°	649.9	670.6	679.4	703.1	722.3	748.8	772.5	819.7	859.6	890.6	926.1
40°	608.5	617.4	633.6	654.3	670.6	691.2	720.8	754.8	797.6	822.7	853.7
42.5°	558.3	565.7	586.4	598.2	624.8	644.0	661.7	703.1	741.5	760.7	791.7
45°	503.7	521.4	534.7	558.3	573.1	596.7	618.9	648.4	683.9	706.0	723.7
47.5°	456.4	474.1	487.4	509.6	533.2	543.5	567.2	598.2	630.7	648.4	673.5
50°	418.0	423.9	449.0	459.4	484.5	505.1	521.4	548.0	583.4	593.8	614.4
52.5°	381.1	385.5	401.7	415.0	437.2	454.9	475.6	500.7	530.2	546.5	562.7
55°	348.6	351.5	358.9	373.7	388.5	410.6	429.8	453.4	478.6	496.3	511.0
57.5°	311.7	317.6	323.5	332.3	347.1	367.8	388.5	410.6	431.3	443.1	462.3
60°	268.8	277.7	288.0	298.4	308.7	323.5	347.1	367.8	387.0	397.3	412.1
62.5°	223.0	240.8	249.6	261.4	270.3	283.6	301.3	324.9	338.2	351.5	363.3
65°	200.9	202.4	203.8	215.6	231.9	245.2	261.4	279.2	299.8	308.7	317.6
67.5°	178.7	180.2	183.1	184.6	190.5	205.3	223.0	242.2	258.5	264.4	273.2
70°	156.6	156.6	162.5	163.9	165.4	166.9	181.7	200.9	215.6	223.0	233.4
72.5°	132.9	134.4	137.4	138.8	141.8	144.7	149.2	159.5	177.2	184.6	196.4
75°	109.3	110.8	112.3	113.7	118.2	119.6	124.1	130.0	137.4	146.2	153.6
77.5°	87.1	87.1	88.6	91.6	94.5	96.0	100.4	103.4	106.3	110.8	116.7
80°	65.0	66.5	66.5	69.4	69.4	70.9	72.4	76.8	79.8	82.7	85.7
82.5°	44.3	47.3	47.3	47.3	48.7	50.2	51.7	51.7	54.6	56.1	60.6
85°	26.6	28.1	28.1	28.1	26.6	29.5	29.5	31.0	31.0	31.0	32.5
87.5°	10.3	8.9	10.3	10.3	10.3	11.8	10.3	10.3	11.8	13.3	13.3
90°	30.4	28.5	30.4	31.4	32.3	31.4	25.7	19.0	14.3	12.8	11.4
92.5°	71.3	81.7	96.0	122.6	146.3	144.4	112.1	76.0	50.4	45.2	39.9
95°	151.1	191.0	248.9	325.9	372.5	329.7	219.5	136.8	93.1	81.7	70.3
97.5°	310.7	406.7	509.3	611.9	607.2	469.4	291.7	176.7	120.7	107.8	95.0
100°	619.5	749.7	867.5	887.5	750.6	516.9	311.7	195.7	145.4	132.1	118.8
102.5°	1011.9	1098.4	1102.2	990.1	755.4	498.8	312.6	212.8	167.2	153.9	140.6
105°	1274.2	1261.8	1154.4	956.8	704.1	474.1	317.4	232.8	188.1	174.8	161.5
107.5°	1351.1	1258.0	1098.4	886.5	656.6	460.8	327.8	252.7	209.0	195.7	182.4
110°	1313.1	1191.5	1021.4	820.9	624.3	457.0	341.1	272.7	230.9	217.1	203.3

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1244.7	1112.6	951.1	775.3	603.4	458.0	355.4	291.7	251.8	237.6	223.3
115°	1166.8	1042.3	896.0	739.2	589.1	461.8	369.6	311.7	270.8	258.0	245.1
117.5°	1097.4	981.5	850.4	714.5	581.5	467.5	384.8	329.7	291.7	278.4	265.1
120°	1036.6	935.9	818.1	695.5	574.8	473.2	400.0	348.7	311.7	298.4	285.0
122.5°	992.0	897.9	792.4	679.4	571.0	479.8	413.3	366.8	332.6	318.8	305.0
125°	949.2	865.6	767.7	664.2	566.3	486.5	427.6	384.8	350.6	337.3	324.0
127.5°	913.1	833.3	743.0	649.9	563.4	493.1	440.9	401.9	368.7	354.9	341.1
130°	876.1	801.0	719.3	635.7	561.5	500.7	453.2	417.1	383.9	370.6	357.3
132.5°	838.0	770.6	696.5	624.3	560.6	508.3	465.6	430.4	399.1	385.8	372.5
135°	801.0	738.3	675.6	613.8	559.6	514.0	476.0	442.8	412.4	399.1	385.8
137.5°	763.9	712.6	658.5	606.2	559.6	519.7	484.6	453.2	422.8	410.4	398.1
140°	731.6	687.9	642.3	599.6	558.7	523.5	491.2	461.8	433.3	421.0	408.6
142.5°	702.2	666.1	629.0	592.9	558.7	526.4	496.9	468.4	440.9	429.5	418.1
145°	677.5	648.0	616.7	587.2	556.8	528.3	501.7	475.1	449.4	439.0	428.5
147.5°	656.6	632.8	607.2	581.5	553.9	529.2	504.5	480.8	456.1	446.6	437.1
150°	637.6	617.6	596.7	573.9	551.1	528.3	506.4	484.6	462.7	454.2	445.6
152.5°	621.4	605.3	586.3	567.2	546.3	526.4	507.4	488.4	469.4	461.8	454.2
155°	606.2	592.0	576.7	558.7	540.6	524.5	508.3	492.2	476.0	468.9	461.8
157.5°	591.0	578.7	565.3	551.1	534.9	520.7	508.3	495.0	480.8	474.6	468.4
160°	575.8	565.3	554.9	542.5	529.2	517.8	508.3	496.9	485.5	480.3	475.1
162.5°	561.5	553.0	544.4	534.9	524.5	515.0	507.4	497.9	488.4	484.6	480.8
165°	547.3	540.6	534.0	526.4	517.8	511.2	505.5	498.8	490.3	487.4	484.6
167.5°	534.0	529.2	523.5	517.8	512.1	507.4	504.5	498.8	492.2	490.3	488.4
170°	522.6	518.8	515.9	511.2	507.4	504.5	502.6	497.9	493.1	491.7	490.3
172.5°	512.1	509.3	507.4	504.5	501.7	500.7	499.8	496.9	494.1	493.2	492.2
175°	503.6	502.6	501.7	498.8	497.9	496.9	497.9	496.0	494.1	493.6	493.1
177.5°	497.9	496.9	496.9	495.0	494.1	495.0	496.9	495.0	494.1	494.1	494.1
180°	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1	494.1

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2125.4	2125.4	2125.4	2125.4
2.5°	2087.0	2082.6	2109.2	2138.7
5°	2044.2	2051.6	2085.5	2126.9
7.5°	1999.9	2016.1	2056.0	2110.7
10°	1937.8	1967.4	2027.9	2084.1
12.5°	1877.3	1917.2	1974.8	2041.2
15°	1809.3	1853.7	1924.6	2004.3
17.5°	1734.0	1784.2	1866.9	1954.1
20°	1654.3	1720.7	1807.9	1902.4
22.5°	1565.6	1645.4	1735.5	1840.4
25°	1480.0	1567.1	1657.2	1778.3
27.5°	1395.8	1481.4	1581.9	1704.5
30°	1311.6	1389.9	1497.7	1629.1
32.5°	1221.5	1302.7	1416.5	1550.9
35°	1138.8	1220.0	1326.4	1459.3
37.5°	1050.2	1137.3	1239.2	1376.6
40°	946.8	1048.7	1147.6	1279.1
42.5°	861.1	968.9	1064.9	1189.0
45°	793.2	895.1	974.8	1095.9
47.5°	729.6	812.4	893.6	1005.8
50°	669.1	732.6	816.8	917.2
52.5°	607.1	661.7	734.1	828.6
55°	550.9	602.6	667.6	740.0
57.5°	499.2	536.2	601.1	666.1
60°	441.6	480.0	530.2	584.9
62.5°	392.9	422.4	469.7	515.5
65°	341.2	369.3	404.7	447.5
67.5°	293.9	319.0	347.1	381.1
70°	251.1	270.3	291.0	320.5
72.5°	205.3	226.0	245.2	268.8
75°	168.4	177.2	193.5	209.7
77.5°	130.0	141.8	150.7	163.9
80°	93.1	103.4	106.3	116.7
82.5°	62.0	67.9	73.9	76.8
85°	35.4	38.4	44.3	45.8
87.5°	13.3	14.8	17.7	20.7
90°	9.5	7.6	3.8	1.0
92.5°	32.3	27.6	20.0	14.3
95°	55.1	46.6	37.1	33.3
97.5°	77.9	65.6	55.1	49.4
100°	99.8	84.6	76.0	73.2
102.5°	120.7	105.5	96.9	95.0
105°	140.6	126.4	119.7	115.9
107.5°	161.5	148.2	141.6	138.7
110°	183.4	171.0	165.3	161.5

TEST NUMBER: P1009798

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	204.3	192.9	186.2	182.4
115°	226.1	214.7	209.0	204.3
117.5°	247.0	236.6	230.9	227.1
120°	266.0	257.5	251.8	248.0
122.5°	286.0	276.5	270.8	267.9
125°	305.0	293.6	287.9	285.0
127.5°	323.1	310.7	303.1	299.3
130°	338.3	325.0	315.5	311.7
132.5°	352.5	338.3	327.8	323.1
135°	363.9	349.7	338.3	334.5
137.5°	376.3	361.1	349.7	344.9
140°	387.7	372.5	361.1	357.3
142.5°	398.1	382.9	372.5	369.6
145°	409.5	395.3	385.8	382.0
147.5°	420.9	407.6	398.1	395.3
150°	431.4	419.0	411.4	408.6
152.5°	440.9	430.4	422.8	421.9
155°	451.3	440.9	435.2	434.2
157.5°	459.9	450.4	445.6	444.7
160°	467.5	459.9	456.1	455.1
162.5°	474.1	468.4	464.6	465.6
165°	479.8	474.1	472.2	473.2
167.5°	484.6	480.8	478.9	479.8
170°	488.4	485.5	484.6	486.5
172.5°	491.2	488.4	489.3	490.3
175°	493.1	491.2	492.2	493.1
177.5°	494.1	492.2	493.1	495.0
180°	494.1	494.1	494.1	494.1

(END OF REPORT)