

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009287

Luminaire Tested: S122DIP-B675D330UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009287
REPORT IS A COMBINATION OF REPORTS P984528 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D330UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3982.5 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009287

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009287

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	61
2	93	85	79	73	87	80	75	70	72	67	64	64	60	57	56	54	52
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	47	44
4	77	66	58	52	73	63	56	50	56	50	46	50	46	42	45	41	38
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	25	32	26	23	28	24	21
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16800	16800	16800
5°	16827	16012	15899
10°	16689	15283	14979
15°	16445	14547	14012
20°	16114	13747	13096
25°	15785	12913	12182
30°	15371	12127	11222
35°	14981	11300	10279
40°	14497	10483	9388
45°	14019	9672	8515
50°	13494	8847	7608
55°	12942	7966	6749
60°	12323	7011	5857
65°	11646	6040	4917
70°	10783	4978	3972
75°	9588	3838	3066
80°	8143	2609	1974
85°	5905	1214	839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14019 cd/sqm

TEST NUMBER: P1009287

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	2.5
10°-20°	281.0	7.1
20°-30°	413.0	10.4
30°-40°	479.7	12.0
40°-50°	479.1	12.0
50°-60°	417.7	10.5
60°-70°	308.8	7.8
70°-80°	174.7	4.4
80°-90°	47.3	1.2
90°-100°	74.5	1.9
100°-110°	251.9	6.3
110°-120°	264.8	6.6
120°-130°	217.7	5.5
130°-140°	174.9	4.4
140°-150°	132.2	3.3
150°-160°	92.9	2.3
160°-170°	54.7	1.4
170°-180°	17.8	0.4
0°-30°	793.9	19.9
0°-40°	1273.6	32.0
0°-60°	2170.4	54.5
0°-90°	2701.2	67.8
90°-120°	591.1	14.8
90°-150°	1115.9	28.0
90°-180°	1281.0	32.2
0°-180°	3982.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1061	1061	1061	1061	1061	
5°	1061	1057	1046	1054	1052	101
15°	1010	1004	991	995	990	285
25°	914	906	889	891	889	421
35°	789	779	762	756	751	493
45°	642	635	619	608	604	495
55°	486	480	467	455	450	434
65°	328	321	311	302	297	324
75°	171	169	164	158	160	183
85°	42	41	40	37	36	47
90°	0	5	12	12	12	3
95°	12	30	138	52	40	13
105°	43	65	262	468	398	46
115°	76	96	219	452	524	75
125°	106	125	211	366	425	94
135°	124	148	208	308	352	96
145°	142	163	207	257	281	89
155°	162	174	201	227	236	74
165°	176	181	193	204	208	50
175°	183	184	185	188	187	17
180°	184	184	184	184	184	

TEST NUMBER: P1009287

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.4	1062.3	1051.0	1061.3	1059.2
5°	1061.3	1057.2	1045.9	1054.1	1052.1
7.5°	1054.1	1048.0	1036.8	1044.9	1042.9
10°	1042.9	1035.7	1023.5	1031.7	1028.6
12.5°	1027.6	1021.5	1009.2	1014.3	1012.3
15°	1010.2	1004.1	990.8	994.9	989.8
17.5°	988.8	982.7	969.4	974.5	969.4
20°	965.3	959.2	944.9	948.0	943.9
22.5°	941.9	932.7	919.4	919.4	917.4
25°	914.3	906.1	888.8	890.8	888.8
27.5°	883.7	876.6	863.3	860.2	855.1
30°	853.1	844.9	829.6	826.6	822.5
32.5°	820.4	814.3	798.0	791.9	787.8
35°	788.8	778.6	762.3	756.1	751.0
37.5°	753.1	743.9	727.6	720.4	715.3
40°	716.3	708.2	691.9	682.7	678.6
42.5°	680.6	672.5	656.1	645.9	639.8
45°	641.9	634.7	619.4	608.2	604.1
47.5°	604.1	597.0	580.6	569.4	563.3
50°	564.3	559.2	544.9	530.6	525.5
52.5°	525.5	518.4	505.1	493.9	486.7
55°	485.7	479.6	467.4	455.1	450.0
57.5°	445.9	440.8	427.6	415.3	411.2
60°	406.1	402.1	387.8	376.5	373.5
62.5°	367.4	360.2	350.0	339.8	335.7
65°	327.6	321.4	311.2	302.0	296.9
67.5°	286.7	281.6	272.5	265.3	261.2
70°	249.0	244.9	235.7	228.6	224.5
72.5°	210.2	206.1	201.0	193.9	190.8
75°	171.4	169.4	164.3	158.2	160.2
77.5°	136.7	132.7	130.6	127.6	124.5
80°	102.0	101.0	99.0	95.9	93.9
82.5°	69.4	69.4	68.4	64.3	64.3
85°	41.8	40.8	39.8	36.7	35.7
87.5°	18.4	16.3	14.3	11.2	10.2
90°	0.4	4.8	12.0	11.5	11.7
92.5°	5.3	16.8	54.4	25.1	21.6
95°	12.4	30.4	138.5	52.3	40.3
97.5°	18.4	40.1	225.8	105.0	67.5
100°	27.2	49.2	279.2	209.0	126.5
102.5°	35.3	57.2	281.0	353.4	246.7
105°	43.1	65.0	261.9	468.1	398.3
107.5°	51.6	72.8	244.2	509.6	500.4
110°	60.1	80.8	232.2	502.9	542.1

TEST NUMBER: P1009287

CATALOG NUMBER: S122DIP-B675D330UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	67.9	88.4	224.4	480.2	541.4
115°	76.0	96.0	219.1	452.2	524.1
117.5°	84.5	103.6	216.3	425.5	498.0
120°	92.2	111.0	213.8	401.6	472.9
122.5°	99.7	118.6	212.4	383.1	446.7
125°	106.0	125.4	210.6	366.4	425.2
127.5°	111.3	132.0	209.6	352.0	405.0
130°	115.9	137.9	208.9	337.5	388.4
132.5°	120.2	143.4	208.5	322.5	371.1
135°	124.4	148.4	208.2	307.8	352.4
137.5°	128.3	152.7	208.2	293.0	334.3
140°	132.9	156.6	207.8	279.9	315.6
142.5°	137.5	159.8	207.8	267.4	296.9
145°	142.1	163.3	207.1	257.1	281.3
147.5°	147.0	166.1	206.0	248.1	267.5
150°	152.0	169.0	205.0	240.3	255.5
152.5°	156.9	171.8	203.2	233.8	245.3
155°	161.5	174.4	201.1	227.4	236.4
157.5°	165.4	176.5	199.0	221.4	228.7
160°	169.3	178.6	196.9	215.4	221.2
162.5°	173.2	180.2	195.1	209.8	214.2
165°	176.0	181.3	192.6	204.3	207.5
167.5°	178.5	182.4	190.5	199.3	201.1
170°	180.9	182.9	188.7	194.8	195.4
172.5°	182.4	183.4	186.6	190.6	190.8
175°	183.4	183.6	185.2	187.5	187.0
177.5°	184.1	183.8	183.8	185.2	184.1
180°	183.8	183.8	183.8	183.8	183.8

(END OF REPORT)