

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009902

Luminaire Tested: S122RDIP-B290D725UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009902
REPORT IS A COMBINATION OF REPORTS P988160 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D725UB35-4F0-XX-W2A-A
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3948.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	28
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	32	32	31	31	31	24
2	85	78	73	68	76	70	66	62	56	52	50	42	40	38	29	28	27	27	27	21
3	78	69	63	57	70	62	57	52	49	45	42	37	35	33	26	25	23	23	23	19
4	72	62	54	49	64	56	49	44	44	40	36	34	31	28	24	22	21	21	21	16
5	66	55	47	42	59	50	43	38	40	35	31	30	27	25	22	20	18	18	18	15
6	61	49	42	36	54	45	38	33	36	31	28	28	24	22	20	18	16	16	16	13
7	56	45	37	32	50	40	34	29	33	28	24	25	22	20	18	16	15	15	15	12
8	52	41	33	28	47	37	30	26	30	25	22	23	20	18	17	15	13	13	13	11
9	48	37	30	25	43	34	28	23	27	23	20	21	18	16	16	14	12	12	12	10
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10112	10112	10112	10112
5°	10136	10742	10171	8581
10°	10024	11353	10096	7086
15°	9806	11356	9972	5323
20°	9545	9388	9752	4391
25°	9228	5866	9428	3736
30°	8823	3755	9063	3216
35°	8330	2887	8599	2752
40°	7782	2427	8114	2407
45°	7194	2065	7495	2021
50°	6593	1755	6901	1749
55°	5926	1525	6246	1504
60°	5335	1162	5617	1149
65°	4781	874	5066	992
70°	4170	699	4500	808
75°	3524	536	3849	612
80°	2802	364	3010	402
85°	1949	188	2133	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9250 cd/sqm

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	1.5
10°-20°	169.1	4.3
20°-30°	217.7	5.5
30°-40°	206.5	5.2
40°-50°	177.0	4.5
50°-60°	134.8	3.4
60°-70°	85.0	2.2
70°-80°	42.4	1.1
80°-90°	12.6	0.3
90°-100°	32.0	0.8
100°-110°	119.2	3.0
110°-120°	316.1	8.0
120°-130°	524.2	13.3
130°-140°	556.8	14.1
140°-150°	517.5	13.1
150°-160°	416.1	10.5
160°-170°	268.1	6.8
170°-180°	92.3	2.3
0°-30°	447.4	11.3
0°-40°	653.9	16.6
0°-60°	965.7	24.5
0°-90°	1105.7	28.0
90°-120°	467.2	11.8
90°-150°	2065.8	52.3
90°-180°	2842.0	72.0
0°-180°	3948.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	639	639	639	639	639	
5°	639	711	642	568	639	61
15°	602	802	613	376	602	169
25°	534	428	546	273	534	245
35°	439	211	453	201	439	274
45°	329	146	343	143	329	254
55°	222	102	234	100	222	200
65°	134	53	142	60	134	133
75°	63	28	69	32	63	68
85°	14	8	15	8	14	16
90°	1	19	1	19	1	3
95°	46	30	46	30	46	54
105°	213	53	213	53	213	228
115°	403	58	403	58	403	397
125°	570	600	570	600	570	509
135°	706	729	706	729	706	545
145°	819	831	819	831	819	512
155°	902	902	902	902	902	415
165°	950	948	950	948	950	268
175°	972	966	972	966	972	92
180°	970	970	970	970	970	

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	642.8	645.5	646.8	648.6	652.6	655.3	659.3	660.2	659.7	661.5	656.6
5°	639.3	645.1	650.4	654.8	661.9	666.4	671.3	677.0	678.4	685.0	681.0
7.5°	634.4	642.8	650.4	659.3	669.9	675.7	683.2	692.1	696.1	704.1	706.3
10°	626.4	638.4	651.3	660.6	675.2	685.5	692.6	706.8	716.1	728.1	726.3
12.5°	613.5	629.1	646.4	661.9	681.0	687.7	701.0	715.6	727.6	738.7	748.5
15°	602.4	620.2	639.3	658.4	680.1	692.6	705.9	725.0	737.8	757.4	765.8
17.5°	587.3	610.0	632.6	653.9	679.7	693.9	710.3	729.0	748.1	766.7	773.4
20°	571.8	596.2	620.6	649.5	678.8	692.6	709.4	732.5	751.2	765.8	765.8
22.5°	553.2	582.9	610.9	638.4	670.4	690.3	707.7	734.7	748.1	751.2	739.2
25°	534.5	564.3	594.9	629.1	665.5	683.2	702.8	728.1	732.5	720.1	689.0
27.5°	512.3	545.6	580.2	617.1	655.3	677.5	695.2	712.1	703.7	670.4	622.0
30°	489.7	525.6	564.7	599.8	645.9	666.4	681.5	686.3	659.7	605.5	542.9
32.5°	466.1	501.2	542.5	584.7	631.3	650.8	660.6	647.7	598.9	530.5	454.2
35°	438.6	478.1	521.2	565.1	611.3	626.0	631.7	600.2	537.6	449.3	373.4
37.5°	413.8	453.3	499.4	544.3	589.1	597.1	591.3	542.1	462.6	375.1	301.0
40°	384.5	426.6	471.9	522.1	558.9	561.2	546.9	483.0	384.5	302.3	256.6
42.5°	357.4	400.0	445.3	496.3	524.3	516.8	497.7	413.8	321.0	260.6	223.8
45°	329.4	369.8	418.6	463.9	483.9	466.1	437.3	348.1	269.5	224.2	195.8
47.5°	302.3	340.1	388.5	432.0	435.5	415.5	381.4	291.7	233.5	197.1	174.0
50°	275.7	313.4	358.7	394.7	391.1	363.6	325.0	253.5	202.9	174.0	154.9
52.5°	249.1	283.2	327.2	355.6	340.5	313.9	275.7	214.9	177.1	151.8	137.2
55°	222.4	254.4	292.1	315.6	291.7	261.0	234.0	184.2	153.6	133.2	122.1
57.5°	200.2	225.5	260.2	274.4	245.5	221.5	198.0	158.5	133.2	118.5	105.7
60°	175.8	198.9	227.3	235.7	206.0	186.5	166.5	134.1	114.1	101.2	92.8
62.5°	154.9	174.0	195.8	195.8	169.6	154.9	139.8	112.3	95.9	85.7	81.7
65°	134.5	148.3	163.8	162.0	139.8	127.0	115.0	92.8	80.4	73.3	69.3
67.5°	114.5	125.2	135.4	129.2	113.2	102.1	91.0	75.0	66.6	61.7	56.4
70°	96.3	104.8	110.1	104.3	88.3	79.0	71.0	60.4	53.7	47.5	44.4
72.5°	80.8	84.4	86.1	79.0	65.7	60.4	54.6	47.1	41.3	38.2	37.3
75°	63.0	66.1	64.8	59.5	48.4	44.4	40.0	34.6	33.3	31.5	30.6
77.5°	49.3	49.3	47.1	42.2	34.6	31.5	29.7	27.1	25.7	25.3	24.4
80°	35.1	34.6	33.3	28.0	23.5	21.8	21.8	20.0	19.5	18.6	18.6
82.5°	23.1	23.1	21.3	16.9	15.5	15.1	14.7	13.8	13.8	13.3	13.3
85°	13.8	12.9	10.7	9.3	8.9	8.9	8.4	8.0	8.4	8.0	8.0
87.5°	6.2	4.9	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
90°	0.7	2.4	4.1	5.8	7.5	8.4	9.0	10.3	11.5	12.8	14.0
92.5°	17.5	16.9	16.3	15.6	15.0	14.7	14.9	15.4	15.9	16.3	16.8
95°	45.6	40.4	35.3	30.1	25.0	22.4	23.0	24.1	25.2	26.3	27.4
97.5°	82.1	69.3	56.5	43.8	31.0	24.6	25.8	28.3	30.8	33.3	35.8
100°	124.2	102.8	81.5	60.1	38.8	28.1	29.4	32.1	34.7	37.4	40.0
102.5°	170.5	170.2	169.9	169.6	169.3	169.1	154.9	126.5	98.2	69.8	41.4
105°	213.3	218.0	222.6	227.3	232.0	234.3	213.0	170.5	127.9	85.4	42.8
107.5°	263.1	267.0	270.9	274.8	278.7	280.6	254.3	201.8	149.3	96.7	44.2
110°	310.8	314.1	317.3	320.6	323.9	325.5	303.0	257.9	212.9	167.8	122.8

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	355.7	358.5	361.3	364.1	366.9	368.3	367.0	364.3	361.7	359.0	356.4
115°	403.4	406.0	408.7	411.3	414.0	415.3	417.2	421.1	425.0	428.9	432.8
117.5°	444.8	447.9	451.0	454.1	457.2	458.8	460.1	462.8	465.4	468.1	470.7
120°	491.1	493.4	495.8	498.1	500.4	501.6	503.0	505.8	508.6	511.4	514.2
122.5°	530.4	532.9	535.4	537.9	540.4	541.6	543.2	546.3	549.4	552.5	555.6
125°	570.3	572.3	574.4	576.4	578.5	579.5	581.0	583.9	586.9	589.8	592.8
127.5°	606.8	609.0	611.2	613.3	615.5	616.6	617.8	620.1	622.5	624.8	627.2
130°	641.2	643.7	646.2	648.7	651.2	652.4	653.3	655.0	656.7	658.4	660.1
132.5°	676.3	678.3	680.3	682.4	684.4	685.4	686.3	688.0	689.7	691.4	693.1
135°	705.7	708.2	710.7	713.2	715.7	717.0	717.7	719.1	720.5	721.9	723.3
137.5°	736.6	738.5	740.3	742.2	744.1	745.0	745.8	747.3	748.9	750.4	752.0
140°	766.8	768.0	769.3	770.5	771.8	772.4	773.3	775.0	776.7	778.4	780.1
142.5°	792.0	793.1	794.2	795.3	796.4	796.9	797.9	800.0	802.0	804.1	806.1
145°	818.7	818.5	818.4	818.2	818.1	818.0	819.3	822.0	824.6	827.3	829.9
147.5°	841.8	841.3	840.9	840.4	839.9	839.7	841.0	843.7	846.4	849.0	851.7
150°	864.3	863.2	862.1	861.0	859.9	859.4	860.6	863.1	865.6	868.1	870.6
152.5°	883.2	882.0	880.7	879.5	878.2	877.6	878.8	881.1	883.4	885.8	888.1
155°	901.5	900.1	898.7	897.3	895.9	895.2	896.1	898.0	899.9	901.7	903.6
157.5°	916.2	915.0	913.7	912.5	911.2	910.6	911.3	912.7	914.1	915.5	916.9
160°	928.8	927.9	926.9	926.0	925.1	924.6	925.1	926.0	926.9	927.9	928.8
162.5°	940.1	939.1	938.2	937.2	936.3	935.8	936.2	937.0	937.8	938.6	939.4
165°	949.9	949.0	948.0	947.1	946.2	945.7	945.9	946.4	946.9	947.3	947.8
167.5°	957.6	956.7	955.7	954.8	953.9	953.4	953.6	954.1	954.6	955.0	955.5
170°	963.9	963.0	962.0	961.1	960.2	959.7	959.9	960.2	960.5	960.8	961.1
172.5°	968.1	967.2	966.2	965.3	964.4	963.9	964.1	964.4	964.7	965.0	965.3
175°	971.6	970.5	969.4	968.3	967.2	966.7	966.9	967.2	967.5	967.8	968.1
177.5°	973.0	971.9	970.8	969.7	968.6	968.1	968.2	968.3	968.5	968.6	968.8
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	661.5	662.4	663.7	669.9	670.8	672.6	671.7	671.7	672.1	671.3	671.7
5°	689.9	691.2	697.9	705.4	707.2	705.4	707.7	710.8	710.8	710.8	709.9
7.5°	716.5	721.4	729.0	740.1	742.3	744.5	748.5	745.8	746.7	750.7	749.4
10°	742.3	749.4	757.8	767.1	772.0	775.1	776.9	780.9	790.2	779.6	783.6
12.5°	766.7	776.9	785.8	796.0	799.6	803.5	804.9	808.4	808.4	808.0	811.1
15°	782.7	792.0	800.0	806.7	807.5	806.7	805.8	806.2	807.5	802.2	805.3
17.5°	786.2	787.1	789.8	787.1	787.6	778.2	772.9	771.6	759.2	759.6	769.8
20°	768.9	753.8	749.8	735.2	726.3	702.3	701.4	694.8	668.6	676.6	674.8
22.5°	721.4	695.7	661.5	644.6	636.2	610.9	591.3	577.6	568.3	558.9	554.9
25°	658.8	617.1	568.7	535.4	530.5	507.0	471.0	454.2	434.2	428.0	438.6
27.5°	578.0	523.9	469.3	418.2	408.9	387.6	369.4	357.4	334.3	333.0	333.8
30°	468.4	413.8	368.0	334.7	311.7	301.9	289.9	281.0	271.7	275.2	276.1
32.5°	384.9	333.0	290.3	272.6	261.9	255.7	245.5	239.7	235.7	234.4	234.0
35°	305.9	271.3	252.2	234.8	228.6	224.2	216.6	214.0	210.4	210.9	210.9
37.5°	261.9	233.1	218.9	210.0	204.2	202.0	197.1	194.4	192.2	191.3	192.7
40°	226.0	206.0	197.1	189.1	184.2	183.4	180.7	177.6	174.9	175.4	176.7
42.5°	199.8	188.2	177.6	171.4	167.8	166.5	164.3	162.0	162.0	160.7	160.3
45°	178.9	169.6	160.7	154.9	152.7	150.9	148.3	147.8	146.1	146.5	146.9
47.5°	160.3	152.7	146.1	140.3	138.1	137.6	135.0	133.2	133.2	132.7	132.3
50°	143.4	135.8	130.1	127.0	123.9	123.0	122.5	122.1	121.2	121.2	121.6
52.5°	129.6	122.1	117.6	115.0	113.2	112.3	112.3	111.9	111.9	111.9	111.4
55°	114.5	108.3	104.8	103.9	103.0	102.6	102.1	101.2	100.8	101.7	100.8
57.5°	100.3	98.1	95.0	94.1	91.9	91.9	90.6	89.7	88.8	89.7	89.7
60°	89.2	86.1	84.4	81.7	79.9	78.1	75.9	75.5	74.6	74.1	73.7
62.5°	77.7	75.0	70.6	66.6	63.9	62.2	61.3	60.8	60.8	60.4	60.4
65°	64.8	58.6	56.4	55.0	54.6	54.2	53.3	52.8	53.3	52.8	53.3
67.5°	50.6	49.7	48.4	47.5	47.1	46.6	46.6	46.2	46.2	46.2	46.2
70°	44.0	41.7	41.3	40.4	40.4	40.0	40.0	40.0	40.0	39.5	40.4
72.5°	36.4	35.1	34.6	34.2	34.2	34.2	33.7	33.7	33.7	33.3	33.7
75°	29.7	29.3	28.4	28.4	28.0	28.4	28.0	28.0	27.5	28.0	28.0
77.5°	24.0	23.5	23.1	23.1	22.6	22.6	22.6	22.6	22.6	22.6	23.1
80°	18.2	17.8	17.3	17.8	17.3	17.8	17.3	17.3	17.8	17.3	17.3
82.5°	13.3	12.9	12.9	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
85°	8.0	7.5	7.5	8.0	7.5	8.0	7.5	7.5	7.5	8.0	8.0
87.5°	3.6	4.0	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.0
90°	14.8	15.6	16.3	17.1	17.5	17.7	18.0	18.3	18.6	18.9	18.6
92.5°	17.1	17.4	17.7	18.0	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.2	29.0	29.7	30.5	30.9	30.8	30.7	30.5	30.4	30.2	30.4
97.5°	36.3	36.7	37.2	37.7	37.9	38.0	38.1	38.3	38.4	38.6	38.4
100°	41.2	42.5	43.7	45.0	45.6	45.8	46.1	46.4	46.7	47.0	46.7
102.5°	43.1	44.8	46.5	48.2	49.1	49.3	49.8	50.3	50.7	51.2	50.7
105°	44.5	46.2	47.9	49.6	50.5	50.8	51.4	52.1	52.7	53.3	52.7
107.5°	45.9	47.6	49.3	51.0	51.9	52.2	52.8	53.5	54.1	54.7	54.1
110°	107.2	91.6	76.0	60.4	52.6	52.9	53.5	54.2	54.8	55.4	54.8

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	289.2	222.0	154.8	87.6	54.0	54.2	54.7	55.2	55.6	56.1	55.6
115°	360.6	288.4	216.3	144.1	108.0	102.4	91.2	79.9	68.7	57.5	68.7
117.5°	448.4	426.1	403.8	381.5	370.4	350.0	309.1	268.3	227.4	186.6	227.4
120°	516.1	517.9	519.8	521.7	522.6	512.1	491.0	470.0	448.9	427.9	448.9
122.5°	556.5	557.5	558.4	559.3	559.8	559.9	560.0	560.2	560.3	560.5	560.3
125°	593.9	595.0	596.1	597.2	597.7	597.9	598.4	598.9	599.3	599.8	599.3
127.5°	628.8	630.3	631.9	633.4	634.2	634.3	634.4	634.6	634.7	634.9	634.7
130°	661.8	663.6	665.3	667.0	667.9	667.8	667.7	667.5	667.4	667.2	667.4
132.5°	694.5	695.9	697.3	698.7	699.4	699.3	699.2	699.0	698.9	698.7	698.9
135°	724.9	726.4	728.0	729.5	730.3	730.1	729.8	729.5	729.2	728.9	729.2
137.5°	753.6	755.2	756.7	758.3	759.1	758.9	758.4	757.9	757.5	757.0	757.5
140°	781.5	782.9	784.3	785.7	786.4	786.0	785.2	784.5	783.7	782.9	783.7
142.5°	807.3	808.6	809.8	811.1	811.7	811.3	810.5	809.8	809.0	808.2	809.0
145°	831.0	832.1	833.2	834.3	834.8	834.4	833.6	832.9	832.1	831.3	832.1
147.5°	852.5	853.3	854.0	854.8	855.2	854.9	854.3	853.6	853.0	852.4	853.0
150°	871.5	872.5	873.4	874.3	874.8	874.4	873.6	872.9	872.1	871.3	872.1
152.5°	889.1	890.0	891.0	891.9	892.4	891.8	890.7	889.6	888.5	887.4	888.5
155°	904.5	905.5	906.4	907.3	907.8	907.2	905.9	904.7	903.4	902.2	903.4
157.5°	918.0	919.1	920.2	921.3	921.8	921.2	919.9	918.7	917.4	916.2	917.4
160°	929.7	930.7	931.6	932.5	933.0	932.5	931.4	930.3	929.2	928.1	929.2
162.5°	940.5	941.6	942.7	943.8	944.3	943.6	942.2	940.8	939.4	938.0	939.4
165°	948.9	950.0	951.1	952.2	952.7	952.2	951.1	950.0	948.9	947.8	948.9
167.5°	956.6	957.7	958.8	959.9	960.4	959.7	958.3	956.9	955.5	954.1	955.5
170°	962.2	963.3	964.4	965.5	966.0	965.3	963.9	962.5	961.1	959.7	961.1
172.5°	966.4	967.5	968.6	969.7	970.2	969.5	968.1	966.7	965.3	963.9	965.3
175°	969.2	970.3	971.4	972.5	973.0	972.2	970.7	969.1	967.6	966.0	967.6
177.5°	969.9	971.0	972.1	973.2	973.7	973.0	971.6	970.2	968.8	967.4	968.8
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	673.5	670.4	669.5	670.4	669.5	669.9	666.8	655.3	658.4	653.5	656.2
5°	711.7	709.0	703.2	702.3	701.4	700.6	696.1	685.9	681.9	675.2	674.8
7.5°	748.1	748.1	743.6	740.5	736.5	733.4	727.6	712.5	706.3	698.3	693.9
10°	784.0	772.5	777.4	774.2	764.5	762.7	752.1	743.2	731.2	723.2	716.1
12.5°	809.8	806.2	801.8	799.1	796.4	790.7	783.6	760.9	754.7	738.7	730.7
15°	808.9	806.7	808.0	808.0	807.1	805.8	800.0	783.6	772.9	757.4	743.6
17.5°	765.4	771.1	776.9	780.9	789.8	793.8	799.1	789.3	782.7	769.4	754.7
20°	689.5	703.7	720.5	724.1	732.1	755.6	766.3	774.7	777.4	772.9	760.9
22.5°	583.8	595.8	636.6	635.7	647.3	675.2	706.3	731.6	751.6	762.7	758.3
25°	457.3	474.1	495.9	512.3	550.1	591.8	630.4	670.8	705.4	736.1	743.6
27.5°	345.8	368.0	385.3	407.1	426.2	475.5	525.2	588.2	628.6	686.8	717.0
30°	279.7	289.9	307.2	317.4	326.7	364.5	420.9	483.0	554.0	621.1	673.0
32.5°	238.8	245.9	258.8	263.3	273.0	298.3	333.8	390.7	463.9	545.2	613.5
35°	214.4	222.0	224.6	228.6	236.6	252.6	277.0	318.3	384.5	463.9	545.6
37.5°	193.6	197.6	205.1	207.8	210.4	222.4	238.8	267.7	311.7	376.9	467.5
40°	178.9	181.1	185.1	187.3	189.1	197.6	212.2	231.7	264.1	313.9	397.3
42.5°	163.4	166.0	168.7	171.4	173.6	180.2	189.1	207.8	229.5	267.3	327.6
45°	148.3	150.1	153.2	154.9	158.0	163.4	171.4	184.2	203.8	227.7	276.6
47.5°	134.5	136.7	138.1	140.3	142.5	148.3	155.8	164.3	180.2	203.8	239.3
50°	122.1	124.7	126.5	127.0	128.7	134.1	140.3	149.6	159.8	178.0	209.1
52.5°	113.2	113.7	115.0	116.8	116.3	119.4	125.2	132.3	143.0	157.6	180.2
55°	103.0	104.3	105.2	105.7	105.7	108.3	111.4	118.1	126.5	138.5	157.6
57.5°	90.1	91.5	94.1	95.0	96.3	97.7	99.0	103.4	110.5	122.1	137.6
60°	76.8	77.7	80.4	82.1	83.0	86.6	88.3	91.9	95.9	104.3	119.0
62.5°	61.7	62.6	63.9	65.7	67.5	72.8	77.2	80.8	83.9	89.7	101.7
65°	53.7	54.2	55.0	55.5	55.9	58.2	62.2	67.0	72.8	77.2	84.4
67.5°	46.6	47.1	47.5	48.4	48.8	49.3	51.1	52.4	58.2	64.4	69.7
70°	40.0	40.8	41.3	41.3	41.7	42.6	43.5	45.3	47.1	50.2	56.8
72.5°	33.7	34.2	35.1	35.1	35.1	36.0	36.8	37.7	38.6	40.4	43.1
75°	28.0	28.9	28.9	28.9	29.3	29.3	30.2	31.1	32.0	33.3	34.2
77.5°	23.1	23.1	23.1	23.1	23.5	23.5	24.0	24.9	25.3	25.7	26.6
80°	17.3	17.8	17.8	17.8	18.2	18.2	18.2	19.1	19.5	19.5	20.4
82.5°	12.9	12.9	12.9	13.3	12.9	13.3	13.3	13.8	13.3	13.8	14.2
85°	8.0	8.0	8.0	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.9
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	18.3	18.0	17.7	17.5	17.1	16.3	15.6	14.8	14.0	12.8	11.5
92.5°	18.6	18.4	18.3	18.2	18.0	17.7	17.4	17.1	16.8	16.3	15.9
95°	30.5	30.7	30.8	30.9	30.5	29.7	29.0	28.2	27.4	26.3	25.2
97.5°	38.3	38.1	38.0	37.9	37.7	37.2	36.7	36.3	35.8	33.3	30.8
100°	46.4	46.1	45.8	45.6	45.0	43.7	42.5	41.2	40.0	37.4	34.7
102.5°	50.3	49.8	49.3	49.1	48.2	46.5	44.8	43.1	41.4	39.8	38.2
105°	52.1	51.4	50.8	50.5	49.6	47.9	46.2	44.5	42.8	41.4	40.0
107.5°	53.5	52.8	52.2	51.9	51.0	49.3	47.6	45.9	44.2	42.8	41.4
110°	54.2	53.5	52.9	52.6	60.4	76.0	91.6	107.2	122.8	167.8	212.9

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.2	54.7	54.2	54.0	87.6	154.8	222.0	289.2	356.4	359.0	361.7
115°	79.9	91.2	102.4	108.0	144.1	216.3	288.4	360.6	432.8	428.9	425.0
117.5°	268.3	309.1	350.0	370.4	381.5	403.8	426.1	448.4	470.7	468.1	465.4
120°	470.0	491.0	512.1	522.6	521.7	519.8	517.9	516.1	514.2	511.4	508.6
122.5°	560.2	560.0	559.9	559.8	559.3	558.4	557.5	556.5	555.6	552.5	549.4
125°	598.9	598.4	597.9	597.7	597.2	596.1	595.0	593.9	592.8	589.8	586.9
127.5°	634.6	634.4	634.3	634.2	633.4	631.9	630.3	628.8	627.2	624.8	622.5
130°	667.5	667.7	667.8	667.9	667.0	665.3	663.6	661.8	660.1	658.4	656.7
132.5°	699.0	699.2	699.3	699.4	698.7	697.3	695.9	694.5	693.1	691.4	689.7
135°	729.5	729.8	730.1	730.3	729.5	728.0	726.4	724.9	723.3	721.9	720.5
137.5°	757.9	758.4	758.9	759.1	758.3	756.7	755.2	753.6	752.0	750.4	748.9
140°	784.5	785.2	786.0	786.4	785.7	784.3	782.9	781.5	780.1	778.4	776.7
142.5°	809.8	810.5	811.3	811.7	811.1	809.8	808.6	807.3	806.1	804.1	802.0
145°	832.9	833.6	834.4	834.8	834.3	833.2	832.1	831.0	829.9	827.3	824.6
147.5°	853.6	854.3	854.9	855.2	854.8	854.0	853.3	852.5	851.7	849.0	846.4
150°	872.9	873.6	874.4	874.8	874.3	873.4	872.5	871.5	870.6	868.1	865.6
152.5°	889.6	890.7	891.8	892.4	891.9	891.0	890.0	889.1	888.1	885.8	883.4
155°	904.7	905.9	907.2	907.8	907.3	906.4	905.5	904.5	903.6	901.7	899.9
157.5°	918.7	919.9	921.2	921.8	921.3	920.2	919.1	918.0	916.9	915.5	914.1
160°	930.3	931.4	932.5	933.0	932.5	931.6	930.7	929.7	928.8	927.9	926.9
162.5°	940.8	942.2	943.6	944.3	943.8	942.7	941.6	940.5	939.4	938.6	937.8
165°	950.0	951.1	952.2	952.7	952.2	951.1	950.0	948.9	947.8	947.3	946.9
167.5°	956.9	958.3	959.7	960.4	959.9	958.8	957.7	956.6	955.5	955.0	954.6
170°	962.5	963.9	965.3	966.0	965.5	964.4	963.3	962.2	961.1	960.8	960.5
172.5°	966.7	968.1	969.5	970.2	969.7	968.6	967.5	966.4	965.3	965.0	964.7
175°	969.1	970.7	972.2	973.0	972.5	971.4	970.3	969.2	968.1	967.8	967.5
177.5°	970.2	971.6	973.0	973.7	973.2	972.1	971.0	969.9	968.8	968.6	968.5
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	652.2	649.9	649.9	648.6	648.6	641.5	641.5	643.7	641.1	638.0	633.5
5°	669.0	664.1	662.8	661.0	655.3	646.4	642.8	641.5	636.2	629.5	622.0
7.5°	685.0	677.0	673.0	669.0	661.5	649.1	642.0	637.1	629.1	618.9	609.1
10°	700.6	690.3	680.1	675.2	664.6	649.1	638.8	630.9	619.3	605.5	591.8
12.5°	714.8	693.4	691.7	681.9	666.4	648.6	633.1	621.5	606.9	590.9	574.9
15°	727.2	705.4	694.8	685.9	665.5	643.3	626.9	612.6	593.1	574.9	555.4
17.5°	733.4	709.9	702.8	688.1	667.3	638.4	616.2	598.9	577.6	555.8	533.6
20°	739.6	712.1	700.6	690.3	661.9	629.1	604.2	584.2	560.7	535.0	510.5
22.5°	742.7	712.1	698.3	684.1	656.6	618.9	589.6	566.0	538.5	512.3	483.0
25°	737.4	709.4	693.0	678.4	647.3	606.4	572.7	546.1	516.8	487.0	457.3
27.5°	724.1	703.2	684.1	669.0	634.4	590.5	554.9	524.7	494.6	461.3	431.1
30°	699.2	689.9	674.8	657.9	620.2	576.2	534.1	503.0	469.7	436.4	404.9
32.5°	660.6	668.6	658.8	644.2	603.3	556.7	511.9	480.4	443.9	408.0	379.1
35°	613.5	642.0	636.6	626.4	585.6	535.8	491.0	452.8	416.4	380.0	351.2
37.5°	562.0	605.1	609.5	603.3	565.1	514.5	465.3	428.0	390.7	353.8	324.5
40°	491.5	557.6	571.8	574.5	543.8	488.8	437.3	400.9	364.0	328.1	292.6
42.5°	426.6	510.1	527.9	539.0	516.8	463.5	411.5	371.1	334.7	302.3	266.8
45°	365.8	452.8	481.7	495.9	486.1	434.6	380.9	343.2	309.9	280.1	245.9
47.5°	303.2	390.7	431.1	453.7	453.7	405.3	351.6	314.3	282.4	257.0	226.9
50°	261.5	334.3	376.0	405.8	413.8	375.6	325.0	288.6	258.4	230.9	207.8
52.5°	222.9	288.1	322.8	353.8	376.9	343.6	295.2	262.4	232.6	206.9	188.7
55°	192.7	241.5	273.0	307.2	333.0	311.2	266.4	234.4	208.7	187.3	171.8
57.5°	163.8	206.4	232.2	262.4	289.9	273.5	237.5	210.0	187.3	168.7	154.9
60°	139.4	174.0	194.0	217.5	251.7	240.2	210.4	185.1	166.9	150.1	138.5
62.5°	118.5	146.1	162.9	179.8	210.9	205.5	182.5	162.9	147.4	133.2	123.4
65°	97.2	119.9	133.2	147.8	172.7	174.9	156.3	142.5	128.3	115.9	107.0
67.5°	78.6	96.3	108.3	120.8	140.7	146.9	134.1	122.5	110.5	100.3	92.3
70°	63.5	75.9	84.8	94.6	111.0	118.5	111.9	103.9	94.1	85.7	78.6
72.5°	50.2	58.2	63.5	71.0	84.4	91.9	91.5	84.4	77.2	71.5	65.7
75°	36.8	43.1	47.5	52.4	63.0	70.1	71.9	68.8	61.7	57.3	52.8
77.5°	28.0	31.5	33.7	37.3	44.8	51.1	53.7	52.8	47.9	44.4	41.3
80°	21.3	22.2	23.1	24.4	30.6	36.4	38.2	37.7	35.1	33.7	30.2
82.5°	15.1	15.5	16.0	16.4	18.6	23.5	25.3	26.2	24.0	22.6	19.5
85°	8.9	9.3	9.3	10.2	10.7	12.0	15.1	15.1	14.7	12.9	12.4
87.5°	4.4	4.4	4.0	4.0	4.4	4.9	5.8	6.7	5.8	5.3	4.9
90°	10.3	9.0	8.4	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.4	14.9	14.7	15.0	15.6	16.3	16.9	17.5	16.9	16.3	15.6
95°	24.1	23.0	22.4	25.0	30.1	35.3	40.4	45.6	40.4	35.3	30.1
97.5°	28.3	25.8	24.6	31.0	43.8	56.5	69.3	82.1	69.3	56.5	43.8
100°	32.1	29.4	28.1	38.8	60.1	81.5	102.8	124.2	102.8	81.5	60.1
102.5°	126.5	154.9	169.1	169.3	169.6	169.9	170.2	170.5	170.2	169.9	169.6
105°	170.5	213.0	234.3	232.0	227.3	222.6	218.0	213.3	218.0	222.6	227.3
107.5°	201.8	254.3	280.6	278.7	274.8	270.9	267.0	263.1	267.0	270.9	274.8
110°	257.9	303.0	325.5	323.9	320.6	317.3	314.1	310.8	314.1	317.3	320.6

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	364.3	367.0	368.3	366.9	364.1	361.3	358.5	355.7	358.5	361.3	364.1
115°	421.1	417.2	415.3	414.0	411.3	408.7	406.0	403.4	406.0	408.7	411.3
117.5°	462.8	460.1	458.8	457.2	454.1	451.0	447.9	444.8	447.9	451.0	454.1
120°	505.8	503.0	501.6	500.4	498.1	495.8	493.4	491.1	493.4	495.8	498.1
122.5°	546.3	543.2	541.6	540.4	537.9	535.4	532.9	530.4	532.9	535.4	537.9
125°	583.9	581.0	579.5	578.5	576.4	574.4	572.3	570.3	572.3	574.4	576.4
127.5°	620.1	617.8	616.6	615.5	613.3	611.2	609.0	606.8	609.0	611.2	613.3
130°	655.0	653.3	652.4	651.2	648.7	646.2	643.7	641.2	643.7	646.2	648.7
132.5°	688.0	686.3	685.4	684.4	682.4	680.3	678.3	676.3	678.3	680.3	682.4
135°	719.1	717.7	717.0	715.7	713.2	710.7	708.2	705.7	708.2	710.7	713.2
137.5°	747.3	745.8	745.0	744.1	742.2	740.3	738.5	736.6	738.5	740.3	742.2
140°	775.0	773.3	772.4	771.8	770.5	769.3	768.0	766.8	768.0	769.3	770.5
142.5°	800.0	797.9	796.9	796.4	795.3	794.2	793.1	792.0	793.1	794.2	795.3
145°	822.0	819.3	818.0	818.1	818.2	818.4	818.5	818.7	818.5	818.4	818.2
147.5°	843.7	841.0	839.7	839.9	840.4	840.9	841.3	841.8	841.3	840.9	840.4
150°	863.1	860.6	859.4	859.9	861.0	862.1	863.2	864.3	863.2	862.1	861.0
152.5°	881.1	878.8	877.6	878.2	879.5	880.7	882.0	883.2	882.0	880.7	879.5
155°	898.0	896.1	895.2	895.9	897.3	898.7	900.1	901.5	900.1	898.7	897.3
157.5°	912.7	911.3	910.6	911.2	912.5	913.7	915.0	916.2	915.0	913.7	912.5
160°	926.0	925.1	924.6	925.1	926.0	926.9	927.9	928.8	927.9	926.9	926.0
162.5°	937.0	936.2	935.8	936.3	937.2	938.2	939.1	940.1	939.1	938.2	937.2
165°	946.4	945.9	945.7	946.2	947.1	948.0	949.0	949.9	949.0	948.0	947.1
167.5°	954.1	953.6	953.4	953.9	954.8	955.7	956.7	957.6	956.7	955.7	954.8
170°	960.2	959.9	959.7	960.2	961.1	962.0	963.0	963.9	963.0	962.0	961.1
172.5°	964.4	964.1	963.9	964.4	965.3	966.2	967.2	968.1	967.2	966.2	965.3
175°	967.2	966.9	966.7	967.2	968.3	969.4	970.5	971.6	970.5	969.4	968.3
177.5°	968.3	968.2	968.1	968.6	969.7	970.8	971.9	973.0	971.9	970.8	969.7
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	631.7	632.2	633.5	629.5	623.3	620.6	612.6	611.3	610.0	610.0	611.3
5°	617.5	615.8	616.2	608.7	599.8	594.4	583.3	585.1	579.4	575.8	576.7
7.5°	602.0	597.1	596.7	586.9	575.8	566.0	554.5	551.8	546.5	540.3	537.6
10°	582.5	578.9	572.3	561.2	546.9	539.0	523.4	514.1	512.8	503.4	499.9
12.5°	562.5	556.3	549.6	534.1	518.1	505.2	493.7	483.5	476.4	468.4	463.0
15°	539.4	531.9	524.3	507.9	489.2	476.4	459.0	443.9	423.1	406.7	397.3
17.5°	514.1	505.7	495.4	477.2	459.0	441.3	409.3	391.6	376.9	367.1	361.4
20°	487.9	478.6	468.4	450.2	418.6	387.6	369.8	356.0	347.2	337.4	330.3
22.5°	460.4	450.6	439.5	411.1	377.8	356.0	342.3	329.4	316.5	311.2	307.7
25°	434.6	425.7	411.5	372.9	346.7	326.7	311.2	302.8	296.1	289.0	282.4
27.5°	408.0	391.6	371.6	339.2	322.8	302.3	291.2	285.0	273.5	268.6	265.5
30°	376.0	357.8	338.7	315.6	296.6	282.4	272.1	261.9	255.3	250.4	245.1
32.5°	343.6	326.3	314.3	290.3	276.1	261.5	251.7	245.5	235.7	232.6	230.4
35°	315.6	301.0	290.3	270.8	257.5	244.2	237.1	227.7	221.5	215.8	212.2
37.5°	288.1	280.1	269.0	252.6	238.4	227.7	218.0	214.9	206.4	203.3	199.8
40°	269.0	257.0	247.7	233.5	221.5	210.0	203.8	196.7	190.9	186.0	184.7
42.5°	245.9	237.1	231.7	216.2	203.8	197.1	189.6	181.6	177.1	173.1	168.3
45°	228.6	220.6	213.1	200.7	189.6	181.1	174.5	169.1	161.6	159.8	152.3
47.5°	210.4	202.4	196.7	184.2	174.0	166.0	161.2	154.1	147.8	143.8	140.3
50°	192.2	185.6	180.2	169.6	160.7	152.3	145.6	138.5	135.8	129.2	127.0
52.5°	174.9	170.5	164.7	154.5	145.6	138.5	131.4	125.6	121.6	118.1	115.4
55°	160.3	153.2	150.5	139.4	131.9	124.3	118.1	114.5	109.7	107.4	105.2
57.5°	143.8	139.8	135.4	127.0	118.5	111.4	107.0	101.7	99.0	96.3	94.6
60°	129.6	123.9	120.3	113.2	105.7	99.0	95.0	91.0	87.5	85.2	81.7
62.5°	113.2	108.8	106.5	99.0	92.8	86.6	83.0	79.0	76.4	72.4	67.9
65°	99.0	95.4	92.8	86.6	80.8	75.0	71.5	66.6	63.0	60.8	60.4
67.5°	86.6	83.9	79.9	74.1	68.4	63.9	59.9	55.9	55.5	54.6	54.6
70°	72.8	70.1	67.9	61.7	56.8	51.9	51.1	49.7	48.4	47.9	47.1
72.5°	60.8	58.6	55.9	50.6	45.7	44.4	43.5	42.6	41.3	40.8	40.4
75°	49.3	46.2	44.4	39.5	38.2	37.3	36.4	35.1	34.2	33.7	32.9
77.5°	37.7	34.6	34.6	32.0	31.1	29.7	28.9	28.0	27.5	26.6	26.6
80°	26.6	26.6	25.7	24.4	23.1	22.6	21.3	20.9	20.4	20.9	20.0
82.5°	19.5	17.8	17.8	16.9	16.0	15.5	14.7	14.7	14.2	14.2	14.2
85°	11.1	11.1	10.7	9.8	9.3	9.3	8.9	8.9	8.4	8.4	8.0
87.5°	4.4	4.0	4.4	4.0	4.0	3.6	3.6	3.6	3.1	3.6	3.1
90°	7.5	8.4	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1
92.5°	15.0	14.7	14.9	15.4	15.9	16.3	16.8	17.1	17.4	17.7	18.0
95°	25.0	22.4	23.0	24.1	25.2	26.3	27.4	28.2	29.0	29.7	30.5
97.5°	31.0	24.6	25.8	28.3	30.8	33.3	35.8	36.3	36.7	37.2	37.7
100°	38.8	28.1	29.4	32.1	34.7	37.4	40.0	41.2	42.5	43.7	45.0
102.5°	169.3	169.1	154.9	126.5	98.2	69.8	41.4	43.1	44.8	46.5	48.2
105°	232.0	234.3	213.0	170.5	127.9	85.4	42.8	44.5	46.2	47.9	49.6
107.5°	278.7	280.6	254.3	201.8	149.3	96.7	44.2	45.9	47.6	49.3	51.0
110°	323.9	325.5	303.0	257.9	212.9	167.8	122.8	107.2	91.6	76.0	60.4

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	366.9	368.3	367.0	364.3	361.7	359.0	356.4	289.2	222.0	154.8	87.6
115°	414.0	415.3	417.2	421.1	425.0	428.9	432.8	360.6	288.4	216.3	144.1
117.5°	457.2	458.8	460.1	462.8	465.4	468.1	470.7	448.4	426.1	403.8	381.5
120°	500.4	501.6	503.0	505.8	508.6	511.4	514.2	516.1	517.9	519.8	521.7
122.5°	540.4	541.6	543.2	546.3	549.4	552.5	555.6	556.5	557.5	558.4	559.3
125°	578.5	579.5	581.0	583.9	586.9	589.8	592.8	593.9	595.0	596.1	597.2
127.5°	615.5	616.6	617.8	620.1	622.5	624.8	627.2	628.8	630.3	631.9	633.4
130°	651.2	652.4	653.3	655.0	656.7	658.4	660.1	661.8	663.6	665.3	667.0
132.5°	684.4	685.4	686.3	688.0	689.7	691.4	693.1	694.5	695.9	697.3	698.7
135°	715.7	717.0	717.7	719.1	720.5	721.9	723.3	724.9	726.4	728.0	729.5
137.5°	744.1	745.0	745.8	747.3	748.9	750.4	752.0	753.6	755.2	756.7	758.3
140°	771.8	772.4	773.3	775.0	776.7	778.4	780.1	781.5	782.9	784.3	785.7
142.5°	796.4	796.9	797.9	800.0	802.0	804.1	806.1	807.3	808.6	809.8	811.1
145°	818.1	818.0	819.3	822.0	824.6	827.3	829.9	831.0	832.1	833.2	834.3
147.5°	839.9	839.7	841.0	843.7	846.4	849.0	851.7	852.5	853.3	854.0	854.8
150°	859.9	859.4	860.6	863.1	865.6	868.1	870.6	871.5	872.5	873.4	874.3
152.5°	878.2	877.6	878.8	881.1	883.4	885.8	888.1	889.1	890.0	891.0	891.9
155°	895.9	895.2	896.1	898.0	899.9	901.7	903.6	904.5	905.5	906.4	907.3
157.5°	911.2	910.6	911.3	912.7	914.1	915.5	916.9	918.0	919.1	920.2	921.3
160°	925.1	924.6	925.1	926.0	926.9	927.9	928.8	929.7	930.7	931.6	932.5
162.5°	936.3	935.8	936.2	937.0	937.8	938.6	939.4	940.5	941.6	942.7	943.8
165°	946.2	945.7	945.9	946.4	946.9	947.3	947.8	948.9	950.0	951.1	952.2
167.5°	953.9	953.4	953.6	954.1	954.6	955.0	955.5	956.6	957.7	958.8	959.9
170°	960.2	959.7	959.9	960.2	960.5	960.8	961.1	962.2	963.3	964.4	965.5
172.5°	964.4	963.9	964.1	964.4	964.7	965.0	965.3	966.4	967.5	968.6	969.7
175°	967.2	966.7	966.9	967.2	967.5	967.8	968.1	969.2	970.3	971.4	972.5
177.5°	968.6	968.1	968.2	968.3	968.5	968.6	968.8	969.9	971.0	972.1	973.2
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	611.3	610.4	607.8	608.7	607.3	607.3	606.4	606.4	606.4	608.7	607.3
5°	578.0	574.9	571.8	570.5	569.1	567.8	567.8	567.4	571.4	570.5	574.0
7.5°	536.7	535.8	529.6	529.6	527.4	526.5	528.7	529.2	529.6	530.5	532.7
10°	499.9	497.7	488.8	489.7	488.3	486.6	487.9	487.0	490.1	491.0	490.1
12.5°	456.4	452.4	442.6	437.7	432.4	428.4	433.3	429.7	442.2	445.7	455.5
15°	398.7	391.1	384.5	384.5	379.6	376.0	378.2	382.2	384.9	388.9	390.7
17.5°	360.0	356.9	351.6	348.5	347.2	345.8	345.8	347.6	353.4	352.9	356.5
20°	327.2	325.4	322.8	318.8	317.4	316.5	316.5	316.5	320.5	324.1	326.3
22.5°	304.5	303.2	301.4	296.1	293.5	292.6	294.8	296.1	299.2	301.9	304.1
25°	281.9	278.8	275.7	273.9	272.6	272.6	273.5	273.9	275.2	276.6	279.2
27.5°	263.3	261.0	256.6	251.7	251.7	250.4	251.3	252.2	255.3	259.7	261.9
30°	242.4	242.0	240.2	238.4	236.6	235.7	237.5	238.8	239.3	241.5	241.5
32.5°	227.3	224.2	221.1	219.3	218.4	218.0	218.4	220.2	220.2	222.9	226.0
35°	212.2	210.4	207.3	204.2	203.3	201.1	202.9	204.7	207.8	209.1	210.4
37.5°	195.8	193.6	192.2	191.3	189.6	190.0	188.7	191.3	194.0	193.6	194.4
40°	183.4	179.4	175.4	174.9	174.5	174.0	174.0	174.5	176.2	178.0	180.7
42.5°	167.4	166.0	162.5	158.9	158.0	157.2	156.3	158.0	161.6	164.7	166.0
45°	150.9	149.2	148.3	145.6	143.8	143.4	142.5	144.7	147.8	149.2	150.1
47.5°	135.8	135.4	132.7	133.2	131.9	132.3	131.9	133.2	133.2	134.5	135.4
50°	125.6	124.3	123.0	122.1	120.8	120.8	120.3	120.8	122.5	124.3	123.9
52.5°	115.4	113.2	112.8	112.3	111.4	112.3	111.0	111.4	113.2	114.1	113.7
55°	103.4	103.0	102.1	101.2	100.8	100.3	100.3	100.3	102.1	103.4	103.9
57.5°	94.1	91.9	90.1	90.1	88.3	87.9	88.8	89.2	90.6	91.5	92.3
60°	81.2	80.4	77.7	76.4	73.7	73.3	73.3	75.0	77.2	80.4	81.2
62.5°	67.5	66.1	65.7	65.7	65.7	65.7	65.7	65.7	65.7	66.1	66.1
65°	59.9	60.4	59.9	59.5	59.9	59.9	59.5	59.5	59.5	59.9	60.4
67.5°	53.7	53.3	53.7	53.3	52.8	52.8	52.4	52.8	53.3	53.7	53.7
70°	46.6	46.6	46.2	46.6	46.2	45.7	45.3	45.3	46.2	46.6	46.6
72.5°	40.0	40.0	39.5	39.5	38.6	38.6	39.1	38.6	38.6	40.0	40.0
75°	33.3	32.9	32.4	32.4	32.0	32.0	32.0	31.5	32.4	32.4	32.9
77.5°	26.2	26.2	26.2	25.7	25.7	25.3	25.3	25.7	25.7	25.7	26.2
80°	20.0	20.0	20.0	19.5	19.1	19.1	19.1	19.1	19.1	19.5	19.1
82.5°	13.8	13.8	13.8	13.8	13.8	13.3	13.3	13.3	13.8	13.8	13.3
85°	8.4	8.0	8.4	8.4	8.0	8.4	8.0	8.0	7.5	7.5	8.0
87.5°	3.6	3.1	2.7	2.7	3.1	2.7	2.7	2.7	3.1	2.7	2.7
90°	17.5	17.7	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.9	30.8	30.7	30.5	30.4	30.2	30.4	30.5	30.7	30.8	30.9
97.5°	37.9	38.0	38.1	38.3	38.4	38.6	38.4	38.3	38.1	38.0	37.9
100°	45.6	45.8	46.1	46.4	46.7	47.0	46.7	46.4	46.1	45.8	45.6
102.5°	49.1	49.3	49.8	50.3	50.7	51.2	50.7	50.3	49.8	49.3	49.1
105°	50.5	50.8	51.4	52.1	52.7	53.3	52.7	52.1	51.4	50.8	50.5
107.5°	51.9	52.2	52.8	53.5	54.1	54.7	54.1	53.5	52.8	52.2	51.9
110°	52.6	52.9	53.5	54.2	54.8	55.4	54.8	54.2	53.5	52.9	52.6

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	54.0	54.2	54.7	55.2	55.6	56.1	55.6	55.2	54.7	54.2	54.0
115°	108.0	102.4	91.2	79.9	68.7	57.5	68.7	79.9	91.2	102.4	108.0
117.5°	370.4	350.0	309.1	268.3	227.4	186.6	227.4	268.3	309.1	350.0	370.4
120°	522.6	512.1	491.0	470.0	448.9	427.9	448.9	470.0	491.0	512.1	522.6
122.5°	559.8	559.9	560.0	560.2	560.3	560.5	560.3	560.2	560.0	559.9	559.8
125°	597.7	597.9	598.4	598.9	599.3	599.8	599.3	598.9	598.4	597.9	597.7
127.5°	634.2	634.3	634.4	634.6	634.7	634.9	634.7	634.6	634.4	634.3	634.2
130°	667.9	667.8	667.7	667.5	667.4	667.2	667.4	667.5	667.7	667.8	667.9
132.5°	699.4	699.3	699.2	699.0	698.9	698.7	698.9	699.0	699.2	699.3	699.4
135°	730.3	730.1	729.8	729.5	729.2	728.9	729.2	729.5	729.8	730.1	730.3
137.5°	759.1	758.9	758.4	757.9	757.5	757.0	757.5	757.9	758.4	758.9	759.1
140°	786.4	786.0	785.2	784.5	783.7	782.9	783.7	784.5	785.2	786.0	786.4
142.5°	811.7	811.3	810.5	809.8	809.0	808.2	809.0	809.8	810.5	811.3	811.7
145°	834.8	834.4	833.6	832.9	832.1	831.3	832.1	832.9	833.6	834.4	834.8
147.5°	855.2	854.9	854.3	853.6	853.0	852.4	853.0	853.6	854.3	854.9	855.2
150°	874.8	874.4	873.6	872.9	872.1	871.3	872.1	872.9	873.6	874.4	874.8
152.5°	892.4	891.8	890.7	889.6	888.5	887.4	888.5	889.6	890.7	891.8	892.4
155°	907.8	907.2	905.9	904.7	903.4	902.2	903.4	904.7	905.9	907.2	907.8
157.5°	921.8	921.2	919.9	918.7	917.4	916.2	917.4	918.7	919.9	921.2	921.8
160°	933.0	932.5	931.4	930.3	929.2	928.1	929.2	930.3	931.4	932.5	933.0
162.5°	944.3	943.6	942.2	940.8	939.4	938.0	939.4	940.8	942.2	943.6	944.3
165°	952.7	952.2	951.1	950.0	948.9	947.8	948.9	950.0	951.1	952.2	952.7
167.5°	960.4	959.7	958.3	956.9	955.5	954.1	955.5	956.9	958.3	959.7	960.4
170°	966.0	965.3	963.9	962.5	961.1	959.7	961.1	962.5	963.9	965.3	966.0
172.5°	970.2	969.5	968.1	966.7	965.3	963.9	965.3	966.7	968.1	969.5	970.2
175°	973.0	972.2	970.7	969.1	967.6	966.0	967.6	969.1	970.7	972.2	973.0
177.5°	973.7	973.0	971.6	970.2	968.8	967.4	968.8	970.2	971.6	973.0	973.7
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	608.7	610.9	610.0	605.1	610.0	611.3	614.0	616.6	618.4	621.1	623.3
5°	570.5	574.9	577.6	574.9	583.8	585.1	591.3	594.9	600.2	604.7	608.2
7.5°	534.5	538.1	543.4	544.3	549.6	555.8	564.7	573.6	582.0	586.5	590.5
10°	495.9	502.1	510.1	508.3	516.3	526.1	535.4	549.6	556.7	564.7	571.8
12.5°	457.3	461.3	471.9	475.5	487.0	494.6	507.4	516.3	534.1	543.4	549.6
15°	389.8	406.2	419.5	435.5	450.6	464.8	476.4	492.3	507.9	515.0	525.2
17.5°	359.2	366.7	374.7	382.7	402.2	427.5	447.9	465.3	478.6	487.9	499.9
20°	327.2	334.7	343.6	351.2	363.2	381.4	406.7	436.4	452.4	462.2	473.7
22.5°	304.5	311.7	317.4	324.1	333.4	346.7	365.8	402.7	424.0	436.0	446.2
25°	280.1	289.0	295.2	300.1	307.7	322.3	337.8	358.7	396.9	406.2	420.4
27.5°	263.3	265.9	273.0	280.6	288.1	296.1	312.1	329.9	355.6	376.0	393.3
30°	243.3	249.9	256.6	259.7	266.4	277.9	287.7	306.8	326.7	342.7	363.6
32.5°	228.2	232.2	236.6	244.2	250.4	258.4	268.1	284.1	301.0	311.2	327.2
35°	211.3	214.0	223.3	226.4	232.6	240.6	250.4	262.8	281.0	289.0	300.6
37.5°	195.3	201.6	204.2	211.3	217.1	225.1	232.2	246.4	258.4	267.7	278.4
40°	182.9	185.6	190.5	196.7	201.6	207.8	216.6	226.9	239.7	247.3	256.6
42.5°	167.8	170.0	176.2	179.8	187.8	193.6	198.9	211.3	222.9	228.6	238.0
45°	151.4	156.7	160.7	167.8	172.3	179.4	186.0	194.9	205.5	212.2	217.5
47.5°	137.2	142.5	146.5	153.2	160.3	163.4	170.5	179.8	189.6	194.9	202.4
50°	125.6	127.4	135.0	138.1	145.6	151.8	156.7	164.7	175.4	178.5	184.7
52.5°	114.5	115.9	120.8	124.7	131.4	136.7	143.0	150.5	159.4	164.3	169.1
55°	104.8	105.7	107.9	112.3	116.8	123.4	129.2	136.3	143.8	149.2	153.6
57.5°	93.7	95.4	97.2	99.9	104.3	110.5	116.8	123.4	129.6	133.2	139.0
60°	80.8	83.5	86.6	89.7	92.8	97.2	104.3	110.5	116.3	119.4	123.9
62.5°	67.0	72.4	75.0	78.6	81.2	85.2	90.6	97.7	101.7	105.7	109.2
65°	60.4	60.8	61.3	64.8	69.7	73.7	78.6	83.9	90.1	92.8	95.4
67.5°	53.7	54.2	55.0	55.5	57.3	61.7	67.0	72.8	77.7	79.5	82.1
70°	47.1	47.1	48.8	49.3	49.7	50.2	54.6	60.4	64.8	67.0	70.1
72.5°	40.0	40.4	41.3	41.7	42.6	43.5	44.8	47.9	53.3	55.5	59.0
75°	32.9	33.3	33.7	34.2	35.5	36.0	37.3	39.1	41.3	44.0	46.2
77.5°	26.2	26.2	26.6	27.5	28.4	28.9	30.2	31.1	32.0	33.3	35.1
80°	19.5	20.0	20.0	20.9	20.9	21.3	21.8	23.1	24.0	24.9	25.7
82.5°	13.3	14.2	14.2	14.2	14.7	15.1	15.5	15.5	16.4	16.9	18.2
85°	8.0	8.4	8.4	8.4	8.0	8.9	8.9	9.3	9.3	9.3	9.8
87.5°	3.1	2.7	3.1	3.1	3.1	3.6	3.1	3.1	3.6	4.0	4.0
90°	17.1	16.3	15.6	14.8	14.0	12.8	11.5	10.3	9.0	8.4	7.5
92.5°	18.0	17.7	17.4	17.1	16.8	16.3	15.9	15.4	14.9	14.7	15.0
95°	30.5	29.7	29.0	28.2	27.4	26.3	25.2	24.1	23.0	22.4	25.0
97.5°	37.7	37.2	36.7	36.3	35.8	33.3	30.8	28.3	25.8	24.6	31.0
100°	45.0	43.7	42.5	41.2	40.0	37.4	34.7	32.1	29.4	28.1	38.8
102.5°	48.2	46.5	44.8	43.1	41.4	69.8	98.2	126.5	154.9	169.1	169.3
105°	49.6	47.9	46.2	44.5	42.8	85.4	127.9	170.5	213.0	234.3	232.0
107.5°	51.0	49.3	47.6	45.9	44.2	96.7	149.3	201.8	254.3	280.6	278.7
110°	60.4	76.0	91.6	107.2	122.8	167.8	212.9	257.9	303.0	325.5	323.9

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	87.6	154.8	222.0	289.2	356.4	359.0	361.7	364.3	367.0	368.3	366.9
115°	144.1	216.3	288.4	360.6	432.8	428.9	425.0	421.1	417.2	415.3	414.0
117.5°	381.5	403.8	426.1	448.4	470.7	468.1	465.4	462.8	460.1	458.8	457.2
120°	521.7	519.8	517.9	516.1	514.2	511.4	508.6	505.8	503.0	501.6	500.4
122.5°	559.3	558.4	557.5	556.5	555.6	552.5	549.4	546.3	543.2	541.6	540.4
125°	597.2	596.1	595.0	593.9	592.8	589.8	586.9	583.9	581.0	579.5	578.5
127.5°	633.4	631.9	630.3	628.8	627.2	624.8	622.5	620.1	617.8	616.6	615.5
130°	667.0	665.3	663.6	661.8	660.1	658.4	656.7	655.0	653.3	652.4	651.2
132.5°	698.7	697.3	695.9	694.5	693.1	691.4	689.7	688.0	686.3	685.4	684.4
135°	729.5	728.0	726.4	724.9	723.3	721.9	720.5	719.1	717.7	717.0	715.7
137.5°	758.3	756.7	755.2	753.6	752.0	750.4	748.9	747.3	745.8	745.0	744.1
140°	785.7	784.3	782.9	781.5	780.1	778.4	776.7	775.0	773.3	772.4	771.8
142.5°	811.1	809.8	808.6	807.3	806.1	804.1	802.0	800.0	797.9	796.9	796.4
145°	834.3	833.2	832.1	831.0	829.9	827.3	824.6	822.0	819.3	818.0	818.1
147.5°	854.8	854.0	853.3	852.5	851.7	849.0	846.4	843.7	841.0	839.7	839.9
150°	874.3	873.4	872.5	871.5	870.6	868.1	865.6	863.1	860.6	859.4	859.9
152.5°	891.9	891.0	890.0	889.1	888.1	885.8	883.4	881.1	878.8	877.6	878.2
155°	907.3	906.4	905.5	904.5	903.6	901.7	899.9	898.0	896.1	895.2	895.9
157.5°	921.3	920.2	919.1	918.0	916.9	915.5	914.1	912.7	911.3	910.6	911.2
160°	932.5	931.6	930.7	929.7	928.8	927.9	926.9	926.0	925.1	924.6	925.1
162.5°	943.8	942.7	941.6	940.5	939.4	938.6	937.8	937.0	936.2	935.8	936.3
165°	952.2	951.1	950.0	948.9	947.8	947.3	946.9	946.4	945.9	945.7	946.2
167.5°	959.9	958.8	957.7	956.6	955.5	955.0	954.6	954.1	953.6	953.4	953.9
170°	965.5	964.4	963.3	962.2	961.1	960.8	960.5	960.2	959.9	959.7	960.2
172.5°	969.7	968.6	967.5	966.4	965.3	965.0	964.7	964.4	964.1	963.9	964.4
175°	972.5	971.4	970.3	969.2	968.1	967.8	967.5	967.2	966.9	966.7	967.2
177.5°	973.2	972.1	971.0	969.9	968.8	968.6	968.5	968.3	968.2	968.1	968.6
180°	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	638.8	638.8	638.8	638.8
2.5°	627.3	626.0	634.0	642.8
5°	614.4	616.6	626.9	639.3
7.5°	601.1	606.0	618.0	634.4
10°	582.5	591.3	609.5	626.4
12.5°	564.3	576.2	593.6	613.5
15°	543.8	557.2	578.5	602.4
17.5°	521.2	536.3	561.2	587.3
20°	497.2	517.2	543.4	571.8
22.5°	470.6	494.6	521.6	553.2
25°	444.8	471.0	498.1	534.5
27.5°	419.5	445.3	475.5	512.3
30°	394.2	417.8	450.2	489.7
32.5°	367.1	391.6	425.7	466.1
35°	342.3	366.7	398.7	438.6
37.5°	315.6	341.8	372.5	413.8
40°	284.6	315.2	344.9	384.5
42.5°	258.8	291.2	320.1	357.4
45°	238.4	269.0	293.0	329.4
47.5°	219.3	244.2	268.6	302.3
50°	201.1	220.2	245.5	275.7
52.5°	182.5	198.9	220.6	249.1
55°	165.6	181.1	200.7	222.4
57.5°	150.1	161.2	180.7	200.2
60°	132.7	144.3	159.4	175.8
62.5°	118.1	127.0	141.2	154.9
65°	102.6	111.0	121.6	134.5
67.5°	88.3	95.9	104.3	114.5
70°	75.5	81.2	87.5	96.3
72.5°	61.7	67.9	73.7	80.8
75°	50.6	53.3	58.2	63.0
77.5°	39.1	42.6	45.3	49.3
80°	28.0	31.1	32.0	35.1
82.5°	18.6	20.4	22.2	23.1
85°	10.7	11.5	13.3	13.8
87.5°	4.0	4.4	5.3	6.2
90°	5.8	4.1	2.4	0.7
92.5°	15.6	16.3	16.9	17.5
95°	30.1	35.3	40.4	45.6
97.5°	43.8	56.5	69.3	82.1
100°	60.1	81.5	102.8	124.2
102.5°	169.6	169.9	170.2	170.5
105°	227.3	222.6	218.0	213.3
107.5°	274.8	270.9	267.0	263.1
110°	320.6	317.3	314.1	310.8

TEST NUMBER: P1009902

CATALOG NUMBER: S122RDIP-B290D725UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	364.1	361.3	358.5	355.7
115°	411.3	408.7	406.0	403.4
117.5°	454.1	451.0	447.9	444.8
120°	498.1	495.8	493.4	491.1
122.5°	537.9	535.4	532.9	530.4
125°	576.4	574.4	572.3	570.3
127.5°	613.3	611.2	609.0	606.8
130°	648.7	646.2	643.7	641.2
132.5°	682.4	680.3	678.3	676.3
135°	713.2	710.7	708.2	705.7
137.5°	742.2	740.3	738.5	736.6
140°	770.5	769.3	768.0	766.8
142.5°	795.3	794.2	793.1	792.0
145°	818.2	818.4	818.5	818.7
147.5°	840.4	840.9	841.3	841.8
150°	861.0	862.1	863.2	864.3
152.5°	879.5	880.7	882.0	883.2
155°	897.3	898.7	900.1	901.5
157.5°	912.5	913.7	915.0	916.2
160°	926.0	926.9	927.9	928.8
162.5°	937.2	938.2	939.1	940.1
165°	947.1	948.0	949.0	949.9
167.5°	954.8	955.7	956.7	957.6
170°	961.1	962.0	963.0	963.9
172.5°	965.3	966.2	967.2	968.1
175°	968.3	969.4	970.5	971.6
177.5°	969.7	970.8	971.9	973.0
180°	969.5	969.5	969.5	969.5

(END OF REPORT)