

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009304

Luminaire Tested: S122DIP-B675D530UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009304
REPORT IS A COMBINATION OF REPORTS P984545 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4571.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009304

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009304

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16749	16749	16749
5°	16776	15964	15853
10°	16640	15238	14936
15°	16396	14504	13971
20°	16067	13707	13057
25°	15738	12875	12146
30°	15326	12092	11188
35°	14937	11266	10249
40°	14455	10451	9361
45°	13978	9644	8489
50°	13454	8821	7586
55°	12905	7942	6730
60°	12287	6990	5840
65°	11610	6022	4904
70°	10749	4963	3959
75°	9560	3826	3057
80°	8119	2601	1968
85°	5890	1211	837

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13978 cd/sqm

TEST NUMBER: P1009304

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	2.2
10°-20°	280.2	6.1
20°-30°	411.8	9.0
30°-40°	478.3	10.5
40°-50°	477.7	10.4
50°-60°	416.5	9.1
60°-70°	307.9	6.7
70°-80°	174.2	3.8
80°-90°	47.9	1.0
90°-100°	41.5	0.9
100°-110°	132.0	2.9
110°-120°	225.9	4.9
120°-130°	297.1	6.5
130°-140°	333.5	7.3
140°-150°	327.1	7.2
150°-160°	274.3	6.0
160°-170°	182.0	4.0
170°-180°	63.6	1.4
0°-30°	791.6	17.3
0°-40°	1269.8	27.8
0°-60°	2164.0	47.3
0°-90°	2693.9	58.9
90°-120°	399.5	8.7
90°-150°	1357.2	29.7
90°-180°	1877.0	41.1
0°-180°	4571.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1058	1058	1058	1058	1058	
5°	1058	1054	1043	1051	1049	100
15°	1007	1001	988	992	987	284
25°	912	904	886	888	886	419
35°	786	776	760	754	749	491
45°	640	633	618	606	602	494
55°	484	478	466	454	449	433
65°	327	320	310	301	296	323
75°	171	169	164	158	160	182
85°	42	41	40	37	36	46
90°	1	7	20	19	19	4
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	230	229	228	227	224
125°	330	335	333	331	331	295
135°	427	433	434	433	432	330
145°	518	522	525	526	524	324
155°	592	594	596	598	597	273
165°	644	644	644	648	645	182
175°	670	669	667	671	668	64
180°	671	671	671	671	671	

TEST NUMBER: P1009304

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1058.1	1058.1	1058.1	1058.1	1058.1
2.5°	1064.2	1059.1	1047.9	1058.1	1056.1
5°	1058.1	1054.0	1042.8	1051.0	1049.0
7.5°	1051.0	1044.9	1033.7	1041.8	1039.8
10°	1039.8	1032.7	1020.5	1028.6	1025.6
12.5°	1024.5	1018.4	1006.2	1011.3	1009.3
15°	1007.2	1001.1	987.9	992.0	986.9
17.5°	985.9	979.8	966.5	971.6	966.5
20°	962.5	956.4	942.1	945.2	941.1
22.5°	939.1	929.9	916.7	916.7	914.7
25°	911.6	903.5	886.2	888.2	886.2
27.5°	881.1	874.0	860.7	857.7	852.6
30°	850.6	842.4	827.2	824.1	820.0
32.5°	818.0	811.9	795.6	789.5	785.4
35°	786.5	776.3	760.0	753.9	748.8
37.5°	750.9	741.7	725.4	718.3	713.2
40°	714.2	706.1	689.8	680.6	676.6
42.5°	678.6	670.5	654.2	644.0	637.9
45°	640.0	632.8	617.6	606.4	602.3
47.5°	602.3	595.2	578.9	567.7	561.6
50°	562.6	557.5	543.3	529.1	524.0
52.5°	524.0	516.8	503.6	492.4	485.3
55°	484.3	478.2	466.0	453.8	448.7
57.5°	444.6	439.5	426.3	414.1	410.0
60°	404.9	400.9	386.6	375.4	372.4
62.5°	366.3	359.1	349.0	338.8	334.7
65°	326.6	320.5	310.3	301.2	296.1
67.5°	285.9	280.8	271.6	264.5	260.5
70°	248.2	244.2	235.0	227.9	223.8
72.5°	209.6	205.5	200.4	193.3	190.3
75°	170.9	168.9	163.8	157.7	159.7
77.5°	136.3	132.3	130.2	127.2	124.1
80°	101.7	100.7	98.7	95.6	93.6
82.5°	69.2	69.2	68.2	64.1	64.1
85°	41.7	40.7	39.7	36.6	35.6
87.5°	18.3	16.3	14.2	11.2	10.2
90°	0.6	7.4	19.8	18.7	19.3
92.5°	12.5	17.0	17.6	18.1	18.1
95°	29.5	35.1	36.3	36.3	35.1
97.5°	49.3	54.4	56.7	56.7	56.7
100°	72.0	76.5	78.2	78.2	77.6
102.5°	95.8	99.2	101.4	102.0	101.4
105°	121.8	123.5	124.6	125.8	125.8
107.5°	147.9	150.1	150.1	150.7	147.9
110°	172.8	176.2	176.2	176.2	174.5

TEST NUMBER: P1009304

CATALOG NUMBER: S122DIP-B675D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.0	203.4	202.8	201.1	200.0
115°	226.6	230.0	228.9	228.3	226.6
117.5°	253.3	257.8	255.0	253.3	251.6
120°	279.9	284.4	279.9	279.9	278.2
122.5°	304.3	309.9	307.1	305.4	304.3
125°	329.7	334.8	333.1	331.4	330.9
127.5°	354.7	360.9	358.6	356.4	354.7
130°	377.9	385.3	384.1	383.0	380.7
132.5°	404.0	409.6	410.2	407.4	405.7
135°	426.6	432.9	434.0	433.4	431.7
137.5°	451.6	456.7	457.8	457.2	455.0
140°	473.7	478.8	481.6	481.6	479.3
142.5°	496.3	501.4	503.1	503.7	501.4
145°	517.9	521.8	525.2	525.8	523.5
147.5°	537.1	542.2	544.5	545.6	543.3
150°	556.9	560.3	562.6	564.3	562.6
152.5°	574.5	577.9	580.7	583.0	580.7
155°	592.1	593.8	595.5	598.3	596.6
157.5°	607.4	608.5	609.6	613.6	610.8
160°	621.0	622.1	622.7	626.1	623.8
162.5°	633.4	633.4	634.0	638.0	635.1
165°	644.2	643.6	643.6	647.6	644.8
167.5°	653.8	652.1	652.1	656.1	653.3
170°	661.2	659.5	658.9	662.9	659.5
172.5°	666.3	664.6	664.0	668.0	664.6
175°	670.3	668.6	667.4	671.4	668.0
177.5°	672.5	670.8	669.7	673.1	669.7
180°	671.4	671.4	671.4	671.4	671.4

(END OF REPORT)