

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009312

Luminaire Tested: S122DIP-B675D530UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009312
REPORT IS A COMBINATION OF REPORTS P984568 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB30-4F0-XX-W2A-F
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4835.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009312

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1009312

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	39	33	55	44	37	31	38	32	28	33	29	25	28	25	22
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	23	20
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	24	21	18
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16891	16891	16891
5°	16919	16102	15987
10°	16782	15368	15062
15°	16536	14627	14090
20°	16204	13824	13168
25°	15873	12984	12249
30°	15456	12195	11284
35°	15064	11362	10336
40°	14578	10541	9441
45°	14096	9725	8563
50°	13569	8896	7650
55°	13014	8010	6787
60°	12393	7049	5890
65°	11710	6075	4946
70°	10844	5005	3993
75°	9644	3859	3084
80°	8191	2622	1985
85°	5947	1220	844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14096 cd/sqm

TEST NUMBER: P1009312

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	2.1
10°-20°	282.6	5.8
20°-30°	415.3	8.6
30°-40°	482.3	10.0
40°-50°	481.7	10.0
50°-60°	420.0	8.7
60°-70°	310.5	6.4
70°-80°	175.7	3.6
80°-90°	47.6	1.0
90°-100°	23.8	0.5
100°-110°	88.8	1.8
110°-120°	235.6	4.9
120°-130°	390.8	8.1
130°-140°	415.1	8.6
140°-150°	385.8	8.0
150°-160°	310.2	6.4
160°-170°	199.9	4.1
170°-180°	68.8	1.4
0°-30°	798.3	16.5
0°-40°	1280.6	26.5
0°-60°	2182.4	45.1
0°-90°	2716.3	56.2
90°-120°	348.3	7.2
90°-150°	1539.9	31.8
90°-180°	2119.0	43.8
0°-180°	4835.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1067	1067	1067	1067	1067	
5°	1067	1063	1052	1060	1058	101
15°	1016	1010	996	1000	995	286
25°	919	911	894	896	894	423
35°	793	783	766	760	755	495
45°	645	638	623	612	608	498
55°	488	482	470	458	452	437
65°	329	323	313	304	299	326
75°	172	170	165	159	161	184
85°	42	41	40	37	36	47
90°	0	6	10	13	14	4
95°	34	17	20	23	22	40
105°	159	175	32	38	40	170
115°	301	310	323	80	43	296
125°	425	432	442	446	447	379
135°	526	534	539	544	543	406
145°	610	610	619	622	620	382
155°	672	667	674	677	672	310
165°	708	705	706	710	706	200
175°	724	721	722	725	720	69
180°	723	723	723	723	723	

TEST NUMBER: P1009312

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.1	1067.1	1067.1	1067.1	1067.1
2.5°	1073.3	1068.2	1056.9	1067.1	1065.1
5°	1067.1	1063.0	1051.8	1060.0	1057.9
7.5°	1060.0	1053.8	1042.5	1050.7	1048.7
10°	1048.7	1041.5	1029.2	1037.4	1034.3
12.5°	1033.3	1027.1	1014.8	1019.9	1017.9
15°	1015.8	1009.7	996.3	1000.5	995.3
17.5°	994.3	988.1	974.8	979.9	974.8
20°	970.7	964.5	950.2	953.3	949.1
22.5°	947.1	937.9	924.5	924.5	922.5
25°	919.4	911.2	893.7	895.8	893.7
27.5°	888.6	881.4	868.1	865.0	859.9
30°	857.8	849.6	834.2	831.1	827.0
32.5°	825.0	818.8	802.4	796.3	792.2
35°	793.2	782.9	766.5	760.3	755.2
37.5°	757.3	748.0	731.6	724.4	719.3
40°	720.3	712.1	695.7	686.5	682.4
42.5°	684.4	676.2	659.8	649.5	643.4
45°	645.4	638.2	622.8	611.6	607.5
47.5°	607.5	600.3	583.9	572.6	566.4
50°	567.4	562.3	547.9	533.6	528.4
52.5°	528.4	521.3	507.9	496.6	489.5
55°	488.4	482.3	470.0	457.6	452.5
57.5°	448.4	443.3	429.9	417.6	413.5
60°	408.4	404.3	389.9	378.6	375.6
62.5°	369.4	362.2	352.0	341.7	337.6
65°	329.4	323.2	313.0	303.7	298.6
67.5°	288.3	283.2	274.0	266.8	262.7
70°	250.4	246.3	237.0	229.8	225.7
72.5°	211.4	207.3	202.1	195.0	191.9
75°	172.4	170.3	165.2	159.0	161.1
77.5°	137.5	133.4	131.3	128.3	125.2
80°	102.6	101.6	99.5	96.5	94.4
82.5°	69.8	69.8	68.7	64.6	64.6
85°	42.1	41.0	40.0	36.9	35.9
87.5°	18.5	16.4	14.4	11.3	10.3
90°	0.5	6.3	10.5	13.1	14.1
92.5°	13.1	11.0	12.6	13.6	14.1
95°	34.0	16.7	20.4	23.0	22.5
97.5°	61.2	18.3	26.7	28.2	28.8
100°	92.6	20.9	29.8	34.0	35.0
102.5°	127.1	126.0	30.9	36.6	38.2
105°	159.0	174.7	31.9	37.7	39.7
107.5°	196.1	209.2	32.9	38.7	40.8
110°	231.7	242.6	91.5	39.2	41.3

TEST NUMBER: P1009312

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	265.1	274.5	265.7	40.3	41.8
115°	300.7	309.6	322.7	80.5	42.9
117.5°	331.5	342.0	350.9	276.1	139.1
120°	366.1	373.9	383.3	389.6	319.0
122.5°	395.3	403.7	414.2	417.3	417.8
125°	425.2	432.0	441.9	445.5	447.1
127.5°	452.3	459.7	467.5	472.7	473.3
130°	478.0	486.3	492.1	497.8	497.3
132.5°	504.1	510.9	516.7	521.4	520.9
135°	526.1	534.4	539.2	544.4	543.3
137.5°	549.1	555.4	560.6	565.8	564.3
140°	571.6	575.8	581.5	586.2	583.6
142.5°	590.4	594.1	600.9	605.0	602.4
145°	610.3	609.8	618.6	622.3	619.7
147.5°	627.5	626.0	634.9	637.5	635.4
150°	644.3	640.6	649.0	652.1	649.5
152.5°	658.4	654.2	662.0	665.2	661.5
155°	672.0	667.3	673.6	676.7	672.5
157.5°	683.0	678.8	683.5	687.1	683.0
160°	692.4	689.2	692.4	695.5	691.9
162.5°	700.7	697.6	700.2	703.9	699.2
165°	708.1	704.9	706.5	710.2	706.5
167.5°	713.8	710.7	712.2	715.9	711.2
170°	718.5	715.4	716.4	720.1	715.4
172.5°	721.7	718.5	719.6	723.2	718.5
175°	724.3	720.6	721.7	725.3	720.1
177.5°	725.3	721.7	722.2	725.8	721.1
180°	722.7	722.7	722.7	722.7	722.7

(END OF REPORT)