

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009313

Luminaire Tested: S122DIP-B675D530UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009313
REPORT IS A COMBINATION OF REPORTS P984569 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4610.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009313

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009313

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16891	16891	16891
5°	16919	16102	15987
10°	16782	15368	15062
15°	16536	14627	14090
20°	16204	13824	13168
25°	15873	12984	12249
30°	15456	12195	11284
35°	15064	11362	10336
40°	14578	10541	9441
45°	14096	9725	8563
50°	13569	8896	7650
55°	13014	8010	6787
60°	12393	7049	5890
65°	11710	6075	4946
70°	10844	5005	3993
75°	9644	3859	3084
80°	8191	2622	1985
85°	5947	1220	844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14096 cd/sqm

TEST NUMBER: P1009313

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	2.2
10°-20°	282.6	6.1
20°-30°	415.3	9.0
30°-40°	482.3	10.5
40°-50°	481.7	10.4
50°-60°	420.0	9.1
60°-70°	310.5	6.7
70°-80°	175.7	3.8
80°-90°	48.3	1.0
90°-100°	41.9	0.9
100°-110°	133.2	2.9
110°-120°	227.8	4.9
120°-130°	299.7	6.5
130°-140°	336.4	7.3
140°-150°	329.9	7.2
150°-160°	276.7	6.0
160°-170°	183.5	4.0
170°-180°	64.1	1.4
0°-30°	798.3	17.3
0°-40°	1280.6	27.8
0°-60°	2182.4	47.3
0°-90°	2716.9	58.9
90°-120°	402.9	8.7
90°-150°	1368.8	29.7
90°-180°	1893.0	41.1
0°-180°	4610.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1067	1067	1067	1067	1067	
5°	1067	1063	1052	1060	1058	101
15°	1016	1010	996	1000	995	286
25°	919	911	894	896	894	423
35°	793	783	766	760	755	495
45°	645	638	623	612	608	498
55°	488	482	470	458	452	437
65°	329	323	313	304	299	326
75°	172	170	165	159	161	184
85°	42	41	40	37	36	47
90°	1	7	20	19	19	4
95°	30	35	37	37	35	33
105°	123	125	126	127	127	130
115°	229	232	231	230	229	226
125°	333	338	336	334	334	297
135°	430	437	438	437	435	332
145°	522	526	530	530	528	326
155°	597	599	600	603	602	275
165°	650	649	649	653	650	183
175°	676	674	673	677	674	64
180°	677	677	677	677	677	

TEST NUMBER: P1009313

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.1	1067.1	1067.1	1067.1	1067.1
2.5°	1073.3	1068.2	1056.9	1067.1	1065.1
5°	1067.1	1063.0	1051.8	1060.0	1057.9
7.5°	1060.0	1053.8	1042.5	1050.7	1048.7
10°	1048.7	1041.5	1029.2	1037.4	1034.3
12.5°	1033.3	1027.1	1014.8	1019.9	1017.9
15°	1015.8	1009.7	996.3	1000.5	995.3
17.5°	994.3	988.1	974.8	979.9	974.8
20°	970.7	964.5	950.2	953.3	949.1
22.5°	947.1	937.9	924.5	924.5	922.5
25°	919.4	911.2	893.7	895.8	893.7
27.5°	888.6	881.4	868.1	865.0	859.9
30°	857.8	849.6	834.2	831.1	827.0
32.5°	825.0	818.8	802.4	796.3	792.2
35°	793.2	782.9	766.5	760.3	755.2
37.5°	757.3	748.0	731.6	724.4	719.3
40°	720.3	712.1	695.7	686.5	682.4
42.5°	684.4	676.2	659.8	649.5	643.4
45°	645.4	638.2	622.8	611.6	607.5
47.5°	607.5	600.3	583.9	572.6	566.4
50°	567.4	562.3	547.9	533.6	528.4
52.5°	528.4	521.3	507.9	496.6	489.5
55°	488.4	482.3	470.0	457.6	452.5
57.5°	448.4	443.3	429.9	417.6	413.5
60°	408.4	404.3	389.9	378.6	375.6
62.5°	369.4	362.2	352.0	341.7	337.6
65°	329.4	323.2	313.0	303.7	298.6
67.5°	288.3	283.2	274.0	266.8	262.7
70°	250.4	246.3	237.0	229.8	225.7
72.5°	211.4	207.3	202.1	195.0	191.9
75°	172.4	170.3	165.2	159.0	161.1
77.5°	137.5	133.4	131.3	128.3	125.2
80°	102.6	101.6	99.5	96.5	94.4
82.5°	69.8	69.8	68.7	64.6	64.6
85°	42.1	41.0	40.0	36.9	35.9
87.5°	18.5	16.4	14.4	11.3	10.3
90°	0.6	7.4	20.0	18.9	19.4
92.5°	12.6	17.1	17.7	18.3	18.3
95°	29.7	35.4	36.6	36.6	35.4
97.5°	49.7	54.9	57.1	57.1	57.1
100°	72.6	77.1	78.9	78.9	78.3
102.5°	96.6	100.0	102.3	102.9	102.3
105°	122.9	124.6	125.7	126.9	126.9
107.5°	149.1	151.4	151.4	152.0	149.1
110°	174.3	177.7	177.7	177.7	176.0



TEST NUMBER: P1009313

CATALOG NUMBER: S122DIP-B675D530UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.7	205.1	204.6	202.8	201.7
115°	228.6	232.0	230.8	230.3	228.6
117.5°	255.4	260.0	257.1	255.4	253.7
120°	282.3	286.8	282.3	282.3	280.6
122.5°	306.8	312.6	309.7	308.0	306.8
125°	332.6	337.7	336.0	334.3	333.7
127.5°	357.7	364.0	361.7	359.4	357.7
130°	381.1	388.6	387.4	386.3	384.0
132.5°	407.4	413.1	413.7	410.8	409.1
135°	430.3	436.6	437.7	437.1	435.4
137.5°	455.4	460.5	461.7	461.1	458.8
140°	477.7	482.8	485.7	485.7	483.4
142.5°	500.5	505.7	507.4	508.0	505.7
145°	522.3	526.3	529.7	530.3	528.0
147.5°	541.7	546.8	549.1	550.3	548.0
150°	561.7	565.1	567.4	569.1	567.4
152.5°	579.4	582.8	585.7	588.0	585.7
155°	597.1	598.8	600.5	603.4	601.7
157.5°	612.5	613.7	614.8	618.8	616.0
160°	626.3	627.4	628.0	631.4	629.1
162.5°	638.8	638.8	639.4	643.4	640.5
165°	649.7	649.1	649.1	653.1	650.3
167.5°	659.4	657.7	657.7	661.7	658.8
170°	666.8	665.1	664.5	668.5	665.1
172.5°	672.0	670.3	669.7	673.7	670.3
175°	676.0	674.3	673.1	677.1	673.7
177.5°	678.3	676.5	675.4	678.8	675.4
180°	677.1	677.1	677.1	677.1	677.1

(END OF REPORT)